

A black and white photograph of a woman with blonde hair tied back, wearing safety glasses and a dark polo shirt with a small Cummins logo on the chest. She is smiling and holding a large cardboard box. The box has a white label on the left side with a Cummins logo and some illegible text. A dark horizontal band across the bottom of the box features the text 'GENUINE PARTS' in white. On the right side of the box, there is a large Cummins logo. The background is slightly blurred, showing what appears to be a retail or service environment.

# CUMMINS WARRANTY QUICK REFERENCE GUIDE

U.S. AND CANADA

## Cummins Engines

Automotive Engines	Months	Mileage/Km/Hrs
4B/ISB4 Series	24	50,000/80,468
2017 EPA B/B6.7/ISB	36	Unlimited
B/B Gas Plus/B LPG Plus/ISB ISV/V5.0	24	Unlimited
ISC/ISL/ISL G/C Gas Plus	24	250,000/402,336/ 6,250
L10/M11/ISM/N14/ISX/ Signature*	24	250,000/402,336/ 6,250
2010 EPA & 2013 EPA ISX11.9 (ISX12) / ISX15	24	250,000/402,336/ 6,250
2017 EPA X12 / X15	24	250,000/402,336/ 6,250
Fire Truck/Crash Truck**	60	100,000/160,935
All Buses (except U.S./Canada school buses)	24	Unlimited
U.S./Canada School Bus	60	100,000/160,935
RV - ISB AD**	36	75,000/120,701
All Other RV Engines**	60	100,000/160,935

\* Injectors are covered for 2 years/125,000 miles/201,169 km/3,125 hours.

\*\* Deductibles apply. Refer to Warranty Administration manual for deductible details.

Industrial Engines	Months	Hours
All Industrial Engines***	24	2,000

\*\*\*If the 2,000-hour limit is exceeded during the first year, coverage continues until the end of the first year.

## Genuine Cummins New Parts

Components	Months	Mileage/Km/Hrs
CENTINEL™		
- Automotive	24	250,000/402,336/3,600
- Industrial	12	Unlimited
N Series/L10/M11/ISM/ISX	12	100,000/160,935/3,600
A, B/B Gas Plus/B Gas International/ B LPG Plus/ISB5.9 G/ISB/QSB, C/C Gas Plus/ISC/QSC, ISF, ISL/ISL G/QSL- engines up to 10L	12	100,000/160,935/3,600
K19/QSK19/QSK23/QSK45/ QSK60/QSK78	12	Unlimited
Cummins Cylinder Kits:		
- All 1991 and Newer N14 TriTech® Plus Cylinder Kits	36	300,000/482,804/10,800
- Single Ni TriTech Plus	24	200,000/321,869/7,200
- Dual Ni TriTech	36	300,000/482,804

**Variable Geometry Turbos (VGT) and VGT Actuators for automotive applications must be diagnosed in on engine condition by an ISX certified repair facility to qualify for warranty exchange.**

**EXTENDED MAJOR COMPONENTS WARRANTY** covers major components (registered parts only) on new engines as follows:

- L10/M11/ISM/N14/ISX/Signature automotive engines – 5 years/500,000 miles/ 804,676 km
- Industrial engines – 3 years/10,000 hours
- Coach/Transit/Shuttle/School Bus – 3 years/10,800 hours/300,000 miles/482,805 km

## Cummins ReCon® Engines/Blocks

Automotive	Months	Mileage/Km
B3.9	24	50,000/80,468
B5.9/ISB/B Gas Plus/B LPG Plus	24	100,000/160,935
ISC/C8.3/ISL/C Gas Plus/ISL G/ L Gas Plus - Up to 225 hp	24	Unlimited
ISC/C8.3/ISL/C Gas Plus/ISL G/ L Gas Plus - 226 hp and Over	24	100,000/160,935
L10/M11/ISM/N/N14	12	100,000/160,935
ISM/ISC/ISL/ISB Transit (excluding hybrid)	24	Unlimited
ISX	24	200,000/321,869
4B/6B/ISB/6C/ISC/ISL Long Blocks	12	50,000/80,468
L10/M11/ISM/N14/ISX Long Blocks	12	100,000/160,935
4B/6B/ISB/6C/ISC/ISL Short/ Service Blocks	6	Unlimited
L10/M11/ISM/N14/ISX Short/ Service Blocks	12	100,000/160,935
Industrial	Months	Hours
All Industrial Engines*	24	2,000
All Marine Engines*	24	2,000
4B/6B/6C/L10/M11/N14/ K19/QSB/QSC/QSL/QSM/ QSX/QSK19 Long Blocks	12	1,000
6B/6C/N14/K19 Oil and Gas Long Blocks	12	Unlimited
4B/6B/6C/QSB/QSC/QSL Short/Service Blocks	6	Unlimited
L10/M11/N14/K19/QSM/ QSX/QSK19 Short/Service Blocks	6	Unlimited

\*If the 2,000-hour limit is exceeded during the first year, coverage continues until the end of the first year.

## Cummins ReCon Parts

Components	Months	Mileage/Km/Hrs	Labor	Other Claimables
ReCon Electrics	12	Unlimited	Y	N
Components - Engines up to 18L (except fuel pumps, injectors and electrics)*	12	100,000/160,935/3,600	Y	Y
ReCon High-Volume Water Pumps**	24	200,000/321,870/7,200	Y	Y
ReCon Premium Gold Cylinder Head***	24	200,000/321,870/7,200	Y	Y
Injectors and Fuel Pumps - engines up to 18L	12	Unlimited	Y	Y
Heavy-Duty ReCon PX Injectors - L10/M11/ISM N14/ISX Pre EPA 2010	24	125,000/201,168/3,600	Y	Y
MidRange ReCon Injectors	12	Unlimited	Y	N
All Other HD Components Except Electrics	12	100,000/160,935/3,600	Y	Y
CELECT™ & HPI RX Injectors for N.A. and Mexico	12	Unlimited	N	N
ReCon RX Injectors for N.A. and Mexico	12	100,000/160,935/3,600	Y	N
HHP ReCon Components	12	Unlimited	] Includes parts, labor and travel	
HHP Major Components - 19L and above	36	10,800 hrs		
ReCon "XX" Products	6	Unlimited		
ReCon RX DPF Not Sold In CA.	12	100,000/160,935/3,600	Y	Y

**\*Variable Geometry Turbos (VGT) and VGT Actuators for automotive applications must be diagnosed in on engine condition by an ISX certified repair facility to qualify for warranty exchange.**

**\*\*Applies only to part numbers: AR4518RX, AR45184-1RX, AR45090RX, AR45090-1RX, 3045943RX, 3801708RX, 3801715RX, 3801788RX, 3803138RX, 3803605RX**

**\*\*\*Applies only to part numbers: 3652600RX, 3652807RX, 3652808RX, 3675504RX, 3675505RX, 3675506RX**

## Cummins Service Tools

Tools	Months	Coverage
QuickCheck™ 5600	12	Labor/Parts
INLINE™ 6	12	Labor/Parts
INLINE™ 7	Manufacturer's Warranty Applies	
INLINE MINI™	Manufacturer's Warranty Applies	
Genuine Tools	Lifetime	Repair or Replace
Electrical Products, Instrumentation, Gauges, Motors and Consumables	12	Repair or Replace
Non-Genuine Tools	Manufacturer's Warranty Applies	

(Refer to Page i-3 of the Cummins Service Products Catalog, Bulletin 3377710-03, for details.)

Note: The warranty terms described within this card are correct at time of printing, subject to change without notice, and apply only to Genuine Cummins products purchased from an authorized Cummins distributor/dealer. Exceptions may apply. See individual warranty certificates for complete warranty coverage. Contact your local Cummins distributor or dealer for more details. The "Warranty Administration Manual" is published on QuickServe as bulletin: 4021290.



**Cummins Inc.**  
**Box 3005**  
**Columbus, IN 47202-3005**  
**U.S.A.**

Phone: 1-800-CUMMINS™ (1-800-286-6467)  
quickserve.cummins.com

Bulletin 4081630 Printed in U.S.A. Rev. 12/18  
©2018 Cummins Inc.