

RV GREEN LABEL PARTS REFERENCE GUIDE

Maximize the performance and life of your generator

Cummins Onan generators are known for their high quality and dependable performance. The best way to maintain that performance is use genuine parts. Green Label Parts are designed and engineered specifically for your Cummins Onan generator to perform at its peak, and are backed by the Cummins Onan parts warranty.



Brand Name Model/Series	Spec Letter	Oil Filter ^{1, 2, 3, 5}	Oil Capacity ^{1, 2, 3, 5}	Air Filters ^{3, 5}	Fuel Filters ^{3, 5}	Glow Plug/ Spark Plug ^{2, 3, 5}	Plug Wires ⁵	Tune-up Kits ⁵
Cummins Onan RV QG 2800 series, RV QG 4000 series, Camp Power, Onan MicroLite, Onan MicroQuiet™								
KVD	A-C	—	1 quart ^C	140-2105 ^C	149-2137 ^H	167-0263-02 ^H	—	Electronic Ignition
KV	A-M	—	1 quart ^C	140-2105 ^C	149-2137 ^I	167-0263-02 ^I	—	Electronic Ignition
KVC	A-C, F	—	1 quart ^C	140-2105 ^C	149-2137 ^H	167-0263-02 ^H	—	Electronic Ignition
KYD 50 Hz	A-B	—	1.6 quarts ^C	140-3280 ^C	149-2457 ^H	167-0305 ^H	—	Electronic Ignition
KYD 60 Hz	A-B	—	1.6 quarts ^C	140-3280 ^C	149-2457 ^H	167-0275 ^H	—	Electronic Ignition
HGJBB	A	—	.6 quarts	A030Y328 ^E	149-2661 ^I	167-1652 ^I	—	Electronic Ignition
KY 50 Hz	B-H	—	1.6 quarts ^C	140-3280 ^E	149-2457 ^I	167-0305 ^I	—	Electronic Ignition
KY 60 Hz	A B-H	—	1.6 quarts ^C	140-2609 ^E 140-3280 ^E	149-2457 ^I	167-0275 ^I	—	Electronic Ignition
KY 50 Hz KY 60 Hz	J-N, P	—	1.6 quarts ^C	140-3280 ^C	149-2457 ^H 167-0275 ^H	167-0305 ^H	—	Electronic Ignition
Cummins Onan RV QG 5500 series, RV QG 7000 series, Emerald Advantage, Onan Marquis Gold, Onan Marquis Platinum™								
Carb - HGJAC LP Liquid/HGJAC LP Vapor/HGJAC	A-K	122-0836 ^C	2 quarts ^C	140-3116 ^C	*See note below ^H 149-2648 ^H	167-1638 ^H	—	Electronic Ignition
Carb - HGJAB LP Liquid/HGJAB LP Vapor/HGJAB	A-K	122-0836 ^C	2 quarts ^C	140-3116 ^C	*See note below ^H 149-2648 ^H	167-1638 ^H	—	Electronic Ignition
EFI/HGJAA LP Liquid/HGJAA LP Vapor/HGJAA	A-K	122-0836 ^C	2 quarts ^C	147-0860 ^H 140-3116 ^C	149-2648 ^H	167-1638 ^H	—	Electronic Ignition
*At fuel pump use 149-2341-01; At carb replace filter with A029S253 adaptor								
Cummins Onan RV QD 3200, RV QD 6000/8000 series, RV QD 10000/12500 series								
HDKAH	A-K L-N	122-0833 ^C	3 quarts ^C	140-2897 ^I	149-2513 ^I 147-0860 ^I	185-5421	—	—
HDKAK	A-K L-N	122-0833 ^C	3 quarts ^C	140-2897 ^I	149-2513 ^I 147-0860 ^I	185-5421	—	—
HDKCA/CB	A-F	122-0893 ^E	5.9 quarts ^E	140-3071 ^I	149-2513 ^I	185-5990	—	—
HDZAA	A-C	Clean every 1000 hrs	1.1 quarts ^E	140-4151 ^I	149-2834 ^I	—	—	—
Onan HQD Series								
HQDPA	A-C	122-0833 ^C	2.2 quarts ^C	140-2897 ^I	147-0860 ^I	185-5421	—	—
HQDPB	A B	185-5835 ^C	2.2 quarts ^C	140-3071 ^I	147-0860 ^I	185-5421 333-0802	—	—
HQDPC	C	122-0833 ^C	2.8 quarts ^C	140-2897 ^I	147-0860 ^I	185-5421	—	—
Onan Emerald™								
BGE	A-E F	122-0645 ^C	3.5 quarts ^C	140-2379 ^C	— 149-2279 ^F	167-0272 ^C	9" 167-1615-01/ 26" 167-1602	160-1378
BGE	G H J-P	122-0645 ^C	3.5 quarts ^C	140-2379 ^F	149-2279 ^I 149-1353 ^I 149-2333 ^I	167-0272 ^I	9" 167-1615-01/ 26" 167-1602	Electronic Ignition
BGEL	A-E	122-0645 ^C	3.5 quarts ^C	140-2379 ^C	148-0898 ^C	167-0272 ^C	9" 167-1615-01/ 26" 167-1602	160-1378
NHE	A-E	122-0800 ^C	3.5 quarts ^C	140-2379 ^C	—	167-0272 ^C	9" 167-1615-01/ 26" 167-1602	160-1378
Prior to 9/87 NHE Begin 9/87 NHE	F	122-0800 ^C	3.5 quarts ^C	140-2379 ^F	149-2279 ^I	167-0272 ^I	160-1378	160-1349-01

Brand Name Model/Series	Spec Letter	Oil Filter ^{1, 2, 3, 5}	Oil Capacity ^{1, 2, 3, 5}	Air Filter ^{3, 5}	Fuel Filter ^{3, 5}	Glow Plug/ Spark Plug ^{2, 3, 5}	Plug Wires ⁵	Tune-up Kit ⁵
Onan Emerald™, continued								
NHE	G H J-P	122-0800 ^C	3.5 quarts ^C	140-2379 ^F	149-2279 ^I 149-1353 ^I 149-2333 ^I	167-0272 ^I	9" 167-1615-01/ 26" 167-1602	Electronic Ignition
NHEL	A-E	122-0800 ^C	3.5 quarts ^C	140-2379 ^F	148-0898 ^I	167-0272 ^I	9" 167-1615-01	160-1378
Prior to 9/87 NHEL Begin 9/87 NHEL	F	122-0645 ^C	3.5 quarts ^C	140-2379 ^F	149-2279 ^I	167-0272 ^I	9" 167-1615-01/ 26" 167-1602	160-1378 160-1349-01
Onan Marquis™								
Gasoline/BGM	A-F G-H	122-0645 ^C	3.5 quarts ^C	140-2379 ^C	149-2279 ^I 149-2341	167-0272 ^I	9" 167-1625-01/ 23" 167-1625-02	Electronic Ignition
Gasoline/NHM	A-F G-H	122-0800 ^C	3.5 quarts ^C	140-2379 ^C	149-2279 ^I 149-2341 ^I	167-0272 ^I	23" 167-1602	Electronic Ignition
LP/NHM	All	122-0800 ^C	3.5 quarts ^C	140-2379 ^C	148-0898 ^I	167-0272 ^G	23" 167-1602	Electronic Ignition
Older Onan® Generators								
BF Power Drawer	A	122-0645 ^D	4 quarts ^B	140-1220 ^D	—	167-0262 ^B	167-1616-01	312-0069
BF RV	A-B	—	4 quarts ^B	140-0495 ^D	—	167-0237 ^B	167-1602	—
BFA RV	A B-D	122-0645 ^C	3.5 quarts ^C	140-0495/ Clean every 150 hours	—	167-0237 ^C 167-0298 ^C	167-1602	—
BGA RV	A B-D	122-0645 ^B	3.5 quarts ^B	140-0495 ^D	—	167-0237 ^B 167-0298 ^B	167-1602	—
BGAL RV	C	122-0645 ^B	3.5 quarts ^B	140-0495 ^D	—	167-0298 ^B	167-1602	—
CCK Mobile/RV	A-Q R-U	122-0800 ^{4, D}	4 quarts ^B	— 140-0495 ^D	—	167-0237 ^B	167-1602	—
LK RV	A-L M	—	2 quarts ^B	— 140-1220 ^D	— 149-1353 ^G	167-0237 ^D	—	—
NH Power Drawer	A	122-0800 ^{4, B}	3.5 quarts ^D	140-1229 ^D	—	167-0262 ^D	167-1616-01	312-0069
NH Power Drawer 9000	A-H	122-0800 ^{4, B}	3.5 quarts ^D	140-1229 ^D	—	167-0262 ^D	167-1616-01	312-0069
NH RV	A-H J-N P-R	122-0800 ^{4, B}	3.5 quarts ^D	140-0495 ^D	167-0241 ^D — 167-0272 ^D	167-0247 ^D	167-1616-01	—
NHL	P	122-0800 ^B	3.5 quarts ^B	140-0495 ^D	—	167-0272 ^B	9" 167-1615-01/ 26" 167-1602	—
Older Onan Diesel Generators								
HDKAG	A-B C D-F G	185-5835 ^B	4.7 quarts ^B	140-2842 ^I	A026K278 ^E	185-6623 185-5421 185-5421 333-0805	—	—
DKC RV	A-B	122-0827 ^B	4 quarts ^B	140-2842 ^I	149-1914-05 ^E	185-2289	—	—
DKD RV	A-E	122-0827 ^B	4 quarts ^B	140-2842 ^I	149-1914-05 ^E	185-2289	—	—
DKG	A	122-0827 ^B	5 quarts ^B	140-2680 ^I	A026K278 ^E	185-2289	—	—
HDCAA/AB	A-D	187-1000 ^E	6.7 quarts ^E	140-3071 ^I	149-2513 ^I	187-1289	—	—
HDKAJ	A-K L	122-0833 ^C	3 quarts ^C	140-2897 ^I	149-2513 ^I 147-0860 ^I	185-5421	—	—
HDKBA	A-E	122-0833 ^C	2 quarts ^C	140-3351 ^I	149-2513 ^I	185-5421	—	—

NOTES

- Interval recommendations assume oil changes are after initial break-in.
- If fewer than the recommended hours then change annually.
- Change more often in dirty and dusty conditions.
Please refer to your operator's manual for more detail.
- If required
- If discrepancy between the guide and your operator's manual, the operator's manual wins

Maintenance intervals

- | | | |
|--------------|--------------|--------------|
| A. 50 hours | D. 200 hours | G. 400 hours |
| B. 100 hours | E. 250 hours | H. 450 hours |
| C. 150 hours | F. 300 hours | I. 500 hours |

Oil and Service/Maintenance Chemicals

OnaMax™ 15W40 Oil (#326-5336) SAE 30 (#326-5339) Maximum protection engine oil formulated to reduce consumption and engine wear due to high temperature oil oxidation and viscosity increase.

OnaFresh™ GXLP Fuel Stabilizer (#326-5365) Specifically formulated for long-lasting prevention of gasoline breakdown during extended RV storage. Protects against gum, varnish, sludge formation, and fuel system corrosion.

Onagard Storage Fogging Spray (#326-5288) Protects small engines and other mechanical equipment during off-season storage.



Cummins Onan



Cummins Power Generation
1400 73rd Ave. NE
Minneapolis, MN 55432
USA
Toll-free 1 800 888 6626
www.cumminsonan.com

Cummins®, Onan® the "C" logo, and Performance you rely on™ are trademarks or registered trademarks of Cummins Inc. ©2013 Cummins Power Generation. All Rights Reserved.