

ONAN P5000IDF EFI



Power when you need it most

5,000-watt dual fuel (Gas/LPG) portable inverter generator

Gas: 3,900 running watts | 5,000 peak watts
Propane: 3,500 running watts | 4,500 peak watts

EFFICIENT CUMMINS ONAN 224CC EFI ENGINE

- Lower fuel use and longer run times vs traditional carbureted engine
- Delivers high altitude performance up to 13,123 ft (4,000 meters) without a carb kit
- Reduced environmental impact with lower engine emissions and evaporative filter

FEATURES

- Battery charging port with charger included
- Limited 3-year warranty
- Retractable handle and easy-grip lift
- Ports for parallel generator operation
- Oil and maintenance tools included



United States Model



PUSH BUTTON AND REMOTE START

Pull cord backup



DUAL FUEL WITH JUST THE FLIP OF A SWITCH

Easily switch from gas to propane with a fuel capacity of 3.4 gallons



ESSENTIAL DATA DISPLAY

VFT Data Center displays lifetime run hours, operating power, remaining fuel, operating voltage, remaining running time



CARBON MONOXIDE DETECTOR

Includes automatic shutoff for safer operation



ONAN P5000IDF EFI

Specifications		
Part number	A075C500	AC outlets
Gasoline running watts	3,900	(1) Duplex 120V 20A (5-20R) (1) Travel trailer 120V 30A (TT-30R)
Gasoline peak watts	5,000	DC outlets
Gasoline running amps	32.5 A @ 120 V	(2) 5V USB-A ports
Gasoline peak amps	41.7 A @ 120 V	Ground
Propane running watts	3,500	Floating neutral
Propane peak watts	4,500	Covered outlets
Propane running amps	29.2 A @ 120 V	Yes
Propane peak amps	37.5 A @ 120V	Manual transfer switch ready
AC voltage	120 Volts	Yes
Frequency	60 Hz	GFCI outlets
Total Harmonic Distortion (THD)	≤3%	No
Automatic voltage regulator	Inverter	RV-ready outlet
Starting system	Electric, remote, recoil	Yes
Battery charger included	Yes	Overload protection (circuit breaker)
Battery included	Yes	Yes
Remote start fob included	Yes (factory paired)	Handle style
Remote start distance (feet/meters)	99ft/30m	Telescoping handle
Push button start	Yes	Wheel kit included
Engine displacement	224cc	Yes (assembled)
Engine brand	Cummins	Wheel size
Engine type	OHV 4-stroke	5.5 in diameter, 1.6 in wide
Engine speed	Variable	Frame thickness in (mm)
Operational volume (dBA)	As low as 52dBA	25
Carburetor kit required to operate at altitude*	No	Emissions
Auto idle control	Yes	EPA, CARB
Economy mode switch	Yes	Spark arrestor
Engine lubrication	Splash	Yes
Recommended oil	SAE 10W30 OIL	Residential warranty
Oil capacity (quarts/ounces)	0.58 Qt / 18.6 oz	3-year limited
Low oil shutdown	Automatic	Commercial warranty
Fuel type	Gasoline or propane	1-year comprehensive
Fuel shut off	Yes	Assembled length in (mm)
Fuel tank capacity (gallons/liters)	3.4 gal (12 L)	25.1 in (637 mm)
Gas - Run Time at 25% Load (hrs)	16.8 hrs	Assembled width in (mm)
Propane - run time at 25% load (hrs) with 20-lb standard propane tank	20 hrs	18.1 in (460 mm)
Gas - run time at 50% load (hrs)	13 hrs	Assembled height in (mm)
Gasoline fuel gauge	Digital	21.2 in (538 mm)
		Extended length in (mm)
		45.4in (1152 mm)
		Carton length in (mm)
		28.9 in (735 mm)
		Carton width in (mm)
		20.3 in (515 mm)
		Carton height in (mm)
		24.2 in (615 mm)
		Dry Unit weight lb (kg)
		108lb (49 kg)
		Shipping weight lb (kg)
		119.7 lb (54.3 kg)
		Compatible accessories:
		Inverter generator paralleling kit, maintenance kit, large generator storage cover, inverter generator running cover, replacement air filter element, key fob, replacement starting battery



Cummins Inc.
Box 3005
Columbus, IN 47202-3005
U.S.A.

cummins.com

Bulletin 6553362 Produced in U.S.A. Rev. 6/26
©2026 Cummins Inc.