

QSK60-G23 GENERATOR SET

INTRODUCING C2750D5BE



ALWAYS ON

Power Generation


Power Generation



IMPROVED PERFORMANCE AND CAPABILITY

INTRODUCING C2750D5BE


- Cummins QSK60-G23, V16 cylinder, four-cycle, diesel engine
- Stamford® P80 Alternator
- Cummins PowerCommand® 3.3 Control System
- Power nodes: 50Hz: 2750kVA - Standby (ESP)
2500kVA - Data Center Continuous (DCC)



COOLING SYSTEM

Full 50°C ambient capability
before de-rate*

*Altitude restrictions apply



**POWERCOMMAND® 3.3
CONTROL SYSTEM**

Provides total genset system integration, including automatic remote start/stop, alarm and status message display with optional masterless load demand

**EPA TIER 2
EMISSIONS CERTIFIED**

**REDESIGNED
CONTROL PANEL**

Provides enhanced options for flexibility



The C2750D5BE model offers a 2-year/1000-hour warranty (Standby ESP) alongside new and enhanced features, including:

- Full 50°C Ambient Capability Before De-rate
- Enhanced Data Center Options
- Tailored Transoptions up to ISO-8528 G3
- EPA Tier 2 Emissions Certified
- Optional Masterless Load Demand
- Enhanced Power Density – Lower per unit costs over equivalent products

GLOBAL REACH, LOCAL FOCUS.

**OVER 8000
DISTRIBUTOR
AND DEALER
LOCATIONS.**

No matter where you are, your local Cummins distributor or dealer is your first line of support for everything from application assistance and on-site commissioning to troubleshooting, maintenance and aftermarket services.

**VISIT [LOCATOR.CUMMINS.COM](https://locator.cummins.com)
TO FIND YOUR LOCAL
DISTRIBUTOR OR DEALER.**



ALWAYS ON™
cummins.com

All rights reserved.

Bulletin 5600539 Rev. 3/20
©2020 Cummins Inc.