



MERITOR® BRAKE PADS



Available in these languages at meritorpartsexpress.com

Language		Catalogue Title
	English	Meritor Brake Pads
	Français	Meritor Plaquettes de Frein
	Deutsch	Meritor Bremsbeläge
	Italiano	Pastiglie dei Freni Meritor
	Nederlands	Meritor-Remblokken
	Español	Pastillas de Freno Meritor
	Polski	Klocki Hamulcowe Meritor
	Русский	Тормозные Колодки Meritor

INTRODUCTION



As part of an ongoing commitment to provide braking solutions across vehicles of all ages and duty cycles, Cummins are pleased to announce some key updates to its commercial vehicle air disc brake pad programme.

In response to customer feedback, and following a comprehensive range review, Cummins brake pad portfolio has been rationalized according to market need, into Meritor Genuine, Premium and Allfit propositions.

The realigned offer, provides customers with a clear choice from Genuine OE first fit product to quality aftermarket products:



GENUINE

Designed and developed in conjunction with vehicle manufacturers for Meritor specific brake system applications, the Genuine range of pads are the exact parts fitted as OE.



PREMIUM

Our Premium brake pad range offers a selection of parts with equivalent quality levels to OE. Designed and developed using quality parts and high specification friction material, the Premium range is tailored to application and market need.



ALLFIT

The Allfit brake pad range provides a quality, aftermarket solution at an affordable price.

MERITOR® OE GENUINE


GENUINE

Designed and developed in conjunction with OE manufacturers for specific Meritor brake system applications, the Genuine range of pads perform to the exact specification and standards set by the vehicle manufacturer. And, because the exact pads are fitted as OE, you can be confident that you are replacing like-for-like, fully compatible parts.

Genuine pads are manufactured with OE homologated friction material in conformity with EEC Regulation 13 braking standards to ensure optimized safety, performance, wear, service and product life.

MERITOR® PREMIUM


The “MAX” premium performance brake pads have been developed for both Meritor and All Makes brakes. Proven to be best in class in terms of friction wear for demanding applications, on CV Heavy Duty Truck, Coach and Trailer applications, and notably, for their high performance on City Bus.



Optimised for:

- **Performance** – Modelled on the characteristics of leading OE material for friction level and stability across a wide range of temperatures.
- **Wear** – Best in class friction wear for arduous and demanding applications but not at the expense of rotors.
- **Refinement** – Mesh interface for high shear strength and thermal interlayer.

Meritor’s “SK” brake pads provide an OE equivalent solution for Meritor brakes. Supplied complete with OE accessory kits and manufactured from high performance friction material tailored to vehicle application, for outstanding endurance.



LOOK FOR THE PAD WITH THE BULL!



Optimised for:

- Meritor brakes. Designed for outstanding brake performance (torque) especially under high temperature braking conditions up to 500°C on Meritor brake applications.
- High fading resistance even at maximum brake pressure in combination with high temperature.
- Enhanced friction level compared with OE material whilst not compromising on rotor wear.

OE ACCESSORIES



OE PWWI's



As part of its ongoing commitment to deliver sustainable solutions, Meritor have brought to market a range of Positive Pad Retraction (PPR) brake pads.

Meritor's patented PPR technology can help improve fuel efficiency, and increase the longevity of brake pads and discs.

The PPR System which can be offered as a retrofit solution – can help mitigate against rising transport costs, whilst also helping the environment through a reduction in CO2 emissions.



Key Benefits of PPR:

- Increases longevity of pads and discs
- Improves fuel efficiency
- Reduces drag
- Patented technology
- Reduces impact on environment

PPR Braking Performance

Dynamometer testing was carried out, with and without Meritor PPR technology.


Brakes were tested in a steady state vehicle operating condition without PPR technology.

The same brakes were then tested with PPR technology.

A significant drag reduction was recorded with PPR technology fitted – an average of 71% drag reduction across the range of tests.

The reduction in drag can translate directly into reduced fuel consumption and improved pad and disc life.


Source Data: Test procedure TP240. Tests: 400147737-1, 400147737-2, 400150653-1, 400150653-2



Manufactured to stringent standards, using quality components and friction material compounds, Meritors' range of Allfit pads are subject to extensive testing for wear and performance for normal braking duty cycles on Truck, Trailer, Bus and Coach applications.

Features and Benefits:

- Hard marked or stamped parts: To aid product identification with clearly legible part numbers and R90 certification, even after periods of service.
- Back Plate composed of high-quality cast iron or precision stamped steel with spigot holes, to provide mechanical locking of friction material.
- Specially developed surface coating on pads, to provide optimum initial braking performance, designed to accelerate bedding, whilst also helping to clean the brake disc surface.
- Unique "shaped" underlayer to reduce heat transfer to the backplate and improve hot and cold shear strength.
- Friction material which complies with and exceeds the performance requirements of ECER90.




As expected from a leading braking expert, Meritor regularly undertake additional testing against the following test parameters:

Hot Shear Testing: In addition to the R90 ambient temperature test, Meritor also conduct Hot shear testing on pads heated to 300°. Tests have proven that shear strength exceeds the R90 min of 250N/cm² of friction material.

Dynamometer Testing: A full range of performance characteristic tests across varying pressures, speeds and temperatures are made on production part samples, ensuring the consistent manufacture of high quality parts.

Inertia Dynamometer Wear Testing: Meritor undertake full scale inertia dynamometer wear testing, including characteristic performance checks between each wear section to ISO 26865.

The chart outlines the Allfit range of pads wear characteristics compared to OE, OES and a generic Aftermarket fit for function part:



CONTENTS



1.	CATALOGUE USERS GUIDE	6
2.	GLOSSARY	8
3.	APPLICATIONS	11
4.	BUYERS GUIDE	71
5.	CROSS REFERENCES	93

1



2



3



4



5





Using This Catalogue

This catalogue has been designed to make it as easy as possible for you to make the correct product identification for your vehicles and applications. The most reliable method of identification is to use the Cross Reference section (Section 5). Although it is always advisable to match the physical features of your brake pad against the Buyers Guide (Section 4). All application details are provided as guidance only as vehicle and trailer manufacturers may change brake pad fitments without notice.

APPLICATIONS – SECTION 3

Vehicle Manufacturer, Type and Model	Caliper Applications	Build Date	Fitting Position	Meritor Reference		
						
						
Volvo						
						
FM Series III	Meritor ELSA 225-3	01/20 >>			MDP5101SK / MDP5104SK / MDP5101PPRK / MDP5104PPRK / MAX174K	MDP3174K / MDP3174KWI
	Meritor ELSA 195	01/20 >>			MDP5093SK	MDP3169K

BUYERS GUIDE – SECTION 4



Meritor Reference

Vehicle Manufacturer
+ = See applications for more

WVA Reference

MDP5000

Berkhof
Caetano
Dennis
Van Hool
Volvo
+

WVA
29173

KIT CONTENTS:

x 4
 x 4
 x 2
 x 2

PWWI: Included / Prepared for / None

215.0 mm

96.5 mm

29.25 mm

Meritor
ELSA 225-1

KIT MBA108
PWWI MBA019

Pad Width

Pad Height

Pad Thickness

Caliper Applications

Optional Fitting Kit and
PWWI



CROSS REFERENCES – SECTION 5

Vehicle
Manufacturer

		
Volvo		
20526568	MAX174K	
20526568	MAX174KWI	
20526568	MDP3174KWI	
20526568	MDP3174K	
20526568	MDP5104	
20526568	MDP5104PPRK	
20526568	MDP5104SK	
20526569	MDP5102	
20526570	MDP5093SK	
20535922	MDP5099	
20560412	MAX174K	
20560412	MAX174KWI	
20560412	MDP3174KWI	
20560412	MDP3174K	
20560412	MDP5104	
20560412	MDP5104PPRK	
20560412	MDP5104SK	
20560414	MDP5106	

Manufacturer
Reference

		
20560414	MDP5106PPRK	
20560414	MDP5106SK	
20560415	MDP5093SK	
20568711	MAX174K	
20568711	MAX174KWI	
20568711	MDP3174KWI	
20568711	MDP3174K	
20568711	MDP5104	
20568711	MDP5104PPRK	
20568711	MDP5104SK	
20568712	MDP5106	
20568712	MDP5106PPRK	
20568712	MDP5106SK	
20568713	MDP3169K	
20568713	MDP5093	
20568713	MDP5093SK	
20568714	MAX174K	
20568714	MAX174KWI	
20568714	MDP3174KWI	

Meritor
Reference

		
20568714	MDP3174K	
20568715	MDP5106	
20568715	MDP5106PPRK	
20568715	MDP5106SK	
20765963	MDP5093SK	
20765963 5	MDP5093	
20768092	MAX125K	
20768092	MDP3125K	
20768092	MDP5057	
20768101	MDP5072	
20768115	MDP5053	
20918891	MAX125K	
20918891	MDP3125K	
20918891	MDP5057	
20931343	MAX125K	
20931343	MDP3125K	
20931343	MDP5057	
20931343	MAX125K	
20931343	MDP3125K	

		
20932682	MAX125K	
20932682	MDP3125K	
20932682	MDP5057	
20976509	MAX131K	
20976509	MDP3131K	
20976509	MDP5099	
21024701	MAX174K	
21024701	MAX174KWI	
21024701	MDP3174KWI	
21024701	MDP3174K	
21024701	MDP5119PPRK	
21024701	MDP5119SK	
21024702	MAX174K	
21024702	MAX174KWI	
21024702	MDP3174KWI	
21024702	MDP3174K	
21024702	MDP5119PPRK	
21024702	MDP5119SK	
21088907	MAX125K	

1



2



3




4



5




GLOSSARY

	Description
	Bus
	Trailer
	Truck
	Refuse Vehicle
	Fire Engine
	Van
	Front
	Rear
	Front / Rear
	Vehicle Manufacturer, Type and Model
	Vehicle Manufacturer
	Build Date
	Caliper Applications
	Genuine Part
	Premium Part
	Allfit Part
	Bolt
	Cable Sleeve
	Cap
	Clip
	Cotter Pin

GLOSSARY



	Description
	Dust Cover
	Grease
	Heatplate Kit
	O-Ring
	Pad Retaining Plate
	Pad Strap
	Pin
	Plug
	Point Spline Drive
	PPR Spring
	PWWI Bracket
	Rivet
	Rubber Cap
	Spring
	Top Spring
	U Bar
	U Spring
	Washer
 ► 7.1	Manufacturers' numbers are for reference only
 ► 7.2	Kit content images shown are for illustration purposes only and may not be an exact representation of the product

1



2



3



4



5





1



2




3



4



5





1



2




3



4



5





1



2



3



4



5



Agrale	13	Liaz	30
Alexander Bus	13	M.C.I. (New Flyer Industries)	30
Autosan	13	MAN	30
Ayats	13	MAN PSV's	36
B.C.I. (Bus & Coach International)	13	MCV	40
Berkhof	14	MCW	40
Beulas	14	Menarini	40
BMC	14	Mercedes	41
Bova	14	Mercedes Axles	44
BPW Axles	14	Mercedes PSV (Inc Evobus)	44
BYD (includes BYD ADL)	15	Meritor (Inc Lucas, Rockwell, ROR)	46
Caetano	15	Moseley	47
Cobus	16	Neoplan (Inc Auwärter)	47
Corona	16	Nicolas Trailers	48
Daewoo Trucks (Avia)	17	Nissan (Inc Motor Iberica)	48
DAF PSV's (Inc Leyland Daf)	17	Nogebus	48
DAF Trucks (Inc Leyland Daf)	17	Optare	49
Den Oudsten	18	Plaxton	49
Dennis	19	Prevost	50
Dennis PSV's	19	Raba	50
Discos	20	Renault Trucks	50
Enterprise Bus	20	Renault Trucks PSV	55
ERF	20	SAF / Sauer	56
Esker	21	Scania	57
Foden	21	Scania PSV (Inc Irizar)	57
Fontenax	22	Schmitz (CargoBull)	58
Foton	22	Seddon Atkinson	58
Freightliner	22	Setra (Inc Kässbohrer)	58
Fruehauf (Inc Crane Fruehauf, GT Trailers)	22	Sinotruk (CNHTC)	60
Goldhofer	22	Sitcar	60
Granning Lynx	22	Solaris Bus	60
Haldex	23	SOR	60
Hendrickson	23	Temsa	61
Heuliez	23	Timoney	61
Higer	23	Trenkamp & Gehle (Inc Gigant, SAE, SMB, Dupillier)	61
Ikarus	23	TVM	61
Ingersoll	23	UD Truck & Bus (Inc Nissan Diesel)	61
Iveco (Inc Iveco Ford)	23	Valx	62
Iveco PSV (Inc Irisbus, Karosa, Recreo)	27	Van Hool	62
Jelcz	29	VDL (Inc Bova, Jonckheere)	64
JMC	29	Volvo	64
Jost	29	Volvo PSV	66
Karsan	29	Wrightbus	67
King Long (Golden Dragon, Golden Journey)	29	York Trailers (Hendrickson)	68
Kögel / Trax	29	Yutong	68
Krone	29	ZF	68
LCV	30	Zhongtong	68
Leciñena	30		



					GENUINE	PREMIUM	ALLFIT
Agrale							
12 Series Bus	Knorr SB7 / SN7	01/16 >>			MAX087K	MDP3087K / MDP3087KP	
15 Series Bus	Knorr SB7 / SN7	01/09 >>			MAX087K	MDP3087K / MDP3087KP	
17 Series Bus	Knorr SB7 / SN7	01/16 >>			MAX087K	MDP3087K / MDP3087KP	
Alexander Bus							
ALX 100 – 8.1 --> 8.5m	Meritor B Frame (2x60)	01/96 >> 12/99		MDP5040		MDP3835K	
ALX 400 – 10.5m	Meritor D LISA	01/97 >>			MAX090K / MDP5042SK	MDP3090K	
	Meritor ELSA 2	01/97 >>			MDP5073SK / MDP5056SK / MAX131K	MDP3131K	
DB 250 Mk II – 10.5m	Knorr SB7 / SN7	01/05 >>			MAX087K	MDP3087K / MDP3087KP	
Ultra Low Floor Bus – 22.5" wheels	Meritor D LISA	01/99 >> 12/02			MAX090K / MDP5042SK	MDP3090K	
Autosan							
Eagle – 17.5" wheels	Wabco Pan 17	01/06 >>			MAX088K	MDP3088 / MDP3088K	
Ayats							
Atlantis – MAN axle	Meritor D3	01/01 >>			MAX030K	MDP3030K	
	Meritor ELSA 1 / D3	01/01 >>			MDP5065SK		
	Meritor ELSA 2	01/01 >>			MDP5073SK / MDP5056SK / MAX131K	MDP3131K	
Atlantis – Scania axle	Knorr SB7 / SN7	01/01 >>			MAX087K	MDP3087K / MDP3087KP	
Bravo – MAN axle	Meritor D3	01/96 >>			MAX030K	MDP3030K	
	Meritor ELSA 1 / D3	01/96 >>			MDP5065SK		
	Meritor ELSA 2	01/96 >>			MDP5073SK / MDP5056SK / MAX131K	MDP3131K	
Bravo – Scania axle	Knorr SB7 / SN7	01/96 >>		MDP9005	MAX087K	MDP3087K / MDP3087KP	
Platinum – MAN axle	Meritor D3	01/00 >>			MAX030K	MDP3030K	
	Meritor ELSA 1 / D3	01/00 >>			MDP5065SK		
	Meritor ELSA 2	01/00 >>			MDP5073SK / MDP5056SK / MAX131K	MDP3131K	
Platinum – Scania axle	Knorr SB7 / SN7	01/00 >>			MAX087K	MDP3087K / MDP3087KP	
B.C.I. (Bus & Coach International)							
Falcon 45	Knorr SB7 / SN7	01/01 >>			MAX087K	MDP3087K / MDP3087KP	

- Refer to Buyers Guide



1



2



3



4



5



								
								
Berkhof								
								
Ambassador – ALE 106-205 --> ALE120-205	Knorr SB7 / SN7	07/07 >>			MAX087K	MDP3087K / MDP3087KP		
Axial – 100 DD	Knorr SB7 / SN7	01/97 >>			MAX087K	MDP3087K / MDP3087KP		
Axial – 50	Meritor D LISA	01/97 >>			MAX090K / MDP5042SK	MDP3090K		
	Meritor D2	10/91 >> 01/97				MDP3043K		
Excellence – 3000HD	Knorr SB7 / SN7	01/96 >>			MAX087K	MDP3087K / MDP3087KP		
Beulas								
								
PSV's – Midi Star	B Frame (2x60)	01/00 >>				MDP3122		
PSV's – Stelar	Knorr SB5 / SN5	01/07 >>			MAX148K	MDP3148K		
BMC								
								
518	Wabco Pan 17	01/97 >>			MAX088K	MDP3088 / MDP3088K		
Condor	Knorr SB7 / SN7	01/04 >>			MAX087K	MDP3087K / MDP3087KP		
Hawk	Wabco Pan 17	01/97 >>			MAX088K	MDP3088 / MDP3088K		
Karisma 15T Bus	Knorr SB6 / SN6	01/06 >>			MAX095K	MDP3095K		
Probus 11T Bus	Wabco Pan 17	01/97 >>			MAX088K	MDP3088 / MDP3088K		
Probus 15T Bus	Knorr SB6 / SN6	01/03 >>			MAX095K	MDP3095K		
School Bus – 1100 FE	Wabco Pan 17	01/03 >>			MAX088K	MDP3088 / MDP3088K		
Bova								
								
ZF Axle	Knorr SB7 / SN7	01/90 >>			MAX087K	MDP3087K / MDP3087KP		
BPW Axles								
								
Eco Plus	Knorr SB6 / SN6	01/98 >>			MAX095K	MDP3095K		
	Knorr SB7 / SN7	01/98 >>			MAX087K	MDP3087K / MDP3087KP		
	Knorr SB6 / SN6	06/03 >>			MAX165K	MDP3165K		
SB3308	Knorr SB5 / SN5	01/98 >>			MAX148K	MDP3148K		
SB3745	Knorr SB6 / SN6	01/98 >>			MAX095K	MDP3095K		
	Knorr SB6 / SN6	06/03 >>			MAX165K	MDP3165K		
SB4309	Knorr SB7 / SN7	01/98 >>			MAX087K	MDP3087K / MDP3087KP		
	Knorr SK7	06/03 >>			MAX171K	MDP3171K		

- Refer to Buyers Guide



		</					

- Refer to Buyers Guide



1



2



3



4



5



- Refer to Buyers Guide



							
							
Daewoo Trucks (Avia)							
							
A60	Wabco 456 F	01/97 >>				MDP3017 / MDP3024	
A75	Wabco 456 F	01/97 >>				MDP3017 / MDP3024	
A80	Wabco 456 F	01/97 >>				MDP3017 / MDP3024	
D100	Wabco 456 F	10/00 >>				MDP3017 / MDP3024	
D120	Wabco 456 F	10/00 >>				MDP3017 / MDP3024	
D60	Wabco 456 F	10/00 >>				MDP3017 / MDP3024	
D75	Wabco 456 F	10/00 >>				MDP3017 / MDP3024	
D80	Wabco 456 F	10/00 >>				MDP3017 / MDP3024	
D90	Wabco 456 F	10/00 >>				MDP3017 / MDP3024	
DAF PSV's (Inc Leyland DAF)							
							
MB, MBG Series – 200, 201, 220, 230	Knorr K85	01/87 >>				MDP3747	
MB, SB, TB 2000 Series – 2100, 2200	Knorr SB7 / SN7	01/74 >> 01/89			MAX087K	MDP3087K / MDP3087KP	
SB 120, SB180, SB 200, SBG 200 Series	Knorr SB6 / SN6	01/99 >>			MAX095K	MDP3095K	
SB 200, SBG 200 Series – 200, 201, 220, 230	Knorr K85	01/87 >>				MDP3747	
SB 2000 Series – 2300 / 2305	Knorr K85	01/87 >>				MDP3747	
	Knorr SB7 / SN7	01/89 >>			MAX087K	MDP3087K / MDP3087KP	
SB, SBK, SBR 3000 Series	Knorr K85	01/87 >>				MDP3747	
	Knorr SB7 / SN7	01/87 >>		MDP9005	MAX087K	MDP3087K / MDP3087KP	
SB, SBR – 3000, 4000 Series	Knorr SB7 / SN7	01/97 >>		MDP9005	MAX087K	MDP3087K / MDP3087KP	
Swift	Wabco 456 F	01/87 >> 01/91				MDP3017 / MDP3024	
DAF Trucks (Inc Leyland DAF)							
							
45 Series	Wabco 456 F	01/91 >> 01/01				MDP3017 / MDP3024	
50 Series	Wabco 1600 V-G	01/93 >> 03/96				MDP3077	
55 Series	Wabco 1600 V-G	01/93 >> 03/96				MDP3077	
	Wabco 1600 V-G	01/95 >> 01/02				MDP3077	
65 CF Series – 180 --> 290	Knorr SB7 / SN7	01/98 >> 12/00			MAX087K	MDP3087K / MDP3087KP	
75 CF Series – 250, 310, 360	Knorr SB7 / SN7	01/98 >> 12/00			MAX087K	MDP3087K / MDP3087KP	
85 CF Series – 340, 380, 430	Knorr SB7 / SN7	01/98 >> 12/00			MAX087K	MDP3087K / MDP3087KP	
95 CF Series – 340 --> 510	Knorr SB7 / SN7	01/97 >> 01/02		MDP9000	MAX087K	MDP3087K / MDP3087KP	
CF 65 Series – 180 --> 300	Knorr SB7 / SN7	01/01 >> 05/13		MDP9000	MAX087K	MDP3087K / MDP3087KP	

- Refer to Buyers Guide



1



2



3



4



5



								
					GENUINE	PREMIUM	ALLFIT	
...DAF Trucks (Inc Leyland DAF)								
								
CF 75 Series – 250 --> 360	Knorr SB7 / SN7	01/01 >> 05/13		MDP9000	MAX087K	MDP3087K / MDP3087KP		
CF 85 Series – 340 --> 510	Knorr SB7 / SN7	01/01 >> 05/13		MDP9000	MAX087K	MDP3087K / MDP3087KP		
CF Series – 230 --> 530	Knorr SB7 / SN7	05/13 >>			MAX087K	MDP3087K / MDP3087KP		
CF Series – FT Electric, FT Hybrid	Knorr SB7 / SN7	01/19 >>			MAX087K	MDP3087K / MDP3087KP		
F Series – FA 1000, FA 1005, FA 1100	Wabco 456 F	12/86 >> 01/93				MDP3017 / MDP3024		
F Series – FA 600, FA 800, FA 900	Wabco 456 F	12/86 >> 01/93				MDP3017 / MDP3024		
FA45	Wabco 1600 V-G	01/96 >> 01/01				MDP3077		
LF 45 Series – FA 45.130 --> FA 45.250	Wabco Pan 17	01/01 >> 01/14			MAX088K	MDP3088 / MDP3088K		
	Wabco Pan 17	01/14 >>			MAX088K	MDP3088 / MDP3088K		
LF 55 Series – FA 55.160 --> FA.55.300	Knorr SB7 / SN7	01/01 >>		MDP9000	MAX087K	MDP3087K / MDP3087KP		
	Wabco Pan 19-1	01/01 >>			MAX126K	MDP3126 / MDP3126K		
	Wabco Pan 19-2	01/01 >>				MDP3141		
LF 55 Series – FA, FAN 55.180 --> FA 55.300	Knorr SB7 / SN7	01/01 >>			MAX087K	MDP3087K / MDP3087KP		
LF Series – FA, FT 150 --> 320	Wabco Pan 19-1	05/13 >>			MAX126K	MDP3126 / MDP3126K		
Roadrunner Series – 6.10, 6.12, 6.13, 6.15	Wabco 456 F	01/86 >> 12/91				MDP3017 / MDP3024		
Roadrunner Series – 8.10, 8.12, 8.13, 8.15	Wabco 456 F	01/86 >> 12/91				MDP3017 / MDP3024		
Roadrunner Series – 10.12, 10.13, 10.15	Wabco 456 F	01/86 >> 12/91				MDP3017 / MDP3024		
XF 95 Series – 380 --> 560	Knorr SB7 / SN7	01/02 >>		MDP9000	MAX087K	MDP3087K / MDP3087KP		
XF 105 Series – 408 --> 560	Knorr SB7 / SN7	01/02 >>		MDP9000	MAX087K	MDP3087K / MDP3087KP		
XF Series – FT 480	Knorr SB7 / SN7	01/20 >>			MAX087K	MDP3087K / MDP3087KP		
XF Series (XG Series) – 410 --> 530	Knorr SB7 / SN7	10/12 >>			MAX087K	MDP3087K / MDP3087KP		
Den Oudsten								
								
PSV's Alliance City Bus – B91	Meritor D3	01/99 >> 12/02			MAX030K	MDP3030K		
	Meritor DX 225	01/99 >> 12/02			MDP5083SK			
	Meritor ELSA 1 / D3	01/99 >> 12/02			MDP5065SK			
	Meritor ELSA 2	01/99 >> 12/02			MDP5073SK / MDP5056SK / MAX131K	MDP3131K		
PSV's Alliance City Bus – B93	Meritor D3	01/99 >> 12/02			MAX030K	MDP3030K		
	Meritor DX 225	01/99 >> 12/02			MDP5083SK			
	Meritor ELSA 1 / D3	01/99 >> 12/02			MDP5065SK			
	Meritor ELSA 2	01/99 >> 12/02			MDP5073SK / MDP5056SK / MAX131K	MDP3131K		

- Refer to Buyers Guide



						 				 	
						GENUINE		PREMIUM		ALLFIT	
...Den Oudsten											
											
PSV's Alliance City Bus – B95	Meritor D3	01/99 >> 12/02				MAX030K	MDP3030K				
	Meritor DX 225	01/99 >> 12/02				MDP5083SK					
	Meritor ELSA 1 / D3	01/99 >> 12/02				MDP5065SK					
	Meritor ELSA 2	01/99 >> 12/02				MDP5073SK / MDP5056SK / MAX131K	MDP3131K				
PSV's Alliance City Bus – B96	Meritor D3	01/99 >> 12/02				MAX030K	MDP3030K				
	Meritor DX 225	01/99 >> 12/02				MDP5083SK					
	Meritor ELSA 1 / D3	01/99 >> 12/02				MDP5065SK					
	Meritor ELSA 2	01/99 >> 12/02				MDP5073SK / MDP5056SK / MAX131K	MDP3131K				
PSV's Almere City Bus – 22.5" wheels	Meritor DX 225	01/99 >>				MDP5083SK					
Dennis											
											
Fire Engines – Dagger	Knorr SB5 / SN5	01/00 >>				MAX148K	MDP3148K				
Fire Engines – Rapier	Bendix SEE 2X67	01/91 >>					MDP3013				
Fire Engines – Sabre	Meritor D LISA	01/95 >>				MAX090K / MDP5042SK	MDP3090K				
											
Refuse Vehicles – Eagle	Meritor D LISA	01/94 >>				MAX090K / MDP5042SK	MDP3090K				
Refuse Vehicles – Elite 2	Meritor D LISA	01/08 >>				MAX090K / MDP5042SK	MDP3090K				
	Meritor D LISA	05/00 >> 01/08		MDP5071		MAX090K / MDP5042SK	MDP3090K				
Refuse Vehicles – Phoenix II	Meritor D LISA	01/00 >>				MAX090K / MDP5042SK	MDP3090K				
Dennis PSV's											
											
Arrow	Meritor D LISA	01/95 >>		MDP5061		MAX090K / MDP5042SK	MDP3090K				
Dart MkII – 19.5" wheels	Wabco Pan 19-2	01/02 >>					MDP3141				
Dart MkII – 22.5" wheels	Meritor D LISA	01/02 >>				MAX090K / MDP5042SK	MDP3090K				
Enviro Line – Enviro 500	Knorr SB7 / SN7	01/02 >>				MAX087K	MDP3087K / MDP3087KP				
Enviro Line – R200, R300, R345, R420, R500	Knorr SB6 / SN6	01/02 >>				MAX095K	MDP3095K				
	Knorr SB7 / SN7	01/02 >>				MAX087K	MDP3087K / MDP3087KP				
	Wabco Pan 19-1	01/02 >>				MAX126K	MDP3126 / MDP3126K				
Iliade – 22.5" wheels	Meritor D3	01/98 >>				MAX030K	MDP3030K				
	Meritor ELSA 1 / D3	01/98 >>				MDP5065SK					
	Meritor ELSA 2	01/98 >>				MDP5073SK / MDP5056SK / MAX131K	MDP3131K				

- Refer to Buyers Guide



1



2



3



4



5



				 			
					GENUINE	PREMIUM	ALLFIT
...Dennis PSV's							
							
Javelin – with Wabco Brakes	Wabco Pan 19-1	01/01 >>			MAX126K	MDP3126 / MDP3126K	
Javelin Mk II – 11m, 12m bus, coach	Meritor D2	01/91 >> 12/95				MDP3043K	
Javelin Mk III – 11m, 12m bus, coach	Meritor D2	01/91 >> 12/95				MDP3043K	
	Meritor D LISA	01/95 >>				MDP3090K	
Lance SLF – 22.5" wheels	Meritor D3	01/95 >>			MAX030K	MDP3030K	
	Meritor ELSA 1 / D3	01/95 >>			MDP5065SK		
	Meritor ELSA 2	01/95 >>			MAX131K / MDP5073SK / MDP5056SK	MDP3131K	
Olympus – OL series 260 --> 301	Knorr SB7 / SN7	10/09 >>			MAX087K	MDP3087K / MDP3087KP	
Panther	Knorr SB7 / SN7	01/99 >>				MDP3087K / MDP3087KP	
R Series – 22.5" wheels	Knorr SB7 / SN7	01/99 >>				MDP3087K / MDP3087KP	
Trident II – 22.5" wheels	Knorr SB7 / SN7	01/01 >>		MDP9005	MAX087K	MDP3087K / MDP3087KP	
Discos							
							
NR Series	Knorr SB7 / SN7	01/99 >>			MAX087K	MDP3087K / MDP3087KP	
TZ Series	Knorr SB6 / SN6	01/99 >>			MAX095K	MDP3095K	
	Knorr SB7 / SN7	01/99 >>			MAX087K	MDP3087K / MDP3087KP	
with Haldex brakes	Haldex Modul X - DB22	01/00 >>				MDP3143K	
with Knorr brakes	Knorr SB7 / SN7	01/99 >>			MAX087K	MDP3087K / MDP3087KP	
with Wabco Brakes	Wabco Pan 19-1	01/00 >>			MAX126K	MDP3126 / MDP3126K	
Enterprise Bus							
							
Plasma – 17.5" wheels	Wabco Pan 17	01/05 >>			MAX088K	MDP3088 / MDP3088K	
ERF							
							
B Series	Knorr SB7 / SN7	01/75 >> 01/83			MAX087K	MDP3087K / MDP3087KP	
ECL Series – RD3, TP3	Knorr SB7 / SN7	11/99 >>			MAX087K	MDP3087K / MDP3087KP	
	Meritor ELSA 2	11/99 >>		MDP5059	MDP5073SK / MDP5056SK		
	Meritor ELSA 2	11/99 >>			MAX087K	MDP3131K	
ECM Series – MTP4	Knorr SB7 / SN7	11/99 >>			MAX087K	MDP3087K / MDP3087KP	
	Meritor ELSA 2	11/99 >>		MDP5059			
	Meritor ELSA 2	11/99 >>			MDP5073SK / MDP5056SK / MAX131K	MDP3131K	

- Refer to Buyers Guide



										
								GENUINE	PREMIUM	ALLFIT
...ERF										
										
ECM Series – RD2	Knorr SB7 / SN7	11/99 >>				MAX087K	MDP3087K / MDP3087KP			
	Meritor D3	11/99 >>				MAX030K	MDP3030K			
	Meritor ELSA 1	11/99 >>		MDP5038						
	Meritor ELSA 1 / D3	11/99 >>				MDP5065SK				
	Meritor ELSA 2	11/99 >>		MDP5059						
	Meritor ELSA 2	11/99 >>				MDP5073SK / MDP5056SK / MAX131K	MDP3131K			
ECM Series – RR3, RDRS3	Knorr SB7 / SN7	11/99 >>				MAX087K	MDP3087K / MDP3087KP			
	Meritor D3	11/99 >>				MAX030K	MDP3030K			
	Meritor ELSA 1	11/99 >>		MDP5038						
	Meritor ELSA 1 / D3	11/99 >>				MDP5065SK				
	Meritor ELSA 2	11/99 >>		MDP5059						
	Meritor ELSA 2	11/99 >>				MDP5073SK / MDP5056SK / MAX131K	MDP3131K			
ECS, ECT, ECX Series – 10 --> 32 Series	Knorr SB6 / SN6	11/99 >>				MAX095K	MDP3095K			
	Knorr SB7 / SN7	11/99 >>				MAX087K	MDP3087K / MDP3087KP			
	Meritor D3	11/99 >>				MAX030K	MDP3030K			
	Meritor ELSA 1	11/99 >>		MDP5038						
	Meritor ELSA 1 / D3	11/99 >>				MDP5065SK				
	Meritor ELSA 2	11/99 >>		MDP5059						
	Meritor ELSA 2	11/99 >>				MDP5073SK / MDP5056SK / MAX131K	MDP3131K			
Esker										
										
Cimo XL	Knorr SB6 / SN6	01/07 >>				MAX095K	MDP3095K			
Divo Cityliner Eurorider	Knorr SB7 / SN7	01/90 >>				MAX087K	MDP3087K / MDP3087KP			
Divo GT VDL	Knorr SB7 / SN7	01/07 >>				MAX087K	MDP3087K / MDP3087KP			
Touring	Knorr SB6 / SN6	01/98 >>				MAX095K	MDP3095K			
Foden										
										
Alpha 2000 – A2-4R	Knorr SB7 / SN7	10/98 >>		MDP9000		MAX087K	MDP3087K / MDP3087KP			
Alpha 3000 – A3-4T	Knorr SB7 / SN7	10/98 >>		MDP9000		MAX087K	MDP3087K / MDP3087KP			
Alpha 3000 – A3-6M	Knorr SB7 / SN7	10/98 >>		MDP9000		MAX087K	MDP3087K / MDP3087KP			
Alpha 3000 – A3-6R	Knorr SB7 / SN7	10/98 >>		MDP9000		MAX087K	MDP3087K / MDP3087KP			
Alpha 3000 – A3-6T	Knorr SB7 / SN7	10/98 >>		MDP9000		MAX087K	MDP3087K / MDP3087KP			

 - Refer to Buyers Guide



1



2



3



4



5



						
						
						
						
						
			GENUINE		PREMIUM	
					ALLFIT	
Fontenax						
						
Iveco axle	Knorr SB7 / SN7	01/98 >>			MAX087K	MDP3087K / MDP3087KP
Mercedes axle	Knorr SB6 / SN6	01/98 >>			MAX095K	MDP3095K
Renault axle	Meritor ELSA 2	01/98 >>			MAX131K	MDP3131K
	Meritor ELSA 2	01/98 >>			MDP5073SK / MDP5056SK	
Foton						
						
BJ6123 Series Electric Bus	Knorr SB7 / SN7	09/07 >>			MAX087K	MDP3087K / MDP3087KP
Freightliner						
						
Cascadia	Knorr SB7 / SN7	01/12 >>			MAX087K	MDP3087K / MDP3087KP
Fruehauf (Inc Crane Fruehauf, GT Trailers)						
						
with Haldex brakes	Haldex Modul X - DB19	01/99 >>				MDP3181K
	Haldex Modul X - DB22	09/96 >>				MDP3143K
with Knorr brakes	Knorr SB7 / SN7	09/96 >>			MAX087K	MDP3087K / MDP3087KP
with Meritor brakes	Meritor DX 195	01/99 >>			MDP5076SK	MDP3124K
	Meritor DX 225	06/00 >>			MDP5083SK	
	Meritor ELSA 195	01/04 >>				MDP3169K
	Meritor ELSA 195	01/04 >>			MDP5093SK	
with Wabco brakes	Wabco Pan 19-2					MDP3141
	Wabco Pan 19-1	01/99 >>			MAX126K	MDP3126 / MDP3126K
	Wabco Pan 22-1	01/99 >>			MAX162K	MDP3162 / MDP3162K
	Wabco Maxx 22T	01/99 >>			MAX162K	MDP3162 / MDP3162K
Goldhofer						
						
SB3308	Knorr SB5 / SN5	01/98 >>			MAX148K	MDP3148K
Granning Lynx						
						
SB 5000	Knorr SB5 / SN5				MAX148K	MDP3148K
SB 6000	Knorr SB6 / SN6	01/00 >>			MAX095K	MDP3095K
SB 7000	Knorr SB7 / SN7	01/00 >>			MAX087K	MDP3087K / MDP3087KP

- Refer to Buyers Guide



						
						
Haldex						
						
DB22	Haldex Modul T - DBT22LT					MDP3415K
DB22LT	Haldex Modul T - DBT22LT					MDP3415K
DBT22LT	Haldex Modul T - DBT22LT					MDP3415K
Hendrickson						
						
SB 5000	Knorr SB5 / SN5				MAX148K	MDP3148K
with Knorr brakes	Knorr SB7 / SN7	01/99 >>			MAX087K	MDP3087K / MDP3087KP
Heuliez						
						
GX137, GX317, GX327, GX337 – Access bus	Meritor ELSA 2	01/93 >>			MDP5073SK / MDP5056SK / MAX131K	MDP3131K
GX217 – Access bus	Meritor D LISA	01/96 >>			MAX090K / MDP5042SK	MDP3090K
GX317, GX327 – Access bus	Meritor D3	01/93 >>			MAX030K	MDP3030K
	Meritor ELSA 1 / D3	01/93 >>			MDP5065SK	
GX417, GX427 – Access bus	Meritor D LISA				MAX090K / MDP5042SK	MDP3090K
GX417, GX427, GX437 – Access bus	Meritor ELSA 2	01/08 >>			MDP5073SK / MDP5056SK / MAX131K	MDP3131K
Higer						
						
6806, 6756, 6896	Knorr SB7 / SN7	01/12 >>			MAX087K	MDP3087K / MDP3087KP
KLQ6806, KLQ6756, KLQ6896	Knorr SB7 / SN7	01/15 >>			MAX087K	MDP3087K / MDP3087KP
Ikarus						
						
200 Series	Meritor D3	01/93 >>		MDP5033	MAX030K	MDP3030K
	Meritor ELSA 1 / D3	01/93 >>			MDP5065SK	
Ingersoll						
						
with Wabco Brakes	Wabco Pan 19-1	01/08 >>			MAX126K	MDP3126 / MDP3126K
Iveco (Inc Iveco Ford)						
						
CargoPlus – 7.5T	B Frame (2x60)	02/02 >>				MDP3122
	Meritor B Frame (2x68)	02/02 >>		MDP5020		
	Brembo	02/02 >>				MDP3256
EuroCargo – 60 E , 65 E Series	B Frame (2x60)	01/96 >> 09/00				MDP3122



- 1
- 2
- 3
- 4
- 5

						
						
...Iveco (Inc Iveco Ford)						
						
EuroCargo – 60 E Series	B Frame (2x60)	09/00 >> 09/06				MDP3122
	B Frame (2x60)	01/06 >>				MDP3122
	Brembo	09/08 >>				MDP3256
EuroCargo – 60.12, 79.14	Wabco 456 F	01/87 >> 01/91				MDP3017
EuroCargo – 65 E Series	B Frame (2x60)	09/00 >> 09/06				MDP3122
	B Frame (2x60)	01/06 >>				MDP3122
	Brembo	09/08 >>				MDP3256
EuroCargo – 75 E Series	B Frame (2x60)	01/96 >> 09/00				MDP3122
	B Frame (2x60)	09/00 >> 09/06				MDP3122
	B Frame (2x60)	01/06 >>				MDP3122
	Brembo	09/00 >>				MDP3256
EuroCargo – 80 E, EL Series	B Frame (2x60)	09/00 >> 09/06				MDP3122
	B Frame (2x60)	01/06 >>				MDP3122
	Brembo	01/06 >>				MDP3256
	Brembo	09/15 >>				MDP3256
EuroCargo – 80, 85 E, EL Series	Meritor B Frame (2x68)	01/96 >> 09/00		MDP5020		
	B Frame (2x60)	01/96 >> 09/00				MDP3122
	Meritor B Frame (2x68)	01/91 >> 09/00		MDP5020		
	B Frame (2x60)	01/91 >> 09/00				MDP3122
EuroCargo – 85 E Series	B Frame (2x60)	09/00 >> 09/06				MDP3122
EuroCargo – 90 E Series	B Frame (2x60)	09/00 >>				MDP3122
	Brembo	01/06 >>				MDP3256
EuroCargo – 95 E Series	Meritor B Frame (2x68)	01/96 >> 09/00		MDP5020		
	B Frame (2x60)	01/96 >> 09/00				MDP3122
	Meritor B Frame (2x68)	01/91 >> 09/00		MDP5020		
	B Frame (2x60)	01/91 >> 09/00				MDP3122
	B Frame (2x60)	09/00 >> 09/06				MDP3122
EuroCargo – 100 E Series	Meritor B Frame (2x68)	01/96 >>		MDP5020		
	B Frame (2x60)	01/96 >>				MDP3122
	Brembo	01/06 >>				MDP3256
EuroCargo – 110 E Series	Bendix ADB3700	09/91 >> 09/00				MDP3032K
	Wabco Pan 17	09/00 >>			MAX088K	MDP3088 / MDP3088K

- Refer to Buyers Guide



								
						GENUINE	PREMIUM	ALLFIT
...Iveco (Inc Iveco Ford)								
								
EuroCargo – 110E --> 150E	Wabco Pan 17	05/13 >>				MAX088K	MDP3088 / MDP3088K	
	Brembo	05/13 >>					MDP3256	
EuroCargo – 120 E Series	B Frame (2x60)	09/00 >> 01/06					MDP3122	
	Wabco Pan 17	09/00 >>				MAX088K	MDP3088 / MDP3088K	
EuroCargo – 120, 130, 135, 140 E Series	Bendix ADB3700	09/91 >> 09/00					MDP3032K	
EuroCargo – 130 E, 135 E Series	Knorr SB6 / SN6	09/00 >>				MAX095K	MDP3095K	
EuroCargo – 130, 135, 140 E Series	Knorr SB6 / SN6	01/06 >>				MAX095K	MDP3095K	
EuroCargo – 140 E Series	Knorr SB6 / SN6	09/00 >>				MAX095K	MDP3095K	
EuroCargo – 150 E Series	Bendix ADB3700	01/91 >> 09/00					MDP3032K	
EuroCargo – 150 E Series	Knorr SB6 / SN6	09/00 >>				MAX095K	MDP3095K	
EuroCargo – 160 E Series	Knorr SB6 / SN6	01/06 >>				MAX095K	MDP3095K	
EuroCargo – 170 E Series	Knorr SB7 / SN7	09/00 >> 01/06		MDP9000		MAX087K	MDP3087K / MDP3087KP	
EuroCargo – 170, 175, 176, 179 E Series	Bendix ADB4300	01/91 >> 08/98					MDP3011K	
	Knorr SB7 / SN7	08/98 >> 09/00				MAX087K	MDP3087K / MDP3087KP	
EuroCargo – 175 E Series	Knorr SB7 / SN7	09/00 >> 01/06		MDP9000		MAX087K	MDP3087K / MDP3087KP	
EuroCargo – 176 E Series	Knorr SB7 / SN7	09/00 >> 01/06		MDP9000		MAX087K	MDP3087K / MDP3087KP	
EuroCargo – 179 E Series	Knorr SB7 / SN7	09/00 >> 01/06		MDP9000		MAX087K	MDP3087K / MDP3087KP	
EuroCargo – 180 E Series	Bendix ADB4300	01/91 >> 08/98					MDP3011K	
	Knorr SB7 / SN7	09/00 >>		MDP9000		MAX087K	MDP3087K / MDP3087KP	
EuroCargo – 210 E Series	Bendix ADB3700	01/91 >> 09/00					MDP3032K	
EuroCargo – 225 E Series	Knorr SB7 / SN7	01/06 >>				MAX087K	MDP3087K / MDP3087KP	
EuroCargo – 230 E Series	Knorr SB7 / SN7	01/06 >>				MAX087K	MDP3087K / MDP3087KP	
EuroCargo – 250 E Series	Bendix ADB3700	01/91 >> 09/00					MDP3032K	
EuroCargo – 260 E Series	Bendix ADB3700	01/91 >> 09/00					MDP3032K	
	Knorr SB7 / SN7	01/06 >>				MAX087K	MDP3087K / MDP3087KP	
EuroCargo – 260, 280 E Series	Knorr SB7 / SN7	09/00 >> 01/06		MDP9000		MAX087K	MDP3087K / MDP3087KP	
EuroCargo – 280 E Series	Bendix ADB3700	01/91 >> 09/00					MDP3032K	
EuroCargo – 320 E Series	Bendix ADB3700	01/91 >> 09/00					MDP3032K	
	Knorr SB7 / SN7	09/00 >> 01/06				MAX087K	MDP3087K / MDP3087KP	
EuroCargo – 325 E Series	Bendix ADB4300	01/91 >> 08/98					MDP3011K	
	Knorr SB7 / SN7	08/98 >> 01/06		MDP9000		MAX087K	MDP3087K / MDP3087KP	

- Refer to Buyers Guide

1



2



3



4



5





1



2



3



4



5



						
						
...Iveco (Inc Iveco Ford)						
						
EuroCargo – 390 E Series	Bendix ADB4300	01/91 >> 08/98				MDP3011K
	Knorr SB7 / SN7	08/98 >> 01/06			MAX087K	MDP3087K / MDP3087KP
EuroMover – 190 E --> 260 E Series	Knorr SB7 / SN7	01/06 >>			MAX087K	MDP3087K / MDP3087KP
EuroStar – LD180 E 38 --> E 52	Knorr SB7 / SN7	01/93 >> 02/02			MAX087K	MDP3087K / MDP3087KP
EuroStar – LD190 E 38 --> E 52	Bendix ADB4300	01/93 >> 02/02				MDP3011K
	Knorr SB7 / SN7	01/93 >> 02/02		MDP9000	MAX087K	MDP3087K / MDP3087KP
EuroStar – LD240 E 38 --> E 52	Bendix ADB4300	01/93 >> 02/02				MDP3011K
	Knorr SB7 / SN7	01/93 >> 02/02		MDP9000	MAX087K	MDP3087K / MDP3087KP
EuroStar – LD260 E 38 --> E 52	Bendix ADB4300	01/93 >> 02/02				MDP3011K
	Knorr SB7 / SN7	01/93 >> 02/02		MDP9000	MAX087K	MDP3087K / MDP3087KP
EuroStar – LD380 E --> LD520 E	Bendix ADB4300	01/93 >> 02/02				MDP3011K
	Knorr SB7 / SN7	01/93 >> 02/02		MDP9000	MAX087K	MDP3087K / MDP3087KP
EuroTech – MH, MP Series	Knorr SB7 / SN7	01/92 >>		MDP9000	MAX087K	MDP3087K / MDP3087KP
	Bendix ADB4300	01/92 >> 01/97				MDP3011K
EuroTech – MT Series	Knorr SB7 / SN7	01/92 >>		MDP9000	MAX087K	MDP3087K / MDP3087KP
	Bendix ADB4300	09/92 >> 01/97				MDP3011K
EuroTrakker – MP Series Cursor 8, Cursor 10	Knorr SB7 / SN7	01/92 >>		MDP9000	MAX087K	MDP3087K / MDP3087KP
EuroTurbo	B Frame (2x60)	01/87 >>				MDP3122
S-Way (Inc NP Models) – 190 --> 440	Knorr SB7 / SN7	01/19 >>			MAX087K	MDP3087K / MDP3087KP
Stralis – Cursor 8 AD, AS, AT Series	Knorr SB7 / SN7	02/02 >>		MDP9000	MAX087K	MDP3087K / MDP3087KP
Stralis – Cursor 10 AD, AS, AT Series	Knorr SB7 / SN7	02/02 >>		MDP9000	MAX087K	MDP3087K / MDP3087KP
Stralis – Cursor 13 AD, AS, AT Series	Knorr SB7 / SN7	02/02 >>		MDP9000	MAX087K	MDP3087K / MDP3087KP
Stralis II – AD, AS, AT	Knorr SB7 / SN7	01/12 >>			MAX087K	MDP3087K / MDP3087KP
Strator – ASN 440	Knorr SB7 / SN7	04/10 >>			MAX087K	MDP3087K / MDP3087KP
SuperCargo – 170 (E15, E18, E23)	Bendix ADB4300	10/92 >>				MDP3011K
SuperCargo – 260, 320 (E27)	Bendix ADB4300	01/93 >>				MDP3011K
SuperCargo – Rigid, Tippers, Tractors	Knorr SB7 / SN7	01/00 >>		MDP9000	MAX087K	MDP3087K / MDP3087KP
Tector – 150 --> 260 (E21--> E28)	Knorr SB7 / SN7	01/12 >>			MAX087K	MDP3087K / MDP3087KP
Trakker – Cursor 8, 10 Series AD, AT	Knorr SB7 / SN7	02/02 >>		MDP9000	MAX087K	MDP3087K / MDP3087KP
Trakker II – AD, AT 190 --> 400	Knorr SB7 / SN7	06/12 >>			MAX087K	MDP3087K / MDP3087KP
Trakker II – AD, AT 260 --> 740	Knorr SB7 / SN7	06/12 >>			MAX087K	MDP3087K / MDP3087KP
X-Way – AD, AS, AT	Knorr SB7 / SN7	01/19 >>			MAX087K	MDP3087K / MDP3087KP
Z Range – 79.13, 109.14	Wabco 456 F	01/87 >> 01/92				MDP3017 / MDP3024

- Refer to Buyers Guide



							
							
...Iveco (Inc Iveco Ford)							
							
Zeta – 60.11 --> 79.14	Wabco 456 F	01/87 >> 01/92					MDP3017 / MDP3024
Zeta – 80.13 --> 109.14	Wabco 456 F	01/87 >> 01/92					MDP3017 / MDP3024
							
EuroFire – 80 E, EL Series	Brembo	09/06 >>					MDP3256
	B Frame (2x60)	09/06 >>					MDP3122
EuroFire – 100 E Series	B Frame (2x60)	01/06 >>					MDP3122
	Brembo	09/06 >>					MDP3256
EuroFire – 130 E	Bendix ADB3700	01/91 >>					MDP3032K
EuroFire – 130 E --> 160 E Series	Wabco Pan 17	01/06 >>			MAX088K		MDP3088 / MDP3088K
	Knorr SB6 / SN6	09/00 >>			MAX095K		MDP3095K
EuroFire – 150 E	Bendix ADB3700	01/91 >>					MDP3032K
Iveco PSV (Inc Irisbus, Karosa, Recreo)							
							
Afriway – 18T Coaches	Knorr SB7 / SN7	01/01 >>			MAX087K		MDP3087K / MDP3087KP
Afriway – 26T Coaches	Knorr SB7 / SN7	01/01 >>			MAX087K		MDP3087K / MDP3087KP
Daily IV, V – 33 --> 70 Series Buses	B Frame (2x60)	05/06 >>					MDP3122
Daily Tourys – 16, 19	B Frame (2x60)	05/06 >>					MDP3122
EuroCity – 12T --> 13T Models	Knorr SB6 / SN6	09/00 >>			MAX095K		MDP3095K
EuroFire – 130E, 140 E Series	Knorr SB6 / SN6	09/00 >>			MAX095K		MDP3095K
EuroFire – 150 E Series	Knorr SB6 / SN6	09/00 >>			MAX095K		MDP3095K
EuroFire – 160 E Series	Knorr SB6 / SN6	09/00 >>			MAX095K		MDP3095K
EuroRider	Knorr SB7 / SN7	01/92 >>			MAX087K		MDP3087K / MDP3087KP
Irisbus – Access Bus 127	Meritor ELSA 2	03/06 >>		MDP5056			
	Meritor D LISA	03/06 >>			MAX090K / MDP5042SK		MDP3090K
	Meritor ELSA 2	03/06 >>			MDP5073SK / MDP5056SK / MAX131K		MDP3131K
Irisbus – Ares	Knorr SB7 / SN7	01/01 >>			MAX087K		MDP3087K / MDP3087KP
Irisbus – Arway 10.6m, 12m, 12.8m	Meritor ELSA 2	06/06 >>			MDP5073SK / MDP5056SK / MAX131K		MDP3131K
Irisbus – Arway 15m	Meritor ELSA 2	06/06 >>		MDP5056			
	Meritor ELSA 2	06/06 >>			MDP5073SK / MDP5056SK / MAX131K		MDP3131K
Irisbus – Axer 12m, 12.8m	Meritor ELSA 2	03/05 >>			MDP5073SK / MDP5056SK / MAX131K		MDP3131K
Irisbus – Citelis 10.5m, 12m	Meritor D LISA	09/05 >>			MAX090K / MDP5042SK		MDP3090K
	Meritor ELSA 2	09/05 >>			MDP5073SK / MDP5056SK / MAX131K		MDP3131K

- Refer to Buyers Guide



GENUINE

PREMIUM

ALLFIT

...Iveco PSV (Inc Irisbus, Karosa, Recreo)



Irisbus – Citelis 18m	Meritor D LISA	09/05 >>			MAX090K / MDP5042SK	MDP3090K
	Meritor ELSA 2	09/05 >>			MDP5073SK / MDP5056SK / MAX131K	MDP3131K
Irisbus – Crealis 12m, 12m NEO	Meritor D LISA	01/05 >>			MAX090K / MDP5042SK	MDP3090K
	Meritor ELSA 2	01/05 >>			MDP5073SK / MDP5056SK / MAX131K	MDP3131K
Irisbus – Crealis 18m, 18m NEO	Meritor D LISA	01/05 >>			MAX090K / MDP5042SK	MDP3090K
	Meritor ELSA 2	01/05 >>			MDP5073SK / MDP5056SK / MAX131K	MDP3131K
Irisbus – Crossway 10.6m, 12m, 12.8m	Meritor ELSA 2	06/06 >>			MDP5073SK / MDP5056SK / MAX131K	MDP3131K
Irisbus – Domino HD, HDH	Knorr SB7 / SN7	10/03 >>			MAX087K	MDP3087K / MDP3087KP
	Meritor ELSA 2	10/03 >>			MDP5073SK / MDP5056SK / MAX131K	MDP3131K
Irisbus – EuroPolis	Knorr SB7 / SN7	01/96 >>			MAX087K	MDP3087K / MDP3087KP
Irisbus – EuroRider	Knorr SB6 / SN6	01/92 >>			MAX095K	MDP3095K
	Knorr SB7 / SN7	01/92 >>			MAX087K	MDP3087K / MDP3087KP
Irisbus – Evadys	Meritor ELSA 2	09/03 >>			MDP5073SK / MDP5056SK / MAX131K	MDP3131K
Irisbus – Magelys	Meritor ELSA 2	08/08 >>			MDP5073SK / MDP5056SK / MAX131K	MDP3131K
Irisbus – Maxim 100 E	B Frame (2x60)	01/98 >>				MDP3122
Irisbus – Maxim 80 E	B Frame (2x60)	01/98 >>				MDP3122
Irisbus – Myway	Knorr SB7 / SN7	08/98 >>			MAX087K	MDP3087K / MDP3087KP
Irisbus – Proway	B Frame (2x60)	01/05 >>				MDP3122
	Meritor ELSA 2	01/05 >>			MDP5073SK / MDP5056SK / MAX131K	MDP3131K
Irisbus – Scholabus 150 E	Knorr SB7 / SN7	08/98 >>			MAX087K	MDP3087K / MDP3087KP
Karosa, Recreo – 930, 930B, 930E, 940E	Knorr SB7 / SN7	01/97 >>			MAX087K	MDP3087K / MDP3087KP
Karosa, Recreo – Agora City Bus	Meritor ELSA 2	01/03 >>			MDP5073SK / MDP5056SK / MAX131K	MDP3131K
	Meritor D3	01/93 >>			MAX030K	MDP3030K
Karosa, Recreo – City Bus	Meritor D3	01/93 >>			MAX030K	MDP3030K
	Meritor ELSA 2	10/03 >>			MDP5073SK / MDP5056SK / MAX131K	MDP3131K
Urbanway	Meritor ELSA 2	01/01 >>			MAX131K / MDP5073SK / MDP5056SK	MDP3131K
Breda Menarini Bus Streparava	Meritor DX 225			MDP5083K / MDP5083		
Daily Tourys – 16, 19	Brembo	02/02 >>				MDP3256
Irisbus – CityClass	Meritor DX 225	01/99 >>			MDP5083SK	
Karosa, Recreo – Agora City Bus	Meritor ELSA 1 / D3	01/93 >>			MDP5065SK	
Karosa, Recreo – City Bus	Meritor ELSA 1 / D3	01/93 >>			MDP5065SK	

- Refer to Buyers Guide



														
Jelcz														
														
Libero – 17.5" wheels				Wabco Pan 17		01/06 >>				MAX088K			MDP3088 / MDP3088K	
JMC														
														
Weilong – HV5				Meritor ELSA 225-3		09/18 >>				MAX174K			MDP3174K / MDP3174KW	
Jost														
														
DCA-L7 – 22.5" Wheels				Haldex Modul T - DBT19LT		01/14 >>							MDP3429K	
with Haldex brakes				Haldex Modul X - DB22LT		01/16 >>				MAX175K				
				Haldex Modul X		01/16 >>							MDP3175K	
with Knorr brakes				Knorr SB6 / SN6						MAX095K			MDP3095K	
				Knorr SB7 / SN7						MAX087K			MDP3087K / MDP3087KP	
Karsan														
														
Atak				Knorr SB7 / SN7		06/14 >>				MAX087K			MDP3087K / MDP3087KP	
Star				Wabco Pan 17		06/14 >>				MAX088K			MDP3088 / MDP3088K	
King Long (Golden Dragon, Golden Journey)														
														
XML, XMQ Series – City Bus				Knorr SB6 / SN6		09/07 >>				MAX095K			MDP3095K	
XML, XMQ Series – Inter City Large Bus				Knorr SB7 / SN7		09/07 >>				MAX087K			MDP3087K / MDP3087KP	
				Meritor D3		09/07 >>				MAX030K			MDP3030K	
				Meritor ELSA 2		09/07 >>				MDP5073SK / MDP5056SK / MAX131K			MDP3131K	
				Meritor ELSA 1 / D3		09/07 >>				MDP5065SK				
Kögel / Trax														
														
ELSA 225-2				Meritor ELSA 225L		05/07 >>				MDP5117SK				
with Haldex brakes				Haldex Modul X - DB22LT		01/10 >>				MAX175K				
				Haldex Modul X		01/10 >>							MDP3175K	
				Haldex Modul T - DBT22LT		01/20 >>							MDP3415K	
Krone														
														
with Haldex brakes				Haldex Modul X - DB22LT		01/10 >>				MAX175K				
				Haldex Modul X		01/10 >>							MDP3175K	
				Haldex Modul T - DBT22LT		01/20 >>							MDP3415K	

- Refer to Buyers Guide



1



2



3



4



5



							
					GENUINE	PREMIUM	ALLFIT
LCV							
							
4307 Series	Knorr SB5 / SN5	05/06 >>			MAX148K	MDP3148K	
4308 Series	Knorr SB5 / SN5	05/06 >>			MAX148K	MDP3148K	
Leciñena							
							
with Knorr brakes	Knorr SB7 / SN7	01/98 >>			MAX087K	MDP3087K / MDP3087KP	
Liaz							
							
400 Series	Knorr SB7 / SN7	01/98 >>		MDP9005	MAX087K	MDP3087K / MDP3087KP	
4292	Knorr SB6 / SN6	01/15 >>			MAX095K	MDP3095K	
M.C.I. (New Flyer Industries)							
							
E Series Buses	Meritor D LISA	09/97 >>			MAX090K / MDP5042SK	MDP3090K	
	Meritor ELSA 225-3	09/97 >>			MAX174K	MDP3174K / MDP3174KWI	
Flyer Bus	Knorr SB7 / SN7	01/12 >>			MAX087K	MDP3087K / MDP3087KP	
Flyer Bus – MAN chassis	Meritor ELSA 2	01/12 >>			MDP5073SK / MDP5056SK / MAX131K	MDP3131K	
MAN							
							
E2000 Series – 18.290 --> 19.480	Meritor D3	01/95 >> 12/05			MAX030K	MDP3030K	
	Meritor ELSA 2	01/95 >> 12/05			MDP5073SK / MDP5056SK / MAX131K	MDP3131K	
	Meritor ELSA 1 / D3	01/95 >>			MDP5065SK		
E2000 Series – 19.314, 19.364, 19.414, 19.464	Meritor ELSA 1	95 >>		MDP5038 / MDP5039			
	Meritor ELSA 2	95 >>		MDP5060			
E2000 Series – 20.290-->28.480	Meritor D3	01/95 >> 12/05			MAX030K	MDP3030K	
	Meritor ELSA 2	01/95 >> 12/05			MDP5073SK / MDP5056SK / MAX131K	MDP3131K	
	Meritor ELSA 1 / D3	01/95 >>			MDP5065SK		
E2000 Series – 20.290-->33.600	Meritor D3	05/00 >>			MAX030K	MDP3030K	
	Meritor ELSA 1 / D3	05/00 >>			MDP5065SK		
	Meritor ELSA 2	05/00 >>			MDP5073SK / MDP5056SK / MAX131K	MDP3131K	
E2000 Series – 24.273, 26.273, 26.293, 26.323, 26.343, 27.273, 27.293, 27.323, 27.343, 28.273, 28.293, 28.323, 28.343, 33.273, 33.293, 33.323, 33.343	Meritor ELSA 1	96 >>		MDP5038 / MDP5039			
E2000 Series – 26.414, 26.464	Meritor ELSA 1	95 >>		MDP5038 / MDP5039			
	Meritor ELSA 2	95 >>		MDP5060			

- Refer to Buyers Guide



						
						
...MAN						
						
E2000 Series – 28.233, 28.314, 28.364, 28.414, 28.464	Meritor ELSA 1	96 >>		MDP5039		
	Meritor ELSA 2	96 >>		MDP5060		
E2000 Series – 29.480-->50.480	Meritor D3	01/95 >> 12/05			MAX030K	MDP3030K
	Meritor ELSA 2	01/95 >> 12/05			MDP5073SK / MDP5056SK / MAX131K	
	Meritor ELSA 1 / D3	01/95 >>			MDP5065SK	
E2000 Series – 30.314, 30.364, 30.414, 30.464, 33.364, 33.414, 33.464	Meritor ELSA 1	97 >>		MDP5038 / MDP5039		
	Meritor ELSA 2	97 >>		MDP5060		
E2000 Series – 32.414, 32.464	Meritor ELSA 2	97 >>		MDP5060		
ERF - ECL - 7.28 RD3 / TP3 – 6871 Platform / C	Meritor ELSA 2	04/04 >>		MDP5099		
F2000 Series – 18.270-->19.610	B Frame (2x60)	01/94 >>				MDP3122
	Knorr SB7 / SN7	01/94 >>			MAX087K	MDP3087K / MDP3087KP
	Meritor D3	01/94 >>		MDP5054	MAX030K	MDP3030K
	Meritor ELSA 1 / D3	01/94 >>			MDP5065SK	
	Meritor ELSA 2	01/94 >>			MDP5073SK / MDP5056SK / MAX131K	MDP3131K
	Meritor ELSA 1	94 >>		MDP5038 / MDP5039 / MDP5065 / MDP5066		
	Meritor ELSA 2	94 >>		MDP5060		
F2000 Series – 23.290-->33.610	B Frame (2x60)	01/94 >>				MDP3122
	Knorr SB7 / SN7	01/94 >>			MAX087K	MDP3087K / MDP3087KP
	Meritor ELSA 2	01/94 >>			MDP5073SK / MDP5056SK / MAX131K	MDP3131K
	Meritor ELSA 1	94 >>		MDP5038 / MDP5039 / MDP5065 / MDP5066		
	Meritor ELSA 2	94 >>		MDP5060		
F2000 Series – 23.290-->40.463	Meritor D3	01/94 >>		MDP5054	MAX030K	MDP3030K
	Meritor ELSA 1 / D3	01/94 >>			MDP5065SK	
F2000 Series – 32.290-->41.610	B Frame (2x60)	01/94 >>				MDP3122
	Knorr SB7 / SN7	01/94 >>			MAX087K	MDP3087K / MDP3087KP
	Meritor D3	01/94 >>		MDP5054	MAX030K	MDP3030K
	Meritor ELSA 1 / D3	01/94 >>			MDP5065SK	
	Meritor ELSA 2	01/94 >>			MDP5073SK / MDP5056SK / MAX131K	MDP3131K
	Meritor ELSA 1	94 >>		MDP5038 / MDP5039 / MDP5065 / MDP5066		
F2000 Series – with Meritor Brakes	Meritor D3	01/00 >>		MDP5054	MAX030K	MDP3030K
	Meritor ELSA 1 / D3	01/00 >>			MDP5065SK	

- Refer to Buyers Guide



1



2



3



4



5



						
				GENUINE	PREMIUM	ALLFIT
...MAN						
						
F90 Series – 15.192 --> 19.502	Meritor D3	01/86 >> 12/97			MAX030K	MDP3030K
	Meritor ELSA 2	01/86 >> 12/97			MDP5073SK / MDP5056SK / MAX131K	MDP3131K
	Meritor ELSA 1 / D3	01/86 >>			MDP5065SK	
F90 Series – 19.192 --> 27.502	Meritor ELSA 2	01/86 >> 12/97			MDP5073SK / MDP5056SK / MAX131K	MDP3131K
F90 Series – 19.192 --> 33.502	Meritor D3	01/86 >> 12/97			MAX030K	MDP3030K
	Meritor ELSA 1 / D3	01/86 >>			MDP5065SK	
F90 Series – 27.242 -->	Meritor D3	01/86 >> 12/97			MAX030K	MDP3030K
	Meritor ELSA 1 / D3	01/86 >>			MDP5065SK	
	Meritor ELSA 2	01/86 >> 12/97			MDP5073SK / MDP5056SK / MAX131K	MDP3131K
F90 Series – with ABS	Meritor ELSA 1	89 >>		MDP5038		
F90 Series – without ABS	Meritor ELSA 1	89 >>		MDP5038		
L2000 Series – 6 Series	Wabco Pan 17	01/96 >>			MAX088K	MDP3088 / MDP3088K
	B Frame (2x60)	11/93 >> 01/96				MDP3122
	Wabco Pan 17	03/05 >>			MAX088K	MDP3088 / MDP3088K
L2000 Series – 7 Series	Wabco Pan 17	01/96 >>			MAX088K	MDP3088 / MDP3088K
	B Frame (2x60)	11/93 >> 01/96				MDP3122
	Wabco Pan 17	03/05 >>			MAX088K	MDP3088 / MDP3088K
L2000 Series – 8 Series	Wabco Pan 17	01/96 >>			MAX088K	MDP3088 / MDP3088K
	B Frame (2x60)	11/93 >> 01/96				MDP3122
	Wabco Pan 17	03/05 >>			MAX088K	MDP3088 / MDP3088K
L2000 Series – 9 Series	Wabco Pan 17	01/96 >>			MAX088K	MDP3088 / MDP3088K
	B Frame (2x60)	11/93 >> 01/96				MDP3122
	Wabco Pan 17	03/05 >>			MAX088K	MDP3088 / MDP3088K
L2000 Series – 10 Series	Wabco Pan 17	01/96 >>			MAX088K	MDP3088 / MDP3088K
	B Frame (2x60)	11/93 >> 01/96				MDP3122
	Wabco Pan 17	03/05 >>			MAX088K	MDP3088 / MDP3088K
L2000 Series – 12 Series	Wabco Pan 17	01/96 >>			MAX088K	MDP3088 / MDP3088K
	Wabco Pan 17	03/05 >>			MAX088K	MDP3088 / MDP3088K
L2000 Series – 14 Series	Knorr SB6 / SN6	01/96 >>			MAX095K	MDP3095K
LE2000 Series – 140 --> 240	Wabco Pan 17	01/00 >>			MAX088K	MDP3088 / MDP3088K
LE2000 Series – LE2000 LE220B, LE250B, LE280B 14-18 tonne (10 hole disc)	Meritor ELSA 1	00 >>		MDP5038		
LE2000 Series – LE2000 LE220B, LE250B, LE280B 14-18 tonne (12 hole disc)	Meritor ELSA 1	00 >>		MDP5038		

- Refer to Buyers Guide



							
					GENUINE	PREMIUM	ALLFIT
...MAN							
							
LE2000 Series – with Knorr Brakes	Knorr SB6 / SN6	01/00 >>			MAX095K	MDP3095K	
M2000 – L Series 18.224, 18.264, 18.294 (10 hole disc)	Meritor ELSA 1	8/95 >>		MDP5038			
M2000 – L Series 18.224, 18.264, 18.294 (12 hole disc)	Meritor ELSA 1	8/95 >>		MDP5038			
M2000 – M Series 18.224, 18.264, 18.284, 25.224, 25.264 (10 hole disc)	Meritor ELSA 1	8/95 >>		MDP5038			
M2000 – M Series 18.224, 18.264, 18.284, 25.224, 25.264 (12 hole disc)	Meritor ELSA 1	8/95 >>		MDP5038			
M2000 L – 14.163-->20.290	Meritor ELSA 1	95 >>		MDP5038 / MDP5065			
	Meritor ELSA 2	95 >>		MDP5060			
M2000 L – 18.223-->19.290	Meritor ELSA 1	95 >>		MDP5038 / MDP5065			
	Meritor ELSA 2	95 >>		MDP5060			
M2000 L – 20.223-->26.290	Meritor ELSA 1	95 >>		MDP5038 / MDP5065			
	Meritor ELSA 2	95 >>		MDP5060			
M2000 M – 18.223-->19.290	Meritor ELSA 1	95 >>		MDP5038 / MDP5065			
	Meritor ELSA 2	95 >>		MDP5060			
M2000 M – 20.223-->26.290	Meritor ELSA 1	95 >>		MDP5038 / MDP5065			
	Meritor ELSA 2	95 >>		MDP5060			
M2000, M2000 L, M2000 M, ME2000 Series – 11.220 -->12.225	Knorr SB6 / SN6	08/95 >>			MAX095K	MDP3095K	
	Wabco Pan 17	08/95 >>			MAX088K	MDP3088 / MDP3088K	
M2000, M2000 L, M2000 M, ME2000 Series – 14.163-->20.290	Knorr SB6 / SN6	08/95 >>			MAX095K	MDP3095K	
	Meritor D3	08/95 >>		MDP5054	MAX030K	MDP3030K	
	Meritor ELSA 1 / D3	08/95 >>			MDP5065SK		
	Meritor ELSA 2	08/95 >>			MDP5073SK / MDP5056SK / MAX131K	MDP3131K	
M2000, M2000 L, M2000 M, ME2000 Series – 18.223-->19.290	Meritor D3	08/95 >>		MDP5054	MAX030K	MDP3030K	
	Meritor ELSA 1 / D3	08/95 >>			MDP5065SK		
	Meritor ELSA 2	08/95 >>			MDP5073SK / MDP5056SK / MAX131K	MDP3131K	
M2000, M2000 L, M2000 M, ME2000 Series – 20.223-->26.290	Meritor D3	08/95 >>		MDP5054	MAX030K	MDP3030K	
	Meritor ELSA 1 / D3	08/95 >>			MDP5065SK		
	Meritor ELSA 2	08/95 >>			MDP5073SK / MDP5056SK / MAX131K	MDP3131K	
	Wabco Pan 17	08/95 >>			MAX088K	MDP3088 / MDP3088K	
M90 Series – 12 T Series	Meritor D3	01/89 >> 06/96			MAX030K	MDP3030K	
	Meritor ELSA 2	01/89 >> 06/96			MAX131K / MDP5073SK / MDP5056SK	MDP3131K	
	Meritor ELSA 1 / D3	01/89 >>			MDP5065SK		

- Refer to Buyers Guide



1



2



3



4



5



						
				GENUINE	PREMIUM	ALLFIT
...MAN						
						
M90 Series – 14 T Series	Meritor D3	01/89 >> 06/96			MAX030K	MDP3030K
	Meritor ELSA 2	01/89 >> 06/96			MAX131K / MDP5073SK / MDP5056SK	MDP3131K
	Meritor ELSA 1 / D3	01/89 >>			MDP5065SK	
M90 Series – 17 T Series	Meritor D3	01/89 >> 01/96			MAX030K	MDP3030K
	Meritor ELSA 2	01/89 >> 01/96			MDP5073SK / MDP5056SK / MAX131K	MDP3131K
	Meritor ELSA 1 / D3	01/89 >>			MDP5065SK	
M90 Series – 17.192 - 24.272 (with ABS)	Meritor ELSA 1	90 >>		MDP5038		
M90 Series – 17.192 - 24.272 (without ABS)	Meritor ELSA 1	89 >>		MDP5038		
ME2000 – 15 - 26 Series	Meritor ELSA 1	96 >>		MDP5038		
TG-A – 18, 19 Series	Knorr SB7 / SN7	03/99 >>		MDP9000	MAX087K	MDP3087K / MDP3087KP
	Meritor D3	03/99 >>			MAX030K	MDP3030K
	Meritor ELSA 2	09/99 >>			MDP5073SK / MDP5056SK / MAX131K	MDP3131K
	Meritor D3	03/99 >> 09/01			MAX030K	MDP3030K
	B Frame (2x60)	09/99 >>				MDP3122
	Meritor ELSA 1 / D3	03/99 >>			MDP5065SK	
	Meritor ELSA 2	09/99 >>		MDP5060		
	Meritor ELSA 1	03/99 >>		MDP5038 / MDP5039 / MDP5066		
TG-A – 24, 26, 27, 28, 32, 33, 40 Series	Knorr SB7 / SN7	03/99 >>		MDP9000	MAX087K	MDP3087K / MDP3087KP
	Meritor D3	03/99 >>			MAX030K	MDP3030K
	Meritor ELSA 2	09/99 >>			MDP5073SK / MDP5056SK / MAX131K	MDP3131K
	Knorr SB6 / SN6	03/99 >>			MAX095K	MDP3095K
	Meritor D3	03/99 >> 09/01			MAX030K	MDP3030K
	B Frame (2x60)	09/99 >>				MDP3122
	Meritor ELSA 1 / D3	03/99 >>			MDP5065SK	
	Meritor ELSA 2	09/99 >>		MDP5060		
	Meritor ELSA 1	03/99 >>		MDP5038 / MDP5039 / MDP5066		
TG-A – 32, 33, 35, 37, 39, 40, 41, 50 Series	Knorr SB7 / SN7	03/99 >>		MDP9000	MAX087K	MDP3087K / MDP3087KP
	Meritor D3	03/99 >> 09/01			MAX030K	MDP3030K
	Meritor ELSA 2	09/99 >>			MDP5073SK / MDP5056SK / MAX131K	MDP3131K
	B Frame (2x60)	09/99 >>				MDP3122
	Meritor ELSA 1 / D3	03/99 >>			MDP5065SK	
	Meritor ELSA 2	09/99 >>		MDP5060		
	Meritor ELSA 1	03/99 >>		MDP5038 / MDP5039 / MDP5066		

 - Refer to Buyers Guide



						
						
...MAN						
						
TG-L – 7 Series	Knorr SB5 / SN5	04/05 >>			MAX148K	MDP3148K
TG-L – 8 Series	Meritor ELSA 2	04/05 >>			MDP5073SK / MDP5056SK / MAX131K	MDP3131K
	Meritor ELSA 2	04/05 >>			MDP5073SK / MDP5056SK / MAX131K	MDP3131K
	Knorr SB5 / SN5	04/05 >>			MAX148K	MDP3148K
	Meritor ELSA 2	04/05 >>		MDP5060		
TG-L – 10 Series	Knorr SB5 / SN5	04/05 >>			MAX148K	MDP3148K
	Meritor ELSA 2	04/05 >>		MDP5060		
TG-L – 12 Series	Knorr SB5 / SN5	04/05 >>			MAX148K	MDP3148K
	Meritor ELSA 2	04/05 >>		MDP5060		
TG-L – 15 Series	Knorr SB6 / SN6	04/05 >>			MAX095K	MDP3095K
TG-L – 18 Series	Knorr SB7 / SN7	10/05 >>			MAX087K	MDP3087K / MDP3087KP
TG-L – 26 Series	Knorr SB7 / SN7	10/05 >>			MAX087K	MDP3087K / MDP3087KP
TG-L II – 7 Series	Knorr SB5 / SN5	02/20 >>			MAX148K	MDP3148K
TG-L II – 8 Series	Knorr SB5 / SN5	02/20 >>			MAX148K	MDP3148K
TG-L II – 10 Series	Knorr SB5 / SN5	02/20 >>			MAX148K	MDP3148K
TG-L II – 12 Series	Knorr SB5 / SN5	02/20 >>			MAX148K	MDP3148K
TG-M – 12 Series	Knorr SB6 / SN6	10/05 >>			MAX095K	MDP3095K
	Knorr SB7 / SN7	10/05 >>			MAX087K	MDP3087K / MDP3087KP
TG-M – 13 Series	Knorr SB6 / SN6	10/05 >>			MAX095K	MDP3095K
TG-M – 15, 16 Series	Knorr SB6 / SN6	10/05 >>			MAX095K	MDP3095K
	Knorr SB7 / SN7	10/05 >>		MDP9000	MAX087K	MDP3087K / MDP3087KP
TG-M – 18 Series	Knorr SB7 / SN7	10/05 >>		MDP9000	MAX087K	MDP3087K / MDP3087KP
TG-M – 22, 26 Series	Knorr SB7 / SN7	10/05 >>		MDP9000	MAX087K	MDP3087K / MDP3087KP
	Knorr SB6 / SN6	10/05 >>			MAX095K	MDP3095K
TG-M II	Knorr SB7 / SN7	01/20 >>			MAX087K	MDP3087K / MDP3087KP
TG-S – 19.440	Meritor ELSA 1	09 >>		MDP5038		
	Meritor ELSA 2	09 >>		MDP5060		
TG-S II, TG-X II	Knorr SB7 / SN7	01/20 >>			MAX087K	MDP3087K / MDP3087KP
	Wabco MAXX22	01/20 >>				MDP3279K
TG-S, TG-X – 15 -->40 Series	Knorr SB7 / SN7	06/06 >>		MDP9000	MAX087K	MDP3087K / MDP3087KP
	Meritor ELSA 2	06/06 >>			MDP5073SK / MDP5056SK / MAX131K	MDP3131K
	Knorr SB6 / SN6	06/06 >>			MAX095K	MDP3095K
	Wabco MAXX22	08/07 >>				MDP3279K

- Refer to Buyers Guide



1



2



3



4



5



											
						GENUINE		PREMIUM		ALLFIT	
...MAN											
											
TG-S, TG-X – 16 --> 41 Series	Knorr SB7 / SN7	06/06 >>		MDP9000	MAX087K	MDP3087K / MDP3087KP					
	Meritor ELSA 2	06/06 >>			MDP5073SK / MDP5056SK / MAX131K	MDP3131K					
	Wabco MAXX22	08/07 >>				MDP3279K					
TG-S, TG-X – 18 --> 21 Series	Knorr SB7 / SN7	06/06 >>		MDP9000	MAX087K	MDP3087K / MDP3087KP					
	Meritor ELSA 2	06/06 >>			MDP5073SK / MDP5056SK / MAX131K	MDP3131K					
	Wabco MAXX22	08/07 >>				MDP3279K					
TG-S, TG-X – 35 --> 49 Series	Knorr SB7 / SN7	09/05 >>		MDP9000	MAX087K	MDP3087K / MDP3087KP					
MAN PSV's											
											
City Bus, Intercity Bus – 10, 11 Series HOCL	Knorr SB6 / SN6	05/87 >>			MAX095K	MDP3095K					
City Bus, Intercity Bus – 12, 13, 14, 16 Series FOCL, HOCL	Knorr SB7 / SN7	01/05 >>			MAX087K	MDP3087K / MDP3087KP					
	Meritor D3	01/96 >>			MAX030K	MDP3030K					
	Meritor ELSA 2	01/96 >>			MDP5073SK / MDP5056SK / MAX131K	MDP3131K					
	Knorr SB6 / SN6	01/98 >>			MAX095K	MDP3095K					
	Meritor ELSA 1 / D3	01/96 >>			MDP5065SK						
City Bus, Intercity Bus – 18, 19 Series FOCL, HOCL	Knorr SB7 / SN7	01/05 >>			MAX087K	MDP3087K / MDP3087KP					
	Meritor ELSA 2	01/96 >>			MDP5073SK / MDP5056SK / MAX131K	MDP3131K					
	Meritor D3	01/96 >>			MAX030K	MDP3030K					
	Meritor ELSA 1 / D3	01/96 >>			MDP5065SK						
City Bus, Intercity Bus – 22, 24, 26 Series FOCL, HOCL	Knorr SB7 / SN7	01/05 >>			MAX087K	MDP3087K / MDP3087KP					
	Meritor D3	01/96 >>			MAX030K	MDP3030K					
	Meritor ELSA 2	01/96 >>			MDP5073SK / MDP5056SK / MAX131K	MDP3131K					
	Meritor ELSA 1 / D3	01/96 >>			MDP5065SK						
City Bus, Intercity Bus – 22.5" Wheels	Meritor ELSA 1	01/96 >>		MDP5065							
City Bus, Intercity Bus – EL Series	Meritor D3	01/93 >>			MAX030K	MDP3030K					
	Meritor ELSA 2	01/93 >>			MDP5073SK / MDP5056SK / MAX131K	MDP3131K					
	Meritor ELSA 1 / D3	01/93 >>			MDP5065SK						
City Bus, Intercity Bus – EM Series	Meritor D3	01/93 >>			MAX030K	MDP3030K					
	Meritor ELSA 2	01/93 >>			MDP5073SK / MDP5056SK / MAX131K	MDP3131K					
	Meritor ELSA 1 / D3	01/93 >>			MDP5065SK						
City Bus, Intercity Bus – ND Series	Knorr SB7 / SN7	06/13 >>			MAX087K	MDP3087K / MDP3087KP					

- Refer to Buyers Guide



						
						
...MAN PSV's						
						
City Bus, Intercity Bus – NG Series	Meritor D3	07/98 >>			MAX030K	MDP3030K
	Meritor ELSA 2	07/98 >>			MDP5073SK / MDP5056SK / MAX131K	MDP3131K
	Meritor ELSA 1 / D3	07/98 >>			MDP5065SK	
City Bus, Intercity Bus – NL 200, 300 Series	Meritor D3	01/89 >>			MAX030K	MDP3030K
	Meritor ELSA 2	01/89 >>			MDP5073SK / MDP5056SK / MAX131K	MDP3131K
	Meritor ELSA 1 / D3	01/89 >>			MDP5065SK	
City Bus, Intercity Bus – NL 200, 300, 400 Series	Knorr SB7 / SN7	01/92 >>			MAX087K	MDP3087K / MDP3087KP
City Bus, Intercity Bus – NU Series	Meritor D3	09/96 >>			MAX030K	MDP3030K
	Meritor ELSA 2	09/96 >>			MDP5073SK / MDP5056SK / MAX131K	MDP3131K
	Meritor ELSA 1 / D3	09/96 >>			MDP5065SK	
City Bus, Intercity Bus – RN, RH Series	Knorr SB7 / SN7	01/96 >>			MAX087K	MDP3087K / MDP3087KP
	Meritor D3	01/96 >>			MAX030K	MDP3030K
	Meritor ELSA 2	01/96 >>			MDP5073SK / MDP5056SK / MAX131K	MDP3131K
	Meritor ELSA 1 / D3	01/96 >>			MDP5065SK	
City Bus, Intercity Bus – SD, SL 150 --> 750	B Frame (2x60)	01/93 >>				MDP3122
City Bus, Intercity Bus – SG 150 --> 750	B Frame (2x60)	01/93 >>				MDP3122
City Bus, Intercity Bus – SU 200, 300 Series	B Frame (2x60)	01/93 >> 06/97				MDP3122
City Bus, Intercity Bus – SU 200, 300, 400 Series	Meritor ELSA 2	01/01 >>			MDP5073SK / MDP5056SK / MAX131K	MDP3131K
	Knorr SB7 / SN7	01/03 >>			MAX087K	MDP3087K / MDP3087KP
City Bus, Intercity Bus – UL 300 Series	Meritor D3	01/96 >>			MAX030K	MDP3030K
	Meritor ELSA 2	01/96 >>			MDP5073SK / MDP5056SK / MAX131K	MDP3131K
	Meritor ELSA 1 / D3	01/96 >>			MDP5065SK	
Lion's City – 19.235 --> 19.300	Meritor D3	01/04 >>			MAX030K	MDP3030K
	Meritor ELSA 2	01/04 >>			MDP5073SK / MDP5056SK / MAX131K	MDP3131K
	Meritor ELSA 1 / D3	01/04 >>			MDP5065SK	
Lion's City – A20 --> A66 Series...	Meritor D3	01/96 >>			MAX030K	MDP3030K
	Meritor ELSA 1 / D3	01/96 >>			MDP5065SK	
	Meritor ELSA 2	01/96 >>			MDP5073SK / MDP5056SK / MAX131K	MDP3131K
	Knorr SB7 / SN7	03/96 >>			MAX087K	MDP3087K / MDP3087KP
	Meritor D3	03/96 >>			MAX030K	MDP3030K
	Meritor ELSA 1 / D3	03/96 >>			MDP5065SK	

- Refer to Buyers Guide



1



2



3



4



5



						  							
								GENUINE		PREMIUM		ALLFIT	
...MAN PSV's													
													
...Lion's City – A20 --> A66 Series	Meritor ELSA 2	03/96 >>				MDP5073SK / MDP5056SK / MAX131K		MDP3131K					
	Meritor D3	01/08 >>				MAX030K		MDP3030K					
	Meritor ELSA 1 / D3	01/08 >>				MDP5065SK							
	Meritor ELSA 2	01/08 >>				MDP5073SK / MDP5056SK / MAX131K		MDP3131K					
Lion's City – Lion's City	Knorr SB7 / SN7	01/04 >>				MAX087K		MDP3087K / MDP3087KP					
	Meritor D3	01/04 >>				MAX030K		MDP3030K					
	Meritor ELSA 1 / D3	01/04 >>				MDP5065SK							
	Meritor ELSA 2	01/04 >>				MDP5073SK / MDP5056SK / MAX131K		MDP3131K					
Lion's City – Lion's City E, Lion's City Electric	Knorr SB7 / SN7	01/20 >>				MAX087K		MDP3087K / MDP3087KP					
Lion's City – Lion's City EfficientHybrid	Knorr SB7 / SN7	01/18 >>				MAX087K		MDP3087K / MDP3087KP					
Lion's City – Lion's City, Lion's City CNG	Knorr SB7 / SN7	01/04 >>				MAX087K		MDP3087K / MDP3087KP					
	Meritor D3	01/04 >>				MAX030K		MDP3030K					
	Meritor ELSA 2	01/04 >>				MDP5073SK / MDP5056SK / MAX131K		MDP3131K					
	Meritor ELSA 1 / D3	01/04 >>				MDP5065SK							
Lion's Coach	Knorr SB7 / SN7	01/04 >>				MAX087K		MDP3087K / MDP3087KP					
Lion's Coach – 400 --> 440	Meritor D3	01/15 >>				MAX030K		MDP3030K					
	Meritor ELSA 2	01/15 >>				MDP5073SK / MDP5056SK / MAX131K		MDP3131K					
	Meritor ELSA 1 / D3	01/15 >>				MDP5065SK							
Lion's Coach – C 440 --> C 480	Meritor D3	01/15 >>				MAX030K		MDP3030K					
	Meritor ELSA 2	01/15 >>				MDP5073SK / MDP5056SK / MAX131K		MDP3131K					
	Meritor ELSA 1 / D3	01/15 >>				MDP5065SK							
Lion's Coach – FRH	Meritor D3	01/96 >>				MAX030K		MDP3030K					
	Meritor ELSA 2	01/96 >>				MDP5073SK / MDP5056SK / MAX131K		MDP3131K					
	Meritor ELSA 1 / D3	01/96 >>				MDP5065SK							
Lion's Coach – NG Series	Meritor D3	11/84 >> 01/96				MAX030K		MDP3030K					
	Meritor ELSA 2	11/84 >> 01/96				MDP5073SK / MDP5056SK / MAX131K		MDP3131K					
	Meritor ELSA 1 / D3	11/84 >>				MDP5065SK							
Lion's Coach – RH, RHC	Meritor D3	01/96 >>				MAX030K		MDP3030K					
	Meritor ELSA 2	01/96 >>				MDP5073SK / MDP5056SK / MAX131K		MDP3131K					
	Meritor ELSA 1 / D3	01/96 >>				MDP5065SK							
Lion's Coach – with ABS	Meritor D3	89 >>				MDP5054							
Lion's Coach – without ABS	Meritor ELSA 1	89 >>				MDP5038							

- Refer to Buyers Guide



						
						
...MAN PSV's						
						
Lion's Comfort – NG, NL, NU Series	Meritor D3	01/89 >> 01/96			MAX030K	MDP3030K
	Meritor ELSA 2	01/89 >> 01/96			MDP5073SK / MDP5056SK / MAX131K	MDP3131K
	Meritor ELSA 1 / D3	01/89 >>			MDP5065SK	
Lion's Comfort – RN Series	Meritor D3	01/96 >>			MAX030K	MDP3030K
	Meritor ELSA 2	01/96 >>			MDP5073SK / MDP5056SK / MAX131K	MDP3131K
	Meritor ELSA 1 / D3	01/96 >>			MDP5065SK	
Lion's Comfort – with ABS	Meritor D3	89 >>		MDP5054		
Lion's Comfort – without ABS	Meritor D3	89 >>		MDP5054		
Lion's Explorer	Knorr SB7 / SN7	01/05 >>			MAX087K	MDP3087K / MDP3087KP
Lion's Intercity	Knorr SB7 / SN7	01/15 >>			MAX087K	MDP3087K / MDP3087KP
Lion's Intercity C	Knorr SB7 / SN7	01/15 >>			MAX087K	MDP3087K / MDP3087KP
Lion's Regio – 320, 360, 400	Knorr SB7 / SN7	01/03 >>			MAX087K	MDP3087K / MDP3087KP
Lion's Star – 352, 353, 402, 403, 422 FRH, RH	Knorr SB7 / SN7	01/93 >>			MAX087K	MDP3087K / MDP3087KP
	Meritor D3	01/93 >>			MAX030K	MDP3030K
	Meritor ELSA 2	01/93 >>			MDP5073SK / MDP5056SK / MAX131K	MDP3131K
	Knorr K85	01/93 >> 01/96				MDP3747
	Meritor ELSA 1 / D3	01/93 >>			MDP5065SK	
Lion's Star – 414, 464 RH, RHS	Knorr SB7 / SN7	01/93 >>			MAX087K	MDP3087K / MDP3087KP
	Meritor D3	01/93 >>			MAX030K	MDP3030K
	Meritor ELSA 2	01/93 >>			MDP5073SK / MDP5056SK / MAX131K	MDP3131K
	Meritor ELSA 1 / D3	01/93 >>			MDP5065SK	
Lion's Star – 414, 464, 484 RH, RHS	Meritor D3	01/04 >>			MAX030K	MDP3030K
	Meritor ELSA 2	01/04 >>			MDP5073SK / MDP5056SK / MAX131K	MDP3131K
	Meritor ELSA 1 / D3	01/04 >>			MDP5065SK	
Lion's Star – Meritor Brake	Meritor ELSA 1	94 >>		MDP5038		
	Meritor D3	94 >>		MDP5054		
NG262	Meritor ELSA 1	98 >>		MDP5065		
	Meritor ELSA 1	3/95 >>		MDP5065		
NG263	Meritor ELSA 1	98 >>		MDP5065		
	Meritor ELSA 1	3/95 >>		MDP5065		
NG272	Meritor ELSA 1	3/95 >>		MDP5065		
NG312	Meritor ELSA 1	98 >>		MDP5065		
	Meritor ELSA 1	3/95 >>		MDP5065		

- Refer to Buyers Guide



1



2



3



4



5



							
					GENUINE	PREMIUM	ALLFIT
...MAN PSV's							
							
NG313	Meritor ELSA 1	98 >>		MDP5065			
	Meritor ELSA 1	3/95 >>		MDP5065			
NL202	Meritor ELSA 1	89 >>		MDP5065			
NL222	Meritor ELSA 1	89 >>		MDP5065			
NL223	Meritor ELSA 1	89 >>		MDP5065			
NL312	Meritor ELSA 1	95 >>		MDP5065			
NL313	Meritor ELSA 1	98 >>		MDP5065			
	Meritor ELSA 1	98 >>		MDP5065			
NM222	Meritor ELSA 1	96 >>		MDP5065			
NM223	Meritor ELSA 1	96 >>		MDP5065			
NU263	Meritor ELSA 1	96 >>		MDP5065			
NU313	Meritor ELSA 2	02 >>		MDP5097			
	Meritor ELSA 1	96 >>		MDP5065			
NU353	Meritor ELSA 1	96 >>		MDP5065			
SG, SL (150 --> 190 Series)	Wabco Pan 17	01/96 >>			MAX088K	MDP3088 / MDP3088K	
SG, SL (230 --> 750 Series)	Wabco Pan 17	01/96 >>			MAX088K	MDP3088 / MDP3088K	
SLF – 12, 14 Series	Knorr SB6 / SN6	01/06 >>			MAX095K	MDP3095K	
SU 210	Wabco Pan 17	01/96 >>			MAX088K	MDP3088 / MDP3088K	
SU 230	Wabco Pan 17	01/96 >>			MAX088K	MDP3088 / MDP3088K	
SU Series – 263, 283, 313	Meritor ELSA 2	09/03 >>			MDP5073SK / MDP5056SK / MAX131K	MDP3131K	
MCV							
							
Evolution – C124RLE	Knorr SB7 / SN7	01/04 >>			MAX087K	MDP3087K / MDP3087KP	
MCW							
							
Metrorider	B Frame (2x60)	01/00 >>				MDP3122	
Menarini							
							
Avancity L, N	Meritor DX 225	01/00 >>			MDP5083SK		
Citymood 10, 12	Knorr SB7 / SN7	01/13 >>			MAX087K	MDP3087K / MDP3087KP	
	Knorr SB7 / SN7	01/16 >>			MAX087K	MDP3087K / MDP3087KP	
	Knorr SB7 / SN7	01/16 >>			MAX087K	MDP3087K / MDP3087KP	

- Refer to Buyers Guide



							
							
...Menarini							
							
Citymood 18	Knorr SB7 / SN7	01/13 >>			MAX087K	MDP3087K / MDP3087KP	
	Knorr SB7 / SN7	01/16 >>			MAX087K	MDP3087K / MDP3087KP	
M 240, M 340 Series – L, LI, N, S, U	Meritor DX 225	01/98 >>			MDP5083SK		
Mercedes							
							
Accelo – 7T & 8T models	Knorr SB5 / SN5	05/03 >>			MAX148K	MDP3148K	
Accelo – 9T & 10T models	Knorr SB5 / SN5	05/03 >>			MAX148K	MDP3148K	
Actros – 1831 --> 2053 models	Knorr SB7 / SN7	04/96 >> 10/02		MDP9000	MAX087K	MDP3087K / MDP3087KP	
Actros – 2531 --> 3357 models	Knorr SB7 / SN7	04/96 >> 10/02		MDP9000	MAX087K	MDP3087K / MDP3087KP	
Actros – 3231 --> 4148 models	Knorr SB7 / SN7	04/96 >> 10/02			MAX087K	MDP3087K / MDP3087KP	
Actros – 2 axle models	Knorr SM7	07/11 >>			MAX246K	MDP3246K	
	Knorr SL7	07/11 >>			MAX244K	MDP3244K	
Actros – 3 axle models	Knorr SM7	07/11 >>			MAX246K	MDP3246K	
	Knorr SL7	07/11 >>			MAX244K	MDP3244K	
Actros MP2, MP3 – 1831 --> 2055 models	Knorr SB7 / SN7	10/02 >> 12/11		MDP9000	MAX087K	MDP3087K / MDP3087KP	
Actros MP2, MP3 – 2430 --> 4036 models	Knorr SB7 / SN7	10/02 >> 12/11		MDP9000	MAX087K	MDP3087K / MDP3087KP	
	Knorr SB5 / SN5	10/02 >>			MAX148K	MDP3148K	
Actros MP2, MP3 – 3230 --> 5048 models	Knorr SB7 / SN7	10/02 >> 12/11		MDP9000	MAX087K / MAX167K	MDP3087K / MDP3087KP / MDP3167K	
Antos – 2 axle models	Knorr SB7 / SN7	05/12 >>		MDP9000	MAX087K	MDP3087K / MDP3087KP	
	Knorr SM7	05/12 >>			MAX246K	MDP3246K	
	Knorr SL7	05/12 >>			MAX244K	MDP3244K	
Antos – 3 axle models	Knorr SB7 / SN7	05/12 >>		MDP9000	MAX087K	MDP3087K / MDP3087KP	
	Knorr SM7	05/12 >>			MAX246K	MDP3246K	
	Knorr SB5 / SN5	05/12 >>			MAX148K	MDP3148K	
	Knorr SL7	05/12 >>			MAX244K	MDP3244K	
Antos – 4 axle models	Knorr SB7 / SN7	05/12 >>		MDP9000	MAX087K	MDP3087K / MDP3087KP	
	Knorr SM7	05/12 >>			MAX246K	MDP3246K	
	Knorr SL7	05/12 >>			MAX244K	MDP3244K	
Arocs – 2 axle models	Knorr SB7 / SN7	05/12 >>		MDP9000	MAX087K	MDP3087K / MDP3087KP	
	Knorr SM7	05/12 >>			MAX246K	MDP3246K	
	Knorr SL7	05/12 >>			MAX244K	MDP3244K	

- Refer to Buyers Guide



- 1
- 2
- 3
- 4
- 5

						
				GENUINE	PREMIUM	ALLFIT
...Mercedes						
						
Arocs – 3 axle models	Knorr SB7 / SN7	05/12 >>		MDP9000	MAX087K	MDP3087K / MDP3087KP
	Knorr SM7	05/12 >>			MAX246K	MDP3246K
	Knorr SB5 / SN5	05/12 >>			MAX148K	MDP3148K
	Knorr SL7	05/12 >>			MAX244K	MDP3244K
Arocs – 4 axle models	Knorr SB7 / SN7	05/12 >>		MDP9000	MAX087K	MDP3087K / MDP3087KP
	Knorr SM7	05/12 >>			MAX246K	MDP3246K
	Knorr SL7	05/12 >>			MAX244K	MDP3244K
Atego – 712 --> 823 models	Knorr SB5 / SN5	01/98 >>			MAX148K	MDP3148K
Atego – 914 --> 1023 models	Knorr SB5 / SN5	01/98 >>			MAX148K	MDP3148K
Atego – 914 --> 1228 models	Knorr SB6 / SN6	01/98 >>			MAX095K	MDP3095K
Atego – 1228 --> 1528 models	Knorr SB6 / SN6	01/98 >>			MAX095K	MDP3095K
Atego – 1823 --> 1833 models	Knorr SB7 / SN7	09/96 >> 10/04		MDP9000	MAX087K	MDP3087K / MDP3087KP
	Knorr SM7	09/96 >>			MAX246K	MDP3246K
	Knorr SL7	09/96 >>			MAX244K	MDP3244K
Atego – 2523 --> 2633 models	Knorr SB7 / SN7	09/96 >> 10/04		MDP9000	MAX087K	MDP3087K / MDP3087KP
	Knorr SM7	09/96 >>			MAX246K	MDP3246K
	Knorr SL7	09/96 >>			MAX244K	MDP3244K
Atego 2 – 712 --> 824 models	Knorr SB5 / SN5	10/04 >>			MAX148K	MDP3148K
Atego 2 – 915 --> 1229 models	Knorr SB5 / SN5	10/04 >>			MAX148K	MDP3148K
Atego 2 – 915 --> 1624 models	Knorr SB6 / SN6	10/04 >>			MAX095K	MDP3095K
Atego 2 – 1823 --> 1833 models	Knorr SB7 / SN7	10/04 >>			MAX087K	MDP3087K / MDP3087KP
Atego 2 – 1924 --> 2400 models	Knorr SB6 / SN6	10/04 >>			MAX095K	MDP3095K
Atego 2 – 2523 --> 2633 models	Knorr SB7 / SN7	10/04 >>			MAX087K	MDP3087K / MDP3087KP
Atego 2 – 2523 --> 2633 models	Knorr SB5 / SN5	01/16 >>			MAX148K	MDP3148K
Atego 2 – 2700 --> 3030 models	Knorr SB5 / SN5	01/16 >>			MAX148K	MDP3148K
Atego 3 – 12T --> 15T Models	Knorr SB6 / SN6	05/12 >>			MAX095K	MDP3095K
Atego 3 – 2100 --> 2633 models	Knorr SB5 / SN5	01/17 >>			MAX148K	MDP3148K
Atego 3 – 6.5T --> 12T Models	Knorr SB5 / SN5	05/12 >>			MAX148K	MDP3148K
Axor – 1823--> 1944	Knorr SB7 / SN7	09/01 >> 10/04		MDP9000	MAX087K	MDP3087K / MDP3087KP
	Knorr SM7	09/01 >>			MAX246K	MDP3246K
	Knorr SL7	09/01 >>			MAX244K	MDP3244K

- Refer to Buyers Guide



--	--	--	---	--	--	--

- Refer to Buyers Guide



GENUINE

PREMIUM

ALLFIT

...Mercedes



with Haldex brakes	Haldex Modul X - DB19	01/99 >>				MDP3181K
	Haldex Modul X - DB22	01/99 >>				MDP3143K
with Knorr brakes	Knorr SB5 / SN5				MAX148K	MDP3148K
	Knorr SB7 / SN7	01/98 >>			MAX087K	MDP3087K / MDP3087KP
	Knorr SB6 / SN6	01/99 >>			MAX095K	MDP3095K
	Knorr SK7	01/99 >>				MDP3158K
with Wabco brakes	Wabco Pan 19-1	01/99 >>			MAX126K	MDP3126 / MDP3126K



Sprinter (BM 905) – 500, 600 Series	Meritor B Frame (2x60)	04/01 >>				MDP3835K
T2 Series – 508 --> 512	Meritor B Frame (2x60)	01/84 >>		MDP5040		MDP3835K
T2 Series – 608 --> 612	Meritor B Frame (2x60)	01/84 >>		MDP5040		MDP3835K
T2 Series – 709D, 709DK, 711D, 714D	Meritor B Frame (2x60)	01/84 >> 06/98		MDP5040		MDP3835K
T2 Series – 809D, 811D, 811DK, 814D, 814DA	Meritor B Frame (2x60)	01/84 >> 06/98		MDP5040		MDP3835K
Vario, Vario Plus – 0409	Meritor B Frame (2x60)	01/96 >>				MDP3835K
Vario, Vario Plus – 512D	Meritor B Frame (2x60)	01/96 >>		MDP5040		MDP3835K
Vario, Vario Plus – 612D, 613D	Meritor B Frame (2x60)	01/96 >>		MDP5040		MDP3835K
Vario, Vario Plus – 614D, 615D, 616D, 618D	Meritor B Frame (2x60)	01/96 >>		MDP5040		MDP3835K
Vario, Vario Plus – 810TD	Meritor B Frame (2x60)	01/96 >>		MDP5040		MDP3835K
Vario, Vario Plus – 812D, 813D, 813DA	Meritor B Frame (2x60)	01/96 >>		MDP5040		MDP3835K
Vario, Vario Plus – 814D, 814DA	Meritor B Frame (2x60)	01/96 >>		MDP5040		MDP3835K
Vario, Vario Plus – 814TD	Meritor B Frame (2x60)	01/96 >>		MDP5040		MDP3835K
Vario, Vario Plus – 815D, 815DA, 816D, 816DA	Meritor B Frame (2x60)	01/96 >>				MDP3835K
Vario, Vario Plus – 818D, 818DA	Meritor B Frame (2x60)	01/96 >>				MDP3835K

Mercedes PSV (Inc Evobus)



0409	Meritor B Frame (2x60)	01/96 >>		MDP5040		MDP3835K
0340, 0350	Meritor D3	01/91 >>			MAX030K	MDP3030K
0340, 0350	Meritor ELSA 1 / D3	01/91 >>			MDP5065SK	
0403 – RHD, SHD	Knorr SB7 / SN7	01/03 >>			MAX087K	MDP3087K / MDP3087KP
0404 Neoplan (10R --> 15R)	Meritor D3	10/91 >> 10/99		MDP5033	MAX030K	MDP3030K
0404 Neoplan (10R --> 15R)	Meritor ELSA 1 / D3	10/91 >>			MDP5065SK	
508D, 510, 511D	Meritor B Frame (2x60)	01/86 >>				MDP3835K
608D, 609D, 0611D, 0614D	Meritor B Frame (2x60)	01/86 >>				MDP3835K

- Refer to Buyers Guide



							
					GENUINE	PREMIUM	ALLFIT
...Mercedes PSV (Inc Evobus)							
							
709D, 711D	Meritor B Frame (2x60)	01/86 >> 06/98					MDP3835K
709D, 711D – 16" wheels	Meritor B Frame (2x60)	01/86 >> 06/98					MDP3835K
809D, 811D, 814D – 16" wheels	Meritor B Frame (2x60)	01/86 >> 06/98					MDP3835K
809D, 811D, 814D – 17.5" wheels	Meritor B Frame (2x60)	01/86 >> 06/98					MDP3835K
CapaCity – 32T Articulated Bus	Knorr SB7 / SN7	04/07 >>				MAX087K	MDP3087K / MDP3087KP
Citaro – 0530 All models diesel, electric and hybrid, rigid and articulated buses	Knorr SB7 / SN7	09/96 >>		MDP9005		MAX087K	MDP3087K / MDP3087KP
Cito – 0520	Knorr SB7 / SN7	09/96 >>		MDP9005		MAX087K	MDP3087K / MDP3087KP
Citybus – 0100	Knorr SB7 / SN7	01/92 >>				MAX087K	MDP3087K / MDP3087KP
Comfort Class 400 series – S415, S416, S417 GT, GT-HD	Knorr SB7 / SN7	10/03 >>				MAX087K	MDP3087K / MDP3087KP
Conecto – 0345 Series C, H, M, UE	Knorr SB7 / SN7	09/96 >>				MAX087K	MDP3087K / MDP3087KP
	Knorr SB7 / SN7	11/01 >>				MAX087K	MDP3087K / MDP3087KP
Gran Viale	Knorr SB7 / SN7	01/07 >>				MAX087K	MDP3087K / MDP3087KP
Integro, Integro L, Integro M – 0550	Meritor D3	01/00 >>				MAX030K	MDP3030K
	Knorr SB7 / SN7	09/96 >>		MDP9005		MAX087K	MDP3087K / MDP3087KP
	Meritor D3	09/96 >>				MAX030K	MDP3030K
	Meritor ELSA 1 / D3	01/00 >>				MDP5065SK	
	Meritor ELSA 1 / D3	09/96 >>				MDP5065SK	
Intouro, Intouro E, Intouro M, Intouro ME	Knorr SB7 / SN7	01/05 >>				MAX087K	MDP3087K / MDP3087KP
Medio	Meritor B Frame (2x60)	10/02 >>					MDP3835K
N Series Bus – NF3	Knorr SB7 / SN7	01/92 >>				MAX087K	MDP3087K / MDP3087KP
OF series – 10T --> 16T	Knorr SB7 / SN7	01/83 >>				MAX087K	MDP3087K / MDP3087KP
OH series – 12T --> 16T	Knorr SB7 / SN7	01/70 >>				MAX087K	MDP3087K / MDP3087KP
Top Class 400 series – S411, S415, S416, S417 HD, HDH	Knorr SB7 / SN7	10/01 >>				MAX087K	MDP3087K / MDP3087KP
	Knorr SB7 / SN7	10/01 >>				MAX087K	MDP3087K / MDP3087KP
Top Class 400 series – S431 DT	Knorr SB7 / SN7	10/02 >>				MAX087K	MDP3087K / MDP3087KP
Tourino	Knorr SB7 / SN7	01/00 >>		MDP9005		MAX087K	MDP3087K / MDP3087KP
	Knorr SB6 / SN6	10/03 >>				MAX095K	MDP3095K
Tourismo – 0340, 0350	Knorr SB7 / SN7	08/95 >>				MAX087K	MDP3087K / MDP3087KP
	Meritor D3	08/95 >>				MAX030K	MDP3030K
	Meritor ELSA 1 / D3	08/95 >>				MDP5065SK	
Touro – 0500	Knorr SB7 / SN7	01/96 >>		MDP9005		MAX087K	MDP3087K / MDP3087KP

- Refer to Buyers Guide



1



2



3



4



5



						
				GENUINE	PREMIUM	ALLFIT
...Mercedes PSV (Inc Evobus)						
						
Travego – 0580	Knorr SB7 / SN7	09/99 >>			MAX087K	MDP3087K / MDP3087KP
Vario, Vario Plus – 0409	Meritor B Frame (2x60)	01/96 >>				MDP3835K
Vario, Vario Plus – 600 Series	Meritor B Frame (2x60)	01/96 >>				MDP3835K
Vario, Vario Plus – 800 Series	Meritor B Frame (2x60)	01/96 >>				MDP3835K
Meritor (Inc Lucas, Rockwell, ROR)						
						
22.5 wheels R1005	Meritor ELSA 225-3				MDP5101SK / MDP5104SK	
B DUCO	Meritor B DUCO					MDP3136K
C DUCO	Meritor C DUCO					MDP3137K
D DUCO	Meritor D DUCO	01/99 >>		MDP5057	MAX125K / MDP5057SK	MDP3125K
D LISA	Meritor D LISA				MAX090K / MDP5042SK	MDP3090K
D3	Meritor D3				MAX030K	MDP3030K
	Meritor ELSA 1 / D3				MDP5065SK	
DX195 Axle	Meritor DX 195	01/99 >>			MDP5076SK	MDP3124K
	Meritor DX 225	06/00 >>			MDP5083SK	
ELSA 1	Meritor D3				MAX030K	MDP3030K
	Meritor ELSA 1 / D3				MDP5065SK	
ELSA 2	Meritor ELSA 2			MDP5073		
	Meritor ELSA 2				MAX131K	MDP3131K
	Meritor ELSA 2				MDP5073SK / MDP5056SK	
ELSA 195 Axle	Meritor ELSA 195	01/04 >>				MDP3169K
	Meritor ELSA 195	01/04 >>			MDP5093SK	
ELSA 225-1	Meritor ELSA 225-1	05/06 >>			MAX173K / MDP5102SK / MDP5106SK / MDP5106PPRK	MDP3173K
ELSA 225-2, ELSA 225L	Meritor ELSA 225L	05/07 >>			MDP5117SK	
ELSA 225-3	Meritor ELSA 225-3	10/08 >>			MAX174K / MDP5119SK	MDP3174K / MDP3174KWI
EX225	Meritor DX 225	01/04 >>			MDP5083SK	
LM, TM	Meritor ELSA 195	01/04 >>		MDP5093		MDP3169K
	Meritor ELSA 195	01/04 >>			MDP5093SK	
	Meritor DX 195	01/99 >>		MDP5076	MDP5076SK	MDP3124K
VGT 195 Axle	Meritor ELSA 195	01/04 >>				MDP3169K
	Meritor ELSA 195	01/04 >>			MDP5093SK	

- Refer to Buyers Guide



							
					GENUINE	PREMIUM	ALLFIT
Moseley							
							
BOVA / Futura		Knorr K85	01/84 >> 01/88				MDP3747
Neoplan (Inc Auwärter)							
							
Centroliner – N44 series	Knorr SB7 / SN7	01/92 >>		MDP9005	MAX087K	MDP3087K / MDP3087KP	
	Meritor ELSA 2	01/92 >>			MDP5073SK / MDP5056SK / MAX131K	MDP3131K	
Centroliner – N45 series	Knorr SB7 / SN7	01/92 >>		MDP9005		MDP3087K / MDP3087KP	
	Meritor ELSA 2	01/92 >>			MDP5073SK / MDP5056SK	MDP3131K	
Cityliner – N116, N166 series	Knorr SB7 / SN7	01/90 >>			MAX087K	MDP3087K / MDP3087KP	
	Knorr SB7 / SN7	09/96 >>		MDP9005	MAX087K	MDP3087K / MDP3087KP	
Cityliner – N1216, N1217, N1218	Knorr SB7 / SN7	01/06 >>			MAX087K	MDP3087K / MDP3087KP	
Cityliner – N122 series	Knorr SB7 / SN7	09/96 >>			MAX087K	MDP3087K / MDP3087KP	
Clubstar – SB 6000	Knorr SB6 / SN6	01/98 >>			MAX095K	MDP3095K	
Economy	Meritor B Frame (2x60)	01/98 >>		MDP5040			
Economy – 17.5" wheels	Meritor B Frame (2x60)	01/98 >>				MDP3835K	
Euroliner – N3316, N3318	Knorr SB7 / SN7	01/92 >>		MDP9005	MAX087K	MDP3087K / MDP3087KP	
EuroStar – 0404 (10R --> 15R)	Meritor D3	10/91 >>			MAX030K	MDP3030K	
	Meritor ELSA 1 / D3	10/91 >>			MDP5065SK		
Jetliner – N200, N300, N400 Series	Knorr K85	>> 09/85				MDP3747	
	Knorr SB7 / SN7	09/90 >>		MDP9005	MAX087K	MDP3087K / MDP3087KP	
	Knorr SB7 / SN7	09/90 >>		MDP9005	MAX087K	MDP3087K / MDP3087KP	
Megaliner – N128/4	Knorr SB7 / SN7	01/93 >> 12/00			MAX087K	MDP3087K / MDP3087KP	
Megashuttle – N128/4	Knorr SB7 / SN7	01/98 >> 12/00			MAX087K	MDP3087K / MDP3087KP	
Megashuttle – N4032/4	Knorr SB7 / SN7	01/94 >>			MAX087K	MDP3087K / MDP3087KP	
Metroliner	Knorr K85	>> 01/94				MDP3747	
N Series Bus – N4007 --> N4026	Knorr SB7 / SN7	01/90 >>			MAX087K	MDP3087K / MDP3087KP	
	Knorr SB7 / SN7	01/90 >>		MDP9005	MAX087K	MDP3087K / MDP3087KP	
N Series Bus – N4007, N4009, N4014, N4016, N4021	Knorr K85	01/92 >>				MDP3747	
N Series Bus – N4407 Centroliner	Wabco 1600 V-G	01/03 >>				MDP3077	
Regioliner – N3014, N3016	Knorr SB7 / SN7	01/92 >>			MAX087K	MDP3087K / MDP3087KP	
Skyliner – N122, N122/3, N138/4	Knorr SB7 / SN7	01/90 >>		MDP9005	MAX087K	MDP3087K / MDP3087KP	
	Knorr SB7 / SN7	01/90 >>		MDP9005	MAX087K	MDP3087K / MDP3087KP	

- Refer to Buyers Guide



1



2



3



4



5



					 			
						GENUINE	PREMIUM	ALLFIT
...Neoplan (Inc Auwärter)								
								
Spaceliner – N117, N117/2, N117/3	Knorr SB7 / SN7	01/90 >>		MDP9005	MAX087K	MDP3087K / MDP3087KP		
	Knorr SB7 / SN7	01/90 >>		MDP9005	MAX087K	MDP3087K / MDP3087KP		
Sportliner – N208	Knorr SB7 / SN7	01/90 >>			MAX087K	MDP3087K / MDP3087KP		
Starliner – N2216 SHD	Knorr SB7 / SN7	01/02 >>		MDP9005	MAX087K	MDP3087K / MDP3087KP		
Starliner – N516, N516/3	Knorr SB7 / SN7	01/02 >>		MDP9005	MAX087K	MDP3087K / MDP3087KP		
	Knorr SB7 / SN7	01/92 >>		MDP9005	MAX087K	MDP3087K / MDP3087KP		
	Knorr SB7 / SN7	01/92 >>		MDP9005	MAX087K	MDP3087K / MDP3087KP		
Starliner – N5217, N5218 SHD, SHDC, SHDL	Knorr SB7 / SN7	01/02 >>		MDP9005	MAX087K	MDP3087K / MDP3087KP		
	Knorr SB7 / SN7	05/05 >>		MDP9005	MAX087K	MDP3087K / MDP3087KP		
Teamstar – 17.5" wheels	Meritor B Frame (2x60)	01/98 >>				MDP3835K		
Tourliner – N2216, N2216/3 SHD, SHDC, SHDL	Knorr SB7 / SN7	01/03 >>			MAX087K	MDP3087K / MDP3087KP		
Transliner – N312, N314, N316	Knorr SB7 / SN7	01/88 >>		MDP9005	MAX087K	MDP3087K / MDP3087KP		
	Knorr SB7 / SN7	01/88 >>		MDP9005	MAX087K	MDP3087K / MDP3087KP		
Transliner – N316, N321/3	Knorr SB7 / SN7	01/88 >>			MAX087K	MDP3087K / MDP3087KP		
Transliner – SHD	Meritor D LISA	01/97 >>			MAX090K / MDP5042SK	MDP3090K		
	Meritor D3	01/97 >>			MAX030K	MDP3030K		
	Meritor D2	10/91 >> 01/97				MDP3043K		
	Meritor ELSA 1 / D3	01/97 >>			MDP5065SK			
Trendliner – N3516, N3516/3	Knorr SB7 / SN7	09/04 >>			MAX087K	MDP3087K / MDP3087KP		
Nicolas Trailers								
								
Modular	Knorr SB5 / SN5	01/98 >>			MAX148K	MDP3148K		
Nissan (Inc Motor Iberica)								
								
D Series – D, D Access, D Wide	Wabco Pan 17	01/13 >>			MAX088K	MDP3088 / MDP3088K		
Ebro / Trade Pick-Up, Van – L60, L75, L80	B Frame (2x60)	01/92 >> 01/98				MDP3122		
NT500	Knorr SB5 / SN5	01/13 >>			MAX148K	MDP3148K		
Nogebus								
								
Catalan – 320	Knorr SB6 / SN6	01/98 >>			MAX095K	MDP3095K		
Catalan – 350, 370	Meritor D3	01/01 >>			MAX030K	MDP3030K		
	Meritor ELSA 1 / D3	01/01 >>			MDP5065SK			

- Refer to Buyers Guide



							
							
Optare							
							
Esteem	Meritor ELSA 225-3	01/06 >>			MAX174K	MDP3174K / MDP3174KWI	
Esteem – Scania axle	Knorr SB7 / SN7	01/06 >>			MAX087K	MDP3087K / MDP3087KP	
Metro Rider	B Frame (2x60)	01/88 >>				MDP3122	
Nouvelle – SR	Meritor B Frame (2x60)	01/96 >>		MDP5040		MDP3835K	
Olympus	Meritor ELSA 225-3	01/06 >>			MAX174K	MDP3174K / MDP3174KWI	
Olympus – 260 --> 301	Knorr SB7 / SN7	11/06 >>			MAX087K	MDP3087K / MDP3087KP	
Sigma	Meritor D3	01/94 >> 01/97			MAX030K	MDP3030K	
	Meritor ELSA 1 / D3	01/94 >>			MDP5065SK		
Solera Corta	Knorr SB6 / SN6	01/02 >>			MAX095K	MDP3095K	
Solera, Solera 2	Knorr SB6 / SN6	06/02 >>			MAX095K	MDP3095K	
Solers HD, SR	Knorr SB6 / SN6	01/03 >>			MAX095K	MDP3095K	
Solo	B Frame (2x60)	01/88 >> 12/02				MDP3122	
Solo – M Series 710, 780, 810, 880, 950, 1020	Wabco Pan 17	06/02 >>			MAX088K	MDP3088 / MDP3088K	
Star Rider	Meritor B Frame (2x60)	01/86 >>				MDP3835K	
Tempo – X1060, X1130, X1200, X1260	Meritor ELSA 225-3	08/04 >>			MAX174K	MDP3174K / MDP3174KWI	
	Meritor ELSA 2	09/04 >>			MDP5073SK / MDP5056SK / MAX131K	MDP3131K	
Toro	Meritor B Frame (2x60)	01/08 >>				MDP3835K	
Versa – 17.5" wheels	Wabco Pan 17	11/06 >>			MAX088K	MDP3088 / MDP3088K	
Plaxton							
							
Beaver	Meritor B Frame (2x60)	10/02 >>				MDP3835K	
Centro – MAN chassis	Knorr SB6 / SN6	06/02 >>			MAX095K	MDP3095K	
Centro – Volvo chassis	Meritor D DUCO	01/00 >>			MAX125K / MDP5057SK	MDP3125K	
	Meritor ELSA 225-3	01/06 >>			MAX174K	MDP3174K / MDP3174KWI	
Cheetah	Meritor B Frame (2x60)	09/96 >>				MDP3835K	
Elite	Meritor D DUCO	01/99 >>			MAX125K / MDP5057SK	MDP3125K	
Elite – Volvo chassis	Meritor D DUCO	01/00 >>			MAX125K / MDP5057SK	MDP3125K	
	Meritor ELSA 225-3	01/06 >>			MAX174K	MDP3174K / MDP3174KWI	
Enigma – 12m MAN chassis	Meritor ELSA 1	01/01 >>		MDP5065			
Javelin Mk III – 11m, 12m bus, coach	Meritor D LISA	01/95 >>			MAX090K / MDP5042SK	MDP3090K	

- Refer to Buyers Guide



1



2



3



4



5



			GENUINE		PREMIUM		ALLFIT	
...Plaxton								
Panther	Meritor ELSA 225-3	01/06 >>			MAX174K	MDP3174K / MDP3174KWI		
	Knorr SB7 / SN7	01/92 >>			MAX087K	MDP3087K / MDP3087KP		
	Meritor D DUCO	01/99 >>			MAX125K / MDP5057SK	MDP3125K		
	Meritor ELSA 2	01/99 >>			MDP5073SK / MDP5056SK / MAX131K	MDP3131K		
Paragon	Meritor D DUCO	01/00 >>			MAX125K / MDP5057SK	MDP3125K		
	Meritor ELSA 225-3	01/06 >>			MAX174K	MDP3174K / MDP3174KWI		
	Knorr SB7 / SN7	01/92 >>			MAX087K	MDP3087K / MDP3087KP		
Paragon – MAN chassis	Meritor ELSA 2	01/99 >>			MDP5073SK / MDP5056SK / MAX131K	MDP3131K		
Primo – 17.5" wheels	Wabco Pan 17	01/05 >>			MAX088K	MDP3088 / MDP3088K		
Profile	Meritor D DUCO	01/00 >>			MAX125K / MDP5057SK	MDP3125K		
	Meritor ELSA 225-3	01/06 >>			MAX174K	MDP3174K / MDP3174KWI		
Touring	Knorr SB6 / SN6	01/96 >>			MAX095K	MDP3095K		
Prevost								
H Series	Knorr SB7 / SN7	01/00 >>			MAX087K	MDP3087K / MDP3087KP		
Rába								
270-79	Wabco Pan 17	01/99 >>			MAX088K	MDP3088 / MDP3088K		
270-80	Wabco Pan 17	01/99 >>			MAX088K	MDP3088 / MDP3088K		
309-69	Knorr SB7 / SN7	01/99 >>			MAX087K	MDP3087K / MDP3087KP		
360-05	Wabco Pan 17	01/99 >>			MAX088K	MDP3088 / MDP3088K		
360-74	Wabco Pan 17	01/99 >>			MAX088K	MDP3088 / MDP3088K		
932-21	Knorr SB7 / SN7	01/99 >>			MAX087K	MDP3087K / MDP3087KP		
with Knorr brakes	Knorr SB6 / SN6	01/99 >>			MAX095K	MDP3095K		
with Meritor brakes	Meritor ELSA 2	01/07 >>			MDP5073SK / MDP5056SK / MAX131K	MDP3131K		
Renault Trucks								
C – C380, C430, C440, C460, C480, C520	Meritor ELSA 225-1	13 >>		MDP5106				
C Series – C38, C40	Knorr SB5 / SN5	01/82 >>			MAX148K	MDP3148K		
C Series	Meritor ELSA 225-1	01/13 >>		MDP5102	MDP5102SK / MDP5106SK / MDP5106PPRK / MAX173K	MDP3173K		
	Meritor ELSA 225-3	01/13 >>		MDP5101	MDP5101SK / MDP5104SK / MDP5101PPRK / MDP5104PPRK / MAX174K	MDP3174K / MDP3174KWI		
	Meritor ELSA 195	01/13 >>			MDP5093SK	MDP3169K		

- Refer to Buyers Guide



- Refer to Buyers Guide



1



GENUINE

PREMIUM

ALLFIT

...Renault Trucks



Magnum Series – AE500, AE520, AE560	Meritor ELSA 2	01/90 >> 06/00		MDP5056		
	Meritor D LISA	01/90 >> 06/00		MDP5042	MAX090K / MDP5042SK	MDP3090K
	Meritor D2	01/90 >> 06/00				MDP3043K
	Meritor D3	01/90 >> 06/00			MAX030K	MDP3030K
	Meritor ELSA 2	01/90 >> 06/00			MDP5073SK / MDP5056SK / MAX131K	MDP3131K
	Meritor ELSA 1 / D3	01/90 >>			MDP5065SK	
Major Series – R340, R350, R380, R385	Meritor D2	01/90 >> 05/93				MDP3043K
	Meritor D3	05/93 >> 06/00			MAX030K	MDP3030K
	Meritor ELSA 1 / D3	05/93 >>			MDP5065SK	
Major Series – R420, R429	Meritor D2	01/90 >> 05/93				MDP3043K
	Meritor D3	05/93 >> 06/00			MAX030K	MDP3030K
	Meritor ELSA 1 / D3	05/93 >>			MDP5065SK	
Manager G Series – G230, G260, G270, G280, G290	Meritor D2	01/90 >> 01/93				MDP3043K
	Meritor D3	01/93 >> 06/00			MAX030K	MDP3030K
	Meritor ELSA 1 / D3	01/93 >>			MDP5065SK	
Manager G Series – G300	Meritor D2	01/90 >> 01/93				MDP3043K
	Meritor D3	01/93 >> 06/00			MAX030K	MDP3030K
	Meritor ELSA 1 / D3	01/93 >>			MDP5065SK	
Manager G Series – G300, G330, G340	Meritor D2	01/90 >> 01/93				MDP3043K
	Meritor D3	01/93 >> 06/00			MAX030K	MDP3030K
	Meritor ELSA 1 / D3	01/93 >>			MDP5065SK	
Manager G Series – G330, G340	Meritor D2	01/90 >> 01/92				MDP3043K
	Meritor D2	01/90 >> 01/93				MDP3043K
	Meritor D3	01/93 >> 06/00			MAX030K	MDP3030K
	Meritor ELSA 1 / D3	01/93 >>			MDP5065SK	
Midliner – M120 - M250	Meritor C LISA	95 >>		MDP5037		
Midliner – ME160.13	Bendix SEE 2X67	01/89 >> 05/95				MDP3013
Midliner – S100, S110 Series	Bendix SEE 2X67	01/86 >> 01/91				MDP3013
Midliner – S12	Bendix SEE 2X67	01/87 >> 01/91				MDP3013
Midliner – S120 --> 210 Series	Meritor B Frame (2x68)	01/95 >>		MDP5005		
	B Frame (2x60)	01/95 >>				MDP3122
	Meritor B Frame (2x68)	09/90 >> 01/95		MDP5005		
	B Frame (2x60)	09/90 >> 01/95				MDP3122

- Refer to Buyers Guide



							
					GENUINE	PREMIUM	ALLFIT
...Renault Trucks							
							
Midliner – S13	Bendix SEE 2X67	01/87 >> 01/91					MDP3013
Midliner – S130 Series	Bendix SEE 2X67	01/83 >> 01/91					MDP3013
Midliner – S150 Series	Bendix SEE 2X67	01/86 >> 01/91					MDP3013
Midliner – S170 Series	Bendix SEE 2X67	01/86 >> 01/91					MDP3013
Midliner – S220 Series	Bendix SEE 2X67	01/86 >> 01/91					MDP3013
Midliner Series – M120.12C, C-P, M120.13C, C-P	Bendix SEE 2X67	01/89 >> 05/93					MDP3013
Midliner Series – M130.12C, C-P, M130.13C, C-P	Bendix SEE 2X67	01/89 >> 05/93					MDP3013
Midliner Series – M140.12C, C-P, M140.13C, C-P	Bendix SEE 2X67	01/89 >> 05/93					MDP3013
Midliner Series – M150.13C	Bendix SEE 2X67	05/93 >> 05/95					MDP3013
Midliner Series – M160.12C, C-P, M160.13C, C-P	Bendix SEE 2X67	01/89 >> 05/95					MDP3013
Midliner Series – M160.12T, M160.13T	Bendix SEE 2X67	01/89 >> 05/95					MDP3013
Midliner Series – M160.15D	Bendix SEE 2X67	01/90 >> 05/93					MDP3013
Midliner Series – M180.12C, M180.13C	Bendix SEE 2X67	05/93 >> 05/95					MDP3013
Midliner Series – M180.15D	Bendix SEE 2X67	05/93 >> 05/95					MDP3013
Midliner Series – M200.10C	Bendix SEE 2X67	01/90 >> 05/93					MDP3013
Midliner Series – M200.12C, C-P, M200.13C, C-P	Bendix SEE 2X67	01/90 >> 05/93					MDP3013
Midliner Series – M200.12T, M200.13T	Bendix SEE 2X67	01/90 >> 05/93					MDP3013
Midliner Series – M210.13C, M210.13CS	Bendix SEE 2X67	05/93 >> 05/95					MDP3013
Midliner Series – M230.13C-T	Bendix SEE 2X67	05/93 >> 05/95					MDP3013
Midliner Series – M230.15D	Bendix SEE 2X67	01/90 >> 05/93					MDP3013
Midlum – 130, 150, 180 Series	Wabco Pan 17	11/99 >> 01/02			MAX088K		MDP3088 / MDP3088K
Midlum – 130, 150 Series	Wabco Pan 17	01/02 >> 05/06			MAX088K		MDP3088 / MDP3088K
Midlum – 160 --> 300 Series	Meritor ELSA 225-1	05/06 >>		MDP5102	MDP5102SK / MDP5106SK / MDP5106PPRK / MAX173K		MDP3173K
	Wabco Pan 17	05/06 >>			MAX088K		MDP3088 / MDP3088K
Midlum – 180 Series	Wabco Pan 19-1	01/02 >>			MAX126K		MDP3126 / MDP3126K
	Wabco Pan 19-2	01/02 >>					MDP3142 / MDP3142K
	Wabco Pan 17	01/02 >> 05/06			MAX088K		MDP3088 / MDP3088K
Midlum – 200 --> 280 Series	Wabco Pan 19-1	01/02 >> /			MAX126K		MDP3126 / MDP3126K
	Wabco Pan 19-2	01/02 >>					MDP3142 / MDP3142K
	Meritor ELSA 2	01/02 >> 05/06			MDP5073SK / MDP5056SK / MAX131K		MDP3131K
	Wabco Pan 17	01/02 >> 05/06			MAX088K		MDP3088 / MDP3088K
Midlum – 210, 220, 250, 270 Series	Wabco Pan 19-2	01/00 >>					MDP3142 / MDP3142K
	Wabco Pan 17	11/99 >> 01/02			MAX088K		MDP3088 / MDP3088K

- Refer to Buyers Guide

1



2



3



4



5





1



2



3



4



5



																		
										GENUINE			PREMIUM			ALLFIT		
...Renault Trucks																		
																		
Midlum – 240--> 460	Meritor ELSA 225-1	05/06 >>		MDP5102	MDP5102SK / MDP5106SK / MDP5106PPRK / MAX173K					MDP3173K								
	Meritor ELSA 195	05/06 >>			MDP5093SK					MDP3169K								
Midlum – 19.5” Wheels - Meritor brakes	Meritor C LISA	11/99 >>		MDP5037														
Premium 2 – Distribution, Lander, Route (05-->)	Meritor ELSA 225-3	10/05 >>		MDP5101	MDP5101SK / MDP5104SK / MDP5101PPRK / MDP5104PPRK / MAX174K					MDP3174K / MDP3174KWI								
	Meritor ELSA 225-1	10/05 >>		MDP5102 / MDP5106	MDP5102SK / MDP5106SK / MDP5106PPRK / MAX173K					MDP3173K								
	Meritor ELSA 195	10/05 >>			MDP5093SK					MDP3169K								
Premium Distribution, Route – 210, 220, 250, 260, 270	Meritor D LISA	01/02 >> 10/05		MDP5042	MAX090K / MDP5042SK					MDP3090K								
	Meritor D3	01/02 >> 10/05			MAX030K					MDP3030K								
	Meritor ELSA 1 / D3	01/02 >>			MDP5065SK													
	Meritor ELSA 1 / D3	01/96 >>			MDP5065SK													
	Meritor ELSA 2	01/96 >> 01/02		MDP5056														
	Meritor D LISA	01/96 >> 01/02		MDP5042	MAX090K / MDP5042SK					MDP3090K								
	Meritor D3	01/96 >> 01/02		MDP5051	MAX030K					MDP3030K								
	Meritor ELSA 2	01/96 >> 01/02			MDP5073SK / MDP5056SK / MAX131K					MDP3131K								
Premium Distribution, Route – 300, 320, 340, 370, 385	Meritor D LISA	01/02 >> 10/05		MDP5042	MAX090K / MDP5042SK					MDP3090K								
	Meritor D3	01/02 >> 10/05			MAX030K					MDP3030K								
	Meritor ELSA 1 / D3	01/02 >>			MDP5065SK													
	Meritor ELSA 1 / D3	01/96 >>			MDP5065SK													
	Meritor ELSA 2	01/96 >> 01/02		MDP5056														
	Meritor D LISA	01/96 >> 01/02		MDP5042	MAX090K / MDP5042SK					MDP3090K								
	Meritor D3	01/96 >> 01/02		MDP5051	MAX030K					MDP3030K								
	Meritor ELSA 2	01/96 >> 01/02			MDP5073SK / MDP5056SK / MAX131K					MDP3131K								
Premium Distribution, Route – 400, 420	Meritor D LISA	01/02 >> 10/05		MDP5042	MAX090K / MDP5042SK					MDP3090K								
	Meritor D3	01/02 >> 10/05			MAX030K					MDP3030K								
	Meritor ELSA 1 / D3	01/02 >>			MDP5065SK													
	Meritor ELSA 1 / D3	01/96 >>			MDP5065SK													
	Meritor ELSA 2	01/96 >> 01/02		MDP5056														
	Meritor D LISA	01/96 >> 01/02		MDP5042	MAX090K / MDP5042SK					MDP3090K								
	Meritor D3	01/96 >> 01/02			MAX030K					MDP3030K								
	Meritor ELSA 2	01/96 >> 01/02			MDP5073SK / MDP5056SK / MAX131K					MDP3131K								

- Refer to Buyers Guide



							
					GENUINE	PREMIUM	ALLFIT
...Renault Trucks							
							
Premium Distribution, Route – 200 Series	Meritor ELSA 2	01/02 >> 10/05		MDP5056			
	Meritor ELSA 2	01/02 >> 10/05			MDP5073SK / MDP5056SK / MAX131K	MDP3131K	
Premium Distribution, Route – 300 Series	Meritor ELSA 225-3	01/02 >>		MDP5101	MDP5101SK / MDP5104SK / MDP5101PPRK / MDP5104PPRK / MAX174K	MDP3174K / MDP3174KWI	
	Meritor ELSA 2	01/02 >> 10/05		MDP5056			
	Meritor ELSA 2	01/02 >> 10/05			MDP5073SK / MDP5056SK / MAX131K	MDP3131K	
Premium Distribution, Route – 400 Series	Meritor ELSA 2	01/02 >> 10/05		MDP5056			
	Meritor ELSA 2	01/02 >> 10/05			MDP5073SK / MDP5056SK / MAX131K	MDP3131K	
Puncher	Meritor ELSA 2	07/04 >>			MDP5073SK / MDP5056SK / MAX131K	MDP3131K	
R Series – R380, R385	Meritor D2	01/89 >> 12/92				MDP3043K	
	Meritor D3	01/93 >> 01/97			MAX030K	MDP3030K	
R Series – R420.19T	Meritor D2	01/89 >> 12/92				MDP3043K	
	Meritor D3	01/93 >> 01/97			MAX030K	MDP3030K	
T Series	Meritor ELSA 225-3	01/13 >>		MDP5101	MDP5101SK / MDP5104SK / MDP5101PPRK / MDP5104PPRK / MAX174K	MDP3174K / MDP3174KWI	
	Meritor ELSA 195	01/13 >>			MDP5093SK	MDP3169K	
Renault Trucks PSV							
							
Agora – D-LISA caliper	Meritor D LISA	01/95 >>		MDP5042	MAX090K / MDP5042SK	MDP3090K	
Agora – D3 caliper	Meritor D3	01/95 >>		MDP5090	MAX030K	MDP3030K	
	Meritor ELSA 1 / D3	01/95 >>			MDP5065SK		
Ares	Knorr SB7 / SN7	01/99 >>			MAX087K	MDP3087K / MDP3087KP	
Iliade – FRH, GTC, GTX	Meritor D3	01/98 >> 06/00		MDP5090	MAX030K	MDP3030K	
	Meritor ELSA 2	06/00 >>			MDP5073SK / MDP5056SK / MAX131K	MDP3131K	
	Meritor ELSA 1 / D3	01/98 >>			MDP5065SK		
Iliade – RT, RTC, RTX, TE	Meritor D3	01/98 >> 06/00		MDP5090	MAX030K	MDP3030K	
	Meritor ELSA 2	06/00 >>			MDP5073SK / MDP5056SK / MAX131K	MDP3131K	
	Meritor ELSA 1 / D3	01/98 >>			MDP5065SK		
Midliner – PP160.09	Meritor B Frame (2x68)	01/92 >> 12/93		MDP5005			
	B Frame (2x60)	01/92 >> 12/93				MDP3122	

- Refer to Buyers Guide



- 1
- 2
- 3
- 4
- 5

							
					GENUINE	PREMIUM	ALLFIT
SAF / Sauer							
							
B9 22 22.5	Haldex Modul T - DBT22LT	01/09 >>				MDP3415K	
B9-19, B9-22, BI9-19, BL9-22	Haldex Modul T - DBT22LT					MDP3195K	
B9-19, B9-22, BI9-19, BI9-22, BL9-22	Knorr ST7	05/08 >>				MDP3328K	
B9, BI9, BIL9, BL9 – 19.5" Wheels	Haldex Modul T - DBT19LT	01/09 >>				MDP3429K	
B9, BI9, BIL9, BL9 – 22.5" Wheels	Haldex Modul T - DBT19LT	01/09 >>				MDP3429K	
BINL9-19, BINL9-22, BIVL9-19, BIVL9-22	Knorr ST7	05/08 >>				MDP3328K	
BINL9-22	Haldex Modul T - DBT22LT					MDP3195K	
SI11-19, SI11-22, SI9-19, SI9-22	Haldex Modul T - DBT22LT					MDP3195K	
SI9, SI11, SIL9 – 22.5" Wheels	Haldex Modul T - DBT19LT	01/09 >>				MDP3429K	
ZI11-22, ZI9-19, ZI9-22	Haldex Modul T - DBT22LT					MDP3195K	
ZI9, ZI11, ZIL9, ZIL11 – 22.5" Wheels	Haldex Modul T - DBT19LT	01/09 >>				MDP3429K	
with Haldex brakes	Haldex Modul X - DB22LT	01/10 >>			MAX175K		
	Haldex Modul X	01/10 >>				MDP3175K	
	Haldex Modul X - DB22	01/99 >>				MDP3143K	
with Knorr brakes	Knorr SB6 / SN6	01/03 >>			MAX095K	MDP3095K	
	Knorr SB5 / SN5	01/99 >>			MAX148K	MDP3148K	
	Knorr SB6 / SN6	01/99 >>			MAX095K	MDP3095K	
	Knorr SB7 / SN7	01/99 >>			MAX087K	MDP3087K / MDP3087KP	
	Knorr SK7	01/99 >>				MDP3158K	
with Meritor brakes	Meritor B DUCO					MDP3136K	
	Meritor C DUCO					MDP3137K	
	Meritor D LISA				MAX090K / MDP5042SK	MDP3090K	
	Meritor D3				MAX030K	MDP3030K	
	Meritor ELSA 1 / D3				MDP5065SK		
	Meritor ELSA 195	01/04 >>				MDP3169K	
	Meritor ELSA 195	01/04 >>			MDP5093SK		
	Meritor D DUCO	01/99 >>		MDP5057	MAX125K / MDP5057SK	MDP3125K	
	Meritor DX 195	01/99 >>			MDP5076SK	MDP3124K	
	Meritor DX 225	06/00 >>			MDP5083SK		
	Meritor ELSA 2	06/00 >>			MAX131K	MDP3131K	
	Meritor ELSA 2	06/00 >>			MDP5073SK / MDP5056SK		

- Refer to Buyers Guide



						
						
...SAF / Sauer						
						
with Wabco brakes	Wabco Pan 19-2	01/04 >>				MDP3141
	Wabco Pan 22-1	01/04 >>			MAX162K	MDP3162 / MDP3162K
	Wabco Pan 19-1	01/09 >>			MAX126K	MDP3126 / MDP3126K
	Wabco Pan 19-1	01/99 >>			MAX126K	MDP3126 / MDP3126K
	Wabco Maxx 22T	01/04 >>			MAX162K	MDP3162 / MDP3162K
Scania						
						
G Series	Knorr SB7 / SN7	01/03 >>				MDP3394K
	Haldex Modul X - DB22	08/07 >>				MDP3143K
L Series	Haldex Modul X - DB22	11/17 >>				MDP3143K
	Knorr SB7 / SN7	11/17 >>				MDP3394K
	Meritor ELSA 225H	11/17 >>			MDP5332SK	
P Series	Knorr SB7 / SN7	06/04 >>				MDP3394K
	Haldex Modul X - DB22	08/07 >>				MDP3143K
R Series – 22.5" wheels	Knorr SB7 / SN7	01/99 >>				MDP3394K
R Series	Knorr SB7 / SN7	02/04 >>				MDP3394K
	Haldex Modul X - DB22	08/07 >>				MDP3143K
R Series – R380, R385	Meritor ELSA 1 / D3	01/93 >>			MDP5065SK	
R Series – R420.19T	Meritor ELSA 1 / D3	01/93 >>			MDP5065SK	
S Series	Knorr SB7 / SN7	01/03 >>				MDP3394K
	Haldex Modul X - DB22	08/07 >>				MDP3143K
	Haldex Modul T - DBT19LT	01/16 >>				MDP3429K
	Meritor ELSA 225H	07/16 >>			MDP5332SK	
Series 4 C, D, G, L, S, T – 94, 114, 124, 144, 164	Haldex Modul X - DB22	05/95 >>				MDP3143K
	Knorr SB7 / SN7	05/95 >>				MDP3394K
T Series	Knorr SB7 / SN7	01/04 >>		MDP9000	MAX087K	MDP3087K / MDP3087KP
Scania PSV (includes Irizar)						
						
94, 113 Series Buses	Knorr SB7 / SN7	01/93 >>			MAX087K	MDP3087K / MDP3087KP
F, K, N Series Buses	Knorr SB7 / SN7	01/06 >>			MAX087K	MDP3087K / MDP3087KP
Irizar – Century	Knorr SB7 / SN7	01/96 >>				MDP3087K / MDP3087KP
Irizar – Intercentury	Knorr SB7 / SN7	01/96 >>				MDP3087K / MDP3087KP

- Refer to Buyers Guide



1



2



3



4



5



...Scania PSV (includes Irizar)													
Irizar – PB	Knorr SB7 / SN7	01/96 >>						MDP3087K / MDP3087KP					
	Knorr SB7 / SN7	10/09 >>				MAX087K		MDP3087K / MDP3087KP					
Irizar – S-Kool	Knorr SB7 / SN7	01/96 >>			MDP9005			MDP3087K / MDP3087KP					
Irizar – Century	Knorr SB7 / SN7	01/96 >>						MDP3394K					
Irizar – Intercentury	Knorr SB7 / SN7	01/96 >>						MDP3394K					
Irizar – PB	Knorr SB7 / SN7	01/96 >>						MDP3394K					
Irizar – S-Kool	Knorr SB7 / SN7	01/96 >>						MDP3394K					
K230UB – SB 7000	Knorr SB7 / SN7	01/96 >>						MDP3087K / MDP3087KP					
	Knorr SB7 / SN7	01/96 >>						MDP3394K					
K280UB – SB 7000	Knorr SB7 / SN7	01/96 >>						MDP3087K / MDP3087KP					
	Knorr SB7 / SN7	01/96 >>						MDP3394K					
K310UB – SB 7000	Knorr SB7 / SN7	01/96 >>						MDP3087K / MDP3087KP					
	Knorr SB7 / SN7	01/96 >>						MDP3394K					
Omnicity, Omnidecker – with Knorr brakes	Knorr SB7 / SN7	01/96 >>			MDP9005			MDP3087K / MDP3087KP					
	Knorr SB7 / SN7	01/96 >>						MDP3394K					
Series 4 Buses	Knorr SB7 / SN7	01/97 >>				MAX087K		MDP3087K / MDP3087KP					
with Knorr brakes	Knorr SB7 / SN7	01/96 >>						MDP3087K / MDP3087KP					
Schmitz (CargoBull)													
SC Trailer axle	Wabco Pan 22-1	01/04 >>				MAX162K		MDP3162 / MDP3162K					
	Wabco Maxx 22T	01/04 >>				MAX162K		MDP3162 / MDP3162K					
with Knorr brakes	Knorr SB6 / SN6	01/99 >>				MAX095K		MDP3095K					
	Knorr SB7 / SN7	01/99 >>				MAX087K		MDP3087K / MDP3087KP					
	Knorr SK7	01/99 >>						MDP3158K					
Seddon Atkinson													
Strato Series	Knorr SB7 / SN7	01/92 >>				MAX087K		MDP3087K / MDP3087KP					
Setra (inc Kässbohrer)													
Evobus	Knorr SB7 / SN7	01/96 >>				MAX087K		MDP3087K / MDP3087KP					
Setra (S Series) – S130 ES	Knorr 2V20	01/82 >>						MDP3498					

- Refer to Buyers Guide



				 			
					GENUINE	PREMIUM	ALLFIT
...Setra (inc Kässbohrer)							
							
Setra (S Series) – S140	Knorr K85	01/83 >>					MDP3747
	Knorr 2V20	01/83 >>					MDP3498
Setra (S Series) – S210	Knorr K85	01/89 >>					MDP3747
	Knorr 2V20	01/83 >>					MDP3498
Setra (S Series) – S211, S212, S213	Knorr 2V20	10/77 >>					MDP3498
Setra (S Series) – S211, S212, S213, S214	Knorr K85	01/89 >>					MDP3747
	Knorr 2V20	01/83 >>					MDP3498
Setra (S Series) – S215	Knorr K85	01/89 >>					MDP3747
	Meritor D3	01/91 >>		MDP5033	MAX030K		MDP3030K
	Knorr 2V20	01/83 >>					MDP3498
	Meritor ELSA 1 / D3	01/91 >>			MDP5065SK		
Setra (S Series) – S216	Knorr K85	01/89 >>					MDP3747
	Knorr 2V20	01/83 >>					MDP3498
Setra (S Series) – S228	Knorr K85	01/89 >>					MDP3747
	Knorr 2V20	01/83 >>					MDP3498
Setra (S Series) – S300	Meritor D3	01/91 >>		MDP5033	MAX030K		MDP3030K
	Meritor ELSA 1 / D3	01/91 >>			MDP5065SK		
Setra (S Series) – S309, S312	Meritor D3	01/91 >>			MAX030K		MDP3030K
	Meritor ELSA 1 / D3	01/91 >>			MDP5065SK		
Setra (S Series) – S313	Meritor D3	01/91 >>		MDP5033	MAX030K		MDP3030K
	Meritor ELSA 1 / D3	01/91 >>			MDP5065SK		
Setra (S Series) – S315	Meritor D3	01/91 >>			MAX030K		MDP3030K
	Knorr SB7 / SN7	01/91 >>			MAX087K		MDP3087K / MDP3087KP
Setra (S Series) – S315	Meritor ELSA 1 / D3	01/91 >>			MDP5065SK		
Setra (S Series) – S317, S319, S321	Knorr SB7 / SN7	01/91 >>			MAX087K		MDP3087K / MDP3087KP
	Meritor D3	01/91 >>		MDP5033	MAX030K		MDP3030K
	Meritor ELSA 1 / D3	01/91 >>			MDP5065SK		
Setra (S Series) – S328	Meritor D3	01/91 >>			MAX030K		MDP3030K
	Knorr SB7 / SN7	01/95 >>		MDP9005	MAX087K		MDP3087K / MDP3087KP
	Meritor ELSA 1 / D3	01/91 >>			MDP5065SK		
Setra (S Series) – S411, S412, S415, S416, S417, S419, S431 ComfortClass, MultiClass, TopClass	Knorr SB7 / SN7	01/01 >>		MDP9005	MAX087K		MDP3087K / MDP3087KP

- Refer to Buyers Guide



1



2



3



4



5



				 			 		
				GENUINE		PREMIUM		ALLFIT	
Sinotruk (CNHTC)									
									
Golden Prince – ZZ Series	Knorr SB7 / SN7	01/05 >>				MAX087K	MDP3087K / MDP3087KP		
Haojun – ZZ Series	Knorr SB7 / SN7	07/05 >>				MAX087K	MDP3087K / MDP3087KP		
Huanghe Commander – ZZ Series	Knorr SB7 / SN7	05/09 >>				MAX087K	MDP3087K / MDP3087KP		
Steyr – ZZ Series	Knorr SB7 / SN7	05/05 >>				MAX087K	MDP3087K / MDP3087KP		
Steyr King – ZZ Series	Knorr SB7 / SN7	05/07 >>				MAX087K	MDP3087K / MDP3087KP		
Sitcar									
									
Beluga – PSV	Meritor B Frame (2x60)	01/00 >>					MDP3835K		
PSV's	Meritor B Frame (2x60)	01/00 >>			MDP5040		MDP3835K		
Solaris Bus									
									
Alpino	Knorr SB7 / SN7	01/07 >>				MAX087K	MDP3087K / MDP3087KP		
	Knorr SB6 / SN6	01/12 >>				MAX095K	MDP3095K		
Citybus	Knorr SB7 / SN7	01/99 >>				MAX087K	MDP3087K / MDP3087KP		
InterUrbino 12	Knorr SB7 / SN7	02/02 >>				MAX087K	MDP3087K / MDP3087KP		
Trolino 12	Knorr SB7 / SN7	02/02 >>				MAX087K	MDP3087K / MDP3087KP		
Trolino 15	Knorr SB7 / SN7	02/02 >>				MAX087K	MDP3087K / MDP3087KP		
Trolino 18	Knorr SB7 / SN7	02/02 >>				MAX087K	MDP3087K / MDP3087KP		
Urbino 12, Urbino 12 Hybrid, Urbino 12 LE	Knorr SB7 / SN7	01/99 >>				MAX087K	MDP3087K / MDP3087KP		
Urbino 12.9	Knorr SB7 / SN7	01/99 >>				MAX087K	MDP3087K / MDP3087KP		
Urbino 15, Urbino 15 CNG, Urbino 15 LE	Knorr SB7 / SN7	01/99 >>				MAX087K	MDP3087K / MDP3087KP		
Urbino 18, Urbino 18 CNG, Urbino 18 Hybrid	Knorr SB7 / SN7	01/99 >>				MAX087K	MDP3087K / MDP3087KP		
Urbino 8.9	Knorr SB6 / SN6	01/12 >>				MAX095K	MDP3095K		
Urbino 9, 10	Knorr SB7 / SN7	01/99 >>				MAX087K	MDP3087K / MDP3087KP		
Vacanza 12	Knorr SB7 / SN7	02/02 >>				MAX087K	MDP3087K / MDP3087KP		
Vacanza 13	Knorr SB7 / SN7	02/02 >>				MAX087K	MDP3087K / MDP3087KP		
SOR									
									
9.5 Series – Citybus B9.5	Meritor C DUCO	04/02 >>			MDP5053				
9.5 Series – Intercity C9.5	Meritor C DUCO	04/02 >>			MDP5053				
9.5 Series – Tourist Bus LC9.5	Meritor C DUCO	04/02 >>			MDP5053				

- Refer to Buyers Guide



						
				GENUINE	PREMIUM	ALLFIT
...SOR						
						
10.5 Series – Citybus B10.5	Meritor C DUCO	04/02 >>		MDP5053		
10.5 Series – Intercity Bus C10.5	Meritor C DUCO	04/02 >>		MDP5053		
10.5 Series – Tourist Bus LH10.5	Meritor C DUCO	04/02 >>		MDP5053		
Temsa						
						
Avenue – 17.5” wheels	Wabco Pan 17	01/06 >>			MAX088K	MDP3088 / MDP3088K
Diamond	Meritor D3	01/03 >>			MAX030K	MDP3030K
	Meritor ELSA 1 / D3	01/03 >>			MDP5065SK	
Timoney						
						
Teledyne / Fire Engines – P23	Meritor D2	08/92 >>				MDP3043K
Trenkamp & Gehle (Inc Gigant, SAE, SMB, Dupillier)						
						
Gigant - DH7, DKH2, DNH7, DNKH2, DOKH2	Haldex Modul T - DBT19LT	01/10 >>				MDP3429K
Gigant - GKH2, GKPS, GNH7	Haldex Modul T - DBT19LT	01/10 >>				MDP3429K
with Haldex brakes	Haldex Modul X - DB22LT	01/10 >>			MAX175K	
	Haldex Modul X	01/10 >>				MDP3175K
	Haldex Modul X - DB19	01/99 >>				MDP3181K
	Haldex Modul X - DB22	01/99 >>				MDP3143K
with Knorr brakes	Knorr SB5 / SN5	01/99 >>			MAX148K	MDP3148K
	Knorr SB6 / SN6	01/99 >>			MAX095K	MDP3095K
	Knorr SB7 / SN7	01/99 >>			MAX087K	MDP3087K / MDP3087KP
with Wabco brakes	Wabco Pan 19-2					MDP3141
	Wabco Pan 22-1	01/04 >>			MAX162K	MDP3162 / MDP3162K
	Wabco Maxx 22T	01/04 >>			MAX162K	MDP3162 / MDP3162K
	Wabco Pan 19-1	01/99 >>			MAX126K	MDP3126 / MDP3126K
TVM						
						
Marbus B3 090 – 19.5” wheels	Knorr SB6 / SN6	01/01 >>			MAX095K	MDP3095K
Marbus B4 080 – 17.5” wheels	Wabco Pan 17	01/01 >>			MAX088K	MDP3088 / MDP3088K
UD Truck & Bus (Inc Nissan Diesel)						
						
Quon – CD, CK, CW, GK, GW, HP series	Meritor ELSA 225-3	01/07 >>			MAX174K	MDP3174K / MDP3174KWI

- Refer to Buyers Guide



1



2



3



4



5



							
					GENUINE	PREMIUM	ALLFIT
Valx							
							
22.5" wheels	Wabco Pan 22-1	01/11 >>			MAX162K	MDP3162 / MDP3162K	
	Wabco Maxx 22T	01/11 >>			MAX162K	MDP3162 / MDP3162K	
Van Hool							
							
913CL	Meritor ELSA 2	07/04 >>		MDP5060			
	Meritor ELSA 2	07/04 >>		MDP5111			
915CL	Meritor ELSA 2	07/04 >>		MDP5060			
	Meritor ELSA 2	07/04 >>		MDP5111			
915TL	Meritor ELSA 2	07/04 >>		MDP5060			
	Meritor ELSA 2	07/04 >>		MDP5111			
A Series – A 420, A 440	Knorr K85	01/79 >>				MDP3747	
A Series – A 600	Knorr SB7 / SN7	01/96 >>			MAX087K	MDP3087K / MDP3087KP	
A300	Meritor ELSA 2	04/04 >>		MDP5097			
A300CNG	Meritor ELSA 2	04/04 >>		MDP5097			
A300T	Meritor ELSA 2	04/04 >>		MDP5097			
A308	Meritor ELSA 2	04/04 >>		MDP5097			
A320	Meritor ELSA 2	04/04 >>		MDP5097			
	Meritor ELSA 1	03 >>		MDP5065			
A320CNG	Meritor ELSA 2	04/04 >>		MDP5097			
A330	Meritor ELSA 2	04/04 >>		MDP5097			
A330CNG	Meritor ELSA 2	04/04 >>		MDP5097			
A360	Meritor ELSA 2	04/04 >>		MDP5097			
A600	Meritor ELSA 2	04/04 >>		MDP5097			
AG300	Meritor ELSA 2	04/04 >>		MDP5097			
AG300CNG	Meritor ELSA 2	04/04 >>		MDP5097			
AG300T	Meritor ELSA 2	04/04 >>		MDP5097			
AG500	Meritor ELSA 2	04/04 >>		MDP5097			
AGG300	Meritor ELSA 2	04/04 >>		MDP5097			
AGG300 – Trailer 1	Meritor ELSA 2	04/04 >>		MDP5097			
AGG300 – Trailer 2	Meritor ELSA 2	04/04 >>		MDP5097			
Alicron – MAN Chassis	Meritor ELSA 1			MDP5038			
Alizee	Knorr SB7 / SN7	06/96 >>		MDP9005	MAX087K	MDP3087K / MDP3087KP	
	Meritor D LISA	06/96 >>		MDP5061			

- Refer to Buyers Guide



					GENUINE	PREMIUM	ALLFIT
...Van Hool							
Astrobel	Meritor D DUCO	01/00 >>			MAX125K / MDP5057SK	MDP3125K	
	Meritor ELSA 225-3	01/06 >>			MAX174K	MDP3174K / MDP3174KW	
	Knorr SB7 / SN7	01/85 >>			MAX087K	MDP3087K / MDP3087KP	
Astron – T917	Meritor ELSA 1			MDP5038			
Eos – 80 --> 223	Knorr K85	01/95 >>				MDP3747	
	Knorr SB7 / SN7	01/95 >>		MDP9005	MAX087K	MDP3087K / MDP3087KP	
Low Floor Buses – A, AG, AGG	Meritor ELSA 1 / D3	01/97 >>			MDP5065SK		
	Meritor D3	01/97 >>			MAX030K	MDP3030K	
Renault chassis	Meritor ELSA 1 / D3	01/97 >>			MDP5065SK		
	Meritor D3	01/97 >>			MAX030K	MDP3030K	
T Series – T8, T9	Meritor ELSA 1 / D3	01/92 >>			MDP5065SK		
	Knorr SB7 / SN7	01/03 >>			MAX087K	MDP3087K / MDP3087KP	
	Meritor ELSA 225-3	01/06 >>			MAX174K	MDP3174K / MDP3174KWI	
	Meritor D3	01/92 >> 01/96			MAX030K	MDP3030K	
	Knorr SB7 / SN7	01/96 >>			MAX087K	MDP3087K / MDP3087KP	
	Meritor D DUCO	10/95 >>			MAX125K / MDP5057SK	MDP3125K	
T911 Alicron	Meritor ELSA 2	07/04 >>		MDP5060			
	Meritor ELSA 2	07/04 >>		MDP5111			
T915	Meritor ELSA 1			MDP5038			
T915 Acron	Meritor ELSA 2	07/04 >>		MDP5060			
	Meritor ELSA 2	07/04 >>		MDP5111			
T915 Alicron	Meritor ELSA 2	07/04 >>		MDP5060			
	Meritor ELSA 2	07/04 >>		MDP5111			
T916 Altano	Meritor ELSA 2	07/04 >>		MDP5060			
T916 Altano – Centre (Drive Axle)	Meritor ELSA 2	07/04 >>		MDP5111			
T917	Meritor ELSA 1			MDP5038			
T917 Acron	Meritor ELSA 2	07/04 >>		MDP5060			
T917 Acron – Centre (Drive Axle)	Meritor ELSA 2	07/04 >>		MDP5111			
T917 Altano	Meritor ELSA 2	07/04 >>		MDP5060			
T917 Altano – Centre (Drive Axle)	Meritor ELSA 2	07/04 >>		MDP5111			
T917 Astron	Meritor ELSA 2	07/04 >>		MDP5060			
T917 Astron – Centre (Drive Axle)	Meritor ELSA 2	07/04 >>		MDP5111			
T918	Meritor ELSA 1			MDP5038			

- Refer to Buyers Guide



1



2



3



4



5



							
					GENUINE	PREMIUM	ALLFIT
...Van Hool							
							
T918 Altano	Meritor ELSA 2	07/04 >>		MDP5060			
T918 Altano – Centre (Drive Axle)	Meritor ELSA 2	07/04 >>		MDP5111			
T924 Astromega DD	Meritor ELSA 2	07/04 >>		MDP5060			
T924 Astromega DD – Centre (Drive Axle)	Meritor ELSA 2	07/04 >>		MDP5111			
T927 Astromega DD	Meritor ELSA 2	07/04 >>		MDP5060			
T927 Astromega DD – Centre (Drive Axle)	Meritor ELSA 2	07/04 >>		MDP5111			
UL Series	Meritor ELSA 1 / D3	01/91 >>			MDP5065SK		
	Meritor D3	01/91 >>			MAX030K	MDP3030K	
VDL (Inc Bova, Jonckheere)							
							
Axial – DD 138 --> 430	Knorr SB7 / SN7	01/92 >>		MDP9005	MAX087K	MDP3087K / MDP3087KP	
Citea	Knorr SB5 / SN5	10/04 >>			MAX148K	MDP3148K	
	B Frame (2x60)	01/10 >>				MDP3122	
	Knorr SB6 / SN6	01/10 >>			MAX095K	MDP3095K	
Divo GT	Knorr SB7 / SN7	01/07 >>			MAX087K	MDP3087K / MDP3087KP	
Futura – FHD, FHM, FVD	Knorr K85	01/82 >> 06/95				MDP3747	
Futura – FHD, FHX, FLD	Knorr SB7 / SN7	06/95 >>			MAX087K	MDP3087K / MDP3087KP	
Futura – FHD, FLD, FVD	Knorr SB7 / SN7	01/03 >>		MDP9005	MAX087K	MDP3087K / MDP3087KP	
	Knorr SB6 / SN6	01/95 >>			MAX095K	MDP3095K	
Lexio – LD123, LD130, LLD123, LLD130	Knorr SB7 / SN7	09/05 >>			MAX087K	MDP3087K / MDP3087KP	
Magiq – HD, MHD, Magnum 120 --> 380 XE	Knorr SB7 / SN7	01/96 >>		MDP9005	MAX087K	MDP3087K / MDP3087KP	
SB200	Knorr SB6 / SN6	01/02 >>			MAX095K	MDP3095K	
Synergy – DD, SDD 130 --> 430 E	Knorr SB7 / SN7	09/05 >>			MAX087K	MDP3087K / MDP3087KP	
Volvo							
							
FE Series	Meritor ELSA 225-3	05/06 >>		MDP5104 / MDP5119	MDP5101SK / MDP5104SK / MDP5101PPRK / MDP5104PPRK / MAX174K	MDP3174K / MDP3174KWI	
	Meritor ELSA 195	05/06 >>			MDP5093SK	MDP3169K	
FE II Series	Meritor ELSA 225-1	05/12 >>		MDP5106	MDP5102SK / MDP5106SK / MDP5106PPRK / MAX173K	MDP3173K	
	Meritor ELSA 225-3	05/12 >>			MDP5101SK / MDP5104SK / MDP5101PPRK / MDP5104PPRK / MAX174K	MDP3174K / MDP3174KWI	
	Meritor ELSA 195	05/12 >>			MDP5093SK	MDP3169K	

- Refer to Buyers Guide



- Refer to Buyers Guide

1



2



3



4



5





1



2



3



4



5



							
					GENUINE	PREMIUM	ALLFIT
...Volvo							
							
FLC Series – 5, 7, 8	B Frame (2x60)	01/96 >> 01/00					MDP3122
FLH, FLL, FLM Series – 160 --> 290 Series	Meritor ELSA 225-1	05/13 >>		MDP5106	MDP5102SK / MDP5106SK / MDP5106PPRK / MAX173K		MDP3173K
FM 7, FM 10 Series – 240-->380 Series	Meritor D DUCO	01/96 >>		MDP5057	MAX125K / MDP5057SK		MDP3125K
FM 9, FM 12 Series	Meritor D DUCO	01/96 >>		MDP5057	MAX125K / MDP5057SK		MDP3125K
FM Series	Meritor ELSA 225-3	01/05 >>			MDP5101SK / MDP5104SK / MDP5101PPRK / MDP5104PPRK / MAX174K		MDP3174K / MDP3174KWI
	Meritor ELSA 195	01/05 >>			MDP5093SK		MDP3169K
FM Series II	Meritor ELSA 225-3	01/12 >>			MDP5101SK / MDP5104SK / MDP5101PPRK / MDP5104PPRK / MAX174K		MDP3174K / MDP3174KWI
	Meritor ELSA 195	01/12 >>			MDP5093SK		MDP3169K
FM Series III	Meritor ELSA 225-3	01/20 >>			MDP5101SK / MDP5104SK / MDP5101PPRK / MDP5104PPRK / MAX174K		MDP3174K / MDP3174KWI
	Meritor ELSA 195	01/20 >>			MDP5093SK		MDP3169K
FMX Series	Meritor ELSA 225-3	04/10 >>			MDP5101SK / MDP5104SK / MDP5101PPRK / MDP5104PPRK / MAX174K		MDP3174K / MDP3174KWI
FMX Series – 330-->540	Meritor D DUCO	04/10 >>		MDP5057	MAX125K / MDP5057SK		MDP3125K
	Meritor DUCO Le	04/10 >>		MDP5072			
	Meritor ELSA 195	04/10 >>		MDP5093	MDP5093SK		MDP3169K
FMX Series II	Meritor ELSA 225-3	01/12 >>			MDP5101SK / MDP5104SK / MDP5101PPRK / MDP5104PPRK / MAX174K		MDP3174K / MDP3174KWI
	Meritor ELSA 195	01/12 >>			MDP5093SK		MDP3169K
FMX Series III	Meritor ELSA 225-3	01/20 >>			MDP5101SK / MDP5104SK / MDP5101PPRK / MDP5104PPRK / MAX174K		MDP3174K / MDP3174KWI
	Meritor ELSA 195	01/20 >>			MDP5093SK		MDP3169K
FS Series – FS7	B Frame (2x60)	10/91 >>					MDP3122
Volvo PSV							
							
7500, 7700	Meritor D DUCO	01/01 >>			MAX125K / MDP5057SK		MDP3125K
	Meritor ELSA 225-3	01/01 >>			MDP5119SK / MDP5119PPRK / MAX174K		
8500, 8700	Meritor D DUCO	01/99 >>			MAX125K / MDP5057SK		MDP3125K
	Meritor ELSA 225-3	01/99 >>			MDP5119SK / MDP5119PPRK / MAX174K		
9500, 9700, 9900	Meritor D DUCO	01/01 >>			MAX125K / MDP5057SK		MDP3125K
	Meritor ELSA 225-3	01/01 >>			MDP5119SK / MDP5119PPRK / MAX174K		
B5, B5L, B5LH, B5R, B5RH, B5TL	Meritor ELSA 225-3	11/08 >>			MDP5119SK / MDP5119PPRK / MAX174K		MDP3174K / MDP3174KWI

 - Refer to Buyers Guide



- Refer to Buyers Guide



1



2



3



4



5



--	--	--	--	--	--	--

- Refer to Buyers Guide



						
				GENUINE	PREMIUM	ALLFIT
...Zhongtong						
						
Lilhe	Knorr SB7 / SN7	01/16 >>			MAX087K	MDP3087K / MDP3087KP
Liven	Knorr SB7 / SN7	01/16 >>			MAX087K	MDP3087K / MDP3087KP
Magnate	Knorr SB7 / SN7	01/13 >>			MAX087K	MDP3087K / MDP3087KP
Navigator	Knorr SB7 / SN7	06/09 >>			MAX087K	MDP3087K / MDP3087KP
Sparkling	Knorr SB7 / SN7	05/09 >>			MAX087K	MDP3087K / MDP3087KP
Spring	Knorr SB7 / SN7	01/13 >>			MAX087K	MDP3087K / MDP3087KP

1



2



3



4



5



 - Refer to Buyers Guide



1



2




3





4



5





1



2



3



4




5



**GENUINE****MDP5005**


Renault




176.0 mm

78.0 mm

22.0 mm

VVA
29067**KIT CONTENTS:****KIT** MBA107**PWWI** MBA009**PWWI:** Included x 2**MDP5020**


Iveco



176.0 mm

77.0 mm

22.0 mm

VVA
29067**KIT CONTENTS:****KIT** MBA107**PWWI** MBA001**PWWI:** Included x 2**MDP5033**Ikarus
Setra
Mercedes


250.0 mm

118.0 mm

28.0 mm

VVA
29030**KIT CONTENTS:****KIT** MBA108**PWWI** MBA010**PWWI:** Included x 2**MDP5037**


Renault



204.0 mm

96.0 mm

24.0 mm

VVA
29100**KIT CONTENTS:****PWWI:** Included x 2**MDP5038**ERF
MAN
Van Hool


250.0 mm

118.0 mm

28.0 mm

VVA
29113**KIT CONTENTS:****KIT** MBA108**PWWI** MBA018
MCK1070**PWWI:** Prepared for**MDP5039**


MAN



250.0 mm

118.0 mm

30.0 mm

VVA
29114**KIT CONTENTS:****PWWI:** Prepared for**MDP5040**Alexander
Neoplan
Mercedes
Optare
Sitcar


175.0 mm

85.0 mm

22.0 mm

VVA
29835**KIT CONTENTS:****KIT** MBA106**PWWI** MBA007**PWWI:** Prepared for**MDP5042**


Renault





250.0 mm



114.0 mm



28.0 mm



VVA
29090**KIT CONTENTS:****KIT** MBA101**PWWI** MBA015**PWWI:** Included x 2**7.2**



**GENUINE**



MDP5051		
Renault		 250.0 mm  118.0 mm  28.0 mm  Meritor D3
VVA 29113	KIT CONTENTS:  x 4  x 6  x 2  x 2	KIT MBA108 PWWI MBA013 PWWI: Included x 2



MDP5052		
Volvo		 176.0 mm  89.0 mm  29.0 mm  Meritor B DUCO
VVA 29136	KIT CONTENTS:  x 4  x 4  x 2	KIT MBA102 PWWI: None



MDP5053		
SOR Volvo		 210.0 mm  102.0 mm  30.0 mm  Meritor C DUCO
VVA 29137	KIT CONTENTS:  x 4  x 4  x 2	KIT MBA103 PWWI: None


MDP5054		
MAN		 250.0 mm  118.0 mm  28.0 mm  Meritor D3
VVA 29113	KIT CONTENTS:  x 4  x 6  x 1	KIT MBA108 PWWI: Prepared for

MDP5056		
Iveco Renault		 250.0 mm  118.0 mm  30.0 mm  Meritor ELSA 2
VVA 29131	KIT CONTENTS:  x 4  x 4  x 2	KIT MBA105 PWWI MBA016 PWWI: Included x 2

MDP5057		
Caetano ROR SAF Sauer Volvo		 250.0 mm  110.0 mm  30.0 mm  Meritor D DUCO
VVA 29125	KIT CONTENTS:  x 4  x 4  x 2	KIT MBA104 PWWI: None

MDP5059		
ERF		 250.0 mm  118.0 mm  30.0 mm  Meritor ELSA 2
VVA 29131	KIT CONTENTS:  x 4  x 4  x 2	KIT MBA105 PWWI: Prepared for

MDP5060		
MAN Van Hool		 250.0 mm  118.0 mm  30.0 mm  Meritor ELSA 2
VVA 29131	KIT CONTENTS:  x 4  x 4  x 2	KIT MBA105 PWWI MCK1141 PWWI: Prepared for


**GENUINE****MDP5061**Caetano
Dennis
Van Hool
Volvo

250.0 mm

114.0 mm

28.0 mm


Meritor
D LISA

WVA
29090**KIT CONTENTS:**

KIT MBA101

PWWI MBA015

PWWI: Prepared for

MDP5065MAN
Plaxton
Van Hool

250.0 mm

118.0 mm

28.0 mm

Meritor
ELSA 1

WVA
29113**KIT CONTENTS:**


KIT MBA108

PWWI MBA018
MBA019

PWWI: Prepared for

MDP5066

MAN



250.0 mm

118.0 mm

30.0 mm


Meritor
ELSA 1

WVA
29114**KIT CONTENTS:**

PWWI: Prepared for

MDP5071

Dennis




250.0 mm

114.0 mm

28.0 mm

Meritor
D LISA

WVA
29090**KIT CONTENTS:**


KIT MBA101

PWWI MBA015

PWWI: Included x 2

MDP5072

Volvo



215.0 mm

97.0 mm

29.0 mm


Meritor
DUCO LE

WVA
29151**KIT CONTENTS:**

PWWI: None

MDP5073

ROR



250.0 mm

118.0 mm

30.0 mm


Meritor
ELSA 2

WVA
29131**KIT CONTENTS:****KIT** MBA105

PWWI: Prepared for

MDP5076

ROR




205.0 mm

102.0 mm

27.0 mm


Meritor
DX 195

WVA
29155**KIT CONTENTS:****KIT** MBA100

PWWI: Prepared for

MDP5079

Iveco




205.0 mm

97.5 mm



27.0 mm



Meritor
DXP 195


KIT CONTENTS:



PWWI: Prepared for


**GENUINE**



MDP5083		
Iveco		 249.0 mm  118.0 mm  30.0 mm  Meritor DX 225
WVA 29150	KIT CONTENTS:  x 4  x 4	PWWI MBA010
PWWI: Prepared for		



MDP5083K		
Iveco		 249.0 mm  118.0 mm  30.0 mm  Meritor DX 225
WVA 29150	KIT CONTENTS:  x 4  x 4  x 4  x 2  x 2	PWWI: Included x 2



MDP5088		
MAN Mercedes		 250.0 mm  118.0 mm  28.0 mm  Meritor D3
WVA 29113	KIT CONTENTS:  x 4  x 4	PWWI: Prepared for

MDP5090		
Renault		 250.0 mm  118.0 mm  28.0 mm  Meritor D3
WVA 29113	KIT CONTENTS:  x 4  x 4  x 2	KIT MBA108 PWWI MBA017
PWWI: Included x 2		

MDP5093		
ROR Volvo		 210.0 mm  101.0 mm  30.0 mm  Meritor ELSA 195
WVA 29169	KIT CONTENTS:  x 4  x 4  x 2	KIT MBA112 PWWI: Prepared for


MDP5097		
MAN Van Hool		 250.0 mm  118.0 mm  30.0 mm  Meritor ELSA 2
WVA 29131	KIT CONTENTS:  x 4  x 4  x 2	KIT MBA105 PWWI MCK1141
PWWI: Prepared for		

MDP5099		
MAN		 250.0 mm  118.0 mm  30.0 mm  Meritor ELSA 2
WVA 29131	KIT CONTENTS:  x 4  x 4	PWWI: Prepared for

MDP5101		
Renault		 250.0 mm  110.0 mm  29.0 mm  Meritor ELSA 225-3
WVA 29174	KIT CONTENTS:  x 4  x 4  x 2	PWWI: Included x 2

**GENUINE****MDP5102**


Renault



216.0 mm

97.0 mm


29.0 mm

 Meritor
ELSA 225-1WVA
29173**KIT CONTENTS:**

PWVI: Included x 2

MDP5104


Volvo




250.0 mm

110.0 mm

29.0 mm

 Meritor
ELSA 225-3WVA
29174**KIT CONTENTS:**


PWVI: Prepared for

MDP5106Renault
Volvo

216.0 mm

100.0 mm


29.0 mm

 Meritor
ELSA 225-1WVA
29173**KIT CONTENTS:**

PWVI: Prepared for

MDP5110

Various



250.0 mm

118.0 mm


29.0 mm

 Meritor
ELSA 1WVA
29030**KIT CONTENTS:**

PWVI: Prepared for

MDP5111

Van Hool




250.0 mm

118.0 mm

30.0 mm

 Meritor
ELSA 2WVA
29131**KIT CONTENTS:****KIT** MBA105**PWVI** MCK1141


PWVI: Included x 2

MDP5115Renault
Volvo

250.0 mm

118.0 mm


30.0 mm

 Meritor
ELSA 2WVA
29131**KIT CONTENTS:**

PWVI: Included x 2

MDP5116


Irisbus



250.0 mm

118.0 mm


30.0 mm

 Meritor
ELSA 2WVA
29131**KIT CONTENTS:**

PWVI: Included x 2

MDP5117


ROR



216.0 mm

113.0 mm


29.0 mm


 Meritor
ELSA 225LWVA
29211**KIT CONTENTS:**


PWVI: Prepared for





**GENUINE**


MDP5118K		
ROR		 216.0 mm  113.0 mm  29.0 mm  Meritor ELSA 225-2
WVA 29211	KIT CONTENTS:  x 4  x 2  x 4  x 2	
PWWI: Prepared for		


MDP5119		
Volvo		 250.0 mm  110.0 mm  29.0 mm  Meritor ELSA 225-3
WVA 29218	KIT CONTENTS:  x 4  x 4  x 2	
PWWI: Prepared for		


MDP5121		
MAN		 250.0 mm  118.0 mm  30.0 mm  Meritor ELSA 2
WVA 29131	KIT CONTENTS:  x 4  x 4  x 2	
PWWI: Included x 2		

MDP5122		
Optare		 250.0 mm  114.0 mm  29.0 mm  Meritor EX225H2
WVA 29187	KIT CONTENTS:  x 4  x 4  x 2	
PWWI: Prepared for		

MDP5124		
Iribus		 250.0 mm  118.0 mm  30.0 mm  Meritor ELSA 2
WVA 29131	KIT CONTENTS:  x 4  x 2  x 4  x 2	
PWWI: Included x 2		

MDP5126		
ZF		 210.5 mm  100.0 mm  29.0 mm  Meritor ELSA 195
WVA 29177	KIT CONTENTS:  x 4	
PWWI: Prepared for		

MDP5127		
Base		 249.5 mm  107.0 mm  29.0 mm  Meritor ELSA 225
WVA 29334	KIT CONTENTS:  x 4  x 4  x 2	
PWWI: Prepared for		


MDP5128		
Alstom		 250.0 mm  110.0 mm  29.0 mm  Meritor EX225H2
	KIT CONTENTS:  x 4  x 4  x 2	
PWWI: Prepared for		



GENUINE

MDP5131

Iveco



250.0 mm

118.0 mm

30.0 mm


Meritor
ELSA 2

WVA
29131

KIT CONTENTS:



x 4



x 4




x 2

PWWI: Prepared for

MDP5132

Iveco



250.0 mm

118.0 mm

30.0 mm


Meritor
ELSA 2

WVA
29131

KIT CONTENTS:



x 4



x 4



x 2




x 2

PWWI: Included x 2

MDP9000

DAF
Foden
Iveco
MAN
Mercedes
Scania



248.0 mm

108.0 mm

30.0 mm


Knorr
SB7 / SN7

WVA
29061
29087
29179

KIT CONTENTS:



x 4



x 4



x 2



x 2



x 2



x 2




x 1

PWWI: Prepared for

KIT
MBA110
MBA120

MDP9005

DAF
Mercedes
Scania
+



248.0 mm

108.0 mm

30.0 mm


Knorr
SB7 / SN7

WVA
29061
29087

KIT CONTENTS:



x 4



x 4



x 2



x 2



x 2



x 2



x 1


PWWI: Prepared for

KIT
MBA110
MBA120



7.2



**PREMIUM****MDP5042SK**Iveco
Renault
Volvo
+

250.0 mm

114.0 mm

28.0 mm

**VVA**
29090**KIT CONTENTS:**

x 4




x 4



x 8



x 8

PWWI MBA015**PWWI:** Included x 2**MDP5056SK**Iveco
MAN
Renault
Volvo
+

250.0 mm

118.0 mm

30.0 mm

**VVA**
29131
29156**KIT CONTENTS:**


x 4



x 4



x 2

PWWI MBA016**PWWI:** Included x 2**MDP5057SK**Caetano
Plaxton
ROR
SAF
Sauer
Van Hool
Volvo
Wrightbus

250.0 mm

110.0 mm

30.0 mm

**VVA**
29125
29277**KIT CONTENTS:**


x 4



x 4



x 2

PWWI: None**MDP5065SK**Iveco
MAN
Mercedes
Renault
Scania
+

250.0 mm

118.0 mm

28.0 mm

**VVA**
29030
29083
29113**KIT CONTENTS:**


x 4



x 4



x 2

KIT MBA108**PWWI** MBA018
MBA019**PWWI:** Prepared for**MDP5073SK**Iveco
MAN
Renault
Volvo
+

250.0 mm

118.0 mm

30.0 mm

**VVA**
29131
29156**KIT CONTENTS:**


x 4



x 4



x 2

PWWI: Prepared for**MDP5076SK**Fruehauf
SAF
Sauer

205.0 mm

102.0 mm

27.0 mm

**VVA**
29124
29155**KIT CONTENTS:**

x 4




x 4



x 2



x 2

PWWI: Prepared for**MDP5083SK**Iveco
SAF
+

249.0 mm

118.0 mm

30.0 mm

**VVA**
29150**KIT CONTENTS:**

x 4



x 4




x 4



x 2



x 2

PWWI: Included x 2**MDP5093SK**Fruehauf
Renault
ROR
SAF
Sauer
Volvo

210.0 mm

101.0 mm

30.0 mm

**VVA**
29169
29177**KIT CONTENTS:**

x 4



x 4



x 2

PWWI: Prepared for

**PREMIUM**

1



2




3



4



5

**MDP5101SK**Renault
Volvo
+


250.0 mm

110.0 mm

29.0 mm

WVA
29174
29218
29273**KIT CONTENTS:**

x 4




x 4



x 2

PWVI: Included x 2

MDP5102SKRenault
Volvo


216.0 mm

97.0 mm

29.0 mm

WVA
29131
29156**KIT CONTENTS:**

x 4




x 4



x 2

PWVI: Included x 2

MDP5104SKRenault
Volvo
+


250.0 mm

110.0 mm

29.0 mm

WVA
29174
29218
29273**KIT CONTENTS:**

x 4




x 4



x 2

PWVI: Prepared for

MDP5106SKRenault
Volvo


216.0 mm

100.0 mm

29.0 mm

WVA
29173
29203**KIT CONTENTS:**

x 4




x 4



x 2

PWVI: Prepared for

MDP5117SKKögel
Trax


216.0 mm

113.0 mm

29.0 mm

WVA
29211**KIT CONTENTS:**

x 4




x 4



x 2

PWVI: Prepared for

MDP5119SKRenault
Volvo
+


250.0 mm

110.0 mm

29.0 mm

WVA
29174**KIT CONTENTS:**

x 4



x 4




x 2

PWVI: Prepared for

MDP5332SK

Scania




249.6 mm

111.0 mm

29.0 mm

WVA
29332**KIT CONTENTS:**

x 4



x 4



x 2

PWVI: None



7.2






PREMIUM



MDP5101PPRK

Renault
Volvo



250.0 mm

110.0 mm

29.0 mm


Meritor
ELSA 225-3

WVA
29174
29218
29273

KIT CONTENTS:



x 4



x 2



x 2



x 4




x 2

PWWI: Included x 2

PWWI MBA065
MBA066

MDP5104PPRK

Renault
Volvo



250.0 mm

110.0 mm

29.0 mm

Meritor
ELSA 225-3

WVA
29174
29218
29273


KIT CONTENTS:



x 4



x 2



x 2



x 4




x 2

PWWI: Prepared for

MDP5106PPRK

Renault
Volvo



216.0 mm

100.0 mm

29.0 mm


Meritor
ELSA 225-1

WVA
29173
29203

KIT CONTENTS:



x 4



x 2



x 2



x 4




x 2

PWWI: Prepared for

MDP5119PPRK

Volvo



250.0 mm

110.0 mm

29.0 mm


Meritor
ELSA 225-3

WVA
29174
29218
29273

KIT CONTENTS:



x 4



x 2



x 2




















x 4



x 2

PWWI: Prepared for

**PREMIUM****MAX030K**Iveco
MAN
Mercedes
Renault
+
 249.0 mm
 118.0 mm
 27.8 mm
 Meritor
D3
VVA
29030
29083
29113**KIT CONTENTS:**
KIT MBA108
PWWI
MBA007 MBA010
MBA011 MBA013
MBA017 MBA018
MBA019 MCK1070
PWWI: Prepared for**MAX087K**DAF
Iveco
MAN
Renault
Volvo
+
 247.0 mm
 109.3 mm
 30.0 mm
 Knorr
SB7 / SN7
VVA
29042 29059 29087
29106 29108 29109
29163 29179 29202
29253 29331**KIT CONTENTS:**
KIT MBA110
MBA120
PWWI: Prepared for**MAX088K**DAF
Iveco
MAN
Renault
Volvo
+
 175.5 mm
 85.8 mm
 25.6 mm
 Wabco
Pan 17
VVA
29088**KIT CONTENTS:****PWWI:** Prepared for**MAX090K**Iveco
Renault
Volvo
+
 248.8 mm
 114.3 mm
 27.8 mm
 Meritor
D LISA
VVA
29090**KIT CONTENTS:**
KIT MBA101
PWWI MBA015
PWWI: Prepared for**MAX095K**DAF
Iveco
MAN
Mercedes
+
 210.5 mm
 92.3 mm
 29.8 mm
 Knorr
SB6 / SN6
VVA
29094
29095
29197**KIT CONTENTS:**
KIT MBA110
MBA121
PWWI: Prepared for**MAX125K**Caetano
Plaxton
ROR
SAF
Sauer
Van Hool
Volvo
Wrightbus
 249.0 mm
 111.0 mm
 29.2 mm
 Meritor
D DUCCO
VVA
29125
29277**KIT CONTENTS:**
KIT MBA104
PWWI: None**MAX126K**DAF
Mercedes
Renault
SAF
+
 210.0 mm
 92.0 mm
 30.0 mm
 Wabco
Pan 19-1
VVA
29126
29159**KIT CONTENTS:****PWWI:** Prepared for**MAX131K**Iveco
MAN
Renault
Volvo
+
 249.6 mm
 118.0 mm
 30.2 mm
 Meritor
ELSA 2
VVA
29131**KIT CONTENTS:**
KIT MBA105
PWWI MBA016
MCK1141
PWWI: Prepared for


**PREMIUM****MAX148K**MAN,
Mercedes
Renault
+

173.5 mm⁽¹⁾
185.0 mm⁽²⁾


83.8 mm⁽¹⁾
86.0 mm⁽²⁾

26.8 mm⁽¹⁾
33.5 mm⁽²⁾

Knorr
SB5 / SN5

VVA
29115
29116
29148
29183**KIT CONTENTS:**

PWWI: None


MAX162KFruehauf
SAF
Sauer
Schmitz,
Valx
Trenkamp & Gehle
York Trailers

210.0 mm

109.2 mm

30.0 mm


Wabco
Pan 22-1 /
Maxx 22T

VVA
29162**KIT CONTENTS:**

PWWI: Prepared for

MAX165K

BPW




210.5 mm

92.3 mm

29.8 mm


Knorr
SB6 / SN6

VVA
29165
29306**KIT CONTENTS:**

PWWI: Prepared for

MAX167K

BPW




247.0 mm

109.3 mm

30.0 mm


Knorr
SB7 / SN7

VVA
29167
29307**KIT CONTENTS:**

PWWI: Prepared for

MAX171K

BPW




210.0 mm


107.8 mm

29.8 mm

Knorr
SK7

VVA
29158
29171
29308**KIT CONTENTS:**

PWWI: Prepared for


MAX173KRenault
ROR
Volvo

215.8 mm


99.6 mm

29.0 mm

Meritor
ELSA 225-1

VVA
29173
29203**KIT CONTENTS:**

PWWI: Prepared for


MAX174KRenault
Volvo
+

249.5 mm

109.7 mm


29.0 mm

Meritor
ELSA 225-3

VVA
29174
29218
29273**KIT CONTENTS:**

PWWI: Prepared for

PWWI: MBA034

MAX175KJost
Kögel
Trax
Krone
SAF
Sauer
Trenkamp & Gehle

210.4 mm

94.0 mm

30.0 mm

Haldex
Modul X -
DB22LT

VVA
29175**KIT CONTENTS:**

PWWI: Prepared for



PREMIUM

1



2



3



4




5



MAX244K

Mercedes



207.6 mm


113.7 mm

35.0 mm

Knorr
SL7

WVA
29244


KIT CONTENTS:



PWWI: None

MAX246K

Mercedes



244.6 mm


113.7 mm

35.0 mm

Knorr
SM7

WVA
29246

KIT CONTENTS:





PWWI: None





ALLFIT





MDP3011K		
Iveco		 241.0 mm  125.3 mm  25.0 mm  Bendix ADB4300
VVA 29011	KIT CONTENTS:  x 4  x 4  x 4	
	PWWI: Prepared for	


MDP3013		
Dennis Renault		 180.0 mm  86.3 mm  20.2 mm  Bendix SEE 2X67
VVA 29013 29014	KIT CONTENTS:  x 4	
	PWWI: Included x 4	


MDP3017		
Daewoo Trucks DAF Iveco		 191.0 mm  86.7 mm  23.0 mm  Wabco 456 F-Ö
VVA 29017	KIT CONTENTS:  x 4	
	PWWI: None	

MDP3024		
Daewoo Trucks DAF Iveco		 191.0 mm  86.7 mm  23.0 mm  Wabco 456 F-Ö
VVA 29024	KIT CONTENTS:  x 4	
	PWWI: Included x 2	

MDP3030K		
Iveco MAN Mercedes Renault +		 249.0 mm  118.0 mm  27.8 mm  Meritor D3
VVA 29030 29083 29113	KIT CONTENTS:  x 4  x 6  x 2	KIT MBA108 PWWI MBA007 MBA010 MBA011 MBA013 MBA017 MBA018 MBA019 MCK1070
	PWWI: Prepared for	

MDP3032K		
Iveco		 206.0 mm  110.2 mm  25.0 mm  Bendix ADB3700
VVA 29032	KIT CONTENTS:  x 4  x 4  x 4	
	PWWI: Prepared for	

MDP3043K		
Berkhof Caetano Dennis Neoplan Renault Timoney		 204.0 mm  97.0 mm  24.0 mm  Meritor D2
VVA 29043	KIT CONTENTS:  x 4	KIT MBA109 PWWI MBA006 MBA014
	PWWI: None	

MDP3077		
DAF Neoplan		 204.2 mm  106.0 mm  26.8 mm  Wabco 1600 V-G
VVA 29077	KIT CONTENTS:  x 4	
	PWWI: Included x 2	



ALLFIT

1



2



3




4



5



MDP3087K

DAF
Iveco
MAN
Mercedes
Renault
Scania
+

247.0 mm


109.3 mm

30.0 mm

Knorr
SB7 / SN7


WVA
29042 29059 29087
29106 29108 29109
29163 29179 29202
29253 29331

KIT CONTENTS:

KIT
MBA110
MBA120

PWVI: Prepared for

MDP3087KP

DAF
Iveco
MAN
Mercedes
Renault
Scania
+

247.0 mm


109.3 mm

30.0 mm

Knorr
SB7 / SN7


WVA
29042 29059 29087
29106 29108 29109
29163 29179 29202
29253 29331

KIT CONTENTS:

KIT
MBA120

PWVI: Prepared for

MDP3088

DAF
Iveco
MAN
Renault
Volvo
+

175.5 mm

85.8 mm

25.6 mm

Wabco
Pan 17


WVA
29088

KIT CONTENTS:



PWVI: Prepared for

MDP3088K

DAF
Iveco
MAN
Renault
Volvo
+

175.5 mm


85.8 mm

25.6 mm

Wabco
Pan 17


WVA
29088

KIT CONTENTS:



PWVI: Prepared for

MDP3090K

Iveco
Renault
Volvo
+

248.8 mm


114.3 mm

27.8 mm

Meritor
D LISA


WVA
29090

KIT CONTENTS:

KIT
MBA101
PWVI
MBA015

PWVI: Prepared for

MDP3095K

DAF
Iveco
MAN
Mercedes
+

210.5 mm


92.3 mm

29.8 mm

Knorr
SB6 / SN6


WVA
29095
29197

KIT CONTENTS:

KIT
MBA110
MBA121

PWVI: Prepared for

MDP3122

Iveco
MAN
Renault
Volvo
+

174.7 mm

85.2 mm

22.0 mm

B Frame
(2x60)


WVA
29122

KIT CONTENTS:

KIT
MBA106
MBA107
MBA117
PWVI
MBA001
MBA009

PWVI: Prepared for

MDP3124K

Fruehauf
ROR
SAF
Sauer

205.4 mm


102.1 mm

27.0 mm

Meritor
DX 195

WVA
29124
29155

KIT CONTENTS:

KIT
MBA100



PWVI: Prepared for










ALLFIT







MDP3125K		
Caetano Plaxton ROR SAF Sauer Van Hool Volvo Wrightbus		 249.0 mm  111.0 mm  29.2 mm  Meritor DUCO
VVA 29125 29277	KIT CONTENTS:  x 4  x 4  x 2	KIT MBA104
PWWI: None		


MDP3126		
DAF Mercedes Renault SAF +		 210.0 mm  92.0 mm  30.0 mm  Wabco Pan 19-1
VVA 29126 29159	KIT CONTENTS:  x 4	
PWWI: Prepared for		



MDP3126K		
DAF Mercedes Renault SAF +		 210.0 mm  92.0 mm  30.0 mm  Wabco Pan 19-1
VVA 29126 29159	KIT CONTENTS:  x 4  x 6  x 2  x 2	
PWWI: Prepared for		

MDP3131K		
Iveco MAN Renault Volvo +		 249.5 mm  118.0 mm  30.2 mm  Meritor ELSA 2
VVA 29131	KIT CONTENTS:  x 4  x 4  x 2	KIT MBA105 PWWI MBA016 MCK1141
PWWI: Prepared for		

MDP3136K		
ROR SAF Sauer Volvo		 175.4 mm  88.8 mm  29.7 mm  Meritor B DUCO
VVA 29136	KIT CONTENTS:  x 4  x 4  x 2	KIT MBA102
PWWI: None		

MDP3137K		
ROR SAF Sauer Volvo		 210.0 mm  102.0 mm  29.7 mm  Meritor C DUCO
VVA 29137	KIT CONTENTS:  x 4  x 4  x 2	KIT MBA103
PWWI: None		

MDP3141		
DAF Dennis Fruehauf SAF Sauer Trenkamp & Gehle Volvo		 204.4 mm  99.6 mm  29.8 mm  Wabco Pan 19-2
VVA 29119 29141	KIT CONTENTS:  x 4	
PWWI: Prepared for		

MDP3142		
Renault		 204.4 mm  99.6 mm  29.8 mm  Wabco Pan 19-2
VVA 29142	KIT CONTENTS:  x 4  x 4	
PWWI: Prepared for		



ALLFIT

1



2



3



4




5



MDP3142K

Renault




204.4 mm

99.6 mm

29.8 mm


Wabco
Pan 19-2VVA
29142

KIT CONTENTS:



PWVI: Prepared for

MDP3143K

Discos
Fruehauf
Mercedes
SAF
Sauer
Scania
Trenkamp & Gehle


247.7 mm

105.0 mm

29.5 mm


Haldex
Modul X -
DB22VVA
29120
29143
29185

KIT CONTENTS:




PWVI: Prepared for

MDP3148K

MAN,
Mercedes
Renault
+173.5 mm⁽¹⁾185.0 mm⁽²⁾83.8 mm⁽¹⁾86.0 mm⁽²⁾26.8 mm⁽¹⁾33.5 mm⁽²⁾Knorr
SB5 / SN5VVA
29115
29116
29148
29183


KIT CONTENTS:



PWVI: None

PWVI
MBA110
MBA120

MDP3158K

BPW Axles
Mercedes
SAF
Sauer
Schmitz
ZF


210.0 mm

108.0 mm

30.0 mm


Knorr
SK7VVA
29158

KIT CONTENTS:



PWVI: Prepared for

MDP3162

Fruehauf
SAF
Sauer
Schmitz
Valx
Trenkamp & Gehle
York Trailers

210.0 mm

109.2 mm

30.0 mm


Wabco
Pan 22-1 /
Maxx 22TVVA
29162

KIT CONTENTS:



PWVI: Prepared for

MDP3162K

Fruehauf
SAF
Sauer
Schmitz
Valx
Trenkamp & Gehle
York Trailers


210.0 mm

109.2 mm

30.0 mm

Wabco
Pan 22-1 /
Maxx 22TVVA
29162


KIT CONTENTS:



PWVI: Prepared for

MDP3165K

BPW



210.5 mm

92.3 mm

29.8 mm

Knorr
SB6 / SN6VVA
29165
29306

KIT CONTENTS:




PWVI: Prepared for

KIT
MBA110
MBA121

MDP3167K

BPW



210.5 mm

109.3 mm

30.0 mm

Knorr
SB7 / SN7VVA
29167
29307

KIT CONTENTS:



PWVI: Prepared for


KIT
MBA110
MBA120


(1) = Inboard Pad (2) = Outboard Pad





ALLFIT





MDP3169K		
Fruehauf ROR Renault SAF Sauer Volvo		 211.0 mm  101.3 mm  30.2 mm  Meritor  ELSA 195
VVA 29169 29177	KIT CONTENTS:  x 4  x 4  x 2	KIT MBA112 PWWI: Prepared for


MDP3171K		
BPW		 210.0 mm  107.8 mm  29.8 mm  Knorr  SK7
VVA 29158 29171 29308	KIT CONTENTS:  x 4  x 4  x 2  x 2  x 2  x 2  x 2	KIT MBA110 MBA121 PWWI: Prepared for



MDP3173K		
Renault ROR Volvo		 215.8 mm  99.6 mm  29.0 mm  Meritor  ELSA 225-1
VVA 29173 29203	KIT CONTENTS:  x 4  x 4  x 2  MAX x 2	KIT MBA112 PWWI MBA034 PWWI: Prepared for

MDP3174K		
Renault Volvo +		 249.5 mm  109.7 mm  29.0 mm  Meritor  ELSA 225-3
VVA 29174 29218 29273	KIT CONTENTS:  x 4  x 4  x 2  MAX x 2	KIT MBA112 PWWI MBA034 PWWI: Prepared for

MDP3174KWI		
Renault Volvo +		 249.5 mm  109.7 mm  29.0 mm  Meritor  ELSA 225-3
VVA 29174 29218 29273	KIT CONTENTS:  x 4  x 4  x 2  MAX x 2	PWWI MBA034 PWWI: Included x 2

MDP3175K		
Jost Kögel Trax Krone SAF Sauer Trenkamp & Gehle		 210.4 mm  94.0 mm  30.0 mm  Haldex  Modul X - DB22LT
VVA 29175	KIT CONTENTS:  x 4  x 4	PWWI: Prepared for

MDP3181K		
Fruehauf Mercedes Trenkamp & Gehle		 210.8 mm  92.2 mm  30.2 mm  Haldex  Modul X - DB19
VVA 29147 29181 29207	KIT CONTENTS:  x 4  x 4	PWWI: Prepared for

MDP3195K		
SAF		 210.0 mm  93.8 mm  29.5 mm  Haldex  Modul T - DBT22LT
VVA 29195	KIT CONTENTS:  x 4  x 2  x 2  x 2 GEN 1  x 2 GEN 2	PWWI: Prepared for



ALLFIT

1



2



3



4




5



MDP3227K

BPW Axles




210.3 mm

94.8 mm

30.0 mm

BPW
TSB 3709WVA
29227


KIT CONTENTS:



PWVI: Prepared for

MDP3228K

BPW Axles




210.3 mm

109.4 mm

30.0 mm

BPW
TSB 4309WVA
29228


KIT CONTENTS:



PWVI: Prepared for

MDP3244K

Mercedes



207.0 mm

113.9 mm

31.0 mm

Knorr
SL7WVA
29244


KIT CONTENTS:



PWVI: None

MDP3246K

Mercedes




244.5 mm

113.9 mm

31.0 mm

Knorr
SM7WVA
29246


KIT CONTENTS:



PWVI: None

MDP3256

Iveco



175.5 mm

95.2 mm

27.0 mm

Brembo

WVA
29256


KIT CONTENTS:



PWVI: Prepared for

MDP3267K

BPW Axles




246.8 mm

106.6 mm

30.0 mm

BPW
TSB 4312WVA
29267


KIT CONTENTS:



PWVI: Prepared for

MDP3279K

MAN




217.8 mm

108.8 mm

30.5 mm

Wabco
MAXX22WVA
29279


KIT CONTENTS:



PWVI: None

MDP3328K

SAF




214.8 mm

107.5 mm

31.0 mm

Knorr
ST7WVA
29328

KIT CONTENTS:





PWVI: Prepared for





ALLFIT





MDP3394K		
Scania		 247.5 mm  107.7 mm  30.0 mm  Knorr SB7 / SN7
WVA 29394	KIT CONTENTS:  x 4  x 4  x 2  x 2  x 2  x 2  x 1	PWWI: Prepared for

MDP3415K		
Haldex Kogel Krone SAF		 210.0 mm  93.4 mm  29.5 mm  Haldex Modul T - DBT22LT
WVA 29415	KIT CONTENTS:  x 4  x 4  x 2 GEN 1  x 2 GEN 2  x 2  x 2	PWWI: Prepared for

MDP3429K		
Gigant Jost SAF Scania		 210.0 mm  91.4 mm  30.0 mm  Haldex Modul T - DBT19LT
WVA 29429	KIT CONTENTS:  x 4  x 4  x 2  x 2  x 2  x 2 GEN 2	PWWI: Prepared for

MDP3498		
Setra (inc Kässbohrer)		 179.3 mm  113.0 mm  20.0 mm  Knorr 2V20
WVA 29498	KIT CONTENTS:  x 4	PWWI: None

MDP3747		
DAF MAN Moseley Neoplan Setra Van Hool VDL		 139.5 mm  121.0 mm  31.5 mm  Knorr K85
WVA 29747	KIT CONTENTS:  x 8  x 8	PWWI: None

MDP3835K		
Alexander Bus Mercedes Neoplan Optare Plaxton Sitcar		 174.8 mm  85.8 mm  21.9 mm  Meritor B Frame (2x60)
WVA 29835	KIT CONTENTS:  x 4  x 4  x 2	KIT MBA106 PWWI MBA007
PWWI: Prepared for		



1



2




3




4



5





1



2



3



4



5





1



2



3



4



5



AD Group		
57451692	MDP5005	
57451734	MDP5020	
57451759	MDP5051	
57451775	MDP5033	
57451783	MDP5038	
57451791	MDP5040	
57451809	MDP5054	
57451833	MDP5065	
57453029	MDP5039	
57453037	MDP5060	
57473415	MDP5066	
57480857	MDP5076	
Allied Signal		
29030	MDP5033	
29030	MDP5038	
29030	MDP5090	
29053	MDP5051	
29090	MDP5042	
29090	MDP5061	
29100	MDP5037	
29125	MDP5057	
29131	MDP5056	
29131	MDP5060	
29131	MDP5073	
29835	MDP5040	
Astra		
98133538AS	MDP5079	
Ayats		
32001296	MDP5056	
Bova		
204552	MDP3087KP	
204552	MAX087K	
204552	MDP3087K	
BPW		
02.0312.14.00	MAX087K	
02.0312.14.00	MDP3087K	
02.0312.14.00	MDP3087KP	
02.0312.17.00	MAX087K	
02.0312.17.00	MDP3087K	
02.0312.17.00	MDP3087KP	
05.362.70.01.0	MAX087K	
05.362.70.01.0	MDP3087K	
05.362.70.01.0	MDP3087KP	
05.362.70.02.0	MAX087K	
05.362.70.02.0	MDP3087K	
05.362.70.02.0	MDP3087KP	
0509290040	MAX165K	
0509290040	MDP3165K	
0509290050	MAX165K	
0509290050	MDP3165K	
0509290070	MAX167K	
0509290070	MDP3167K	

0509290090	MAX167K	
0509290090	MDP3167K	
0509290100	MAX165K	
0509290100	MDP3165K	
0536270020	MAX087K	
0536270020	MAX167K	
0536270020	MDP3087K	
0536270020	MDP3087KP	
0536270020	MDP3167K	
09.801.02.20.0	MAX087K	
09.801.02.20.0	MDP3087K	
09.801.02.20.0	MDP3087KP	
09.801.02.57.0	MAX087K	
09.801.02.57.0	MDP3087K	
09.801.02.57.0	MDP3087KP	
09.801.02.92.0	MAX087K	
09.801.02.92.0	MDP3087K	
09.801.02.92.0	MDP3087KP	
09.801.06.20.0	MAX087K	
09.801.06.20.0	MDP3087K	
09.801.06.20.0	MDP3087KP	
09.801.06.36.0	MAX087K	
09.801.06.36.0	MDP3087K	
09.801.06.36.0	MDP3087KP	
0980102570	MAX087K	
0980102570	MAX167K	
0980102570	MDP3087K	
0980102570	MDP3087KP	
0980102570	MDP3167K	
0980102750	MAX165K	
0980102750	MDP3165K	
0980102920	MAX087K	
0980102920	MAX167K	
0980102920	MDP3087K	
0980102920	MDP3087KP	
0980102920	MDP3167K	
0980102930	MAX165K	
0980102930	MDP3165K	
0980106200	MAX087K	
0980106200	MAX167K	
0980106200	MDP3087K	
0980106200	MDP3087KP	
0980106200	MDP3167K	
0980106210	MAX165K	
0980106210	MDP3165K	
0980106350	MAX165K	
0980106350	MDP3165K	
0980106360	MAX167K	
0980106360	MDP3167K	
0980106430	MAX165K	
0980106430	MDP3165K	
0980106450	MAX167K	
0980106450	MDP3167K	

0980106960	MAX167K	
0980106960	MDP3167K	
0980107090	MAX165K	
0980107090	MDP3165K	
0980108150	MAX165K	
0980108150	MDP3165K	
0980108160	MAX171K	
0980108160	MDP3171K	
509290040	MAX165K	
509290040	MDP3165K	
509290050	MAX165K	
509290050	MDP3165K	
509290070	MAX167K	
509290070	MDP3167K	
509290090	MAX167K	
509290090	MDP3167K	
509290100	MAX165K	
509290100	MDP3165K	
509290120	MDP3227K	
509290130	MDP3228K	
509290131	MDP3228K	
509290151	MDP3227K	
509290331	MDP3228K	
536270020	MAX167K	
536270020	MDP3087KP	
536270020	MAX087K	
536270020	MDP3087K	
536270020	MDP3167K	
900061790	MDP3227K	
980102570	MAX167K	
980102570	MDP3087KP	
980102570	MAX087K	
980102570	MDP3087K	
980102570	MDP3167K	
980102750	MAX165K	
980102750	MDP3165K	
980102920	MAX167K	
980102920	MDP3087KP	
980102920	MAX087K	
980102920	MDP3087K	
980102920	MDP3167K	
980102930	MAX165K	
980102930	MDP3165K	
980106200	MAX167K	
980106200	MDP3087KP	
980106200	MAX087K	
980106200	MDP3087K	
980106200	MDP3167K	
980106200	MAX165K	
980106200	MDP3165K	
980106200	MDP3167K	
980106210	MAX165K	
980106210	MDP3165K	
980106350	MAX165K	
980106350	MDP3165K	
980106360	MAX167K	
980106360	MDP3167K	
980106430	MAX165K	
980106430	MDP3165K	
980106450	MAX167K	
980106450	MDP3167K	

980106360	MDP3167K	
980106430	MAX165K	
980106430	MDP3165K	
980106450	MAX167K	
980106450	MDP3167K	
980106960	MAX167K	
980106960	MDP3167K	
980107090	MAX165K	
980107090	MDP3165K	
980107550	MDP3227K	
980107570	MDP3228K	
980107590	MDP3267K	
980107940	MDP3227K	
980107960	MDP3228K	
980107971	MDP3228K	
980107980	MDP3267K	
980108150	MAX165K	
980108150	MDP3165K	
980108160	MAX171K	
980108160	MDP3171K	
980108370	MDP3227K	
Bredamenarini		
0254625/K	MDP5083	
Casals		
MD304	MDP5020	
MD310	MDP5038	
MD311	MDP5039	
MD312	MDP5040	
MD313	MDP5042	
MD315	MDP5051	
MD316	MDP5061	
MD373	MDP5076	
Coherma Semirremolques SL		
420314	MDP5076	
420319	MDP5057	
420475	MDP5073	
DAF		
1436901	MDP3088K	
1436901	MAX088K	
1436901	MDP3088	
1439324	MDP3087KP	
1439324	MAX087K	
1439324	MDP3087K	
1440504	MDP3141	
1489199	MDP5057	
1489983	MDP5073	
1489984	MDP5076	
1519449	MDP5071	
1522057	MDP5060	
1522061	MDP5038	
1522172	MDP5040	
1522181	MDP5051	
1522183	MDP5042	

*Product definition found in buyers guide



...DAF		
1522188	MDP5005	
1522191	MDP5037	
1522202	MDP5020	
1524600	MDP5101	
1524600	MDP5101SK	
1525329	MDP5106	
1525329	MDP5106SK	
1525335	MDP5072	
1525812	MDP5102	
1525819	MDP5104	
1525819	MDP5104SK	
1526529	MAX131K	
1526529	MDP3131K	
1526653	MDP3124K	
1617343	MDP3087KP	
1617343	MAX087K	
1617343	MDP3087K	
1628064	MAX126K	
1628064	MDP3126K	
1628064	MDP3126	
1665013	MDP5093	
1797053	MDP3087KP	
1797053	MAX087K	
1797053	MDP3087K	
1800830	MDP3087KP	
1800830	MAX087K	
1800830	MDP3087K	
1878030	MDP3087KP	
1878030	MAX087K	
1878030	MDP3087K	
866282	MDP5056	
887686	MDP3087KP	
887686	MAX087K	
887686	MDP3087K	
905252	MDP3087KP	
905252	MAX087K	
905252	MDP3087K	
BBU8177	MDP3077	
BBU8178	MDP3077	
Dennis		
1519449	MDP5071	
616441	MDP5071	
655377-1	MDP5061	
ERF		
35403127373	MDP5076	
35503084795	MDP5059	
35503112160	MDP5073	
81508205072	MDP5059	
MDP5093	MDP5093	
STRMDP5038	MDP5038	
STRMDP5053	MDP5053	
STRMDP5057	MDP5057	

STRMDP5093 MDP5093		
Europart		
1509015330	MDP5066	
1509015355	MDP5057	
1509015375	MDP5056	
2129030282	MDP5038	
7600000050	MDP5076	
Evobus		
8285408534	MDP5033	
82854085340	MDP5033	
Fodon		
1489199	MDP5057	
1489983	MDP5073	
1489984	MDP5076	
1519449	MDP5071	
1665013	MDP5093	
TP08015015	MDP5059	
Fruehauf		
CF103915	MDP5076	
CF104034	MDP5057	
CF104296	MDP5073	
CF104440	MDP5093	
DDMP5059	MDP5059	
General Trailer		
CF104034	MDP5057	
CF104296	MDP5073	
DDMP5059	MDP5059	
DSB2A	MDP5076	
Gigant		
703010372	MDP3429K	
9291072	MDP3195K	
Haldex		
640001002	MDP3195K	
93200	MDP3195K	
93887	MDP3195K	
95053	MDP3195K	
95396	MDP3195K	
Hendrickson		
S305608	MDP3195K	
S30674	MDP3195K	
Irisbus		
28060035	MDP5111	
5006028410	MDP5056	
Iveco		
10906070	MDP3024	
1906043	MDP3122	
1906043	MDP5020	
1906170	MDP3032K	
1906297	MDP3122	
1906297	MDP5020	
1906345	MDP3017	
1906416	MDP3122	
1906439	MDP3087KP	

1906439	MAX087K	
1906439	MDP3087K	
1906467	MDP3088K	
1906467	MAX088K	
1906467	MDP3088	
254625	MDP5083	
299 5637	MAX087K	
299 5637	MDP3087K	
299 5637	MDP3087KP	
299 6378	MAX087K	
299 6378	MDP3087K	
299 6378	MDP3087KP	
299 6515	MAX087K	
299 6515	MDP3087K	
299 6515	MDP3087KP	
2992336	MAX095K	
2992336	MDP3095K	
2992348	MDP3087KP	
2992348	MAX087K	
2992348	MDP3087K	
2992476	MDP3087KP	
2992476	MAX087K	
2992476	MDP3087K	
2992476	MDP3087K	
2992669	MDP5083K	
2995552	MDP5083	
2995637	MAX087K	
2995637	MDP3087KP	
2995637	MDP3087K	
2995809	MDP3087KP	
2995809	MAX087K	
2995809	MDP3087K	
2995819	MDP3087KP	
2995819	MAX087K	
2995819	MDP3087K	
2995938	MDP3087KP	
2995938	MAX087K	
2995938	MDP3087K	
2996065	MDP5116	
2996068	MDP5116	
2996189	MDP3087KP	
2996189	MAX087K	
2996189	MDP3087K	
2996378	MDP3087KP	
2996378	MAX087K	
2996378	MDP3087K	
2996468	MAX095K	
2996468	MDP3095K	
2996515	MAX087K	
2996515	MDP3087KP	
2996515	MDP3087K	
2996518	MDP3087KP	
2996518	MAX087K	
2996518	MDP3087K	

41211278	MDP3087KP	
41211278	MAX087K	
41211278	MDP3087K	
41211279	MDP3087KP	
41211279	MAX087K	
41211279	MDP3087K	
42555669	MDP3122	
42583124	MDP5097	
42583125	MDP5116	
42583126	MDP5121	
42583127	MDP5131	
42583128	MDP5132	
500054632	MDP3087KP	
500054632	MAX087K	
500054632	MDP3087K	
500055019	MAX095K	
500055019	MDP3095K	
500083553	MDP5131	
500086356	MDP5132	
500363646	MAX095K	
500363646	MDP3095K	
5006028410	MDP5056	
5006028410	MDP5116	
99476098	MDP3087KP	
99476098	MAX087K	
99476098	MDP3087K	
E2992336	MAX095K	
E2992336	MDP3095K	
V2992348	MAX087K	
V2992348	MDP3087K	
V2992348	MDP3087KP	
Jost		
JAE0250410020	MDP3415K	
JAE0250420020	MDP3415K	
Karosa		
5006028410	MDP5056	
Kässbohrer		
8285408463	MDP5110	
8285515573	MAX087K	
8285515573	MDP3087K	
8285515573	MDP3087KP	
Knorr Bremse		
II180220062	MAX087K	
II180220062	MDP3087K	
II180220062	MDP3087KP	
II376580062	MAX095K	
II376580062	MDP3095K	
K046771K50	MAX087K	
K046771K50	MDP3087K	
K046771K50	MDP3087KP	
K094436K50	MAX087K	
K094436K50	MDP3087K	
K094436K50	MDP3087KP	



1



2



3



4



5



...Knorr Bremse	
K097533K50	MDP3328K
K097533K64	MDP3328K
K108020K50	MDP3328K
K180908K50	MDP3328K
Leciñena	
5820099	MDP5076
5820127	MDP5073
5820174	MDP5093
Leyland	
LBM DP5033	MDP5033
LBM DP5076	MDP5076
MDP3087K	MAX087K
MDP3087K	MDP3087K
MDP3087K	MDP3087KP
MDP3131K	MAX131K
MDP3131K	MDP3131K
MDP5057	MDP5057
MDP5073	MDP5073
MDP5093	MDP5093
MAN	
35503084795	MDP5059
35503112160	MDP5073
81 50820 5091	MAX030K
81 50820 5091	MDP3030K
81 50820 5099	MAX087K
81 50820 5099	MDP3087K
81 50820 5099	MDP3087KP
81 50820 6044	MAX030K
81 50820 6044	MDP3030K
81 50820 6046	MAX030K
81 50820 6046	MDP3030K
81 50820 6056	MAX087K
81 50820 6056	MDP3087K
81 50820 6056	MDP3087KP
81.50820.6014	MDP5038
81.50820.6015	MDP5039
8150805005	MDP5090
81508080003	MDP5038
81508080004	MDP5039
81508205023	MDP3088K
81508205023	MAX088K
81508205023	MDP3088
81508205025	MDP3088K
81508205025	MAX088K
81508205025	MDP3088
81508205029	MDP3088K
81508205029	MAX088K
81508205029	MDP3088
81508205054	MDP3122
81508205064	MDP5065
81508205072	MAX131K
81508205072	MDP3131K

81508205072	MDP5059
81508205072	MDP5060
81508205072	MDP5099
81508205080	MAX131K
81508205080	MDP3131K
81508205087	MDP5054
81508205088	MDP5066
81508205091	MDP5038
81508205092	MDP5039
81508206000	MAX030K
81508206000	MDP3030K
81508206000	MDP5065
81508206002	MAX030K
81508206002	MDP3030K
81508206002	MDP5038
81508206004	MAX030K
81508206004	MDP3030K
81508206004	MDP5038
81508206005	MDP5039
81508206006	MDP3088K
81508206006	MAX088K
81508206006	MDP3088
81508206008	MAX095K
81508206008	MDP3095K
81508206014	MAX030K
81508206014	MDP3030K
81508206014	MDP5038
81508206015	MDP5039
81508206016	MAX030K
81508206016	MDP3030K
81508206016	MDP5038
81508206017	MDP5039
81508206020	MDP3088K
81508206020	MAX088K
81508206020	MDP3088
81508206022	MAX095K
81508206022	MDP3095K
81508206025	MAX030K
81508206025	MDP3030K
81508206025	MDP5054
81508206028	MDP3122
81508206030	MDP3087KP
81508206030	MAX087K
81508206030	MDP3087K
81508206031	MAX131K
81508206031	MDP3131K
81508206031	MDP5060
81508206032	MDP3087KP
81508206032	MAX087K
81508206032	MDP3087K
81508206033	MDP3087KP
81508206033	MAX087K
81508206033	MDP3087K

81508206034	MAX030K
81508206034	MDP3030K
81508206034	MDP5038
81508206035	MDP5039
81508206036	MAX030K
81508206036	MDP3030K
81508206036	MDP5065
81508206037	MDP5066
81508206038	MAX030K
81508206038	MDP3030K
81508206038	MDP5054
81508206041	MAX131K
81508206041	MDP3131K
81508206041	MDP5060
81508206041	MDP5099
81508206042	MDP3088K
81508206042	MAX088K
81508206042	MDP3088
81508206043	MAX148K
81508206043	MDP3148K
81508206044	MDP5065
81508206045	MDP5039
81508206045	MDP5066
81508206046	MDP5038
81508206046	MDP5088
81508206051	MAX131K
81508206051	MDP3131K
81508206051	MDP5060
81508206051	MDP5099
81508206052	MAX131K
81508206052	MDP3131K
81508206052	MDP5097
81508206054	MAX148K
81508206054	MDP3148K
81508206055	MDP3087KP
81508206055	MAX087K
81508206055	MDP3087K
81508206056	MAX087K
81508206056	MDP3087KP
81508206056	MDP3087K
81508206057	MAX095K
81508206057	MDP3095K
81508206059	MAX095K
81508206059	MDP3095K
81508206060	MDP9000
81508206060	MAX095K
81508206060	MDP3095K
81508206061	MDP3087KP
81508206061	MAX087K
81508206061	MDP3087K
81508206063	MAX148K
81508206063	MDP3148K
81508206068	MAX087K

81508206068	MDP3087KP
81508206068	MDP3087K
MDP5093	MDP5093
N2508200009	MDP5059
N2508200012	MDP5093
N2508206007	MDP5038
N2508206009	MDP5059
N2508206022	MDP5076
N2508206025	MDP5057
N2508206026	MDP5073
STRM DP5038	MDP5038
STRM DP5053	MDP5053
STRM DP5057	MDP5057
STRM DP5093	MDP5093
ZG002940002	MDP5076
Mercedes	
000 421 05 10	MAX087K
000 421 05 10	MDP3087K
000 421 05 10	MDP3087KP
000 421 18 10	MAX087K
000 421 18 10	MDP3087K
000 421 18 10	MDP3087KP
000 421 43 10	MAX087K
000 421 43 10	MDP3087K
000 421 43 10	MDP3087KP
000 423 66 10	MAX087K
000 423 66 10	MDP3087K
000 423 66 10	MDP3087KP
002 420 49 20	MAX087K
002 420 49 20	MDP3087K
002 420 49 20	MDP3087KP
002 420 70 20	MAX087K
002 420 70 20	MDP3087K
002 420 70 20	MDP3087KP
003 420 10 20	MAX087K
003 420 10 20	MDP3087K
003 420 10 20	MDP3087KP
003 420 16 20	MAX087K
003 420 16 20	MDP3087K
003 420 16 20	MDP3087KP
003 420 20 20	MAX087K
003 420 20 20	MDP3087K
003 420 20 20	MDP3087KP
003 420 22 20	MAX087K
003 420 22 20	MDP3087K
003 420 22 20	MDP3087KP
003 420 35 20	MAX087K
003 420 35 20	MDP3087K
003 420 35 20	MDP3087KP
004 420 22 20	MAX087K
004 420 22 20	MDP3087K
004 420 22 20	MDP3087KP
006 420 14 20	MAX244K

*Product definition found in buyers guide



	OE	
...Mercedes		
006 420 14 20	MAX246K	
006 420 14 20	MDP3244K	
006 420 14 20	MDP3246K	
006 420 52 20	MAX246K	
006 420 52 20	MDP3246K	
14211710	MAX095K	
14211710	MDP3095K	
24200820	MDP5088	
2420222010	MDP3087KP	
2420222010	MAX087K	
2420222010	MDP3087K	
24204920	MDP3087KP	
24204920	MAX087K	
24204920	MDP3087K	
24204970	MDP3087KP	
24204970	MAX087K	
24204970	MDP3087K	
24205520	MDP5110	
24207820	MAX095K	
24207820	MDP3095K	
24207920	MAX095K	
24207920	MDP3095K	
34201120	MAX148K	
34201120	MDP3148K	
34201220	MAX148K	
34201220	MDP3148K	
34201620	MDP3087KP	
34201620	MAX087K	
34201620	MDP3087K	
34202020	MDP3087KP	
34202020	MAX087K	
34202020	MDP3087K	
34202220	MDP3087KP	
34202220	MAX087K	
34202220	MDP3087K	
34203520	MDP3087KP	
34203520	MAX087K	
34203520	MDP3087K	
34205520	MDP5090	
34205520	MDP5110	
34206620	MAX148K	
34206620	MDP3148K	
34207220	MAX148K	
34207220	MDP3148K	
34207320	MAX148K	
34207320	MDP3148K	
4210510	MDP3087KP	
4210510	MAX087K	
4210510	MDP3087K	
4210710	MAX095K	
4210710	MDP3095K	
4214310	MDP3087KP	

	OE	
4214310	MAX087K	
4214310	MDP3087K	
44202220	MDP3087KP	
44202220	MAX087K	
44202220	MDP3087K	
44206020	MDP3087KP	
44206020	MAX087K	
44206020	MDP3087K	
44206120	MAX148K	
44206120	MDP3148K	
54202320	MAX095K	
54202320	MDP3095K	
64201020	MDP3087KP	
64201020	MAX087K	
64201020	MDP3087K	
64201120	MDP3087KP	
64201120	MAX087K	
64201120	MDP3087K	
64201520	MDP3244K	
64201520	MAX244K	
64205320	MAX244K	
64205320	MDP3244K	
A0004210510	MAX087K	
A0004210510	MDP3087K	
A0004210510	MDP3087KP	
A0004210710	MAX095K	
A0004210710	MDP3095K	
A0004211810	MAX087K	
A0004211810	MDP3087K	
A0004211810	MDP3087KP	
A0004214310	MAX087K	
A0004214310	MDP3087K	
A0004214310	MDP3087KP	
A0004236610	MAX087K	
A0004236610	MDP3087K	
A0004236610	MDP3087KP	
A0014211710	MAX095K	
A0014211710	MDP3095K	
A0024201520	MDP5040	
A0024204920	MAX087K	
A0024204920	MDP3087K	
A0024204920	MDP3087KP	
A0024207020	MAX087K	
A0024207020	MDP3087K	
A0024207020	MDP3087KP	
A0024207820	MAX095K	
A0024207820	MDP3095K	
A0024207920	MAX095K	
A0024207920	MDP3095K	
A0034201020	MAX087K	
A0034201020	MDP3087K	
A0034201020	MDP3087KP	
A0034201520005	MDP5040	

	OE	
A0034201620	MAX087K	
A0034201620	MDP3087K	
A0034201620	MDP3087KP	
A0034202020	MAX087K	
A0034202020	MDP3087K	
A0034202020	MDP3087KP	
A0034202220	MAX087K	
A0034202220	MDP3087K	
A0034202220	MDP3087KP	
A0034203520	MAX087K	
A0034203520	MDP3087K	
A0034203520	MDP3087KP	
A0034206220	MDP5040	
A0034207720	MDP5040	
A0044202220	MAX087K	
A0044202220	MDP3087K	
A0044202220	MDP3087KP	
A0054202320	MAX095K	
A0054202320	MDP3095K	
A006 420 14 20	MAX244K	
A006 420 14 20	MAX246K	
A006 420 14 20	MDP3244K	
A006 420 14 20	MDP3246K	
A006 420 15 20	MAX244K	
A006 420 15 20	MDP3244K	
A006 420 52 20	MAX246K	
A006 420 52 20	MDP3246K	
A0064201020	MAX087K	
A0064201020	MDP3087K	
A0064201020	MDP3087KP	
A0064201520	MAX244K	
A0064201520	MDP3244K	
A0064205320	MAX244K	
A0064205320	MDP3244K	
Meritor		
20568713	MDP5093	
20765963 5	MDP5093	
2114543	MDP5117	
35503112160	MDP5073	
5001864380	MDP5093	
5021139271	MDP5076	
5021174771	MDP5073	
68324665	MDP5093	
C73222F2476	MDP5128	
MDB1373	MAX087K	
MDB1373	MDP3087K	
MDB1373	MDP3087KP	
MDP011K	MDP3011K	
MDP1277	MAX148K	
MDP1277	MDP3148K	
MDP5106SK	MAX173K	
MDP5106SK	MDP3173K	

	OE	
MDP5106SK	MDP5102	
MDP5106SK	MDP5106	
N2508206022	MDP5076	
Neoplan		
0821.351.00	MAX087K	
0821.351.00	MDP3087K	
0821.351.00	MDP3087KP	
0821.351.00	MDP9005	
82135100	MAX087K	
82135100	MDP3087K	
82135100	MDP3087KP	
Optare		
28060035	MDP5111	
UNMDP5057	MDP5057	
UNMDP5061	MDP5061	
Paccar		
1526706	MDP3088K	
1526952	MAX148K	
1526966	MAX165K	
1489199	MDP5057	
1489983	MDP5073	
1489984	MDP5076	
1519449	MDP5071	
1522057	MDP5060	
1522172	MDP5040	
1522183	MDP5042	
1522234	MDP5059	
1524045	MDP9000	
1524600	MDP5101	
1524600	MDP5101SK	
1525329	MDP5106	
1525329	MDP5106SK	
1525335	MDP5072	
1525522	MDP5053	
1525812	MDP5102	
1525819	MDP5104	
1525819	MDP5104SK	
1526529	MAX131K	
1526529	MDP3131K	
1526653	MDP3124K	
1526665	MAX090K	
1526665	MDP3090K	
1526667	MDP3169K	
1526680	MAX125K	
1526680	MDP3125K	
1526706	MAX088K	
1526706	MDP3088	
1526951	MDP3122	
1526952	MDP3148K	
1526960	MDP3137K	
1526965	MAX030K	
1526965	MDP3030K	
1526966	MDP3165K	



1



2



3



4



5



	OE	
...Paccar		
1527520	MDP3043K	
1665013	MDP5093	
2166142	MDP5101	
2166142	MDP5101SK	
866282	MDP5056	
879683	MDP5052	
905252	MAX087K	
905252	MDP3087K	
905252	MDP3087KP	
905556	MAX095K	
905556	MDP3095K	
906245	MDP5117	
Raba		
654114	MDP5033	
Remco		
29067220T819	MDP5020	
29090282T3016	MDP5042	
29124270T3018	MDP5076	
29125292D7500	MDP5057	
29136292T7500	MDP5052	
29137292T7500	MDP5053	
Renault		
20568713	MDP5093	
20765963 5	MDP5093	
50 01 864 363	MAX174K	
50 01 864 363	MDP3174K	
50 01 864 363	MDP3174KWI	
50 01 864 364	MAX174K	
50 01 864 364	MDP3174K	
50 01 864 364	MDP3174KWI	
50 01 864 380	MDP5093SK	
5001014704	MDP5005	
5001825639	MDP5005	
5001831161	MAX090K	
5001831161	MDP3090K	
5001831161	MDP5042	
5001833114	MDP5042	
5001846034	MAX090K	
5001846034	MDP3090K	
5001846034	MDP5042	
5001848363	MAX030K	
5001848363	MDP3030K	
5001854341	MDP5051	
5001854342	MAX030K	
5001854342	MDP3030K	
5001855646	MAX131K	
5001855646	MDP3131K	
5001855646	MDP5056	
5001857615	MDP5037	
5001864363	MAX174K	
5001864363	MDP3174KWI	
5001864363	MDP3174K	

	OE	
5001864363	MDP5101	
5001864363	MDP5101PPRK	
5001864363	MDP5101SK	
5001864363	MDP5115	
5001864364	MAX174K	
5001864364	MDP3174KWI	
5001864364	MDP3174K	
5001864364	MDP5101	
5001864364	MDP5101PPRK	
5001864364	MDP5101SK	
5001864364	MDP5115	
5001864365	MDP5102	
5001864380	MDP5093	
5001864380	MDP5093SK	
5001866951	MAX088K	
5001866951	MDP3088K	
5001866951	MDP3088	
5010848607	MDP3088K	
5010848607	MAX088K	
5010848607	MDP3088	
5021139271	MDP5076	
5021174771	MDP5073	
5021179951	MDP5057	
5021200730	MDP5038	
5021200739	MDP5053	
5021200757	MDP5088	
5021200761	MDP5093	
5021200787	MDP9000	
5021200792	MDP9005	
68324665	MDP5093	
74 20 560 415	MDP5093SK	
74 21 399 929	MAX174K	
74 21 399 929	MDP3174K	
74 21 399 929	MDP3174KWI	
74 21 496 557	MDP5093SK	
7420560415	MDP5093SK	
7421399915	MDP5102	
7421399929	MAX174K	
7421399929	MDP3174KWI	
7421399929	MDP3174K	
7421399929	MDP5101	
7421399929	MDP5101PPRK	
7421399929	MDP5101SK	
7421496555	MAX174K	
7421496555	MDP3174KWI	
7421496555	MDP3174K	
7421496555	MDP5101	
7421496555	MDP5101PPRK	
7421496555	MDP5101SK	
7421496556	MDP5106	
7421496557	MDP5093SK	
7422921057	MAX174K	
7422921057	MDP3174KWI	

	OE	
7422921057	MDP3174K	
7422921064	MAX174K	
7422921064	MDP3174KWI	
7422921064	MDP3174K	
7422921066	MDP5093SK	
7423149533	MAX174K	
7423149533	MDP3174KWI	
7423149533	MDP3174K	
7424990544	MDP3077	
7424990545	MAX090K	
7424990545	MDP3090K	
7424990546	MAX126K	
7424990546	MDP3126K	
7424990546	MDP3126	
7424990547	MDP3017	
7424990548	MDP3835K	
7424990549	MDP3024	
7424990580	MDP3122	
7424990581	MDP3747	
7424990582	MDP3013	
7424990583	MDP3011K	
7424990584	MAX030K	
7424990584	MDP3030K	
7424990585	MDP3043K	
7424990586	MDP3032K	
Rhiag		
47095	MDP5005	
47097	MDP5020	
47099	MDP5033	
47100	MDP5040	
47101	MDP5054	
Rockwell		
46222	MDP5093SK	
68324665	MDP5093SK	
68325492	MDP5093SK	
ROR		
20568713	MDP5093	
20765963 5	MDP5093	
2114543	MDP5117	
35503112160	MDP5073	
5001864380	MDP5093	
5021139271	MDP5076	
5021174771	MDP5073	
68324665	MDP5093	
N2508206022	MDP5076	
Roulunds		
495181	MDP5040	
SAE-SMB		
9317202	MDP3087KP	
9317202	MAX087K	
9317202	MDP3087K	
9317-202	MAX087K	
9317-202	MDP3087K	

	OE	
9317-202	MDP3087KP	
M100669	MAX087K	
M100669	MDP3087K	
M100669	MDP3087KP	
SAF		
3057000600	MDP3328K	
3057001400	MDP3429K	
3057001500	MDP3195K	
3057007700	MDP3087KP	
3057007700	MAX087K	
3057007700	MDP3087K	
3057007800	MAX095K	
3057007800	MDP3095K	
3057007900	MDP3087KP	
3057007900	MAX087K	
3057007900	MDP3087K	
3057008000	MAX126K	
3057008000	MDP3126K	
3057008000	MDP3126	
3057009600	MDP3195K	
3057009601	MDP3195K	
3080008700	MDP3328K	
4057427700	MDP3087KP	
4057427700	MAX087K	
4057427700	MDP3087K	
4057439600	MDP3195K	
5317002300	MDP3087KP	
5317002300	MAX087K	
5317002300	MDP3087K	
5317002400	MAX095K	
5317002400	MDP3095K	
Scania		
1034092	MDP5076	
1390428	MDP3087KP	
1390428	MAX087K	
1390428	MDP3087K	
1521979	MDP3087KP	
1521979	MAX087K	
1521979	MDP3087K	
1734529	MDP3087KP	
1734529	MAX087K	
1734529	MDP3087K	
1856 08	MAX087K	
1856 08	MDP3087K	
1856 08	MDP3087KP	
1856108	MDP3087KP	
1856108	MAX087K	
1856108	MDP3087K	
1890861	MDP3087KP	
1890861	MAX087K	
1890861	MDP3087K	
2114536	MDP3124K	
2114537	MAX131K	

*Product definition found in buyers guide



...Scania		
2114537	MDP3131K	
2114539	MDP3169K	
2114540	MDP5073	
2114541	MDP5076	
2114542	MDP5093	
2127745	MDP5332SK	
2272502	MDP5332SK	
2272503	MDP5332SK	
2325212	MDP3394K	
Setra		
8 285 388 435	MAX030K	
8 285 388 435	MDP3030K	
81508206016	MDP5038	
Schmitz Cargobull		
1178243	MDP3328K	
UD Trucks		
5222828321	MAX174K	
5222828321	MDP3174KWI	
5222828321	MDP3174K	
Volvo		
20526568	MAX174K	
20526568	MDP3174KWI	
20526568	MDP3174K	
20526568	MDP5104	
20526568	MDP5104PPRK	
20526568	MDP5104SK	
20526569	MDP5102	
20526570	MDP5093SK	
20535922	MDP5099	
20560412	MAX174K	
20560412	MDP3174KWI	
20560412	MDP3174K	
20560412	MDP5104	
20560412	MDP5104PPRK	
20560412	MDP5104SK	
20560414	MDP5106	
20560414	MDP5106PPRK	
20560414	MDP5106SK	
20560415	MDP5093SK	
20568711	MAX174K	
20568711	MDP3174KWI	
20568711	MDP3174K	
20568711	MDP5104	
20568711	MDP5104PPRK	
20568711	MDP5104SK	
20568712	MDP5106	
20568712	MDP5106PPRK	
20568712	MDP5106SK	
20568713	MDP3169K	
20568713	MDP5093	
20568713	MDP5093SK	
20568714	MAX174K	

20568714	MDP3174KWI	
20568714	MDP3174K	
20568715	MDP5106	
20568715	MDP5106PPRK	
20568715	MDP5106SK	
20765963	MDP5093SK	
20765963 5	MDP5093	
20768092	MAX125K	
20768092	MDP3125K	
20768092	MDP5057	
20768101	MDP5072	
20768115	MDP5053	
20918891	MAX125K	
20918891	MDP3125K	
20918891	MDP5057	
20931343	MAX125K	
20931343	MDP3125K	
20931343	MDP5057	
209313430	MAX125K	
209313430	MDP3125K	
20932682	MAX125K	
20932682	MDP3125K	
20932682	MDP5057	
20976509	MAX131K	
20976509	MDP3131K	
20976509	MDP5099	
21024701	MAX174K	
21024701	MDP3174KWI	
21024701	MDP3174K	
21024701	MDP5119PPRK	
21024701	MDP5119SK	
21024702	MAX174K	
21024702	MDP3174KWI	
21024702	MDP3174K	
21024702	MDP5119PPRK	
21024702	MDP5119SK	
21088907	MAX125K	
21088907	MDP3125K	
21088907	MDP5057	
21309468	MAX131K	
21309468	MDP3131K	
21309468	MDP5099	
21352570	MDP3174KWI	
21352570	MAX174K	
21352570	MDP3174K	
21352573	MDP5106	
21352573	MDP5106PPRK	
21352573	MDP5106SK	
21488185	MDP3174KWI	
21488185	MAX174K	
21488185	MDP3174K	
21488186	MDP5106	
21496550	MDP3174KWI	

21496550	MAX174K	
21496550	MDP3174K	
21496550	MDP5104	
21496550	MDP5104PPRK	
21496550	MDP5104SK	
21496551	MDP5106	
21496551	MDP5106PPRK	
21496551	MDP5106SK	
21496552	MDP3169K	
21496552	MDP5093	
21496552	MDP5093SK	
23149532	MAX174K	
23149532	MDP3174KWI	
23149532	MDP3174K	
3086396	MDP5057	
3093531	MDP3136K	
3093531	MDP5052	
3093532	MDP5053	
3093919	MDP5057	
3093919	MDP5061	
3095396	MAX125K	
3095396	MDP3125K	
3095396	MDP5057	
3099533	MDP5072	
3198394	MDP5072	
3903532	MDP5053	
5001864365	MDP5106	
5001864365	MDP5106PPRK	
5001864365	MDP5106SK	
5001864380	MDP5093	
68324665	MDP5093	
68324665	MDP5093SK	
85107768	MAX131K	
85107768	MDP3131K	
85107768	MDP5099	
8550611	MDP5061	
AMMDP3087K	MAX087K	
AMMDP3087K	MDP3087K	
AMMDP3087K	MDP3087KP	
AMMDP5057	MDP5057	
AMMDP5073	MDP5073	
AMMDP5076	MDP5076	
AMMDP5093	MDP5093	
WVA		
29011	MDP3011K	
29013	MDP3013	
29014	MDP3013	
29017	MDP3017	
29024	MDP3024	
29030	MAX030K	
29030	MDP3030K	
29030	MDP5033	
29030	MDP5065SK	

29030	MDP5110	
29032	MDP3032K	
29042	MAX087K	
29042	MDP3087K	
29042	MDP3087KP	
29043	MDP3043K	
29059	MAX087K	
29059	MDP3087K	
29059	MDP3087KP	
29061	MDP9000	
29061	MDP9005	
29067	MDP5005	
29067	MDP5020	
29068	MAX087K	
29068	MDP3087K	
29068	MDP3087KP	
29077	MDP3077	
29083	MAX030K	
29083	MDP3030K	
29083	MDP5065SK	
29087	MAX087K	
29087	MDP3087K	
29087	MDP3087KP	
29087	MDP9000	
29087	MDP9005	
29088	MAX088K	
29088	MDP3088	
29088	MDP3088K	
29090	MAX090K	
29090	MDP3090K	
29090	MDP5042	
29090	MDP5042SK	
29090	MDP5061	
29090	MDP5071	
29094	MAX095K	
29094	MDP3095K	
29095	MAX095K	
29095	MDP3095K	
29100	MDP5035	
29100	MDP5037	
29106	MAX087K	
29106	MDP3087K	
29106	MDP3087KP	
29108	MAX087K	
29108	MDP3087K	
29108	MDP3087KP	
29109	MAX087K	
29109	MDP3087K	
29109	MDP3087KP	
29113	MAX030K	
29113	MDP3030K	
29113	MDP5038	
29113	MDP5051	



1



2



3



4



5



	OE	
...WVA		
29113	MDP5054	
29113	MDP5065	
29113	MDP5065SK	
29113	MDP5088	
29113	MDP5090	
29114	MDP5039	
29114	MDP5066	
29115	MAX148K	
29115	MDP3148K	
29116	MAX148K	
29116	MDP3148K	
29119	MDP3141	
29120	MDP3143K	
29122	MDP3122	
29124	MDP3124K	
29124	MDP5076SK	
29125	MAX125K	
29125	MDP3125K	
29125	MDP5057	
29125	MDP5057SK	
29126	MAX126K	
29126	MDP3126	
29126	MDP3126K	
29131	MAX131K	
29131	MDP3131K	
29131	MDP5056	
29131	MDP5056SK	
29131	MDP5059	
29131	MDP5060	
29131	MDP5073	
29131	MDP5073SK	
29131	MDP5097	
29131	MDP5099	
29131	MDP5111	
29131	MDP5115	
29131	MDP5116	
29131	MDP5121	
29131	MDP5124	
29131	MDP5131	
29131	MDP5132	
29136	MDP3136K	
29136	MDP5052	
29137	MDP3137K	
29137	MDP5053	
29141	MDP3141	
29141	MDP3141K	
29142	MDP3142	

	OE	
29142	MDP3142K	
29143	MDP3143K	
29147	MDP3181K	
29148	MAX148K	
29148	MDP3148K	
29150	MDP5083	
29150	MDP5083K	
29150	MDP5083SK	
29151	MDP5072	
29155	MDP3124K	
29155	MDP5076	
29155	MDP5076SK	
29156	MDP5056SK	
29156	MDP5073SK	
29158	MAX171K	
29158	MDP3158K	
29158	MDP3171K	
29159	MAX126K	
29159	MDP3126	
29159	MDP3126K	
29162	MAX162K	
29162	MDP3162	
29162	MDP3162K	
29163	MAX087K	
29163	MDP3087K	
29163	MDP3087KP	
29165	MAX165K	
29165	MDP3165K	
29167	MAX167K	
29167	MDP3167K	
29169	MDP3169K	
29169	MDP5093	
29169	MDP5093SK	
29171	MAX171K	
29171	MDP3171K	
29173	MAX173K	
29173	MDP3173K	
29173	MDP5102	
29173	MDP5102SK	
29173	MDP5106	
29173	MDP5106PPRK	
29173	MDP5106SK	
29174	MAX174K	
29174	MDP3174K	
29174	MDP3174KWI	
29174	MDP5101	
29174	MDP5101PPRK	
29174	MDP5101SK	

	OE	
29174	MDP5104	
29174	MDP5104PPRK	
29174	MDP5104SK	
29174	MDP5119PPRK	
29174	MDP5119SK	
29175	MAX175K	
29175	MDP3175K	
29177	MDP3169K	
29177	MDP5093SK	
29177	MDP5126	
29179	MAX087K	
29179	MDP3087K	
29179	MDP3087KP	
29179	MDP9000	
29181	MDP3181K	
29183	MAX148K	
29183	MDP3148K	
29185	MDP3143K	
29187	MDP5122	
29195	MDP3195K	
29197	MAX095K	
29197	MDP3095K	
29202	MAX087K	
29202	MDP3087K	
29202	MDP3087KP	
29203	MAX173K	
29203	MDP3173K	
29203	MDP5102SK	
29203	MDP5106PPRK	
29203	MDP5106SK	
29207	MDP3181K	
29211	MDP5117	
29211	MDP5117SK	
29211	MDP5118K	
29218	MAX174K	
29218	MDP3174K	
29218	MDP3174KWI	
29218	MDP5101PPRK	
29218	MDP5101SK	
29218	MDP5104PPRK	
29218	MDP5104SK	
29218	MDP5119	
29218	MDP5119PPRK	
29227	MDP3227K	
29228	MDP3228K	
29244	MAX244K	
29244	MDP3244K	
29246	MAX246K	

	OE	
29246	MDP3246K	
29253	MAX087K	
29253	MDP3087K	
29253	MDP3087KP	
29256	MDP3256	
29267	MDP3267K	
29273	MAX174K	
29273	MDP3174K	
29273	MDP3174KWI	
29273	MDP5101PPRK	
29273	MDP5101SK	
29273	MDP5104PPRK	
29273	MDP5104SK	
29273	MDP5119PPRK	
29277	MAX125K	
29277	MDP3125K	
29277	MDP5057SK	
29279	MDP3279K	
29306	MAX165K	
29306	MDP3165K	
29307	MAX167K	
29307	MDP3167K	
29308	MAX171K	
29308	MDP3171K	
29328	MDP3328K	
29332	MDP5332SK	
29331	MAX087K	
29331	MDP3087K	
29331	MDP3087KP	
29334	MDP5127	
29394	MDP3394K	
29415	MDP3415K	
29429	MDP3429K	
29498	MDP3498	
29747	MDP3747	
29835	MDP3835K	
29835	MDP5040	
ZF		
501211881	MDP5090	
501213827	MDP5088	
501213830	MDP5065	
501213830	MDP5066	
501215021	MDP5099	
501215027	MDP5056	
501215036	MDP5097	

*Product definition found in buyers guide



1



2



3



4



5





1



2



3



4



5







Vehicle models, trademarks, brands and names depicted herein are the property of their respective owners, and may not be associated with Cummins Inc. and Meritor, Inc. or its affiliates.



Cummins Inc.
Box 3005
Columbus, IN 47202-3005
U.S.A.

cummins.com

SP-2420
Bulletin 6715482 Produced in U.K. Rev. 8/26
©2026 Meritor, Inc.