


PRERELEASE ISSUE



MERITOR® BRAKE DISCS



August 2026

Meritor powered by



Available in these languages at meritorpartsexpress.com

Language		Catalogue Title
	English	Meritor Brake Discs
	Français	Disques de frein Meritor
	Deutsch	Meritor-Bremsscheiben
	Italiano	Dischi dei freni Meritor
	Nederlands	Meritor-remschijven
	Español	Discos de freno Meritor
	Polski	Tarcze hamulcowe Meritor
	Русский	Тормозные диски Meritor

MERITOR® BRAKE DISCS



Built on a strong heritage of braking excellence. Meritor's comprehensive brake disc range is engineered to deliver consistent, reliable performance across all commercial vehicle applications.

Our proven expertise in braking systems, combined with continuous investment in product development, ensures we offer a market leading friction portfolio to meet the demanding needs of today's commercial vehicle fleets.

MERITOR® GENUINE

GENUINE

Features and Benefits:

- Developed in partnership with OE manufacturers for bespoke and vehicle specific brake system applications.
- Engineered to meet the precise specifications and performance standards defined by the vehicle manufacturer.
- Ensures full confidence in part compatibility, delivering a true like for like replacement solution.
- Homologated to EEC Regulation 13 braking standards, supporting safety and compliance across all applications.



MERITOR® ALLFIT

ALLFIT


Features and Benefits:

- ECE R90 certified, ensuring compliance with OE level braking performance standards.
- Optimised weight, geometry and venting designs deliver predictable, stable braking across a wide range of operating conditions.
- Manufactured from high quality G3000 grey cast iron, providing strong resistance to fade, heat related stress, and heavy load cycle wear for long lasting durability.



ECE R90 CERTIFIED

Produced in world-class IATF 16949 certified facilities, every Meritor disc is manufactured to stringent quality standards. All products are ECE R90 certified as required, and carry the trusted Meritor brand marking for clear product identification and assurance.



MERITOR® BRAKE PADS

As part of our ongoing commitment to providing braking solutions for vehicles of all ages and duty cycles, Cummins offers a comprehensive range of brake pads to complement our disc range.

GENUINE



Designed and developed in conjunction with vehicle manufacturers for Meritor specific brake system applications, the Genuine range of brake pads is manufactured to the same specifications as the OE.

PREMIUM



Our premium brake pad range offers OE equivalent quality and performance, featuring high-specification friction materials and precision-engineered components. Tailored to specific vehicle applications, it delivers dependable braking performance.

ALLFIT



The Allfit brake pad range provides a quality, aftermarket solution at an affordable price.

CONTENTS



1.	CATALOGUE USER GUIDE	4
2.	GLOSSARY	7
3.	APPLICATIONS	9
4.	BUYERS GUIDE	51
5.	CROSS REFERENCES	117

1



2



3



4



5





Using This Catalogue

This catalogue has been designed to make it as easy as possible for you to make the correct product identification for your vehicles and applications. The most reliable method of identification is to use the Cross Reference section (Section 5). Although, it is always advisable to match the physical features of your brake disc against the Buyers Guide (Section 4). All application details are provided as guidance only, as vehicle and trailer manufacturers may change brake disc fitments without notice.

APPLICATIONS – SECTION 3

Vehicle Manufacturer, Type and Model	Fitting Position	Build Date	Meritor Reference
	  		 GENUINE ALLFIT
Volvo			
			
FL6 Series - FL6.08, 6.09, 6.10, 6.11		01/87 >> 02/90	MBR5021

BUYERS GUIDE – SECTION 4

Genuine Brake Discs



Allfit Brake Discs

Meritor Reference

Brake Disc
End Elevation

Refer to Glossary
for Description

Brake Disc
Side Elevation

MBR###											
	<table><tr><td>Disc Type (Solid/Vented)</td><td>Solid</td></tr><tr><td>Position</td><td></td></tr><tr><td>Number of Holes</td><td>14</td></tr><tr><td>Bolt Hole Circle Diameter (mm)</td><td>275</td></tr><tr><td>Warranty Period (Months)</td><td>24</td></tr></table>	Disc Type (Solid/Vented)	Solid	Position		Number of Holes	14	Bolt Hole Circle Diameter (mm)	275	Warranty Period (Months)	24
Disc Type (Solid/Vented)	Solid										
Position											
Number of Holes	14										
Bolt Hole Circle Diameter (mm)	275										
Warranty Period (Months)	24										
	<table><tr><td>A Outer Diameter (mm)</td><td>375</td></tr><tr><td>B Thickness (Max/Min) (mm)</td><td>45/39</td></tr><tr><td>C Inner Diameter (mm)</td><td>162</td></tr><tr><td>D Height (mm)</td><td>116</td></tr><tr><td>E Centering Diameter (mm)</td><td>215</td></tr></table>	A Outer Diameter (mm)	375	B Thickness (Max/Min) (mm)	45/39	C Inner Diameter (mm)	162	D Height (mm)	116	E Centering Diameter (mm)	215
A Outer Diameter (mm)	375										
B Thickness (Max/Min) (mm)	45/39										
C Inner Diameter (mm)	162										
D Height (mm)	116										
E Centering Diameter (mm)	215										

Brake Disc
Information

Brake Disc
Dimensions



CROSS REFERENCES – SECTION 5

Vehicle
Manufacturer

Manufacturer
Reference

Meritor
Reference

		
Renault		
5000297808		MBR2693
5000450158		MBR2693
5000545242		MBR2693
5001667798		MBR5141
5001864498		MBR5140
5010216437		MBR5056
5010216437		MBR9008
5010216931		MBR5109
5010216932		MBR5095
5010260101		MBR5109
5010260102		MBR5095
5010422262		MBR5117
5010422263		MBR5112
5010422264		MBR5101
5010422363		MBR5056
5010422363		MBR9008
5010422364		MBR5101

		
5010422593		MBR5056
5010422593		MBR9008
5010525014		MBR5104
5010525014		MBR5119
5010525015		MBR5115
5010525308		MBR5117
5010525326		MBR9011
5010525362		MBR5115
5010525508		MBR9012
5010598306		MBR5115
5021139169		MBR9018
5021170653		MBR9004
5021180772		MBR9018
5021200798		MBR1588
5021200800		MBR1761
5021200802		MBR1831
5021200803		MBR1832
5021200804		MBR2648

		
5021200805		MBR2649
5021200806		MBR2693
5021200808		MBR2695
5021200812		MBR5002
5021200813		MBR5003
5021200816		MBR5006
5021200817		MBR5010
5021200818		MBR5011
5021200819		MBR5012
5021200820		MBR5013
5021200821		MBR5014
5021200822		MBR5015
5021200823		MBR5016HD
5021200824		MBR5021
5021200825		MBR5025
5021200827		MBR5029
5021200828		MBR5031
5021200829		MBR5032

		
5021200840		MBR5046
5021200841		MBR5047
5021200842		MBR5048
5021200843		MBR5049
5021200858		MBR9014
5021200858		MBR9015
5021210521		MBR9017
7420515093		MBR5140
7421526754		MBR5142
7421866443		MBR5112
7421866446		MBR5112
7421867375		MBR5104
7421867375		MBR5119
7482194787		MBR5056
7482194787		MBR9008
7482421131		MBR5115
85103805		MBR5167
21024702		MDP3174K

1



2



3



4



5





1



2



3



4



5



GLOSSARY



	Description
	Bus
	Trailer
	Truck
	Refuse Vehicle
	Fire Engine
	Van
	Front
	Rear
	Front / Rear
	Vehicle Manufacturer, Type and Model
	Vehicle Manufacturer
	Build Date
	Caliper Applications
	Genuine Part
	Allfit Part
	Disc Quantity in Packaging
	Generic Images
	Disc includes Fitting Kit
 7.1	Manufacturers' numbers are for reference only
 7.2	Brake disc images shown are for illustration purposes only and may not be an exact representation of the product

1



2



3



4



5





1



2



3




4



5





1



2



3



4



5





1



2



3



4



5



Alexander Bus	11	MCV	32
Ayats	11	MCW	32
Benalu Trailers	11	Menarinibus (BredaMenarinibus, Industria Italiana	
Berkhof	11	Autobus, Bredabus)	32
Beulas	11	Mercedes	32
BMC	11	Mercedes Axles	34
Bova	12	Mercedes PSV's (Inc Evobus)	34
BPW Axles	12	Meritor (Inc Lucas, Rockwell, ROR)	35
BYD (includes BYD ADL)	13	Neoplan (Inc Auwärter)	35
Caetano	13	Nogebus	36
Cobus	13	Optare (Switch Mobility, NABI)	37
DAF PSV's (Inc Leyland DAF)	13	Otokar	37
DAF Trucks (Inc Leyland DAF)	14	Plaxton	37
Den Oudsten	14	Raba	38
Dennis	15	Renault Trucks	38
Dennis PSV's (inc Alexander Dennis, Dennis Eagle)	15	Renault Trucks PSV's	41
Discos	15	ROR	42
ERF	16	SAF	42
Esker	17	SAF / Sauer	42
Estepe	17	Scania	43
Fontenax	17	Scania PSV's (includes Irizar)	43
Freightliner	17	Schmitz (CargoBull)	44
Fruehauf (Inc Crane Fruehauf, GT Trailers)	17	Seddon Atkinson	44
Fuwa K Hitch	18	Setra (inc Kassbohrer)	44
Granning Lynx	18	Sitcar	44
Hendrickson	18	Solaris Bus	45
Heuliez	18	Tecma	45
Ikarus	19	Temsa	45
Isuzu	19	Trailer Axles (with Knorr, Meritor, Wabco Brakes)	45
Iveco (Inc Iveco Ford)	19	Trenkamp & Gehle (Inc Gigant, SAE, SMB, Dupillier)	46
Iveco PSV's (Inc Irisbus, Karosa, Recreo)	24	Valx	46
Jost	26	Van Hool	46
Kässbohrer	26	VDL (includes Bova, Jonckheere)	48
King Long (Golden Dragon, Golden Journey)	26	Volvo	48
Lecinena	26	Volvo PSV's	49
Leyland	26	Wrightbus	49
MAN	27	York Trailers (Hendrickson)	49
MAN PSV's	30	ZF Axles	49



	  			
				
Alexander Bus				
				
ALX400 - 10.5m		01/00 >>		MBR5108
DB 250 Mk II - 10.5m - DAF chassis		01/05 >>		MBR5032
DB 250 Mk II		01/05 >>		MBR5016HD
Ultra Low Floor Bus - D LISA caliper		01/99 >> 12/02		MBR5056
Ayats				
				
Atlantis - ZF axle		01/01 >>		MBR5032
Bravo - Scania axle		01/96 >>		MBR5025
Bravo		01/96 >>		MBR5032
Platinum - Scania axle		01/00 >>		MBR5025
Platinum		01/00 >>		MBR5032
Benalu Trailers				
				
With Knorr brakes - SB7000		01/14 >>		MBR5016HD
Berkhof				
				
Axial 50 - 12m Coach - Dennis Chassis		01/97 >>	MBR9010	
Radial - 12m Coach - Dennis Chassis		01/97 >>	MBR9010	
				
Excellence - 3000HD - Scania axle		01/96 >>		MBR5025
Beulas				
				
Cygnas		01/97 >>		MBR5016HD
PSV's - Stelar		01/07 >>		MBR5066
		01/07 >>		MBR5070
BMC				
				
Probus 11T Bus		01/97 >>		MBR5013
School Bus - 1100 FE		01/03 >>		MBR5013

- Refer to Buyers Guide



1



GENUINE

ALLFIT

BMC



518		01/97 >>		MBR5013
628		01/97 >>		MBR5032
Condor		01/04 >>		MBR5032
Falcon		01/03 >>		MBR5032
Hawk		01/97 >>		MBR5013

Bova



Futura - FHD		01/86 >> 01/94		MBR2695
ZF Axle - Knorr SB7000 caliper		01/90 >>		MBR5048

BPW Axles



Eco Plus - ABS		01/98 >>		MBR5061
		01/98 >> 05/03		MBR5025
		05/03 >>		MBR5025
Eco Plus - non ABS		01/98 >> 05/03		MBR5048
		05/03 >>		MBR5025
		05/03 >>		MBR5105
Eco Plus - with ABS		01/98 >>		MBR5047
SB3745 - ABS		01/98 >>		MBR5061
SB4309 - ABS		01/98 >> 05/03		MBR5025
SB4309 - non ABS		01/98 >> 05/03		MBR5048
		06/03 >>		MBR5105
SB4345 - non ABS		>> 06/03		MBR5048
		06/03 >>		MBR5105
SH Series - SK7000 caliper				MBR5180
SH Series - with ABS location		>> 04/03		MBR5047
		05/03 >>		MBR5047
SK7 9T axles - non ABS		06/03 >>		MBR5105
SKH, SKM - 10 hole disc - ABS		>> 04/03		MBR5102
		04/03 >>		MBR5102

- Refer to Buyers Guide



		  		 GENUINE ALLFIT	
...BPW Axles					
					
SKH, SKM - 10 hole disc - non ABS		>> 04/03		MBR5060	
		04/03 >>		MBR5099	
SKH, SKM - 8 hole disc - ABS		>> 04/03		MBR5062	
		04/03 >>		MBR5062	
SKH, SKM		04/03 >>		MBR5071	
TSB 4309 - SH		01/08 >>		MBR5105	
BYD (Inc BYD ADL)					
					
eBus, eCoach - K series 18m		09/10 >>		MBR5032	
eBus, eCoach - K series 6m → 14m		09/10 >>		MBR5032	
Caetano					
					
Cutlass - with Dennis chassis - Knorr brakes		01/01 >>		MBR5183	
Cutlass		01/97 >>	MBR9010		
Enigma - 12m Dennis Chassis		01/97 >>	MBR9010		
Enigma - 12m MAN chassis		01/01 >>		MBR5068	
Enigma - with Dennis chassis - Knorr brakes		01/01 >>		MBR5183	
		01/01 >>		MBR5184	
Porto - Dennis Chassis		01/97 >>	MBR9010		
Cobus					
					
3000		10/04 >>		MBR5066	
DAF PSV's (Inc Leyland DAF)					
					
DB250 MkII		01/05 >>		MBR5016HD	
MB - 220		01/89 >>		MBR2695	
MB - 230		01/89 >>		MBR2695	
SB - 2300		01/86 >>		MBR2695	
SB - 2305		01/87 >>		MBR2695	
SB - 3000		01/89 >>		MBR2695	
SB 2000 Series - 2300 / 2305		01/89 >>		MBR5032	

- Refer to Buyers Guide





GENUINE

ALLFIT

...DAF PSV's (Inc Leyland DAF)



SB, SBK, SBR 3000 Series		01/89 >>		MBR5032
		01/87 >>		MBR5032
SBG - 220		01/89 >>		MBR2695
SBR - 3000		01/89 >>		MBR2695
SKB - 3000		01/89 >>		MBR2695

DAF Trucks (Inc Leyland DAF)



45 Series - FA45.120 - FA45.210 6.2t to 7.7t		01/91 >>		MBR1832
45 Series - FA45.130 - FA45.210 10t to 11t		01/91 >>		MBR5006
55 Series - FA55.150 - FA55.230		01/95 >>		MBR5049
F Series - FA1000, FA1005		01/87 >>		MBR5006
FA45 Series - FA45		01/96 >> 01/00		MBR5049
		01/96 >> 01/00		MBR5006
FA55 Series - FA55		01/96 >> 01/00		MBR5049
		01/96 >> 01/00		MBR5006
LF 45 Series - 12t - Pan 17 caliper		01/01 >>		MBR5103
LF 45 Series - FA 45.130 -> FA 45.250 - 7.5T - non ABS		01/01 >> 01/14		MBR5097
LF 45 Series - FA 45.130 -> FA 45.250 - 7.5T - PAN 17 caliper		01/01 >> 01/14		MBR5100
LF 55 Series - FA 55.160 -> FA.55.300 - MAXX 19 caliper		01/01 >>		MBR5104
		01/01 >>		MBR5106
LF 55 Series - FA 55.160 -> FA.55.300 - PAN 19-1 caliper		01/01 >>		MBR5104
		01/01 >>		MBR5106
LF 55 Series - FA 55.160 -> FA.55.300 - PAN 19-2 caliper		01/01 >>		MBR5104
		01/01 >>		MBR5106
LF Series - LF 45.130, LF 45.150, LF 45.170, LF 45.180, LF 45.220		01/01 >> 01/06		MBR5103
LF Series - LF 45.140, LF 45.160, LF 45.180, LF 45.210, LF 45.220, LF 45.250		01/06 >>		MBR5103
LF Series (05/13 ->) - FA, FT 150 -> 320 - 13T -> 16T		05/13 >>		MBR5104
		05/13 >>		MBR5106
Wabco brakes - PAN 17				MBR5201

Den Oudsten



PSV's's Almere City Bus - DX225 caliper		01/99 >> 12/02		MBR5124
---	--	----------------	--	---------

- Refer to Buyers Guide



	  			
			GENUINE	ALLFIT
Dennis				
				
Knorr brakes - SB7				MBR5196
				
Fire Engines - Dagger		01/00 >>		MBR5066
Sabre		01/95 >>	MBR9010	
				
Refuse Vehicles - Elite 2 -> 6 - 240 -> 340 - Rear Steering Axle		01/08 >>		MBR5128
Elite - 2		01/00 >>	MBR9010	
Dennis PSV's (Inc Alexander Dennis, Dennis Eagle)				
				
Arrow		01/95 >>	MBR9010	
DB250 MkII		01/05 >>		MBR5016HD
Dart		06/02 >>		MBR5185
Dart		06/02 >>		MBR5186
Enviro 200 Dart		04/06 >>		MBR5185
Enviro 200 Dart		04/06 >>		MBR5186
Enviro 300		04/06 >>		MBR5185
Enviro 300		04/06 >>		MBR5186
Enviro Line - R200, R300, R345, R420, R500		01/02 >>		MBR5183
Enviro Line - R200, R300, R345, R420, R500		01/02 >>		MBR5106
Javelin		01/97 >> 01/00	MBR9010	
Lance SLF		01/95 >>		MBR5076
Panther - non ABS		01/99 >>		MBR5184
Panther		01/99 >>		MBR5183
R Series - non ABS		01/99 >>		MBR5184
R Series		01/99 >>		MBR5183
Trident II - non ABS		01/01 >>		MBR5184
Trident II		01/01 >>		MBR5183
Discos				
				
Haldex brakes - DB20		01/00 >>		MBR5016HD
Knorr Brakes - SB5000		01/99 >>		MBR5070
Knorr Brakes - SB6000		01/99 >>		MBR5071

 - Refer to Buyers Guide

1



2



3



4



5





1



GENUINE

ALLFIT

...Discos



Knorr Brakes - SB6000		01/99 >>		MBR5077
Knorr Brakes - SB7000		01/99 >>		MBR5016HD
NR Series - Knorr Brakes - SB7000		01/99 >>		MBR5016HD
TE, TZ - Knorr Brakes - SB7000		01/99 >>		MBR5016HD
TZ Series - Knorr Brakes - SB6000		01/99 >>		MBR5071
TZ Series - Knorr Brakes - SB7000		01/99 >>		MBR5016HD
Wabco Brakes - MAXX 19		01/00 >>		MBR5071
Wabco brakes - MAXX 22T		01/00 >>		MBR5016HD
Wabco Brakes - PAN 19-1		01/00 >>		MBR5071
Wabco Brakes - PAN 22		01/00 >>		MBR5016HD
Wabco brakes - PAN 22-1		01/00 >>		MBR5016HD

ERF



C Series - C38, C40		01/82 >> 12/86		MBR5066
		01/82 >> 12/86		MBR5070
ECL Series - RD3, TP3		11/99 >>		MBR5057
		11/99 >>		MBR5014
		11/99 >>		MBR5068
ECL Series - RD3, TP3 - D3 caliper		11/99 >>		MBR5057
		11/99 >>		MBR5068
ECM Series - MTP4		11/99 >>		MBR5057
		11/99 >>		MBR5068
ECM Series - RD2		11/99 >>		MBR5057
		11/99 >>		MBR5068
ECM Series - RD2 - D3 caliper		11/99 >>		MBR5057
		11/99 >>		MBR5068
ECM Series - RR3, RDRS3		11/99 >>		MBR5057
		11/99 >>		MBR5014
ECM Series - RR3, RDRS3 - D3 caliper		11/99 >>		MBR5068
		11/99 >>		MBR5057
ECM Series - RR3, RDRS3 - SB7000 / SN7000 caliper		11/99 >>		MBR5068

- Refer to Buyers Guide



	  		  	
...ERF				
				
ECS, ECT, ECX Series - 10 → 32 Series		11/99 >>		MBR5057
		11/99 >>		MBR5014
		11/99 >>		MBR5068
ECS, ECT, ECX Series - 10 → 32 Series - D3 caliper		11/99 >>		MBR5057
		11/99 >>		MBR5068
ECS, ECT, ECX Series - 10 → 32 Series - SB7000 / SN7000 caliper		11/99 >>		MBR5057
		11/99 >>		MBR5068
Esker				
				
Cimo XL - 1523		01/07 >>		MBR5077
Cimo XL - 1523		01/07 >>		MBR5071
Divo Cityliner Eurorider		01/90 >>		MBR6037
Touring - 1523		01/98 >>		MBR5077
Touring - 1523		01/98 >>		MBR5071
Touring XL		01/07 >>		MBR5016HD
Estepe				
				
		01/10 >>		MBR5066
Fontenax				
				
Iveco axle - SB7000 caliper		01/98 >>		MBR6036
Mercedes axle - SB6000 caliper		01/98 >>		MBR5071
Mercedes axle - SB7000 caliper		01/98 >>		MBR5016HD
Freightliner				
				
Argosy / Sterling		01/12 >>		MBR5057
Fruehauf (Inc Crane Fruehauf, GT Trailers)				
				
Haldex brakes - DB20		09/96 >>		MBR5064
Knorr brakes - SB6000		01/98 >>		MBR5096
Knorr brakes - SB7000		09/96 >>		MBR5064

- Refer to Buyers Guide

1



2



3



4



5





1



GENUINE

ALLFIT

...Fruehauf (Inc Crane Fruehauf, GT Trailers)



Knorr brakes - SB7000 / SN7000 caliper		09/96 >>		MBR5064
Knorr brakes - SB7000 / SN7000 caliper		01/98 >>		MBR5064
Meritor brakes - DX195 Axle		01/99 >>		MBR5073
Meritor brakes - VGT 195 Axle		01/04 >>		MBR5073
Wabco brake - MAXX 22T		01/04 >>		MBR5064
Wabco brake - PAN 22		01/98 >>		MBR5064
Wabco brake - PAN 22-1		01/99 >>		MBR5064
Wabco brakes - MAXX 19		01/04 >>		MBR5096
Wabco brakes - MAXX 19		01/99 >>		MBR5096
Wabco brakes - PAN 19-1		01/99 >>		MBR5096

Fuwa K Hitch



Knorr brakes - SN7000				MBR5048
Wabco brakes - PAN 19-1 - KF, KK, TN		01/02 >>		MBR5096

Granning Lynx



Knorr brakes - SB7000 caliper		01/00 >>		MBR5016HD
-------------------------------	--	----------	--	-----------

Hendrickson



Knorr brakes - SB7000		01/99 >>		MBR5016HD
Knorr brakes - SB7000 / SN7000 caliper		01/99 >>		MBR5016HD
Knorr brakes - SB7000 / SN7000 caliper I with flat disc		01/99 >>		MBR5025
Knorr brakes - SB7000 - with flat disc		01/99 >>		MBR5025

Heuliez



GX117, GX127, GX137 - Access bus		01/08 >>		MBR5056
		01/93 >>		MBR5056
GX317, GX327, GX337 - Access bus		01/08 >>		MBR5056
		01/93 >>		MBR5056
GX417, GX427, GX437 - Access bus		01/08 >>		MBR5056

- Refer to Buyers Guide



	  			
				
Ikarus				
				
200 Series (84 ->)		01/93 >>		MBR5076
Isuzu				
				
Citiport - 12m		01/21 >>		MBR5032
Citiport - 18m		01/21 >>		MBR5032
Iveco (Inc Iveco Ford)				
				
Brembo brakes				MBR5200
				MBR5199
Cargoplus - 18T		02/02 -		MBR2649
Cargoplus - 7.5T		02/02 -		MBR2648
		02/02 -		MBR2648
EuroCargo - 100E.17, 100E.17P, 100E.17FP, 100E.18, 100E.18FP, 100E.18P, 100E.21, 100E.21FP, 100E.21P		01/00 - 01/07		MBR2649
EuroCargo - 100E.18, 100E.18FP, 100E.18P, 100E.22, 100E.22FP, 100E.22P		01/05 - 01/07		MBR2649
EuroCargo - 110 E Series - E15 -> E28 Tector		01/06 -		MBR6025
EuroCargo - 110 E Series - E15, E17, E18, E21		09/00 - 01/06		MBR6025
EuroCargo - 110E -> 150E		05/13 -		MBR6025
EuroCargo - 110E15, E18, E23		09/91 - 08/00		MBR5002
EuroCargo - 110E15, EL17, E18, EL21, E23, E24, E28		09/91 - 08/00		MBR5002
EuroCargo - 120 E Series - E15 -> E28 Tector		01/06 -		MBR6025
EuroCargo - 120 E Series - E15, E17, E18, E24, E28 Tector		09/00 - 01/06		MBR6025
EuroCargo - 130, 135, 140 E Series - E18 -> E28 Tector - SB 6000		01/06 -		MBR6029
		01/06 -		MBR6028
EuroCargo - 130E, 135E - E15, E17, E18, E21, E23, E24, E28 Tector - ABS - SB6		09/00 - 01/06		MBR5116
EuroCargo - 130E, 135E - E15, E17, E18, E21, E23, E24, E28 Tector - non ABS - SB6		09/00 - 01/06		MBR6029
EuroCargo - 130E.18, 130E.18FP, 130E.18P, 130E.21, 130E.21P, 130E.24, 130E.24FP, 130E.24P, 130E.28, 130E.28FP, 130E.28P		01/00 - 01/07		MBR6027
EuroCargo - 130E15, E18, E23, E24, E28		01/91 - 01/00		MBR5002
EuroCargo - 135E18, E23		09/91 - 08/00		MBR5002
EuroCargo - 140 E Series - E18, E24, E28 - ABS - SB 6000		09/00 - 01/06		MBR5116
EuroCargo - 140 E Series - E18, E24, E28 - non ABS - SB 6000		09/00 - 01/06		MBR6029

 - Refer to Buyers Guide

1



2



3



4



5





GENUINE

ALLFIT

...Iveco (Inc Iveco Ford)



EuroCargo - 140E18, E21, E23, E24, E27		09/91 - 08/00		MBR5002
EuroCargo - 150 E Series - E15, E18, E24, E28 - SB6000 caliper		09/00 - 01/06		MBR6026
EuroCargo - 150 E Series - E18 -> E28 Tector - SB6000 caliper		01/06 -		MBR6029
		01/06 -		MBR6028
EuroCargo - 160 E Series - E18 -> E30 Tector - SB6000 caliper		01/06 -		MBR6029
		01/06 -		MBR6028
EuroCargo - 170 E Series		09/00 - 01/06		MBR6036
		09/00 - 01/06		MBR6037
EuroCargo - 170, 175, 176, 179 E Series		08/98 - 09/00		MBR6036
		08/98 - 09/00		MBR6037
EuroCargo - 175 E Series		09/00 - 01/06		MBR6036
		09/00 - 01/06		MBR6037
EuroCargo - 176 E Series		09/00 - 01/06		MBR6036
		09/00 - 01/06		MBR6037
EuroCargo - 179 E Series		09/00 - 01/06		MBR6036
		09/00 - 01/06		MBR6037
EuroCargo - 180 E Series - E21 -> E32 Tector		01/06 -		MBR6036
		01/06 -		MBR6037
EuroCargo - 180 E Series - E21, E24, E28		09/00 - 01/06		MBR6036
		09/00 - 01/06		MBR6037
EuroCargo - 225 E Series - E21 -> E30 Tector		01/06 -		MBR6036
EuroCargo - 230 E Series - E21 -> E30 Tector		01/06 -		MBR6036
EuroCargo - 260 E Series - E21 -> E30 Tector		01/06 -		MBR6036
EuroCargo - 260, 280 E Series - E23, E27, E28		09/00 - 01/06		MBR6036
		09/00 - 01/06		MBR6037
EuroCargo - 320 E Series - E27, E28		09/00 - 01/06		MBR6036
		09/00 - 01/06		MBR6037
EuroCargo - 325 E Series		08/98 - 09/00		MBR6036
		08/98 - 09/00		MBR6037
		09/00 - 01/06		MBR6036
		09/00 - 01/06		MBR6037

- Refer to Buyers Guide



					
					
...Iveco (Inc Iveco Ford)					
					
EuroCargo - 390 E Series		08/98 - 09/00		MBR6036	
		08/98 - 09/00		MBR6037	
		09/00 - 01/06		MBR6036	
		09/00 - 01/06		MBR6037	
EuroCargo - 60E12, 60E14, 65E12, 65E14, 75E12, 75E14, TECTOR		09/91 - 01/94		MBR2648	
		01/94 - 08/00		MBR2648	
EuroCargo - 75E.13, 75E.13P, 75E.14, 75E.15, 75E.15P, 75E.17, 75E.17P, 75E.18, 75E.18P		01/00 - 01/07		MBR2648	
EuroCargo - 75E.14P, 75E.16, 75E.16P, 75E.18, 75E.18P		01/05 - 01/07		MBR2648	
EuroCargo - 80E15, 80E15R, 100E15, 100E18, 100E21, 109E14 & ZETA 95.14		06/91 - 06/94		MBR2649	
		05/97 - 01/98		MBR2649	
		01/99 -		MBR2649	
EuroCargo - E260E23, E28		09/91 -		MBR5002	
EuroMover - 190 E -> 260 E Series - E21 -> E30 Tector		01/06 -		MBR6036	
EuroStar - LD180 E 38 -> E 52 - VIN 4196457 / C044258 ->		01/93 - 02/02		MBR6036	
EuroStar - LD190 E 38 -> E 52 - VIN 4196457 / C044258 ->		01/93 - 02/02		MBR5063	
		01/93 - 02/02		MBR6036	
		01/93 - 02/02		MBR6037	
EuroStar - LD240 E 38 -> E 52		01/93 - 02/02		MBR5063	
		01/93 - 02/02		MBR6036	
		01/93 - 02/02		MBR6037	
EuroStar - LD260 E 38 -> E 52		01/93 - 02/02		MBR5063	
		01/93 - 02/02		MBR6036	
		01/93 - 02/02		MBR6037	
EuroStar - LD380 E -> LD520 E		01/93 - 02/02		MBR5063	
		01/93 - 02/02		MBR6036	
		01/93 - 02/02		MBR6037	
EuroTech - MH, MP Series - 180 -> 190 (E24 -> E43)		01/92 -		MBR5063	
		01/92 -		MBR6036	
		01/97 -		MBR5063	
		01/97 -		MBR6036	
		01/97 -		MBR6037	

 - Refer to Buyers Guide



GENUINE

ALLFIT

...Iveco (Inc Iveco Ford)



EuroTech - MH, MP Series - 240 → 260 (E24 → E43)



01/92 -

MBR5063



01/92 -

MBR6036



01/97 -

MBR5063



01/97 -

MBR6036



01/97 -

MBR6037

EuroTech - MH, MP Series - 260E38, 260E42



01/92 -

MBR5063



01/92 -

MBR6036



01/97 -

MBR5063



01/97 -

MBR6036



01/97 -

MBR6037

EuroTech - MH, MP Series - 400 → 450 (E34 → E43)



01/92 -

MBR6036



01/97 -

MBR6036



01/92 -

MBR5063



01/97 -

MBR5063



01/97 -

MBR6037

EuroTech - MH, MP Series - 4300 → 4500



01/02 -

MBR5063



01/02 -

MBR6036

EuroTech - MT Series - 180 → 400 (E24 → E43)



01/92 -

MBR6036



01/97 -

MBR6036



01/97 -

MBR6037

EuroTrakker - MP Series Cursor 8, Cursor 10 - 180 → 450 (E24 → E48)



01/92 -

MBR6036



01/93 -

MBR6036



01/93 -

MBR6037

EuroTrakker - MP Series Cursor 8, Cursor 10 - 260 → 720 (E30 → E48)



01/93 -

MBR6036



01/93 -

MBR6037

S-Way (Inc NP Models) - 190 → 440 - RIGIDS, Tippers, Tractors



01/19 -

MBR6036



01/19 -

MBR5063

Stralis - Cursor 10 AD, AS, AT Series - 190



02/02 -

MBR5063



02/02 -

MBR6036



02/02 -

MBR6037

- Refer to Buyers Guide



				
				
...Iveco (Inc Iveco Ford)				
				
Stralis - Cursor 10 AD, AS, AT Series - 260		02/02 -		MBR5063
		02/02 -		MBR6036
		02/02 -		MBR6037
Stralis - Cursor 10 AD, AS, AT Series - 400, 440		02/02 -		MBR5063
		02/02 -		MBR6036
		02/02 -		MBR6037
Stralis - Cursor 13 AD, AS, AT Series - 190		02/02 -		MBR5063
		02/02 -		MBR6036
		02/02 -		MBR6037
Stralis - Cursor 13 AD, AS, AT Series - 260		02/02 -		MBR5063
		02/02 -		MBR6036
		02/02 -		MBR6037
Stralis - Cursor 13 AD, AS, AT Series - 260 → 800		02/02 -		MBR5063
		02/02 -		MBR6036
Stralis - Cursor 13 AD, AS, AT Series - 400, 440		02/02 -		MBR5063
		02/02 -		MBR6036
		02/02 -		MBR6037
Stralis - Cursor 8 AD, AS, AT Series - 190		02/02 -		MBR5063
		02/02 -		MBR6036
		02/02 -		MBR6037
Stralis - Cursor 8 AD, AS, AT Series - 260		02/02 -		MBR5063
		02/02 -		MBR6036
		02/02 -		MBR6037
Stralis - Cursor 8 AD, AS, AT Series - 400, 440		02/02 -		MBR5063
		02/02 -		MBR6036
		02/02 -		MBR6037
SuperCargo - Rigid, Tippers, Tractors		01/00 -		MBR6036
Trakker - Cursor 8, 10 Series AD, AT - 190		09/04 -		MBR6036
		09/04 -		MBR6037
Trakker - Cursor 8, 10 Series AD, AT - 260		09/04 -		MBR6036
		09/04 -		MBR6037
Trakker - Cursor 8, 10 Series AD, AT - 260 → 740		02/02 -		MBR5063

 - Refer to Buyers Guide

1



2



3



4



5





1



GENUINE

ALLFIT

...Iveco (Inc Iveco Ford)



Trakker - Cursor 8, 10 Series AD, AT - 260 → 800		02/02 -		MBR6036
Trakker - Cursor 8, 10 Series AD, AT - 340 → 740		09/04 -		MBR6036
		09/04 -		MBR6037
Trakker - Cursor 8, 10 Series AD, AT - 340 → 740 - ABS		09/04 -		MBR6037
Trakker - Cursor 8, 10 Series AD, AT - 340 → 740 - non ABS		09/04 -		MBR6036
		09/04 -		MBR6037
X-Way - AD, AS, AT - 240 → 550		01/19 -		MBR5063
		01/19 -		MBR6036
Zeta - 60.12 - Eurocargo		01/00 -		MBR6025
Zeta - 65.12 - 79.14		01/83 -		MBR1761



Eurofire - 130E, 150E		09/91 >>		MBR5002
EuroFire - 130E, 140 E Series - E18, E24, E28 - ABS - SB6000 caliper		09/00 >>		MBR6026
EuroFire - 130E, 140 E Series - E18, E24, E28 - SB6000 caliper		09/00 >>		MBR6028
EuroFire - 150 E Series - E18, E24, E28 - ABS - SB6000 caliper		09/00 >>		MBR6026
EuroFire - 150 E Series - E18, E24, E28 - SB6000 caliper		09/00 >>		MBR6028
EuroFire - 160 E Series - E18, E24, E28 - ABS - SB6000 caliper		09/00 >>		MBR6026
EuroFire - 160 E Series - E18, E24, E28 - SB6000 caliper		09/00 >>		MBR6028



				MBR5194
--	--	--	--	---------

Iveco PSV's (Inc Irisbus, Karosa, Recreo)



Afriway - 26T Coaches		01/01 >>		MBR5068
BredaMenariniBus Strepavara				MBR5129
Cityclass 491,591 98 →				MBR5146
CityClass - DX225 caliper		01/99 >>		MBR5063
EuroCity, Euroschool - 12T → 15T - SB6000		09/00 >>		MBR6026
EuroCity, Euroschool - 12T → 15T - SB6000		09/00 >>		MBR6028
Euroclass 92 →				MBR5146
EuroRider		01/92 >>		MBR5016HD
Eurorider 92 →				MBR5146
Irisbus - Agora		01/95 >>		MBR5056

- Refer to Buyers Guide



		  		 GENUINE ALLFIT
...Iveco PSV's (Inc Irisbus, Karosa, Recreo)				
				
Irisbus - Ares		01/01 >>		MBR5057
		01/95 >>		MBR5056
		01/01 >>		MBR5016HD
		01/01 >>		MBR6037
		01/01 >>		MBR5068
Irisbus - Ares - D LISA caliper		01/95 >>		MBR5056
Irisbus - Arway 10.6m, 12m, 12.8m - Renault chassis		06/06 >>		MBR5056
Irisbus - Arway 15m - Renault chassis		06/06 >>		MBR5056
		06/06 >>		MBR5057
		06/06 >>		MBR5068
Irisbus - Citelis 10.5m, 12m, - Renault chassis		09/05 >>		MBR5056
Irisbus - Citelis 18m, - Renault chassis		09/05 >>		MBR5057
		09/05 >>		MBR5068
Irisbus - CityClass - DX225 caliper		01/99 >>		MBR5063
Irisbus - Crealis 12m, 12m NEO, - Renault chassis		01/05 >>		MBR5056
Irisbus - Crealis 18m, 18m NEO, - Renault chassis		01/05 >>		MBR5057
		01/05 >>		MBR5068
Irisbus - Domino HD, HDH - SB7000 / SN7000 caliper		10/03 >>		MBR6036
		10/03 >>		MBR6037
Irisbus - EuroPolis		01/96 >>		MBR6037
Irisbus - EuroRider		01/92 >>		MBR6026
		01/92 >>		MBR5016HD
		01/92 >>		MBR6037
Irisbus - Evadys - H, HD - ELSA 2 caliper		09/03 >>		MBR5056
Irisbus - Magelys - H, HD - ELSA 2 caliper		08/08 >>		MBR5056
Irisbus - Myway - 393.29 -> 399.35		08/98 >>		MBR6036
		08/98 >>		MBR6037
Irisbus - Scholabus 150 E		08/98 >>		MBR5063
		08/98 >>		MBR6036
		08/98 >>		MBR6037
Iveco				MBR5145

 - Refer to Buyers Guide



1



GENUINE

ALLFIT

...Iveco PSV's (Inc Irisbus, Karosa, Recreo)



Karosa, Recreo - 930, 930B, 930E, 940E		01/97 >>		MBR6037
Karosa, Recreo - Agora City Bus - Renault chassis		01/03 >>		MBR5057
		01/03 >>		MBR5068
Karosa, Recreo - City Bus - Renault chassis		01/93 >>		MBR5056
Karosa, Recreo - Transit Bus		01/93 >>		MBR5056
Myway 393.35 99 ->				MBR5146

Jost



Knorr brakes - SN6				MBR5071
--------------------	--	--	--	---------

Kässbohrer



S140		01/83 >>		MBR5003
S210		01/89 >>		MBR5003
S211		01/83 >>		MBR5003
S212		01/76 >>		MBR5003
S213		01/76 >>		MBR5003
S214		01/83 >>		MBR5003
S215		01/83 >> 01/90		MBR5003
S216		01/80 >>		MBR5003
S228		01/83 >> 01/89		MBR5003

King Long (Golden Dragon, Golden Journey)



XML, XMQ Series - Inter City Large Bus - ZF axle		09/07 >>		MBR5032
--	--	----------	--	---------

Lecinena



Knorr brakes - SB7000 / SN7000 caliper		01/98 >>		MBR5025
--	--	----------	--	---------

Leyland



Swift		01/87 >>		MBR5006
-------	--	----------	--	---------

- Refer to Buyers Guide



						
MAN						
						
E2000 - 30.314, 30.364, 30.414, 30.464, 33.364, 33.414, 33.464		01/97 >> 01/05			MBR5011	
E2000 - 32.314, 32.364, 35.414, 35.464		01/96 >> 01/05			MBR5011	
E2000 - 32.414, 32.464		01/97 >> 01/05			MBR5011	
E2000 - 41.464, 41.604, 50.414, 50.464		01/96 >> 01/04			MBR5011	
F2000 - 18.273, 19.603, 19.604		01/94 >> 01/01			MBR5011	
F2000 - 18.314, 18.373, 18.403, 18.423, 18.463, 19.233, 19.314, 19.364, 19.373, 19.403, 19.414, 19.423, 19.463, 19.464, 26.314, 26.364, 26.373, 26.403, 26.414, 26.423, 26.463, 26.464		01/94 >> 01/05			MBR5011	
F2000 - 22.273, 22.293, 22.314, 22.323, 22.364, 22.373, 22.403, 22.414, 22.423, 22.463, 22.464, 23.273, 23.293, 23.323, 23.343, 23.344, 26.233, 28.273, 28.293, 28.323, 28.343		01/94 >> 01/05			MBR5011	
F2000 - 23.314, 23.364, 23.403, 23.414, 23.463, 23.464, 26.314, 26.364, 26.373, 26.403, 26.414, 26.423, 26.463, 26.464		01/94 >> 01/04			MBR5011	
F2000 - 26.603, 26.604, 28.603		01/96 >> 01/01			MBR5011	
F2000 - 27.314, 27.364, 27.414, 27.464		01/94 >> 01/05			MBR5011	
F2000 - 27.603, 33.604		01/96 >> 01/01			MBR5011	
F2000 - 28.314, 28.364, 28.414, 28.464		01/94 >> 01/01			MBR5011	
F2000 - 32.293, 32.323, 32.343		01/95 >> 01/00			MBR5011	
		01/95 >> 01/01			MBR5011	
F2000 - 32.314, 32.364, 32.373, 32.403, 32.414, 32.423, 32.464, 35.293, 35.323, 35.343, 35.364, 35.373, 35.403, 35.414, 35.423, 35.463, 35.464, 37.314, 37.323, 37.343, 37.364, 37.414, 37.464, 41.323, 41.343, 41.364, 41.373, 41.403, 41.414, 41.423, 41.463, 41.464		01/95 >> 01/03			MBR5011	
F2000 - Inner Ø 200mm		01/94 >>			MBR5011	
F2000 Series - 18.270 → 19.610		01/94 >>			MBR5057	
		01/94 >>			MBR5068	
F2000 Series - 23.290 → 33.610		01/94 >>			MBR5057	
		01/94 >>			MBR5068	
F2000 Series - 23.290 → 40.463		01/94 >>			MBR5057	
		01/94 >>			MBR5068	
F2000 Series - 32.290 → 41.610		01/94 >>			MBR5057	
		01/94 >>			MBR5068	
F90 - with ABS		01/89 >> 01/96			MBR5078	

 - Refer to Buyers Guide

1



2



3



4



5





GENUINE

ALLFIT

...MAN



F90 Series - 15.192 → 19.502		01/86 >> 12/97		MBR5057
		01/86 >> 12/97		MBR5068
F90 Series - 19.192 → 27.502		01/86 >> 12/97		MBR5057
		01/86 >> 12/97		MBR5068
F90 Series - 19.192 → 33.502		01/86 >> 12/97		MBR5057
		01/86 >> 12/97		MBR5068
F90 Series - 27.242 →		01/86 >> 12/97		MBR5057
		01/86 >> 12/97		MBR5068
L2000 - 6.103 - 10.224 (without ABS)		10/93 >> 12/95		MBR5010
L2000 Series - 10 Series - 10.145 → 10.225		01/96 >>		MBR5092
L2000 Series - 12 Series - 12.185 → 12.225		01/96 >>		MBR5092
L2000 Series - 6 Series		01/96 >>		MBR5092
L2000 Series - 7 Series		01/96 >>		MBR5092
L2000 Series - 8 Series - 8.103 → 8.225		01/96 >>		MBR5092
L2000 Series - 9 Series - 9.145 → 9.225		01/96 >>		MBR5092
LE2000 Series - 140 → 240		01/00 >>		MBR5092
LE2000 Series - 14T → 18T		01/94 >>		MBR5057
LE2000 Series - LE2000 LE220B, LE250B, LE280B 14-18 tonne (10 hole disc)		01/00 >>		MBR5011
M2000 - L Series 18.224, 18.264, 18.294 (10 hole disc)		08/95 >> 09/00		MBR5011
M2000 - M Series 18.224, 18.264, 18.284, 25.224, 25.264 (10 hole disc)		08/95 >> 09/00		MBR5011
M2000 L - 18.224, 18.225, 18.255, 18.263, 18.264, 18.284, 18.285		01/95 >> 01/07		MBR5011
M2000 M - 26.224, 26.225, 26.255, 26.284, 26.285		01/95 >> 01/04		MBR5011
M2000, M2000 L, M2000 M, ME2000 Series - 14.163 → 20.290		08/95 >>		MBR5057
M2000, M2000 L, M2000 M, ME2000 Series - 18.223 → 19.290		08/95 >>		MBR5057
M2000, M2000 L, M2000 M, ME2000 Series - 20.223 → 26.290		08/95 >>		MBR5057
M90 - 17.192 - 24.272 (with ABS)		01/90 >> 01/97		MBR5078
M90 Series - 12 T Series		01/89 >> 06/96		MBR5068
M90 Series - 14 T Series		01/89 >> 06/96		MBR5068
M90 Series - 17 T Series		01/89 >> 01/96		MBR5068
ME2000 - 15 - 26 Series		01/96 >>		MBR5011
TGA - (with ABS)		03/00 >>		MBR5078

- Refer to Buyers Guide



		  		 GENUINE ALLFIT
...MAN				
				
TG-A - 18, 19 Series - 280 → 680 - non ABS		03/99 >>		MBR5068
		03/99 >> 09/01		MBR5068
		09/99 >>		MBR5068
TG-A - 18, 19 Series - 280 → 680 - VOK axle		03/99 >>		MBR5057
		09/99 >>		MBR5057
TG-A - 24, 26, 27, 28, 32, 33, 40 Series - 280 → 680 - exc VHK axle		03/99 >>		MBR5057
		09/99 >>		MBR5057
TG-A - 24, 26, 27, 28, 32, 33, 40 Series - 280 → 680 - non ABS		03/99 >>		MBR5068
		03/99 >> 09/01		MBR5068
		09/99 >>		MBR5068
TG-A - 32, 33, 35, 37, 39, 40, 41, 50 Series - 280 → 680 - exc VHK axle		03/99 >>		MBR5057
		03/99 >> 09/01		MBR5057
		09/99 >>		MBR5057
TG-A - 32, 33, 35, 37, 39, 40, 41, 50 Series - 280 → 680 - non ABS		03/99 >>		MBR5068
		03/99 >> 09/01		MBR5068
		09/99 >>		MBR5068
TG-L - 18 Series - 240 → 380		10/05 >>		MBR5057
		10/05 >>		MBR5068
TG-L - 26 Series - 240 → 380		10/05 >>		MBR5057
		10/05 >>		MBR5068
TG-M - 15, 16 Series - 240 → 340		10/05 >>		MBR5057
TG-M - 18 Series - 240 → 380		10/05 >>		MBR5057
		10/05 >>		MBR5068
TG-M - 22, 26 Series - 240 → 380		10/05 >>		MBR5057
		10/05 >>		MBR5068
TG-S, TG-X - 15 → 40 Series - 310 → 560 - exc VHK axle		06/06 >>		MBR5057
		08/07 >>		MBR5057
TG-S, TG-X - 15 → 40 Series - 310 → 560 - non ABS		06/06 >>		MBR5068
		08/07 >>		MBR5068
TG-S, TG-X - 16 → 41 Series - 310 → 680 - exc VHK axle		06/06 >>		MBR5057
		08/07 >>		MBR5057

 - Refer to Buyers Guide



1



GENUINE

ALLFIT

...MAN



TG-S, TG-X - 16 -> 41 Series - 310 -> 680 - non ABS



06/06 >>

MBR5068



08/07 >>

MBR5068

TG-S, TG-X - 18 -> 21 Series - 310 -> 560 - non ABS



06/06 >>

MBR5068



08/07 >>

MBR5068

TG-S, TG-X - 18 -> 21 Series - 310 -> 560 - VOK axle



06/06 >>

MBR5057



08/07 >>

MBR5057

MAN PSV's



SG150 - 750



01/93 >> 01/96

MBR5010

SL150 - 750



01/93 >> 01/96

MBR5010

SU210



01/93 >> 01/96

MBR5010

City Bus - 22.5" Wheels



01/96 >>

MBR5078

City Bus, Intercity Bus - NL 200, 300, 400 Series



01/92 >>

MBR5068

City Bus, Intercity Bus - NU Series



09/96 >>

MBR5057



09/96 >>

MBR5068

City Bus, Intercity Bus - SU 200, 300, 400 Series



01/03 >>

MBR5057



01/03 >>

MBR5068

City Bus, Intercity Bus - UL 300 Series



01/96 >>

MBR5057



01/96 >>

MBR5068

Lion's City - 19.235 -> 19.300



01/04 >>

MBR5057



01/04 >>

MBR5068

Lion's City - A20 -> A66 Series



01/08 >>

MBR5057



01/96 >>

MBR5057



03/96 >>

MBR5057



01/08 >>

MBR5068



01/96 >>

MBR5068



03/96 >>

MBR5068

Lion's City - Lion's City



01/04 >>

MBR5057



01/04 >>

MBR5068

Lion's City - Lion's City, Lion's City CNG



01/04 >>

MBR5057



01/04 >>

MBR5068

- Refer to Buyers Guide



					
					
...MAN PSV's					
					
Lion's Coach - FRH - 352, 402		01/96 >>		MBR5057	
		01/96 >>		MBR5068	
Lion's Coach - NG Series		11/84 >> 01/96		MBR5057	
Lion's Coach - RH, RHC - 353, 403, 413, 414, 440, 463, 464, 480		01/96 >>		MBR5057	
		01/96 >>		MBR5068	
Lion's Coach		01/04 >>		MBR5068	
Lion's Coach - with ABS		01/89 >> 01/96		MBR5078	
Lion's Comfort - NG, NL, NU Series - 262, 263, 312, 313		01/89 >> 01/96		MBR5057	
		01/89 >> 01/96		MBR5068	
Lion's Comfort - RN Series - RN313, RN353		01/96 >>		MBR5057	
		01/96 >>		MBR5068	
Lion's Comfort - with ABS		01/89 >> 01/96		MBR5078	
Lion's Explorer		01/05 >>		MBR5068	
Lion's Intercity		01/15 >>		MBR5068	
Lion's Intercity C		01/15 >>		MBR5068	
Lion's Regio - 320, 360, 400		01/03 >>		MBR5068	
Lion's Star - 352, 353, 402, 403, 422 FRH, RH		01/93 >>		MBR5057	
		01/93 >>		MBR5068	
Lion's Star - 414, 464 RH, RHS		01/93 >>		MBR5057	
		01/93 >>		MBR5068	
Lion's Star - 414, 464, 484 RH, RHS		01/93 >>		MBR5057	
		01/93 >>		MBR5068	
Lion's Star - Knorr Brake		01/94 >>		MBR5011	
Lion's Star - Meritor Brake		01/94 >>		MBR5011	
NG262		03/95 >> 07/98		MBR5011	
NG262 - with ABS		01/98 >>		MBR5078	
NG263		03/95 >> 07/98		MBR5011	
NG263 - with ABS		01/98 >>		MBR5078	
NG272		03/95 >> 07/98		MBR5011	
NG312		03/95 >> 07/98		MBR5011	
NG312 - with ABS		01/98 >>		MBR5078	

 - Refer to Buyers Guide



1



GENUINE

ALLFIT

...MAN PSV's



NG313		03/95 >> 07/98		MBR5011
NG313 - (with ABS)		01/98 >>		MBR5078
NL312		01/95 >> 01/98		MBR5011
NL313 - (with ABS)		01/98 >>		MBR5078
NM222		01/96 >>		MBR5011
NM223		01/96 >>		MBR5011
SG150 - 750		01/93 >> 01/96		MBR5010
SL150 - 750		01/93 >> 01/96		MBR5010
SU210		01/93 >> 01/96		MBR5010
SU Series 03 -> - 263, 283, 313		09/03 >>		MBR5068

MCV



Evolution - C124RLE		01/04 >>		MBR5068
---------------------	--	----------	--	---------

MCW



Metrorider - Optional Disc Brake		01/87 >>		MBR1831
----------------------------------	--	----------	--	---------

Menarinibus (BredaMenarinibus, Industria Italiana Autobus, Bredabus)



Citymood 18		01/13 >>		MBR5032
		01/16 >>		MBR5032

Mercedes



Econic II (2013 ->) - -> 32T Range		03/13 >>		MBR5128
-------------------------------------	--	----------	--	---------



Accelo - 7T & 8T		05/03 >>		MBR5066
		05/03 >>		MBR5070
Accelo - 9T & 10T		05/03 >>		MBR5066
Actros MP2, MP3 - 1831 -> 2055		10/02 >> 12/11		MBR5128
Actros MP2, MP3 - 2430 -> 4036		10/02 >> 12/11		MBR5128
Actros MP2, MP3 - 3230 -> 5048		10/02 >> 12/11		MBR5128
Actros MP4 - 18T Range		07/11 >>		MBR5128

- Refer to Buyers Guide



		  			
				GENUINE	ALLFIT
...Mercedes					
					
Actros MP4 - 20T → 26T Range		07/11 >>			MBR5128
Antos - → 32T Range		05/12 >>			MBR5128
Antos - 18T Range		05/12 >>			MBR5128
Antos - 20T → 26T Range		05/12 >>			MBR5066
		05/12 >>			MBR5128
Arocs - → 32T Range		05/12 >>			MBR5128
Arocs - 18T Range		05/12 >>			MBR5128
Arocs - 20T → 26T Range		05/12 >>			MBR5128
		05/12 >>			MBR5066
Atego - 1228 → 1528		01/98 >> 10/04			MBR5077
		01/98 >> 10/04			MBR5071
Atego - 712 → 823		01/98 >> 10/04			MBR5066
Atego - 712 → 823 - 5T axle		01/98 >> 10/04			MBR5070
		01/98 >> 10/04			MBR5092
Atego - 914 → 1023		01/98 >> 10/04			MBR5066
Atego - 914 → 1023 - 5T axle		01/98 >> 10/04			MBR5070
Atego - 914 → 1023 - 7.5T axle		01/98 >> 10/04			MBR5092
Atego - 914 → 1228		01/98 >> 10/04			MBR5077
		01/98 >> 10/04			MBR5071
Atego 2 - 712 → 824		10/04 >>			MBR5066
Atego 2 - 712 → 824 - 5T axle		10/04 >>			MBR5070
Atego 2 - 915 → 1229		10/04 >>			MBR5066
Atego 2 - 915 → 1229 - 5T axle		10/04 >>			MBR5070
Atego 2 - 915 → 1229 - 7.5T axle		10/04 >>			MBR5092
Atego 2 - 915 → 1624		10/04 >>			MBR5077
		10/04 >>			MBR5071
Atego 3 - 12T → 15T		05/12 >>			MBR5077
		05/12 >>			MBR5071
Atego 3 - 6.5T → 12T		05/12 >>			MBR5066
		05/12 >>			MBR5070

 - Refer to Buyers Guide



1



2



3



4



5



			  	
...Mercedes				
				
Axor 2 - 1823 → 2044		10/04 >>		MBR5128
Axor 2 - 2436 → 4144		10/04 >>		MBR5128
Axor 2 - 2623 → 4144		10/04 >>		MBR5128
T1 Series - L207, L208, L209, L210		01/77 >> 01/95		MBR1577
T1 Series - L307, L308, L309 D, L310		01/77 >> 01/95		MBR1577
T2 Series - 508D, 510, 511D, 608D, 609D		01/86 >>		MBR1588
T2 Series - 809D, 811D, 814D - 16” wheels		01/86 >> 01/98		MBR1588
T2 Series - L709 - 16” wheels		01/86 >>		MBR1588
T2 Series - L711 - 16” wheels		01/86 >>		MBR1588
With Knorr brakes - SM7				MBR5191
Zetros (2008 →) - 18T Range		08/08 >>		MBR5128
Zetros (2008 →) - 20T → 26T Range		08/08 >>		MBR5128
Mercedes Axles				
				
19.5” brake, trailer TE4-TE5				MBR5132
Knorr brakes - SK7 RB, RS, RZ		01/99 >>		MBR5071
Wabco brakes - MAXX 19		01/99 >>		MBR5071
Wabco brakes - PAN 19-1		01/99 >>		MBR5071
Mercedes PSV's (Inc Evobus)				
				
0409		01/86 >>		MBR1588
Citaro II - GNC series, 12m, 18m. All models		01/11 >>		MBR5128
Citaro II - GNC series, 12m, 18m. All models - 10 hole disc 168mm PCD		01/11 >>		MBR5128
Cito - 520		09/96 >>		MBR5032
Integro, Integro L, Integro M - 0550, 0560		01/00 >>		MBR5076
		09/96 >>		MBR5076
Tourino		10/03 >>		MBR5077
		10/03 >>		MBR5071
Tourismo - 0340, 0350		08/95 >>		MBR5128
		09/96 >>		MBR5128

 - Refer to Buyers Guide



		  		 GENUINE ALLFIT	
Meritor (Inc Lucas, Rockwell, ROR)					
					
D DUC0		01/99 >>			MBR5124
ELSA 2					MBR5124
DX195 Axle		01/99 >>			MBR5073
DX225 Axle		06/00 >>			MBR5124
EX225		01/04 >>			MBR5124
LM - D DUC0 Axial (M20)		02/00 >> 06/01	MBR9004		
LM - DX195 (8 stud w/o pole wheel)		01/98 >>	MBR9017		
LM - DX195 (8 stud with pole wheel)		01/98 >>	MBR9014		
LM - DX195 (10 stud ABS & Non ABS)		01/98 >>	MBR9018		
LM - ELSA 195 (8 stud w/o pole wheel)		01/03 >> 06/04	MBR9017		
LM - ELSA 195 (8 stud with pole wheel)		01/03 >> 06/04	MBR9014		
LM - ELSA 195 (10 stud ABS & Non ABS)		01/03 >> 06/04	MBR9018		
LM - ELSA 2		07/01 >>	MBR9004		
LM, TM		01/04 >>			MBR5073
TA - D DUC0 Axial (M20)		06/01 >> 01/02	MBR9004		
TA - D DUC0 Axial (M20)		02/00 >> 06/01	MBR9004		
TA - ELSA 2		07/01 >>	MBR9004		
TM - DX195 (8 stud w/o pole wheel)		01/98 >>	MBR9017		
TM - DX195 (8 stud with pole wheel)		01/98 >>	MBR9014		
TM - ELSA 195		01/03 >> 06/04	MBR9018		
TM - ELSA 195 (8 stud w/o pole wheel)		01/03 >> 06/04	MBR9017		
TM - ELSA 195 (8 stud with pole wheel)		01/03 >> 06/04	MBR9014		
VGT 195 Axle		01/04 >>			MBR5073
Neoplan (Inc Auwarter)					
					
Centroliner - N44 series		01/92 >>			MBR5032
Centroliner - N44 series - ELSA 2 caliper		01/92 >>			MBR5057
		01/92 >>			MBR5068
Centroliner - N45 series		01/92 >>			MBR5032
Centroliner - N45 series - ELSA 2 caliper		01/92 >>			MBR5057
		01/92 >>			MBR5068

- Refer to Buyers Guide



1



GENUINE

ALLFIT

...Neoplan (Inc Auwärter)



Cityliner - N116, N166 series		01/90 >>		MBR5032
Clubstar - SB 6000		01/98 >>		MBR5077
		01/98 >>		MBR5071
Euroliner - N3316, N3318 - SB 7000		01/92 >>		MBR5032
Jetliner - N200, N300, N400 Series - 208 → 426 - SB7000 caliper		09/90 >>		MBR5032
Jetliner - N200, N300, N400 Series - 208 → 426 - SB7000 / SN7000 caliper		09/90 >>		MBR5032
N Series Bus - N4007 → N4026 - Low Chassis Bus		01/90 >>		MBR5032
Regioliner - N3014, N3016		01/92 >>		MBR5032
Skyliner - N122, N122/3, N138/4		01/90 >>		MBR5032
Spaceliner - N117, N117/2, N117/3		01/90 >>		MBR5032
Starliner - N2216 SHD - MAN chassis		01/02 >>		MBR5057
		01/02 >>		MBR5068
Starliner - N2216 SHD - SB7000 caliper		01/02 >>		MBR5032
Starliner - N516, N516/3 - SB7000 caliper		01/02 >>		MBR5032
		01/92 >>		MBR5032
Starliner - N516, N516/3 - SB7000 / SN7000 caliper		01/92 >>		MBR5032
Starliner - N5217, N5218 SHD, SHDC, SHDL - SB7000 caliper		01/02 >>		MBR5032
		05/05 >>		MBR5032
Starliner - N5217, N5218 SHD, SHDC, SHDL - SB7000 / SN7000 caliper		05/05 >>		MBR5032
Tourliner - N2216, N2216/3 SHD, SHDC, SHDL		01/03 >>		MBR5057
		01/03 >>		MBR5068
Transliner - N312, N314, N316		01/88 >>		MBR5032
Transliner - N316, N321/3		01/88 >>		MBR5032
Trendliner - N3516, N3516/3		09/04 >>		MBR5057
		09/04 >>		MBR5068

Nogebus



Catalan - 320		01/98 >>		MBR5077
		01/98 >>		MBR5071
Catalan - 350, 370		01/01 >>		MBR5068
Catalan - 350 with ABS		01/98 >>		MBR5078
Catalan - 370 with ABS		01/98 >>		MBR5078

- Refer to Buyers Guide



		  		 GENUINE ALLFIT	
Optare (Inc Switch Mobility, NABI)					
					
Metrorider		01/89 >>			MBR1831
Sigma		01/94 >> 01/97			MBR5076
Solera Corta		01/02 >> 01/06			MBR5077
		01/02 >> 01/06			MBR5071
Solera, Solera 2		06/02 >>			MBR5077
		06/02 >>			MBR5071
Solers HD, SR		01/03 >>			MBR5077
		01/03 >>			MBR5071
Solo		01/88 >> 01/02			MBR1831
Solo - M Series 710, 780, 810, 880, 950, 1020		06/02 >>			MBR5100
Solo - M Series 710, 780, 810, 880, 950, 1020 - non ABS		06/02 >>			MBR5097
Tempo - X1060, X1130, X1200, X1260 - ELSA 225-3 caliper		08/04 >>			MBR5057
Versa - PAN 17 - non ABS		11/06 >>			MBR5097
Otokar					
					
Sultan		01/03 >>			MBR5066
		01/03 >>			MBR5097
Plaxton					
					
Elite - Volvo chassis		01/99 >>			MBR5184
Panther - Dennis R chassis		01/99 >>			MBR5183
Panther - Dennis R chassis - non ABS		01/99 >>			MBR5184
Panther - Iveco Eurorider chassis		01/92 >>			MBR6037
Panther - MAN chassis		01/02 >>			MBR5057
		01/06 >>			MBR5057
		01/02 >>			MBR5068
Panther		01/99 >>			MBR5057
		01/99 >>			MBR5068
Paragon - Dennis R chassis		01/99 >>			MBR5183
Paragon - Dennis R chassis - non ABS		01/99 >>			MBR5184

 - Refer to Buyers Guide

1



2



3



4



5





1



GENUINE

ALLFIT

...Plaxton



Paragon - Iveco Eurorider chassis



01/92 >>

MBR6037



01/92 >>

MBR6037

Paragon - MAN chassis



01/99 >>

MBR5057



01/99 >>

MBR5068

Touring



01/96 >>

MBR5077



01/96 >>

MBR5071

Raba



309-69 - 309-69



01/99 >>

MBR5025

309-69 - 309-69 - SB7000 / SN7000 caliper



01/99 >>

MBR5025

932-21 - 932-21



01/99 >>

MBR5025

932-21 - 932-21 - SB7000 / SN7000 caliper



01/99 >>

MBR5025

Renault Trucks



C - C250, C280, C320



01/13 >>

MBR9008

C Series - CM, KM, P, PK, RM, RX, T, TK



01/13 >>

MBR5056

C Series - CM, KM, P, PK, RM, RX, T, TK - ELSA 225-3 caliper



01/13 >>

MBR5056

D - D250, D280



01/13 >>

MBR9008

D - D320



01/13 >>

MBR9008

Magnum - 390.18, 390.19, 430.18, 430.19, 470.18, 470.19, 560.18, 560.19



01/96 >> 01/00

MBR9008



01/96 >> 01/00

MBR5101

Magnum - 390.24, 390.26, 430.22, 430.24, 430.26, 470.22, 470.24, 470.26



01/96 >> 01/00

MBR9008



01/96 >> 01/00

MBR9008



01/96 >> 01/00

MBR5101

Magnum - 400.18, 400.19



01/99 >> 01/05

MBR9008



01/99 >> 01/05

MBR9011



01/99 >> 01/05

MBR5101

Magnum - 400.24, 400.26, 440.18, 440.19, 440.22, 440.24, 440.26, 480.18, 480.19, 480.22, 480.24, 480.26



01/99 >> 01/05

MBR9008



01/99 >> 01/05

MBR9011



01/99 >> 01/05

MBR5101

- Refer to Buyers Guide



				
				
...Renault Trucks				
				
Magnum - 420.18, 420.19		01/96 >> 01/96	MBR9008	
Magnum - 420.18, 420.19		01/96 >> 01/96		MBR5101
Magnum - 420.24, 420.26		01/96 >> 01/96	MBR9008	
Magnum - 420.24, 420.26		01/96 >> 01/96	MBR9008	
Magnum - 420.24, 420.26		01/96 >> 01/96		MBR5101
Magnum - 440.18, 440.19, 480.18, 480.19		01/96 >> 01/05	MBR9008	
Magnum - 440.18, 440.19, 480.18, 480.19		01/96 >> 01/05	MBR9011	
Magnum - 440.18, 440.19, 480.18, 480.19		01/96 >> 01/05		MBR5101
Magnum - 560.22, 560.24, 560.26		01/96 >> 01/00	MBR9008	
Magnum - 560.22, 560.24, 560.26		01/96 >> 01/00	MBR9008	
Magnum - 560.22, 560.24, 560.26		01/96 >> 01/00		MBR5101
Magnum - AE380, AE385, AE390, AE420, AE430, AE520, AE560 - D LISA caliper		01/93 >> 01/00	MBR9008	
Magnum E Tech - 400, 440, 480 - D3 caliper		01/02 >>	MBR9008	
Magnum E Tech - 400, 440, 480 - ELSA 2 caliper		01/02 >>	MBR9008	
Magnum E Tech - 400, 440, 480 - D3 caliper		01/02 >>		MBR5101
Magnum E Tech - 400, 440, 480 - ELSA 2 caliper		01/02 >>		MBR5101
Magnum Series - 400, 440, 480 E TECH - ELSA 2 caliper		01/02 >> 10/04		MBR5056
Magnum Series - 400, 440, 480 E TECH - D3 caliper		01/02 >>		MBR5056
Magnum Series - 400, 440, 480 E TECH - D3 caliper		06/00 >> 01/02		MBR5056
Magnum Series - 400.18 → 400.19 - D LISA caliper		01/96 >> 09/05		MBR5056
Magnum Series - 440.18 → 440.26 - D LISA caliper		01/96 >> 09/05		MBR5056
Magnum Series - 480.18 → 480.26 - D LISA caliper		01/96 >> 09/05		MBR5056
Magnum Series - AE380, AE385, AE390 - ELSA 2 caliper		01/90 >> 06/00		MBR5056
Magnum Series - AE380, AE385, AE390 - D3 caliper		01/90 >> 06/00		MBR5056
Magnum Series - AE380, AE385, AE390 - D LISA caliper		01/90 >> 06/00		MBR5056
Magnum Series - AE420, AE430, AE470 - ELSA 2 caliper		01/90 >> 06/00		MBR5056
Magnum Series - AE420, AE430, AE470 - D3 caliper		01/90 >> 06/00		MBR5056
Magnum Series - AE420, AE430, AE470 - D LISA caliper		01/90 >> 06/00		MBR5056
Magnum Series - AE500, AE520, AE560 - ELSA 2 caliper		01/90 >> 06/00		MBR5056
Magnum Series - AE500, AE520, AE560 - D3 caliper		01/90 >> 06/00		MBR5056
Magnum Series - AE500, AE520, AE560 - D LISA caliper		01/90 >> 06/00		MBR5056

 - Refer to Buyers Guide



GENUINE

ALLFIT

...Renault Trucks



Major		01/93 >> 01/00	MBR9008	
Major Series - R340, R350, R380, R385 - D3 caliper		05/93 >> 06/00		MBR5056
Major Series - R420, R429 - D3 caliper		05/93 >> 06/00		MBR5056
Manager		01/93 >> 01/00	MBR9008	
Manager G Series - G230, G260, G270, G280, G290 - except D LISA caliper		01/93 >> 06/00		MBR5056
Manager G Series - G300 - except D LISA caliper		01/93 >> 06/00		MBR5056
Manager G Series - G300, G330, G340 - except D LISA caliper		01/93 >> 06/00		MBR5056
Manager G Series - G330, G340 - except D LISA caliper		01/93 >> 06/00		MBR5056
Midliner - M120 - M250		01/89 >> 01/95		MBR2693
		01/95 >> 01/01		MBR2693
Midliner - S120-S210		01/90 >> 01/95		MBR2693
		01/95 >>		MBR5095
		01/95 >>		MBR5109
Midlum - 17.5" Wheels		11/99 >>		MBR5117
		11/99 >>		MBR5112
Midlum - 19.5" Wheels - Meritor brakes		11/99 >>		MBR5119
		11/99 >>		MBR5115
Midlum - 19.5" Wheels - Wabco PAN19 - 2 brakes		01/99 >> 01/03		MBR5119
		01/99 >> 01/03		MBR5115
Midlum - 19.5" Wheels - Wabco PAN19 - 1 plus brakes		01/03 >>		MBR5119
		01/03 >>		MBR5115
Midlum - 200 -> 280 Series - 16T -> 18T		01/02 >> 05/06		MBR5056
Premium		01/96 - 01/02	MBR9008	
		01/96 - 01/97	MBR9008	
		01/02 -	MBR9008	
		01/02 -		MBR5101
Premium - 210.16		01/96 - 01/01	MBR9008	
Premium - 220.16, 220.18, 270.16, 270.18, 270.19, 320.16		01/00 - 01/06	MBR9008	
Premium - 240.16 D		01/05 - 01/09	MBR9008	
Premium - 240.26, 280.26 D, 320.24 D, 320.25 D, 320.26 D, 320.26		01/05 - 01/09	MBR9008	
Premium - 260.26		01/96 - 01/99	MBR9008	
Premium - 270.16		01/09 -	MBR9008	

- Refer to Buyers Guide



				
				
...Renault Trucks				
				
Premium - 300.16, 300.18, 300.19, 300.26, 340.18, 340.19, 340.18, 340.19, 385.18, 385.19, 385.24, 420.18, 420.19		01/96 - 01/01	MBR9008	
Premium - 300.26		01/96 - 01/99	MBR9008	
Premium - 310.24, 310.25, 310.26, 340.24, 340.25, 340.26, 340.26		01/09 -	MBR9008	
Premium - 320.18		01/00 - 01/06	MBR9008	
Premium - 320.18		01/00 - 01/06	MBR9011	
Premium - 320.18		01/00 - 01/06		MBR5101
Premium - 320.24, 320.26, 370.24, 370.26, 320.26, 370.24, 370.26, 420.24, 420.25, 420.26		01/01 - 01/06	MBR9008	
Premium - 385.18, 385.19		01/96 - 01/03	MBR9008	
Premium - 400.18, 400.19, 400.24		01/98 - 01/03	MBR9008	
Premium - 400.26		01/98 - 01/01	MBR9008	
Premium Distribution, Route - 210, 220, 250, 260, 270 - ELSA 2 caliper		01/96 >> 01/02		MBR5056
Premium Distribution, Route - 210, 220, 250, 260, 270 - D3 caliper		01/96 >> 01/02		MBR5056
Premium Distribution, Route - 210, 220, 250, 260, 270 - D LISA caliper		01/96 >> 01/02		MBR5056
Premium Distribution, Route - 300, 320, 340, 370, 385 - ELSA 2 caliper		01/96 >> 01/02		MBR5056
Premium Distribution, Route - 300, 320, 340, 370, 385 - D3 caliper		01/96 >> 01/02		MBR5056
Premium Distribution, Route - 300, 320, 340, 370, 385 - D LISA caliper		01/96 >> 01/02		MBR5056
Premium Distribution, Route - 400, 420 - ELSA 2 caliper		01/96 >> 01/02		MBR5056
Premium Distribution, Route - 400, 420 - D3 caliper		01/96 >> 01/02		MBR5056
Premium Distribution, Route - 400, 420 - D LISA caliper		01/96 >> 01/02		MBR5056
Premium Distribution, Route - 200 Series - ELSA 2 caliper		01/02 >> 10/05		MBR5068
Premium Distribution, Route - 300 Series - ELSA 2 caliper		01/02 >> 10/05		MBR5068
Premium Distribution, Route - 400 Series - ELSA 2 caliper		01/02 >> 10/05		MBR5068
Puncher - ELSA 2 caliper		07/04 >>		MBR5056
With Haldex Brakes - DB19				MBR5193
With Wabco brakes - PAN 17				MBR5192
With Wabco brakes - MAXX 19				MBR5193
Renault Trucks PSV's				
				
Agora		01/95 >> 01/98	MBR9008	
		01/98 >>	MBR9008	
Agora - D3 caliper		01/95 >>		MBR5056
Agora - D LISA caliper		01/95 >>		MBR5056

 - Refer to Buyers Guide



1



GENUINE

ALLFIT

...Renault Trucks PSV's



Ares - D3 caliper		01/95 >>		MBR5056
Ares - D LISA caliper		01/95 >>		MBR5056
Ares		01/99 >>		MBR6037
Illiade		01/98 >>	MBR9008	
Illiade - FRH, GTC, GTX - ELSA 2 caliper		06/00 >>		MBR5056
Illiade - FRH, GTC, GTX - D3 caliper		01/98 >> 06/00		MBR5056
Illiade - RT, RTC, RTX, TE - ELSA 2 caliper		06/00 >>		MBR5056
Illiade - RT, RTC, RTX, TE - D3 caliper		01/98 >> 06/00		MBR5056
Midliner - PP160		01/92 >> 05/93		MBR2693

ROR



LM - DX195 (8 stud w/o pole wheel)		01/98 >>		MBR5079
LM - ELSA 195 (8 stud w/o pole wheel)		01/03 >> 06/04		MBR5079
TM - DX195 (8 stud w/o pole wheel)		01/98 >>		MBR5079
TM - ELSA 195 (8 stud w/o pole wheel)		01/03 >> 06/04		MBR5079

SAF



SAF (SAUER)				MBR5139
SKRB 9022 K1				MBR5125

SAF / Sauer



Haldex brakes - 19.5"				MBR5197
Haldex brakes - SK/RB 9022 - 12 hole disc		01/99 >>		MBR5046
Haldex brakes - SK/RS 9022 - 10 hole disc		01/99 >>		MBR5074
Knorr brakes - B19				MBR5197
Knorr brakes - SB/SN6				MBR5197
Knorr brakes - SK7				MBR5195
Knorr brakes - SK7 RB, RS, RZ - 10 hole disc		01/99 >>		MBR5074
Knorr brakes - SK7 RB, RS, RZ - 12 hole disc		01/99 >>		MBR5046
Knorr brakes - SK9019 / 10019K - RB, RS, RZ		01/03 >>		MBR5072
Knorr brakes - SK9019 / 10019K - RB, RS, RZ - exc Interdisc		01/99 >>		MBR5059
Knorr brakes - SK9022 → RB, RS, RZ - 10 hole disc		01/99 >>		MBR5074
Knorr brakes - SK9022 → RB, RS, RZ - 12 hole disc		01/99 >>		MBR5046

- Refer to Buyers Guide



			 GENUINE ALLFIT	
...SAF / Sauer				
				
Knorr brakes - SK9022 axles RB, RS, RZ - 10 hole disc		01/99 >>		MBR5074
Knorr brakes - SK9022 axles RB, RS, RZ - 12 hole disc		01/99 >>		MBR5046
Knorr brakes - SK9022 axles RB, RS, RZ - with flat disc		01/99 >>		MBR5025
Meritor brakes - DX195 Axle		01/99 >>		MBR5073
Meritor brakes - VGT 195 Axle		01/04 >>		MBR5073
Wabco brakes - MAXX 19 - SK9019/11019 W Intradisc plus - RB, RS, RZ		01/99 >>		MBR5072
Wabco brakes - PAN 19-1 - SK9019/11019 W Intradisc plus - RB, RS, RZ		01/99 >>		MBR5072
Wabco brakes - SK9019 / 10019K - RB, RS, RZ - exc Interdisc		01/99 >>		MBR5059
Wabco brakes - SK9022 → RB, RS, RZ - PAN 22 caliper - 10 hole disc		01/99 >>		MBR5074
Wabco brakes - SK9022 → RB, RS, RZ - PAN 22 caliper - 12 hole disc		01/99 >>		MBR5046
Scania				
				
Series 4 C, D, G, L, S, T - 94, 114, 124, 144, 164		05/95 >> 12/08		MBR5025
		05/95 >> 12/08		MBR5077
Scania PSV's (Inc Irizar)				
				
94, 113 Series Buses		01/93 >> 01/16		MBR5025
		01/93 >> 01/16		MBR5032
East Lancs - OmniCity, OmniDekka, OmniLink, OmniTown - Knorr brakes		01/04 >>		MBR5025
		01/04 >>		MBR5032
F, K, N Series Buses		01/06 >>		MBR5025
Irizar - Century - Club, Style, Topline		01/96 >>		MBR5025
Irizar - Intercentury		01/96 >>		MBR5025
Irizar - PB		01/96 >>		MBR5025
		10/09 >>		MBR5025
Irizar - S-Kool		01/96 >>		MBR5025
K230UB - SB7000 caliper		01/96 >>		MBR5025
K280UB - SB7000 caliper		01/96 >>		MBR5025
K310UB - SB7000 caliper		01/96 >>		MBR5025
Series 4 Buses		01/97 >> 01/16		MBR5025
With Knorr brakes - SB7000		01/96 >>		MBR5025
With Knorr brakes - SB7000 / SN7000 caliper		01/96 >>		MBR5025

- Refer to Buyers Guide



1



GENUINE

ALLFIT

Schmitz (CargoBull)



Knorr brakes - SB6000		01/99 >>		MBR5071
Knorr brakes - SB7000		01/99 >>		MBR5143
Knorr brakes - SB7000 / SN7000		01/99 >>		MBR5143
Knorr brakes - SK7 9T axles		01/99 >>		MBR5071
Knorr brakes - ST7-430		01/16 >>		MBR5046
SC Trailer axle - MAXX 22T		01/13 >>		MBR5143
SC Trailer axle - PAN 22-1		01/13 >>		MBR5143
Wabco brakes - PAN 19-1				MBR5202

Seddon Atkinson



Strato Series - 22, 26 Series		01/92 >>		MBR6036
-------------------------------	--	----------	--	---------

Setra (Inc Kassbohrer)



Setra (S Series) - S215 - NR		01/91 >>		MBR5076
Setra (S Series) - S300 - NC City		01/91 >>		MBR5076
Setra (S Series) - S309, S312 - HD, HDH		01/91 >>		MBR5076
Setra (S Series) - S309, S312 - Knorr brakes		01/91 >>		MBR5032
Setra (S Series) - S313 - Knorr brakes		01/91 >>		MBR5032
Setra (S Series) - S313 - NC City		01/91 >>		MBR5076
Setra (S Series) - S313 - UL		01/91 >>		MBR5076
Setra (S Series) - S315 - HD, HDH		01/91 >>		MBR5076
Setra (S Series) - S315 - NF, UL		01/91 >>		MBR5076
Setra (S Series) - S317, S319, S321 - GT-HD, HD, HDH, NF, UL		01/91 >>		MBR5076
Setra (S Series) - S328 - DT		01/91 >>		MBR5076
		01/95 >>		MBR5032
Setra (S Series) - S411, S412, S415, S416, S417, S419, S431 - DT, GT, GT-HD, HD, HDH		01/01 >>		MBR5032
		01/01 >>		MBR5032
Setra (S Series) - S417 ComfortClass, MultiClass, TopClass - GT-HD		01/01 >>		MBR5128

Sitcar



PSV's - Marlin		01/07 >>		MBR5066
		01/07 >>		MBR5070

- Refer to Buyers Guide



	  			
				
Solaris Bus				
				
Alpino		01/07 >>		MBR5063
Citybus		01/99 >>		MBR5032
InterUrbino 12		02/02 >>		MBR5063
Trolino 12		02/02 >>		MBR5063
Trolino 15		02/02 >>		MBR5063
Trolino 18		02/02 >>		MBR5063
Urbino 12, Urbino 12 Hybrid, Urbino 12 LE		01/99 >>		MBR5063
Urbino 12.9		01/99 >>		MBR5063
Urbino 15, Urbino 15 CNG, Urbino 15 LE		01/99 >>		MBR5063
Urbino 18, Urbino 18 CNG, Urbino 18 Hybrid		01/99 >>		MBR5063
Urbino 9, 10		01/99 >>		MBR5063
Vacanza 12		02/02 >>		MBR5063
Vacanza 13		02/02 >>		MBR5063
Tecma				
				
Knorr brakes - SB7000		01/99 >>		MBR5128
Temsa				
				
Diamond		01/03 >>		MBR5025
Safari		01/05 >>		MBR5032
Trailer Axles - Various				
				
Knorr brakes - SB7 / SN7		01/98 >>		MBR5025
Knorr brakes - SK7 9T axles		01/99 >>		MBR5071
Knorr brakes - SN6000		06/03 >>		MBR5061
Knorr brakes - SN7000		06/03 >>		MBR5048
Knorr brakes - SN7 9T axles		01/99 >>		MBR5071
Meritor brakes - DX195 axles		01/99 >>		MBR5073
Meritor brakes - VGT 195 axles		01/04 >>		MBR5073
Wabco brakes - MAXX 22		07/11 >>		MBR5068
		08/07 >>		MBR5068

 - Refer to Buyers Guide

1



2



3



4



5





GENUINE

ALLFIT

Trenkamp & Gehle (Inc Gigant, SAE, SMB, Dupillier)



Haldex brakes - DB19		01/99 >>		MBR5061
Haldex brakes - non ABS		01/99 >>		MBR5048
Knorr brakes - SB6000		01/99 >>		MBR5061
Knorr brakes - SB7000		01/99 >>		MBR5064
Knorr brakes - SB7000 / SN7000		01/99 >>		MBR5025
Knorr brakes - SB7000 / SN7000		01/99 >>		MBR5064
Knorr brakes - SB7000 / SN7000 - non ABS		01/99 >>		MBR5048
Knorr brakes - SB7000 - non ABS		01/99 >>		MBR5048
Wabco brake - non ABS		01/99 >>		MBR5048
Wabco brakes - MAXX 19		01/99 >>		MBR5096
Wabco brakes - PAN 19-1		01/99 >>		MBR5096
Wabco brakes - PAN 19-2		01/99 >>		MBR5061
Wabco brakes - PAN 22-1		01/04 >>		MBR5064

Valx



Wabco brakes - PAN 19-1				MBR5204
Wabco brakes - PAN 22-1				MBR5203

Van Hool



Knorr brakes - SB7				MBR5196
--------------------	--	--	--	---------



913CL		07/04 >>	MBR9016	
915CL		07/04 >>	MBR9016	
915TL		07/04 >>	MBR9016	
A Series - A 600		01/96 >>		MBR5025
A300		04/04 >>	MBR9013	
A300CNG		04/04 >>	MBR9013	
A300T		04/04 >>	MBR9013	
A308		04/04 >>	MBR9013	
A320		01/03 >>	MBR9013	
		04/04 >>	MBR9013	
A320CNG		04/04 >>	MBR9013	

- Refer to Buyers Guide



	  			
				
...Van Hool				
				
A330		04/04 >>	MBR9013	
A330CNG		04/04 >>	MBR9013	
AG300		04/04 >>	MBR9013	
AG300CNG		04/04 >>	MBR9013	
AG300T		04/04 >>	MBR9013	
AG500		04/04 >>	MBR9013	
AGG300 - Trailer 1		04/04 >>	MBR9013	
AGG300 - Trailer 2		04/04 >>	MBR9013	
Alicron - MAN Chassis				MBR5011
Alizee		06/96 >>		MBR5025
Alizee - 12m - Volvo Chassis		01/95 >> 01/98		MBR5108
Astrobel		01/85 >> 12/95		MBR5025
Astron - T917				MBR5011
C Series - C2045		01/05 >>		MBR5057
C Series - C2045		01/97 >> 01/05		MBR5057
EOS - 80 -> 223		01/95 >>		MBR5025
EOS 200				MBR5003
T Series - T8		01/96 >>		MBR5057
T Series - T8, T9 - Scania chassis		01/96 >>		MBR5032
T Series - T8, T9 - Scania chassis		01/96 >>		MBR5025
T Series - T9		01/08 >>		MBR5032
T Series - T9		01/08 >>		MBR5057
T911 Alicron		07/04 >>	MBR9016	
T915				MBR5011
T915 Acron		07/04 >>	MBR9016	
T915 Alicron		07/04 >>	MBR9016	
T916 Altano - Centre (Drive Axle)		07/04 >>	MBR9016	
T917				MBR5011
T917 Acron - Centre (Drive Axle)		07/04 >>	MBR9016	
T917 Altano - Centre (Drive Axle)		07/04 >>	MBR9016	
T917 Astron - Centre (Drive Axle)		07/04 >>	MBR9016	

 - Refer to Buyers Guide



1



2



3



4



5



				 GENUINE ALLFIT	
...Van Hool					
					
T918				MBR5011	
T918 Altano - Centre (Drive Axle)		07/04 >>	MBR9016		
T924 Astromega DD - Centre (Drive Axle)		07/04 >>	MBR9016		
T927 Astromega DD - Centre (Drive Axle)		07/04 >>	MBR9016		
TX Alicron		01/16 >>		MBR5057	
UL Series		01/91 >>		MBR5076	
VDL (Inc Bova, Jonckheere)					
					
Axial - DD 138 → 430 - Twin axle - SB 7000		01/92 >>		MBR5032	
Citea - all models		01/08 >>		MBR5032	
		10/04 >>		MBR5070	
Futura - FHD, FHX, FLD - 14, 15 Magnum - Triple axle		06/95 >>		MBR5032	
Futura - FHD, FLD, FVD - 10, 12, 13, 14, 15 series - Twin axle - SB 7000		01/95 >> 01/03		MBR5032	
Futura - FHD, FLD, FVD - 10, 12, 13, 14, 15 series - Twin axle - SB7000 / SN7000 caliper		01/95 >> 01/03		MBR5032	
Lexio - LD123, LD130, LLD123, LLD130		09/05 >>		MBR5032	
Magiq - HD, MHD, Magnum 120 → 380 XE - Triple axle		01/96 >>		MBR5032	
Magiq - HD, MHD, Magnum 120 → 380 XE - Twin axle		01/96 >>		MBR5032	
Volvo					
					
FE II Series (12 →)		05/12 >>		MBR5056	
FH 12, 16 Series II (12 →)		05/12 >>		MBR5056	
FL Series - 17.5" Wheels - B DUCO caliper		05/00 >>	MBR9002		
FL Series - 180, 205, 220, 250		01/00 >> 01/06	MBR9000		
FL Series - 180, 205, 220, 250		01/00 >> 01/06	MBR9002		
FL Series - 19.5" Wheels - C DUCO caliper		05/00 >>	MBR9000		
FL4 Series - FL4.06, 4.08, 4.11		01/87 >> 02/90		MBR5029	
FL6 Series - FL6.08, 6.09, 6.10, 6.11		01/87 >> 02/90		MBR5021	
		01/87 >> 02/90		MBR5031	
FLC Series - FLC5		01/97 >> 01/99		MBR5029	
FLC Series - FLC7		01/97 >> 01/99		MBR5021	
		01/97 >> 01/99		MBR5031	
FLC Series - FLC8		01/97 >> 01/99		MBR5021	
		01/97 >> 01/99		MBR5031	

 - Refer to Buyers Guide



				
				
...Volvo				
				
FS Series - FS7.16, 7.17, 7.18, 7.19		10/91 >>		MBR5021
With Haldex brakes - DB19				MBR5193
With Wabco brakes - MAXX 19				MBR5193
Volvo PSV's				
				
B7		01/95 >> 01/00		MBR5108
B10B		01/95 >>		MBR5108
B9, B9 L, B9 R, B9 TL - D DUCO caliper		01/99 >>		MBR5056
B10L		01/95 >> 01/98		MBR5108
B10L		01/99 >>		MBR5108
B12		01/95 >> 01/00		MBR5108
B12, B12 L, M, R - ELSA 225-3 caliper		01/06 >> 05/12		MBR5056
Merit - PAN 19-2 caliper		01/01 >>		MBR5104
Wrightbus				
				
Meridian		01/89 >>		MBR5068
Routemaster (NBfL) - all models		01/11 >>		MBR5032
Solar		01/96 >>		MBR5025
StreetLite - PAN 17 caliper		10/04 >>		MBR5066
StreetLite - PAN 17 caliper		10/04 >>		MBR5070
StreetLite		10/04 >>		MBR5070
York Trailers (Hendrickson)				
				
Knorr brakes - SB6000		01/98 >>		MBR5071
Knorr Brakes - SB5000		01/99 >>		MBR5070
Knorr brakes - SB6000		01/98 >>		MBR5077
Knorr brakes - SB7000		01/98 >>		MBR5025
Knorr brakes - SB7000		05/07 >>		MBR5025
ZF Axles				
				
Knorr brakes - SN6000		06/03 >>		MBR5061

 - Refer to Buyers Guide



1



2



3




4



5





1



2



3



4





5







GENUINE

3218E1539



Disc Type (Solid/Vented)	Vented
Position	
Number of Holes	10
Bolt Hole Circle Diameter (mm)	240
Warranty Period (Months)	24
A Outer Diameter (mm)	434
B Thickness (Max) (mm)	45
C Inner Diameter (mm)	184
D Height (mm)	138.5
E Centering Diameter (mm)	210

3218F1514




Disc Type (Solid/Vented)	Vented
Position	
Number of Holes	12
Bolt Hole Circle Diameter (mm)	240
Warranty Period (Months)	24
A Outer Diameter (mm)	434
B Thickness (Max/Min) (mm)	45/37
C Inner Diameter (mm)	184
D Height (mm)	138.5
E Centering Diameter (mm)	210




GENUINE



3218M1495



①



Disc Type (Solid/Vented) Vented

Position

Number of Holes 8

Bolt Hole Circle Diameter (mm) 275

Warranty Period (Months) 24

A Outer Diameter (mm) 375


B Thickness (Max) (mm) 45

C Inner Diameter (mm) 160


D Height (mm) 150

E Centering Diameter (mm) 225

3218N1340PK2



②



Disc Type (Solid/Vented) Vented

Position

Number of Holes 10

Bolt Hole Circle Diameter (mm) 238

Warranty Period (Months) 24

A Outer Diameter (mm) 436

B Thickness (Max/Min) (mm) 45/39

C Inner Diameter (mm) 185.5


D Height (mm) 138

E Centering Diameter (mm) 210



**GENUINE****MBR9000**

①



Disc Type (Solid/Vented)

Solid

Position



Number of Holes


14

Bolt Hole Circle Diameter (mm)

275

Warranty Period (Months)

24



A Outer Diameter (mm)

375

B Thickness (Max/Min) (mm)

45/39

C Inner Diameter (mm)

162

D Height (mm)


116

E Centering Diameter (mm)

215

MBR9002

①



Disc Type (Solid/Vented)

Solid

Position



Number of Holes


10

Bolt Hole Circle Diameter (mm)

120

Warranty Period (Months)

24



A Outer Diameter (mm)

336.8

B Thickness (Max/Min) (mm)

30/28

C Inner Diameter (mm)

146

D Height (mm)

100

E Centering Diameter (mm)

91.5

**7.2**




GENUINE




MBR9004

①




Disc Type (Solid/Vented)	Vented
Position	
Number of Holes	10
Bolt Hole Circle Diameter (mm)	250
Warranty Period (Months)	24




A Outer Diameter (mm)	434
B Thickness (Max/Min) (mm)	45/39
C Inner Diameter (mm)	192
D Height (mm)	150
E Centering Diameter (mm)	222

MBR9008

①




Disc Type (Solid/Vented)	Vented
Position	
Number of Holes	10
Bolt Hole Circle Diameter (mm)	165
Warranty Period (Months)	24



A Outer Diameter (mm)	434
B Thickness (Max/Min) (mm)	45/39
C Inner Diameter (mm)	194.75
D Height (mm)	97
E Centering Diameter (mm)	131

**GENUINE****MBR9010**

①



Disc Type (Solid/Vented)

Vented

Position



Number of Holes


10

Bolt Hole Circle Diameter (mm)

165

Warranty Period (Months)

24



A Outer Diameter (mm)

438

B Thickness (Max/Min) (mm)

45/39

C Inner Diameter (mm)

194.5

D Height (mm)


130

E Centering Diameter (mm)

136

MBR9011

①



Disc Type (Solid/Vented)

Solid

Position



Number of Holes


10

Bolt Hole Circle Diameter (mm)

335

Warranty Period (Months)

24



A Outer Diameter (mm)

434

B Thickness (Max/Min) (mm)

45/39

C Inner Diameter (mm)

186.25

D Height (mm)

163

E Centering Diameter (mm)

260.1


**7.2**




GENUINE



MBR9012




Disc Type (Solid/Vented)	Solid
Position	
Number of Holes	10
Bolt Hole Circle Diameter (mm)	335
Warranty Period (Months)	24




A Outer Diameter (mm)	434
B Thickness (Max/Min) (mm)	45/39
C Inner Diameter (mm)	186.25
D Height (mm)	170
E Centering Diameter (mm)	264

MBR9013



Disc Type (Solid/Vented)	Vented
Position	
Number of Holes	10
Bolt Hole Circle Diameter (mm)	235
Warranty Period (Months)	24





A Outer Diameter (mm)	434
B Thickness (Max/Min) (mm)	45/39
C Inner Diameter (mm)	190.25
D Height (mm)	130
E Centering Diameter (mm)	203.1





GENUINE

MBR9014



Disc Type (Solid/Vented)	Vented
Position	
Number of Holes	8
Bolt Hole Circle Diameter (mm)	275
Warranty Period (Months)	24
A Outer Diameter (mm)	377
B Thickness (Max/Min) (mm)	45/39
C Inner Diameter (mm)	160
D Height (mm)	150
E Centering Diameter (mm)	225

MBR9015




Disc Type (Solid/Vented)	Vented
Position	
Number of Holes	10
Bolt Hole Circle Diameter (mm)	285.75
Warranty Period (Months)	24
A Outer Diameter (mm)	377
B Thickness (Max/Min) (mm)	45/39
C Inner Diameter (mm)	167
D Height (mm)	150
E Centering Diameter (mm)	225




GENUINE



MBR9016



①



Disc Type (Solid/Vented) Vented

Position

Number of Holes 10

Bolt Hole Circle Diameter (mm) 220

Warranty Period (Months) 24

A Outer Diameter (mm) 434


B Thickness (Max/Min) (mm) 45/41

C Inner Diameter (mm) 169.5


D Height (mm) 135

E Centering Diameter (mm) 194

MBR9017



①



Disc Type (Solid/Vented) Vented

Position

Number of Holes 8

Bolt Hole Circle Diameter (mm) 275

Warranty Period (Months) 24

A Outer Diameter (mm) 377

B Thickness (Max/Min) (mm) 45/39

C Inner Diameter (mm) 167

D Height (mm) 150


E Centering Diameter (mm) 225



GENUINE

MBR9018

①



Disc Type (Solid/Vented)

Vented

Position



Number of Holes


10

Bolt Hole Circle Diameter (mm)

250

Warranty Period (Months)

24



A Outer Diameter (mm)

377

B Thickness (Max/Min) (mm)

45/39

C Inner Diameter (mm)

166.5

D Height (mm)


150

E Centering Diameter (mm)

222

MBR9020

① ⑥



Disc Type (Solid/Vented)

Vented

Position



Number of Holes


10

Bolt Hole Circle Diameter (mm)

165

Warranty Period (Months)

24



A Outer Diameter (mm)

434

B Thickness (Max/Min) (mm)

45/39

C Inner Diameter (mm)

194.75

D Height (mm)

108

E Centering Diameter (mm)

131



7.2






GENUINE



MBR9025




Disc Type (Solid/Vented) Vented

Position

Number of Holes 8

Bolt Hole Circle Diameter (mm) 275

Warranty Period (Months) 24



A Outer Diameter (mm) 377


B Thickness (Max/Min) (mm) 45/39

C Inner Diameter (mm) 160

D Height (mm) 150

E Centering Diameter (mm) 225

MBR9026




Disc Type (Solid/Vented) Vented

Position

Number of Holes 10

Bolt Hole Circle Diameter (mm) 235

Warranty Period (Months) 24



A Outer Diameter (mm) 434

B Thickness (Max/Min) (mm) 45/39

C Inner Diameter (mm) 190

D Height (mm) 129.8


E Centering Diameter (mm) 203.1



ALLFIT

MBR1577

①



Disc Type (Solid/Vented)

Solid

Position



Number of Holes


5

Bolt Hole Circle Diameter (mm)

112

Warranty Period (Months)

24



A Outer Diameter (mm)

280

B Thickness (Max/Min) (mm)

16/14.4

C Inner Diameter (mm)

133.5

D Height (mm)


78.7

E Centering Diameter (mm)

88

MBR1588

①



Disc Type (Solid/Vented)

Vented

Position



Number of Holes


6

Bolt Hole Circle Diameter (mm)

140

Warranty Period (Months)

24



A Outer Diameter (mm)

303.8

B Thickness (Max/Min) (mm)

30/26

C Inner Diameter (mm)

118

D Height (mm)


91

E Centering Diameter (mm)

118



ALLFIT

**MBR1761**


Disc Type (Solid/Vented) Vented

Position

Number of Holes 6

Bolt Hole Circle Diameter (mm) 205

Warranty Period (Months) 24




A Outer Diameter (mm) 315

B Thickness (Max/Min) (mm) 26/23

C Inner Diameter (mm) 137

D Height (mm) 118.4

E Centering Diameter (mm) 160

MBR1831


Disc Type (Solid/Vented) Vented

Position

Number of Holes 12

Bolt Hole Circle Diameter (mm) 215

Warranty Period (Months) 24




A Outer Diameter (mm) 322

B Thickness (Max/Min) (mm) 30/28

C Inner Diameter (mm) 149

D Height (mm) 110

E Centering Diameter (mm) 166

**ALLFIT****MBR1832**


Disc Type (Solid/Vented) Vented

Position

Number of Holes 10

Bolt Hole Circle Diameter (mm) 138

Warranty Period (Months) 24




A Outer Diameter (mm) 315

B Thickness (Max/Min) (mm) 26/24

C Inner Diameter (mm) 119

D Height (mm) 121.6

E Centering Diameter (mm) 119

MBR2648


Disc Type (Solid/Vented) Vented

Position

Number of Holes 6

Bolt Hole Circle Diameter (mm) 205

Warranty Period (Months) 24



A Outer Diameter (mm) 304

B Thickness (Max/Min) (mm) 30/27.75


C Inner Diameter (mm) 128

D Height (mm) 128.5


E Centering Diameter (mm) 165



MBR2649




Disc Type (Solid/Vented)	Vented
Position	
Number of Holes	8
Bolt Hole Circle Diameter (mm)	275
Warranty Period (Months)	24




A Outer Diameter (mm)	322
B Thickness (Max/Min) (mm)	30/27.75
C Inner Diameter (mm)	136.845
D Height (mm)	134
E Centering Diameter (mm)	215.05

MBR2693



Disc Type (Solid/Vented)	Vented
Position	
Number of Holes	10
Bolt Hole Circle Diameter (mm)	151
Warranty Period (Months)	24




A Outer Diameter (mm)	354
B Thickness (Max/Min) (mm)	30/26
C Inner Diameter (mm)	128
D Height (mm)	82
E Centering Diameter (mm)	128



ALLFIT

MBR2695



Disc Type (Solid/Vented)

Vented

Position



Number of Holes


10

Bolt Hole Circle Diameter (mm)

195

Warranty Period (Months)

24



A Outer Diameter (mm)

460

B Thickness (Max/Min) (mm)

48/40

C Inner Diameter (mm)

170


D Height (mm)

119

E Centering Diameter (mm)

170

MBR5002



Disc Type (Solid/Vented)

Vented

Position



Number of Holes


8

Bolt Hole Circle Diameter (mm)

275

Warranty Period (Months)

24



A Outer Diameter (mm)

370

B Thickness (Max/Min) (mm)

45/41

C Inner Diameter (mm)

150

D Height (mm)

209.3

E Centering Diameter (mm)

215




7.2




ALLFIT



MBR5003




Disc Type (Solid/Vented)	Vented
Position	
Number of Holes	10
Bolt Hole Circle Diameter (mm)	215
Warranty Period (Months)	24




A Outer Diameter (mm)	405.8
B Thickness (Max/Min) (mm)	48/38
C Inner Diameter (mm)	176
D Height (mm)	175
E Centering Diameter (mm)	194

MBR5006



Disc Type (Solid/Vented)	Vented
Position	
Number of Holes	12
Bolt Hole Circle Diameter (mm)	155
Warranty Period (Months)	24



A Outer Diameter (mm)	312
B Thickness (Max/Min) (mm)	30/27.5
C Inner Diameter (mm)	133
D Height (mm)	137
E Centering Diameter (mm)	133.5

1



2



3



4



5






ALLFIT

MBR5010

①



Disc Type (Solid/Vented)

Vented

Position



Number of Holes


10

Bolt Hole Circle Diameter (mm)

158

Warranty Period (Months)

24



A Outer Diameter (mm)

324

B Thickness (Max/Min) (mm)

30/26

C Inner Diameter (mm)

138

D Height (mm)


102

E Centering Diameter (mm)

135

MBR5011

①



Disc Type (Solid/Vented)

Vented

Position



Number of Holes


10

Bolt Hole Circle Diameter (mm)

235

Warranty Period (Months)

24



A Outer Diameter (mm)

438

B Thickness (Max/Min) (mm)

45/35

C Inner Diameter (mm)

186

D Height (mm)

135

E Centering Diameter (mm)


200



7.2



MBR5012



①


Disc Type (Solid/Vented) Vented

Position

Number of Holes 10

Bolt Hole Circle Diameter (mm) 158

Warranty Period (Months) 24



A Outer Diameter (mm) 330


B Thickness (Max/Min) (mm) 34/30

C Inner Diameter (mm) 135

D Height (mm) 104

E Centering Diameter (mm) 135

MBR5013



①


Disc Type (Solid/Vented) Vented

Position

Number of Holes 12

Bolt Hole Circle Diameter (mm) 180

Warranty Period (Months) 24



A Outer Diameter (mm) 330

B Thickness (Max/Min) (mm) 34/31

C Inner Diameter (mm) 130.3

D Height (mm) 124

E Centering Diameter (mm) 157

1



2



3



4




5






ALLFIT

MBR5014




Disc Type (Solid/Vented)	Vented
Position	
Number of Holes	10
Bolt Hole Circle Diameter (mm)	195
Warranty Period (Months)	24




A Outer Diameter (mm)	377
B Thickness (Max/Min) (mm)	45/38
C Inner Diameter (mm)	160
D Height (mm)	128
E Centering Diameter (mm)	162

MBR5015



Disc Type (Solid/Vented)	Vented
Position	
Number of Holes	10
Bolt Hole Circle Diameter (mm)	235
Warranty Period (Months)	24



A Outer Diameter (mm)	438
B Thickness (Max/Min) (mm)	45/41
C Inner Diameter (mm)	186
D Height (mm)	135
E Centering Diameter (mm)	195




7.2



ALLFIT



MBR5016HD



①


Disc Type (Solid/Vented) Vented

Position

Number of Holes 10

Bolt Hole Circle Diameter (mm) 238

Warranty Period (Months) 24



A Outer Diameter (mm) 430


B Thickness (Max/Min) (mm) 45/37

C Inner Diameter (mm) 198

D Height (mm) 132.5

E Centering Diameter (mm) 211

MBR5021



①


Disc Type (Solid/Vented) Vented

Position

Number of Holes 8

Bolt Hole Circle Diameter (mm) 154

Warranty Period (Months) 24



A Outer Diameter (mm) 322

B Thickness (Max/Min) (mm) 30/28

C Inner Diameter (mm) 132

D Height (mm) 90

E Centering Diameter (mm) 132

1



2



3



4




5





ALLFIT

MBR5025



Disc Type (Solid/Vented)

Vented

Position



Number of Holes


10

Bolt Hole Circle Diameter (mm)

237

Warranty Period (Months)

24



A Outer Diameter (mm)

429.5

B Thickness (Max/Min) (mm)

45/41

C Inner Diameter (mm)

198


D Height (mm)

131

E Centering Diameter (mm)

208

MBR5029



Disc Type (Solid/Vented)

Vented

Position



Number of Holes


6

Bolt Hole Circle Diameter (mm)

154

Warranty Period (Months)

24



A Outer Diameter (mm)

322

B Thickness (Max/Min) (mm)

30/27

C Inner Diameter (mm)

132

D Height (mm)

90

E Centering Diameter (mm)

132




7.2




ALLFIT



MBR5031




Disc Type (Solid/Vented)	Vented
Position	
Number of Holes	8
Bolt Hole Circle Diameter (mm)	275
Warranty Period (Months)	24




A Outer Diameter (mm)	322.2
B Thickness (Max/Min) (mm)	30/27
C Inner Diameter (mm)	144.4
D Height (mm)	138.1
E Centering Diameter (mm)	216

MBR5032



Disc Type (Solid/Vented)	Vented
Position	
Number of Holes	10
Bolt Hole Circle Diameter (mm)	235
Warranty Period (Months)	24



A Outer Diameter (mm)	430
B Thickness (Max/Min) (mm)	45/37
C Inner Diameter (mm)	198
D Height (mm)	131
E Centering Diameter (mm)	203

1



2



3



4




5






ALLFIT

MBR5046




Disc Type (Solid/Vented)	Vented
Position	
Number of Holes	12
Bolt Hole Circle Diameter (mm)	168
Warranty Period (Months)	24




A Outer Diameter (mm)	430
B Thickness (Max/Min) (mm)	45/37
C Inner Diameter (mm)	196.1
D Height (mm)	130
E Centering Diameter (mm)	131

MBR5047



Disc Type (Solid/Vented)	Vented
Position	
Number of Holes	10
Bolt Hole Circle Diameter (mm)	335
Warranty Period (Months)	24



A Outer Diameter (mm)	430
B Thickness (Max/Min) (mm)	45/37
C Inner Diameter (mm)	188
D Height (mm)	159.5
E Centering Diameter (mm)	290




7.2



ALLFIT



MBR5048




Disc Type (Solid/Vented) Vented

Position

Number of Holes 10

Bolt Hole Circle Diameter (mm) 335

Warranty Period (Months) 24



A Outer Diameter (mm) 430


B Thickness (Max/Min) (mm) 45/38

C Inner Diameter (mm) 201

D Height (mm) 159.5

E Centering Diameter (mm) 290.05

MBR5049




Disc Type (Solid/Vented) Vented

Position

Number of Holes 10

Bolt Hole Circle Diameter (mm) 185

Warranty Period (Months) 24



A Outer Diameter (mm) 375

B Thickness (Max/Min) (mm) 44/40

C Inner Diameter (mm) 154

D Height (mm) 128


E Centering Diameter (mm) 154



ALLFIT

MBR5056

①



Disc Type (Solid/Vented)

Vented

Position



Number of Holes


5+5

Bolt Hole Circle Diameter (mm)

165

Warranty Period (Months)

24



A Outer Diameter (mm)

434

B Thickness (Max/Min) (mm)

45/41

C Inner Diameter (mm)

194

D Height (mm)


96.75

E Centering Diameter (mm)

131

MBR5057

①



Disc Type (Solid/Vented)

Vented

Position



Number of Holes


12

Bolt Hole Circle Diameter (mm)

168

Warranty Period (Months)

24



A Outer Diameter (mm)

432

B Thickness (Max/Min) (mm)

45/37

C Inner Diameter (mm)

200

D Height (mm)

130

E Centering Diameter (mm)

131



7.2







ALLFIT



MBR5059




Disc Type (Solid/Vented)	Vented
Position	
Number of Holes	12
Bolt Hole Circle Diameter (mm)	168
Warranty Period (Months)	24




A Outer Diameter (mm)	375
B Thickness (Max/Min) (mm)	45/38
C Inner Diameter (mm)	196.05
D Height (mm)	139
E Centering Diameter (mm)	131

MBR5060



Disc Type (Solid/Vented)	Vented
Position	
Number of Holes	10
Bolt Hole Circle Diameter (mm)	335
Warranty Period (Months)	24



A Outer Diameter (mm)	376.8
B Thickness (Max/Min) (mm)	45/38
C Inner Diameter (mm)	188
D Height (mm)	169.3
E Centering Diameter (mm)	290

1



2



3



4




5






ALLFIT

MBR5061




Disc Type (Solid/Vented)	Vented
Position	
Number of Holes	10
Bolt Hole Circle Diameter (mm)	335
Warranty Period (Months)	24




A Outer Diameter (mm)	382.5
B Thickness (Max/Min) (mm)	45/37
C Inner Diameter (mm)	172
D Height (mm)	159.5
E Centering Diameter (mm)	290

MBR5062



Disc Type (Solid/Vented)	Vented
Position	
Number of Holes	8
Bolt Hole Circle Diameter (mm)	275
Warranty Period (Months)	24




A Outer Diameter (mm)	377
B Thickness (Max/Min) (mm)	45/37
C Inner Diameter (mm)	171
D Height (mm)	159.5
E Centering Diameter (mm)	230.05




ALLFIT



MBR5063




Disc Type (Solid/Vented)	Vented
Position	
Number of Holes	12
Bolt Hole Circle Diameter (mm)	240
Warranty Period (Months)	24




A Outer Diameter (mm)	436
B Thickness (Max/Min) (mm)	45/37
C Inner Diameter (mm)	180
D Height (mm)	138.5
E Centering Diameter (mm)	210.015

MBR5064



Disc Type (Solid/Vented)	Vented
Position	
Number of Holes	10
Bolt Hole Circle Diameter (mm)	335
Warranty Period (Months)	24



A Outer Diameter (mm)	430
B Thickness (Max/Min) (mm)	45/38
C Inner Diameter (mm)	180
D Height (mm)	155
E Centering Diameter (mm)	280



1



2



3



4



5






ALLFIT

MBR5066

①



Disc Type (Solid/Vented)

Vented

Position



Number of Holes


10

Bolt Hole Circle Diameter (mm)

120

Warranty Period (Months)

24



A Outer Diameter (mm)

335

B Thickness (Max/Min) (mm)

34/31

C Inner Diameter (mm)

91.5

D Height (mm)


102.5

E Centering Diameter (mm)

91.5

MBR5068

①



Disc Type (Solid/Vented)

Vented

Position



Number of Holes


10

Bolt Hole Circle Diameter (mm)

235

Warranty Period (Months)

24



A Outer Diameter (mm)

432

B Thickness (Max/Min) (mm)

45/35

C Inner Diameter (mm)

186

D Height (mm)

135

E Centering Diameter (mm)

208




7.2






MBR5070




Disc Type (Solid/Vented)	Vented
Position	
Number of Holes	8
Bolt Hole Circle Diameter (mm)	177
Warranty Period (Months)	24




A Outer Diameter (mm)	335
B Thickness (Max/Min) (mm)	34/31
C Inner Diameter (mm)	131
D Height (mm)	111
E Centering Diameter (mm)	145

MBR5071



Disc Type (Solid/Vented)	Vented
Position	
Number of Holes	8
Bolt Hole Circle Diameter (mm)	201
Warranty Period (Months)	24




A Outer Diameter (mm)	376.8
B Thickness (Max/Min) (mm)	45/37
C Inner Diameter (mm)	164.1
D Height (mm)	138.4
E Centering Diameter (mm)	176



ALLFIT

MBR5072



Disc Type (Solid/Vented)

Vented

Position



Number of Holes


8

Bolt Hole Circle Diameter (mm)

275

Warranty Period (Months)

24



A Outer Diameter (mm)

377

B Thickness (Max/Min) (mm)

45/38

C Inner Diameter (mm)

169


D Height (mm)

157.5

E Centering Diameter (mm)

169

MBR5073



Disc Type (Solid/Vented)

Vented

Position



Number of Holes


10

Bolt Hole Circle Diameter (mm)

250

Warranty Period (Months)

24



A Outer Diameter (mm)

377

B Thickness (Max/Min) (mm)

45/38

C Inner Diameter (mm)

161

D Height (mm)

150

E Centering Diameter (mm)


222




ALLFIT



MBR5074




Disc Type (Solid/Vented)	Vented
Position	
Number of Holes	10
Bolt Hole Circle Diameter (mm)	335
Warranty Period (Months)	24




A Outer Diameter (mm)	430
B Thickness (Max/Min) (mm)	45/37
C Inner Diameter (mm)	192
D Height (mm)	160.3
E Centering Diameter (mm)	192

MBR5076



Disc Type (Solid/Vented)	Vented
Position	
Number of Holes	10
Bolt Hole Circle Diameter (mm)	220
Warranty Period (Months)	24



A Outer Diameter (mm)	431.7
B Thickness (Max/Min) (mm)	45/35
C Inner Diameter (mm)	186
D Height (mm)	135
E Centering Diameter (mm)	194

1



2



3



4



5






ALLFIT

MBR5077

①



Disc Type (Solid/Vented)

Vented

Position



Number of Holes


14

Bolt Hole Circle Diameter (mm)

138

Warranty Period (Months)

24



A Outer Diameter (mm)

377

B Thickness (Max/Min) (mm)

44.9/37

C Inner Diameter (mm)

105.7

D Height (mm)


133.8

E Centering Diameter (mm)

105.7

MBR5078

①



Disc Type (Solid/Vented)

Vented

Position



Number of Holes


10

Bolt Hole Circle Diameter (mm)

235

Warranty Period (Months)

24



A Outer Diameter (mm)

432

B Thickness (Max/Min) (mm)

45/35

C Inner Diameter (mm)

179

D Height (mm)

135

E Centering Diameter (mm)

208



7.2







ALLFIT



MBR5079




Disc Type (Solid/Vented)	Vented
Position	
Number of Holes	8
Bolt Hole Circle Diameter (mm)	275
Warranty Period (Months)	24




A Outer Diameter (mm)	377.5
B Thickness (Max/Min) (mm)	45/38
C Inner Diameter (mm)	167
D Height (mm)	150
E Centering Diameter (mm)	225

MBR5092



Disc Type (Solid/Vented)	Vented
Position	
Number of Holes	8
Bolt Hole Circle Diameter (mm)	177
Warranty Period (Months)	24



A Outer Diameter (mm)	330
B Thickness (Max/Min) (mm)	34/26
C Inner Diameter (mm)	119.5
D Height (mm)	129
E Centering Diameter (mm)	145

1



2



3




4




5




**ALLFIT****MBR5095**

①




Disc Type (Solid/Vented)	Vented
Position	
Number of Holes	6
Bolt Hole Circle Diameter (mm)	245
Warranty Period (Months)	24

A Outer Diameter (mm)	322
B Thickness (Max/Min) (mm)	30/26
C Inner Diameter (mm)	142
D Height (mm)	140
E Centering Diameter (mm)	290

MBR5096

①



Disc Type (Solid/Vented)	Vented
Position	
Number of Holes	8
Bolt Hole Circle Diameter (mm)	196
Warranty Period (Months)	24

A Outer Diameter (mm)	377
B Thickness (Max/Min) (mm)	45/38
C Inner Diameter (mm)	164
D Height (mm)	138.5
E Centering Diameter (mm)	169


**7.2**



ALLFIT



MBR5097




Disc Type (Solid/Vented) Vented

Position

Number of Holes 12

Bolt Hole Circle Diameter (mm) 175

Warranty Period (Months) 24



A Outer Diameter (mm) 330


B Thickness (Max/Min) (mm) 34/28

C Inner Diameter (mm) 127

D Height (mm) 119

E Centering Diameter (mm) 150

MBR5099




Disc Type (Solid/Vented) Vented

Position

Number of Holes 10

Bolt Hole Circle Diameter (mm) 335

Warranty Period (Months) 24



A Outer Diameter (mm) 377

B Thickness (Max/Min) (mm) 45/37

C Inner Diameter (mm) 188

D Height (mm) 159.5

E Centering Diameter (mm) 189

1



2



3



4



5






ALLFIT

MBR5100

①



Disc Type (Solid/Vented)

Vented

Position



Number of Holes


12

Bolt Hole Circle Diameter (mm)

138

Warranty Period (Months)

24



A Outer Diameter (mm)

330

B Thickness (Max/Min) (mm)

34/30

C Inner Diameter (mm)

117

D Height (mm)


123

E Centering Diameter (mm)

117

MBR5101

①



Disc Type (Solid/Vented)

Solid

Position



Number of Holes


12

Bolt Hole Circle Diameter (mm)

256

Warranty Period (Months)

24



A Outer Diameter (mm)

434

B Thickness (Max/Min) (mm)

45/38

C Inner Diameter (mm)

190

D Height (mm)

160

E Centering Diameter (mm)

224



7.2







ALLFIT



MBR5102




Disc Type (Solid/Vented)	Vented
Position	
Number of Holes	10
Bolt Hole Circle Diameter (mm)	335
Warranty Period (Months)	24




A Outer Diameter (mm)	380
B Thickness (Max/Min) (mm)	45/41
C Inner Diameter (mm)	188
D Height (mm)	159.5
E Centering Diameter (mm)	293.5

MBR5103



Disc Type (Solid/Vented)	Vented
Position	
Number of Holes	16
Bolt Hole Circle Diameter (mm)	155
Warranty Period (Months)	24



A Outer Diameter (mm)	330
B Thickness (Max/Min) (mm)	34/30
C Inner Diameter (mm)	133
D Height (mm)	143.5
E Centering Diameter (mm)	133.5

1



2



3



4




5






ALLFIT

MBR5104




Disc Type (Solid/Vented)	Vented
Position	
Number of Holes	10
Bolt Hole Circle Diameter (mm)	144
Warranty Period (Months)	24




A Outer Diameter (mm)	374.8
B Thickness (Max/Min) (mm)	45/38
C Inner Diameter (mm)	117
D Height (mm)	99
E Centering Diameter (mm)	117

MBR5105



Disc Type (Solid/Vented)	Vented
Position	
Number of Holes	10
Bolt Hole Circle Diameter (mm)	335
Warranty Period (Months)	24




A Outer Diameter (mm)	430
B Thickness (Max/Min) (mm)	45/40
C Inner Diameter (mm)	202
D Height (mm)	159.5
E Centering Diameter (mm)	293.5




ALLFIT



MBR5106




Disc Type (Solid/Vented)	Vented
Position	
Number of Holes	10
Bolt Hole Circle Diameter (mm)	209
Warranty Period (Months)	24




A Outer Diameter (mm)	375
B Thickness (Max/Min) (mm)	45/38
C Inner Diameter (mm)	150
D Height (mm)	146
E Centering Diameter (mm)	179

MBR5108



Disc Type (Solid/Vented)	Vented
Position	
Number of Holes	10
Bolt Hole Circle Diameter (mm)	235
Warranty Period (Months)	24



A Outer Diameter (mm)	438
B Thickness (Max/Min) (mm)	45/38
C Inner Diameter (mm)	188
D Height (mm)	127
E Centering Diameter (mm)	195

1



2



3



4




5





ALLFIT

MBR5109



Disc Type (Solid/Vented)

Vented

Position



Number of Holes


6

Bolt Hole Circle Diameter (mm)

205

Warranty Period (Months)

24



A Outer Diameter (mm)

304

B Thickness (Max/Min) (mm)

30/28

C Inner Diameter (mm)

127


D Height (mm)

135

E Centering Diameter (mm)

250

MBR5112



Disc Type (Solid/Vented)

Vented

Position



Number of Holes


6

Bolt Hole Circle Diameter (mm)

245

Warranty Period (Months)

24



A Outer Diameter (mm)

330

B Thickness (Max/Min) (mm)

34/28

C Inner Diameter (mm)

125

D Height (mm)

137

E Centering Diameter (mm)

194



7.2







ALLFIT



MBR5115




Disc Type (Solid/Vented)	Vented
Position	
Number of Holes	8
Bolt Hole Circle Diameter (mm)	275
Warranty Period (Months)	24




A Outer Diameter (mm)	375
B Thickness (Max/Min) (mm)	45/38
C Inner Diameter (mm)	171
D Height (mm)	166
E Centering Diameter (mm)	222

MBR5116



Disc Type (Solid/Vented)	Vented
Position	
Number of Holes	8
Bolt Hole Circle Diameter (mm)	275
Warranty Period (Months)	24



A Outer Diameter (mm)	377
B Thickness (Max/Min) (mm)	45/38
C Inner Diameter (mm)	159
D Height (mm)	151
E Centering Diameter (mm)	215

1



2



3



4



5






ALLFIT

MBR5117

①



Disc Type (Solid/Vented)

Vented

Position



Number of Holes


10

Bolt Hole Circle Diameter (mm)

118

Warranty Period (Months)

24



A Outer Diameter (mm)

330

B Thickness (Max/Min) (mm)

34/30

C Inner Diameter (mm)

95

D Height (mm)


80

E Centering Diameter (mm)

95

MBR5119

①



Disc Type (Solid/Vented)

Vented

Position



Number of Holes


10

Bolt Hole Circle Diameter (mm)

144

Warranty Period (Months)

24



A Outer Diameter (mm)

375

B Thickness (Max/Min) (mm)

45/38

C Inner Diameter (mm)

117

D Height (mm)

99

E Centering Diameter (mm)

117




7.2





ALLFIT

**MBR5124**


Disc Type (Solid/Vented) Vented

Position

Number of Holes 10

Bolt Hole Circle Diameter (mm) 250

Warranty Period (Months) 24




A Outer Diameter (mm) 434

B Thickness (Max/Min) (mm) 45/38

C Inner Diameter (mm) 192

D Height (mm) 150

E Centering Diameter (mm) 222

MBR5125


Disc Type (Solid/Vented) Vented

Position

Number of Holes 10

Bolt Hole Circle Diameter (mm) 190

Warranty Period (Months) 24



A Outer Diameter (mm) 430

B Thickness (Max/Min) (mm) 45/39

C Inner Diameter (mm) 164


D Height (mm) 48

E Centering Diameter (mm) 170.5




ALLFIT

MBR5128




Disc Type (Solid/Vented)	Vented
Position	$\varnothing C$
Number of Holes	10
Bolt Hole Circle Diameter (mm)	168
Warranty Period (Months)	24




A Outer Diameter (mm)	429.7
B Thickness (Max/Min) (mm)	45/37
C Inner Diameter (mm)	131
D Height (mm)	143.3
E Centering Diameter (mm)	131

MBR5129



Disc Type (Solid/Vented)	Vented
Position	$\varnothing C$
Number of Holes	12
Bolt Hole Circle Diameter (mm)	168
Warranty Period (Months)	24



A Outer Diameter (mm)	436
B Thickness (Max/Min) (mm)	45/37
C Inner Diameter (mm)	196
D Height (mm)	131
E Centering Diameter (mm)	135




7.2



ALLFIT

**MBR5129PK2**

②




Disc Type (Solid/Vented) Vented

Position

Number of Holes 12

Bolt Hole Circle Diameter (mm) 168

Warranty Period (Months) 24



A Outer Diameter (mm) 436

B Thickness (Max/Min) (mm) 45/37


C Inner Diameter (mm) 196

D Height (mm) 131

E Centering Diameter (mm) 135

MBR5132

①




Disc Type (Solid/Vented) Vented

Position

Number of Holes 10

Bolt Hole Circle Diameter (mm) 238

Warranty Period (Months) 24



A Outer Diameter (mm) 377

B Thickness (Max/Min) (mm) 45/37

C Inner Diameter (mm) 181.5

D Height (mm) 131.5

E Centering Diameter (mm) 211

1



2



3



4




5





ALLFIT

MBR5134



Disc Type (Solid/Vented)

Vented

Position



Number of Holes


N/A

Bolt Hole Circle Diameter (mm)

N/A

Warranty Period (Months)

24



A Outer Diameter (mm)

432

B Thickness (Max/Min) (mm)

45/37

C Inner Diameter (mm)

N/A


D Height (mm)

45

E Centering Diameter (mm)

258

MBR5139



Disc Type (Solid/Vented)

Vented

Position



Number of Holes


10

Bolt Hole Circle Diameter (mm)

190

Warranty Period (Months)

24



A Outer Diameter (mm)

376

B Thickness (Max/Min) (mm)

45/38

C Inner Diameter (mm)

164

D Height (mm)


57.5

E Centering Diameter (mm)


164



MBR5140



① ⊕



Disc Type (Solid/Vented) Vented

Position

Number of Holes N/A

Bolt Hole Circle Diameter (mm) N/A

Warranty Period (Months) 24

A Outer Diameter (mm) 434


B Thickness (Max/Min) (mm) 45/41

C Inner Diameter (mm) N/A


D Height (mm) 45

E Centering Diameter (mm) 220

MBR5141



① ⊕



Disc Type (Solid/Vented) Vented

Position

Number of Holes N/A

Bolt Hole Circle Diameter (mm) N/A

Warranty Period (Months) 24

A Outer Diameter (mm) 410

B Thickness (Max/Min) (mm) 45/41

C Inner Diameter (mm) N/A

D Height (mm) 45

E Centering Diameter (mm) 220

1



2



3



4




5





ALLFIT

MBR5142



Disc Type (Solid/Vented)

Solid

Position



Number of Holes


N/A

Bolt Hole Circle Diameter (mm)

N/A

Warranty Period (Months)

24



A Outer Diameter (mm)

434

B Thickness (Max/Min) (mm)

45/35

C Inner Diameter (mm)

N/A


D Height (mm)

45

E Centering Diameter (mm)

220

MBR5143



Disc Type (Solid/Vented)

Vented

Position



Number of Holes


10

Bolt Hole Circle Diameter (mm)

335

Warranty Period (Months)

24



A Outer Diameter (mm)

430

B Thickness (Max/Min) (mm)

45/37

C Inner Diameter (mm)

203

D Height (mm)

168.5

E Centering Diameter (mm)


290.056



ALLFIT



MBR5145



①


Disc Type (Solid/Vented) Vented

Position

Number of Holes 10

Bolt Hole Circle Diameter (mm) 335

Warranty Period (Months) 24



A Outer Diameter (mm) 425


B Thickness (Max/Min) (mm) 45/41

C Inner Diameter (mm) 200

D Height (mm) 170.5

E Centering Diameter (mm) 200

MBR5146



①


Disc Type (Solid/Vented) Vented

Position

Number of Holes 10

Bolt Hole Circle Diameter (mm) 186

Warranty Period (Months) 24



A Outer Diameter (mm) 416

B Thickness (Max/Min) (mm) 28/25.5

C Inner Diameter (mm) 159


D Height (mm) 67

E Centering Diameter (mm) 159



ALLFIT

MBR5153



Disc Type (Solid/Vented)

Solid

Position



Number of Holes


N/A

Bolt Hole Circle Diameter (mm)

N/A

Warranty Period (Months)

24



A Outer Diameter (mm)

410

B Thickness (Max/Min) (mm)

45/41

C Inner Diameter (mm)

N/A


D Height (mm)

45

E Centering Diameter (mm)

220

MBR5167



Disc Type (Solid/Vented)

Solid

Position



Number of Holes


N/A

Bolt Hole Circle Diameter (mm)

N/A

Warranty Period (Months)

24



A Outer Diameter (mm)

375

B Thickness (Max/Min) (mm)

45/41

C Inner Diameter (mm)

N/A

D Height (mm)

45

E Centering Diameter (mm)

181







ALLFIT



MBR5180




Disc Type (Solid/Vented)	Vented
Position	
Number of Holes	10
Bolt Hole Circle Diameter (mm)	335
Warranty Period (Months)	24




A Outer Diameter (mm)	377
B Thickness (Max/Min) (mm)	45/37
C Inner Diameter (mm)	171
D Height (mm)	159.5
E Centering Diameter (mm)	290

MBR5181



Disc Type (Solid/Vented)	Vented
Position	
Number of Holes	10
Bolt Hole Circle Diameter (mm)	176
Warranty Period (Months)	24




A Outer Diameter (mm)	335
B Thickness (Max/Min) (mm)	34/28
C Inner Diameter (mm)	125
D Height (mm)	118
E Centering Diameter (mm)	154



ALLFIT

MBR5182

①



Disc Type (Solid/Vented)

Vented

Position



Number of Holes


10

Bolt Hole Circle Diameter (mm)

122

Warranty Period (Months)

24



A Outer Diameter (mm)

334.8

B Thickness (Max/Min) (mm)

34/30

C Inner Diameter (mm)

90

D Height (mm)


93.1

E Centering Diameter (mm)

90

MBR5183

①



Disc Type (Solid/Vented)

Vented

Position



Number of Holes


14

Bolt Hole Circle Diameter (mm)

165

Warranty Period (Months)

24



A Outer Diameter (mm)

430

B Thickness (Max/Min) (mm)

45/37

C Inner Diameter (mm)

135

D Height (mm)

105

E Centering Diameter (mm)

135






ALLFIT



MBR5184



①


Disc Type (Solid/Vented) Vented

Position

Number of Holes 10

Bolt Hole Circle Diameter (mm) 235

Warranty Period (Months) 24



A Outer Diameter (mm) 430


B Thickness (Max/Min) (mm) 45/39

C Inner Diameter (mm) 198

D Height (mm) 131

E Centering Diameter (mm) 203

MBR5185



①


Disc Type (Solid/Vented) Vented

Position

Number of Holes 10

Bolt Hole Circle Diameter (mm) 144

Warranty Period (Months) 24



A Outer Diameter (mm) 375

B Thickness (Max/Min) (mm) 45/37

C Inner Diameter (mm) 168


D Height (mm) 108

E Centering Diameter (mm) 117



ALLFIT

MBR5186



Disc Type (Solid/Vented)

Vented

Position



Number of Holes


8

Bolt Hole Circle Diameter (mm)

196

Warranty Period (Months)

24



A Outer Diameter (mm)

375

B Thickness (Max/Min) (mm)

45/37

C Inner Diameter (mm)

150.5


D Height (mm)

138.5

E Centering Diameter (mm)

169

MBR5190



Disc Type (Solid/Vented)

Vented

Position



Number of Holes


10

Bolt Hole Circle Diameter (mm)

215

Warranty Period (Months)

24



A Outer Diameter (mm)

430

B Thickness (Max/Min) (mm)

45/37

C Inner Diameter (mm)

189.5

D Height (mm)

131.5

E Centering Diameter (mm)

189




7.2






MBR5191




Disc Type (Solid/Vented)	Vented
Position	
Number of Holes	10
Bolt Hole Circle Diameter (mm)	168
Warranty Period (Months)	24




A Outer Diameter (mm)	430
B Thickness (Max/Min) (mm)	45/37
C Inner Diameter (mm)	199
D Height (mm)	131
E Centering Diameter (mm)	131

MBR5192



Disc Type (Solid/Vented)	Vented
Position	
Number of Holes	6
Bolt Hole Circle Diameter (mm)	245
Warranty Period (Months)	24




A Outer Diameter (mm)	330
B Thickness (Max/Min) (mm)	34/28
C Inner Diameter (mm)	194.1
D Height (mm)	137
E Centering Diameter (mm)	194.1




ALLFIT

MBR5193




Disc Type (Solid/Vented)	Vented
Position	
Number of Holes	10
Bolt Hole Circle Diameter (mm)	142
Warranty Period (Months)	24




A Outer Diameter (mm)	375
B Thickness (Max/Min) (mm)	45/37
C Inner Diameter (mm)	174.7
D Height (mm)	119
E Centering Diameter (mm)	111

MBR5194



Disc Type (Solid/Vented)	Vented
Position	
Number of Holes	6
Bolt Hole Circle Diameter (mm)	215
Warranty Period (Months)	24



A Outer Diameter (mm)	306
B Thickness (Max/Min) (mm)	28/25
C Inner Diameter (mm)	190
D Height (mm)	132
E Centering Diameter (mm)	178.2



7.2







ALLFIT



MBR5195




Disc Type (Solid/Vented)	Vented
Position	
Number of Holes	10
Bolt Hole Circle Diameter (mm)	215
Warranty Period (Months)	24




A Outer Diameter (mm)	377
B Thickness (Max/Min) (mm)	45/37
C Inner Diameter (mm)	189
D Height (mm)	141
E Centering Diameter (mm)	189

MBR5196



Disc Type (Solid/Vented)	Vented
Position	
Number of Holes	10
Bolt Hole Circle Diameter (mm)	235
Warranty Period (Months)	24



A Outer Diameter (mm)	430
B Thickness (Max/Min) (mm)	45/37
C Inner Diameter (mm)	200
D Height (mm)	131
E Centering Diameter (mm)	203

1



2



3



4




5





ALLFIT

MBR5197



Disc Type (Solid/Vented)

Vented

Position



Number of Holes


10

Bolt Hole Circle Diameter (mm)

193

Warranty Period (Months)

24



A Outer Diameter (mm)

376

B Thickness (Max/Min) (mm)

45/37

C Inner Diameter (mm)

164


D Height (mm)

145

E Centering Diameter (mm)

164

MBR5199



Disc Type (Solid/Vented)

Vented

Position



Number of Holes


6

Bolt Hole Circle Diameter (mm)

245

Warranty Period (Months)

24



A Outer Diameter (mm)

330

B Thickness (Max/Min) (mm)

32/29

C Inner Diameter (mm)

128

D Height (mm)

129.5

E Centering Diameter (mm)

185



7.2







ALLFIT



MBR5200




Disc Type (Solid/Vented)	Vented
Position	
Number of Holes	6
Bolt Hole Circle Diameter (mm)	245
Warranty Period (Months)	24




A Outer Diameter (mm)	330
B Thickness (Max/Min) (mm)	32/29
C Inner Diameter (mm)	146
D Height (mm)	129.5
E Centering Diameter (mm)	185

MBR5201



Disc Type (Solid/Vented)	Vented
Position	
Number of Holes	10
Bolt Hole Circle Diameter (mm)	120
Warranty Period (Months)	24



A Outer Diameter (mm)	330
B Thickness (Max/Min) (mm)	34/28
C Inner Diameter (mm)	142
D Height (mm)	112.8
E Centering Diameter (mm)	95

1



2



3




4




5




**ALLFIT****MBR5202**


Disc Type (Solid/Vented)	Vented
Position	
Number of Holes	10
Bolt Hole Circle Diameter (mm)	335
Warranty Period (Months)	24



A Outer Diameter (mm)	375
B Thickness (Max/Min) (mm)	45/37
C Inner Diameter (mm)	198
D Height (mm)	168.5
E Centering Diameter (mm)	290

MBR5203

Disc Type (Solid/Vented)	Vented
Position	
Number of Holes	10
Bolt Hole Circle Diameter (mm)	335
Warranty Period (Months)	24



A Outer Diameter (mm)	430
B Thickness (Max/Min) (mm)	45/37
C Inner Diameter (mm)	206
D Height (mm)	187.5
E Centering Diameter (mm)	300


**7.2**




ALLFIT



MBR5204




Disc Type (Solid/Vented)	Vented
Position	
Number of Holes	10
Bolt Hole Circle Diameter (mm)	335
Warranty Period (Months)	24




A Outer Diameter (mm)	380
B Thickness (Max/Min) (mm)	45/37
C Inner Diameter (mm)	191
D Height (mm)	187.5
E Centering Diameter (mm)	300

MBR6025



Disc Type (Solid/Vented)	Vented
Position	
Number of Holes	8
Bolt Hole Circle Diameter (mm)	275
Warranty Period (Months)	24



A Outer Diameter (mm)	330
B Thickness (Max/Min) (mm)	34/31
C Inner Diameter (mm)	127
D Height (mm)	141
E Centering Diameter (mm)	215



7.2




MERITOR



ALLFIT

MBR6026



Disc Type (Solid/Vented)

Vented

Position



Number of Holes


8

Bolt Hole Circle Diameter (mm)

275

Warranty Period (Months)

24



A Outer Diameter (mm)

377

B Thickness (Max/Min) (mm)

45/37

C Inner Diameter (mm)

159


D Height (mm)

151

E Centering Diameter (mm)

215

MBR6027



Disc Type (Solid/Vented)

Vented

Position



Number of Holes


8

Bolt Hole Circle Diameter (mm)

275

Warranty Period (Months)

24



A Outer Diameter (mm)

377

B Thickness (Max/Min) (mm)

45/37

C Inner Diameter (mm)

163

D Height (mm)

223

E Centering Diameter (mm)

225







ALLFIT



MBR6028




Disc Type (Solid/Vented)	Vented
Position	
Number of Holes	8
Bolt Hole Circle Diameter (mm)	275
Warranty Period (Months)	24




A Outer Diameter (mm)	377
B Thickness (Max/Min) (mm)	45/37
C Inner Diameter (mm)	163
D Height (mm)	222
E Centering Diameter (mm)	225

MBR6029



Disc Type (Solid/Vented)	Vented
Position	
Number of Holes	14
Bolt Hole Circle Diameter (mm)	144
Warranty Period (Months)	24




A Outer Diameter (mm)	376
B Thickness (Max/Min) (mm)	45/38
C Inner Diameter (mm)	113
D Height (mm)	107
E Centering Diameter (mm)	113



ALLFIT

MBR6036

①



Disc Type (Solid/Vented)

Vented

Position



Number of Holes


12

Bolt Hole Circle Diameter (mm)

240

Warranty Period (Months)

24



A Outer Diameter (mm)

432

B Thickness (Max/Min) (mm)

45/41

C Inner Diameter (mm)

234

D Height (mm)


138.5

E Centering Diameter (mm)

210

MBR6037

①



Disc Type (Solid/Vented)

Vented

Position



Number of Holes


12

Bolt Hole Circle Diameter (mm)

240

Warranty Period (Months)

24



A Outer Diameter (mm)

432

B Thickness (Max/Min) (mm)

45/37

C Inner Diameter (mm)

184

D Height (mm)

154.5

E Centering Diameter (mm)

210



7.2





1



2



3



4



5





1



2



3



4



5



		
Auwarter		
082135830		MBR5184
Bova		
0004200172		MBR5184
1238372		MBR2695
1415147		MBR5032
204566		MBR5076
234110		MBR5184
299095		MBR2695
4200172		MBR5184
501314498		MBR5032
501315288		MBR5032
82135830		MBR5032
8285472000		MBR5032
8285472000		MBR5184
B221412		MBR5032
BPW		
03.088.34.01.7		MBR5047
03.088.34.02.0		MBR5061
03.088.34.03.0		MBR5062
03.088.34.03.7		MBR5062
03.088.34.04.0		MBR5061
03.088.34.04.7		MBR5061
03.088.34.06.0		MBR5061
03.088.34.08.0		MBR5060
03.088.34.08.7		MBR5060
03.088.34.10.0		MBR5099
03.088.34.10.7		MBR5099
03.088.34.13.0		MBR5102
03.088.35.01.0		MBR5047
03.088.35.03.0		MBR5048
03.088.35.05.0		MBR5105
03.088.35.05.7		MBR5105
0308834020		MBR5061
0308834020		MBR5180
0308834030		MBR5062
0308834037		MBR5062
0308834040		MBR5061
0308834047		MBR5061
0308834060		MBR5061
0308834067		MBR5061
0308834067		MBR5180
0308834080		MBR5060
0308834087		MBR5060
0308834100		MBR5099
0308834107		MBR5099
0308834130		MBR5102
0308835010		MBR5047
0308835030		MBR5048
0308835050		MBR5105
0308835057		MBR5105
308834020		MBR5061
308834020		MBR5180

		
308834030		MBR5062
308834037		MBR5062
308834040		MBR5061
308834047		MBR5061
308834060		MBR5061
308834067		MBR5061
308834067		MBR5180
308834080		MBR5060
308834087		MBR5060
308834100		MBR5099
308834107		MBR5099
308834130		MBR5102
308835010		MBR5047
308835030		MBR5048
308835050		MBR5105
308835057		MBR5105
SB3745		MBR5180
Coherma		
420404		MBR9004
DAF		
1137179		MBR5184
1142132		MBR5096
1238372		MBR2695
1387439		MBR5134
1400069		MBR5104
1400069		MBR5119
1400163		MBR5100
1400273		MBR5097
1400284		MBR5106
1403758		MBR5103
1408252		MBR5100
1408253		MBR5103
1408672		MBR5097
1415147		MBR5032
1521148		MBR5184
1525365		MBR5184
1526575		MBR5124
1526583		MBR5057
1526597		MBR5068
1526603		MBR5108
1536415		MBR5106
1703801		MBR5201
1716711		MBR5104
1716711		MBR5119
1716712		MBR5106
1812563		MBR5134
1812582		MBR5134
1962280		MBR5184
1962308		MBR5092
1962314		MBR5132
1962317		MBR5132
1962320		MBR5112
1962321		MBR5115

		
1962326		MBR9015
1962329		MBR5072
1962331		MBR5074
1962335		MBR5143
1963980		MBR5104
1963980		MBR5119
204566		MBR5076
299095		MBR2695
352281		MBR2695
867922		MBR9004
879087		MBR9014
882577		MBR9018
882578		MBR9017
AMPA014		MBR5049
AMPB481		MBR5049
AMPB860		MBR5049
AMPB887		MBR5006
AMPB889		MBR1832
B221412		MBR5032
JAE0110400012		MBR5132
MAK2487		MBR5006
MAK2578		MBR5006
NJK2785		MBR5049
PAK3545		MBR1832
PAK3546		MBR5006
PAK5513		MBR5006
Dana		
829693		MBR5096
Dennis		
13162046		MBR5185
13162047		MBR5186
655750		MBR9010
657126		MBR5184
657303		MBR5183
657303		MBR5184
6580943		MBR5096
658439		MBR5183
658470		MBR5183
65847039		MBR5184
65851737		MBR5184
658621		MBR5185
658622		MBR5186
944046		MBR5096
DE1050		MBR5183
DEP100013		MBR9010
DP044215		MBR5096
DP044270		MBR5096
UNCVBD201		MBR5108
UNX1857658		MBR1831
Dennison		
657126		MBR5184
657303		MBR5184
658517		MBR5184

		
658537		MBR5184
ERF		
STR68323825		MBR9004
STRMBR5073		MBR5073
STRMBR9018		MBR9018
Evobus		
8.285.000.589		MBR5184
9424230112		MBR5016HD
9424230212		MBR5016HD
9424231212		MBR5016HD
A8.285.000.589		MBR5184
Foden		
867922		MBR9004
879087		MBR9014
Fruehauf		
103696		MBR5064
CF104297		MBR9004
M069018		MBR5064
M200135		MBR5064
M20013501		MBR5064
Irisbus		
2996418		MBR5199
2996419		MBR5200
5010216437		MBR9008
5010422363		MBR9008
5010422593		MBR9008
68325978IB		MBR9013
Iveco		
0299 2271		MBR5116
0299 6706		MBR5116
02994031		MBR5129
0718 3775		MBR5116
0718 3804		MBR5116
0718 9859		MBR5116
1904532		MBR1761
1906438		MBR5063
1906461		MBR5063
1906466		MBR6025
1907526		MBR2649
1907527		MBR2649
1907528		MBR2648
1907529		MBR2648
1907530		MBR2649
1907568		MBR5002
1907725		MBR2648
1907726		MBR2649
1907764		MBR5145
1908577		MBR2648
1908578		MBR2649
299 2271		MBR5116
299 6706		MBR5116
2992271		MBR5116
2992291		MBR6026

*Product definition found in buyers guide



	OE	
...Iveco		
2992470	MBR5063	
2992477	MBR6036	
2992635	MBR6027	
2992636	MBR6028	
2994031	MBR5129	
2994084	3218N1340PK2	
2995702	MBR6029	
2995812	MBR6037	
2995894	MBR6029	
2996049	MBR5194	
2996327	MBR6036	
2996328	MBR6037	
2996329	MBR5063	
2996353	MBR5056	
2996353	MBR9008	
2996707	MBR6026	
2996708	MBR6029	
2996709	MBR6027	
2996710	MBR6028	
2997450	MBR6025	
42063700	MBR5145	
42541277	MBR5184	
42549008	MBR6025	
42552008	MBR5056	
42552008	MBR9008	
42557315	MBR5063	
5 0004 2066	MBR5129	
5 0004 2241	MBR5116	
500041360	3218F1514	
500041924	3218N1340PK2	
500055596	MBR5056	
5001860184	3218F1514	
50043169	3218F1514	
5006172150	MBR5056	
5006172150	MBR9008	
5010216437	MBR9008	
5010422363	MBR9008	
5010422593	MBR9008	
503131307	MBR9013	
503142233	3218F1514	
503621162	MBR5056	
503621162	MBR9008	
504134958	MBR5056	
504134958	MBR9008	
6754210112	MBR5132	
7168368	MBR1761	
7171274	MBR1761	
7172018	MBR2649	
7172880	MBR5002	
7172881	MBR5002	
7172930	MBR5002	

	OE	
7173036	MBR2648	
718 3775	MBR5116	
718 3804	MBR5116	
718 9859	MBR5116	
7182199	MBR6025	
7182681	MBR2648	
7182682	MBR2649	
7183632	MBR6025	
7183776	MBR6026	
7183804	MBR5116	
7183805	MBR6026	
7184077	MBR6027	
7184078	MBR6028	
7184136	MBR6036	
7185503	MBR6037	
7187541	MBR6029	
7187712	MBR6026	
7187713	MBR6027	
7187714	MBR6028	
7189475	MBR6036	
7189476	MBR6037	
7189976	MBR6029	
93161407	MBR5146	
9754210012	MBR5132	
9754210112	MBR5132	
9754210212	MBR5132	
9754210512	MBR5132	
A6754210112	MBR5132	
A9754210012	MBR5132	
A9754210112	MBR5132	
A9754210212	MBR5132	
A9754210512	MBR5132	
AN6754210012	MBR5132	
AN6754210112	MBR5132	
AN9754210012	MBR5132	
AN9754210112	MBR5132	
AN9754210212	MBR5132	
AN9754210512	MBR5132	
E503128761	MBR9013	
II30676	MBR5132	
N6754210012	MBR5132	
N6754210112	MBR5132	
N9754210012	MBR5132	
N9754210112	MBR5132	
N9754210212	MBR5132	
N9754210512	MBR5132	
V1906461	MBR5063	
V2992477	MBR6036	
Kassbohrer		
0501313313	MBR5076	
17924111111	MBR5003	
1.79241E+11	MBR5003	

	OE	
6274210012	MBR5076	
68320820	MBR5076	
8284000208	MBR5003	
828539000	MBR5076	
8285390000	MBR5076	
8285543000	MBR5184	
II351605	MBR5003	
Knorr Bremse		
II37191	MBR5032	
II371910061	MBR5032	
II376380061	MBR5016HD	
II39290F	MBR5014	
K000810	MBR5025	
K005938	MBR5046	
K013569	MBR5183	
Z000557	MBR5032	
Kogel		
28089103	MBR9020	
6604915	MBR9020	
6607394	MBR5190	
Krone		
550016521	MBR5190	
550027979	MBR5190	
Lecinena		
5820103	MBR9018	
5820130	MBR9004	
Leyland		
21227349	MBR9018	
AMPA014	MBR5049	
MAK2487	MBR5006	
NUK2785	MBR5049	
PAK3545	MBR1832	
PAK3546	MBR5006	
RAK5412	MBR1832	
RAK7404	MBR1832	
Lucas		
DF1577	MBR1577	
DF1588	MBR1588	
DF1761	MBR1761	
DF1764	MBR5029	
DF1765	MBR5021	
DF1831	MBR1831	
DF1832	MBR1832	
DF2648	MBR2648	
DF2649	MBR2649	
DF2693	MBR2693	
DF2695	MBR2695	
DF5002	MBR5002	
DF5003	MBR5003	
MAN		
1907764	MBR5145	
36.50803.0002	MBR5184	

	OE	
36508030000	MBR5184	
81501100010	MBR5010	
81508020010	MBR5010	
81508030001	MBR5011	
81508030009	MBR5011	
81508030010	MBR5010	
81508030014	MBR5011	
81508030015	MBR5011	
81508030020	MBR5014	
81508030021	MBR5068	
81508030022	MBR5013	
81508030023	MBR5057	
81508030024	MBR5012	
81508030026	MBR5012	
81508030027	MBR5014	
81508030028	MBR5078	
81508030031	MBR5057	
81508030033	MBR5057	
81508030034	MBR5057	
81508030035	MBR5057	
81508030036	MBR5057	
81508030038	MBR5057	
81508030039	MBR5092	
81508030040	MBR5057	
81508030041	MBR5068	
81508030042	MBR5182	
81508030046	MBR5057	
81508030047	MBR5068	
81508030048	MBR5078	
81508030053	MBR5182	
81508030054	MBR5181	
81508030057	MBR5014	
81508030061	MBR5013	
81508030062	MBR5181	
81508030063	MBR5181	
9754210112	MBR5077	
9754230312	MBR5071	
N101101.5508	MBR5184	
N1011015508	MBR5184	
N2508030028	MBR9018	
N2508030029	MBR5073	
N2508030030	MBR9004	
STR68323825	MBR9004	
STRMBR5073	MBR5073	
ZG001030007	MBR9014	
ZG004070002	MBR9018	
ZG004130007	MBR5025	
ZG038260007	MBR2648	
ZG047720007	MBR5032	
MCW		
X1857658	MBR1831	
X2057948	MBR1831	



1



2



3



4



5



		
Mercedes		
000 420 0172	MBR5184	
000 420 0272	MBR5184	
000 421 01 12	MBR5076	
000 421 0312	MBR5184	
006 832 05 20	MBR5076	
050 131 61 23	MBR5076	
34564210312	MBR5015	
3564210312	MBR5015	
3564211012	MBR5015	
3564211212	MBR5015	
5010216932	MBR5095	
5010260102	MBR5095	
6014200072	MBR1577	
6014200272	MBR1577	
6014215012	MBR1577	
6014215112	MBR1577	
6137127082	MBR5076	
623 100 08 70	MBR5076	
627 421 00 12	MBR5076	
6384210112	MBR5066	
6694210112	MBR1588	
6694210612	MBR1588	
6754210012	MBR5132	
9424210912	MBR5016HD	
9424211012	MBR5016HD	
9424211112	MBR5016HD	
9424211212	MBR5016HD	
9424211312	MBR5046	
9424212112	MBR5016HD	
9424212312	MBR5016HD	
9424212512	MBR5016HD	
9424212612	MBR5016HD	
9424230012	MBR5016HD	
9424230112	MBR5016HD	
9434210312	MBR5128	
9434210412	MBR5128	
9434210512	MBR5128	
9604210312	MBR5191	
970 423 02 12	MBR5092	
970 423 0212	MBR5092	
970 423 09 12	MBR5092	
9704210012	MBR5066	
9704210112	MBR5066	
9704210212	MBR5066	
9704210612	MBR5066	
9704210712	MBR5066	
9704230212	MBR5092	
9704230412	MBR5070	
9704230612	MBR5070	
9754120112	MBR5077	
9754210012	MBR5077	

		
9754210112	MBR5077	
9754210212	MBR5077	
9754230012	MBR5071	
9754230312	MBR5071	
9754230612	MBR5071	
A000 420 0172	MBR5184	
A000 420 0272	MBR5184	
A000 421 0312	MBR5184	
A3564210312	MBR5015	
A3564211012	MBR5015	
A3564211212	MBR5015	
A5010216932	MBR5095	
A5010260102	MBR5095	
A6014200272	MBR1577	
A6014215112	MBR1577	
A6384210112	MBR5066	
A6694210112	MBR1588	
A6754210012	MBR5132	
A81508030039	MBR5092	
A8285000589	MBR5184	
A9424210912	MBR5016HD	
A9424211012	MBR5016HD	
A9424211112	MBR5016HD	
A9424211212	MBR5016HD	
A9424212112	MBR5016HD	
A9424230012	MBR5016HD	
A9424230112	MBR5016HD	
A9434210312	MBR5128	
A970 423 02 12	MBR5092	
A970 423 0212	MBR5092	
A970 423 09 12	MBR5092	
A9704210012	MBR5066	
A9704210112	MBR5066	
A9704210212	MBR5066	
A9704210612	MBR5066	
A9704230212	MBR5092	
A9704230412	MBR5070	
A9704230912	MBR5092	
A9754210112	MBR5077	
A9754210212	MBR5077	
A9754230012	MBR5071	
A9754230312	MBR5071	
A9754230612	MBR5071	
AN0004200172	MBR5184	
AN0004200272	MBR5184	
AN0004210312	MBR5184	
AN81508030039	MBR5092	
AN8285000589	MBR5184	
AN9704230212	MBR5092	
AN9704230912	MBR5092	
N0004200172	MBR5184	
N0004200272	MBR5184	

		
N0004210312	MBR5184	
N81508030039	MBR5092	
N8285000589	MBR5184	
N9704230212	MBR5092	
N9704230912	MBR5092	
Meritor		
08325371	MBR9015	
08325373	MBR9015	
21224263	MBR5079	
21225115	MBR5073	
21227349	MBR5073	
3218R1500	MBR9025	
5021180772	MBR9018	
5021200858	MBR9014	
5021210521	MBR9017	
68323231	MBR9002	
68323736	MBR9016	
68323740	MBR9011	
68323825	MBR5124	
68323825	MBR9004	
MBP9004	MBR5124	
MBR9018	MBR5073	
Neoplan		
000234110	MBR5184	
011015508	MBR5184	
0501316953	MBR5184	
072136218	MBR5184	
080455010	MBR5184	
082133300	MBR5184	
082135830	MBR5184	
11015508	MBR5184	
14008002	MBR5076	
1415147	MBR5032	
1415147	MBR5184	
22591141183	MBR5029	
299095	MBR2695	
6779208	MBR5029	
67792085	MBR5029	
81508030001	MBR5011	
81508030009	MBR5011	
82133300	MBR5184	
82135830	MBR5032	
82135830	MBR5184	
8285472000	MBR5032	
9754210112	MBR5077	
9754230312	MBR5071	
9755420012	MBR5071	
B221412	MBR5032	
II37191	MBR5184	
II371910061	MBR5184	
Optare		
28050090	MBR5057	

		
28050090#B	MBR5057	
UN20400566	MBR5076	
UNNMBR5108	MBR5108	
UNNMBR5108#B	MBR5108	
X1857658	MBR1831	
Paccar		
1525297	MBR5073	
1526537	MBR1832	
1526538	MBR5006	
1526575	MBR5124	
1526576	MBR5046	
1526577	MBR5016HD	
1526578	MBR2648	
1526579	MBR5025	
1526580	MBR5112	
1526581	MBR5066	
1526583	MBR5057	
1526584	MBR5072	
1526585	MBR5063	
1526587	MBR5117	
1526588	MBR5064	
1526590	MBR5012	
1526591	MBR5056	
1526592	MBR5105	
1526593	MBR5059	
1526594	MBR5047	
1526595	MBR5079	
1526596	MBR5092	
1526597	MBR5068	
1526598	MBR5074	
1526599	MBR2649	
1526603	MBR5108	
1526604	MBR5048	
1526606	MBR5070	
1526682	MBR5097	
1526683	MBR5100	
1526684	MBR5103	
1526886	MBR5077	
1527130	MBR5014	
1527286	MBR5071	
1527288	MBR5099	
867922	MBR9004	
879087	MBR9014	
882577	MBR9018	
882578	MBR9017	
887687	MBR5061	
905650	MBR5062	
9600006	MBR9010	
Renault		
5000297808	MBR2693	
5000450158	MBR2693	
5000545242	MBR2693	

*Product definition found in buyers guide



		
...Renault		
5001667798	MBR5141	
5001864498	MBR5140	
5010216437	MBR5056	
5010216437	MBR9008	
5010216931	MBR5109	
5010216932	MBR5095	
5010260101	MBR5109	
5010260102	MBR5095	
5010422262	MBR5117	
5010422263	MBR5112	
5010422264	MBR5101	
5010422363	MBR5056	
5010422363	MBR9008	
5010422364	MBR5101	
5010422593	MBR5056	
5010422593	MBR9008	
5010525014	MBR5104	
5010525014	MBR5119	
5010525015	MBR5115	
5010525308	MBR5117	
5010525326	MBR9011	
5010525362	MBR5115	
5010525508	MBR9012	
5010598304	MBR5192	
5010598305	MBR5193	
5010598306	MBR5115	
5021139169	MBR9018	
5021170653	MBR9004	
5021180772	MBR9018	
5021200798	MBR1588	
5021200800	MBR1761	
5021200802	MBR1831	
5021200803	MBR1832	
5021200804	MBR2648	
5021200805	MBR2649	
5021200806	MBR2693	
5021200808	MBR2695	
5021200812	MBR5002	
5021200813	MBR5003	
5021200816	MBR5006	
5021200817	MBR5010	
5021200818	MBR5011	
5021200819	MBR5012	
5021200820	MBR5013	
5021200821	MBR5014	
5021200822	MBR5015	
5021200823	MBR5016HD	
5021200824	MBR5021	
5021200825	MBR5025	
5021200827	MBR5029	
5021200828	MBR5031	

		
5021200829	MBR5032	
5021200840	MBR5046	
5021200841	MBR5047	
5021200842	MBR5048	
5021200843	MBR5049	
5021200858	MBR9014	
5021200858	MBR9015	
5021210521	MBR9017	
7420515093	MBR5140	
7421526754	MBR5142	
7421866443	MBR5112	
7421866446	MBR5112	
7421867375	MBR5104	
7421867375	MBR5119	
7482194787	MBR5056	
7482194787	MBR9008	
7482421131	MBR5115	
85103805	MBR5167	
ROR		
21224263	MBR5079	
21225115	MBR5073	
21227349	MBR5073	
3218R1500	MBR9025	
68323825	MBR5124	
SAE-SMB		
103696	MBR5064	
103836	MBR5096	
M069018	MBR5064	
M078157	MBR5096	
M200135	MBR5064	
M20013501	MBR5064	
SAF		
1079000400	MBR5072	
4079000300	MBR5074	
4079000301	MBR5074	
4079000400	MBR5072	
4079000401	MBR5072	
4079000500	MBR5046	
4079000501	MBR5046	
4079000502	MBR5046	
4079000700	MBR5059	
40790007001	MBR5059	
4079000701	MBR5059	
4079001000	MBR5139	
4079001001	MBR5139	
4079001003	MBR5139	
4079001300	MBR5125	
4079001301	MBR5125	
4079001302	MBR5125	
4079001303	MBR5125	
4079001700	MBR5190	
4079001701	MBR5190	

		
4079001751	MBR5190	
4.079.0018.01	MBR5195	
Scania		
11402272	MBR5025	
1402272	MBR5025	
1415147	MBR5032	
1415147	MBR5184	
1852817	MBR5025	
2114496	MBR5073	
2114497	MBR5124	
2114498	MBR9004	
2114499	MBR9014	
2114500	MBR9017	
2114501	MBR9018	
82135830	MBR5032	
8285472000	MBR5032	
B221412	MBR5032	
Schmitz Cargobull		
017870	MBR5143	
1004657	MBR5074	
1088133	MBR5202	
1142408	MBR5190	
17870	MBR5143	
4079001600	MBR5197	
Setra		
2069432001	MBR5076	
501313313	MBR5076	
6274210012	MBR5076	
68320820	MBR5076	
8.225.000.589	MBR5184	
8.285.000.589	MBR5184	
9434210312	MBR5128	
A8.285.000.589	MBR5184	
H31025	MBR5184	
H37257	MBR5076	
Valx		
50390001	MBR5203	
50390002	MBR5204	
6622256114	MBR5203	
Van Hool		
10721062	MBR9016	
10977055	MBR9016	
11047678	MBR5196	
1402272	MBR5025	
20564467	MBR9013	
20995144	MBR9013	
920924972	MBR5184	
VDL		
234110	MBR5184	
Volvo		
20428193	MBR5140	
20442374	MBR5153	

		
20515083	MBR5140	
20515097	MBR5141	
20564467	MBR9013	
20700509	MBR5193	
20704423	MBR5115	
20995144	MBR9013	
21526754	MBR5142	
21575071	MBR5140	
22591141183	MBR5029	
22591141184	MBR5021	
3092224 S2	MBR5153	
3092710	MBR5142	
3095632	MBR9002	
3095652	MBR9002	
3095672	MBR9000	
3112965	MBR5108	
3173047	MBR5167	
6774686	MBR5021	
6774686/7	MBR5021	
67746867	MBR5021	
6775227	MBR5031	
67752273	MBR5031	
67752279	MBR5031	
6779208	MBR5029	
6779208/5	MBR5029	
67792085	MBR5029	
68323232	MBR9000	
68325978VT	MBR9013	
82421140	MBR5115	
85103803	MBR5140	
85103804	MBR5141	
85103806	MBR5153	
85110494	MBR5167	
85110495	MBR5141	
85110496	MBR5140	
AMMBR5016HD	MBR5016HD	
AMMBR5046	MBR5046	
AMMBR9004	MBR9004	
AMMBR9014	MBR9014	
AMMBR9018	MBR9018	
Wabco		
12999813	MBR5097	
ZF		
0501316953	MBR5032	
501318082	MBR9013	



1



2



3



4



5





1



2



3



4



5





1



2



3



4



5







Vehicle models, trademarks, brands and names depicted herein are the property of their respective owners, and may not be associated with Cummins Inc. and Meritor, Inc. or its affiliates.



Cummins Inc.
Box 3005
Columbus, IN 47202-3005
U.S.A.

cummins.com

SP-2439
Bulletin 6715474 Produced in U.K. 8/26
©2026 Meritor, Inc.