

PORTABLE GENERATOR RUNNING COVERS

Safety and Protection During the Storm



OPEN FRAME GENERATORS
A076C159



INVERTER GENERATORS
A076C160



Toolless Installation
Instalación Sin Herramienta
Installation Sans Outil



NFPA Flame Retardant Generator Tent
Carpa de Generador Ignífuga NFPA
Tente de Générateur Ignifuge Conforme à la Norme NFPA



Cummins 1-Year Limited Parts Warranty
Garantía Limitada de Piezas de 1 Año de Cummins
Pièces Cummins Avec Une Garantie Limitée D'Un An



Transparent Apron and Door for Easy View, Easy Fuel
Delantal y Puerta Transparentes Para Fácil Visualización y Fácil Combustible
Tablier et Porte Translucides Pour Une Supervision et Ravitaillement de Carburant Facile



Keep Generator Safely Outside in Bad Weather
Mantenga el Generador de Forma Segura Afuera Cuando Hace Mal Tiempo
Maintient Votre Générateur à L'Extérieur en Sécurité Par Mauvais Temps



Protects From Wind & Rain up to 70mph and 18" of Snow
Protege Del Viento y la Lluvia Hasta 70 Mph y 18" de Nieve
Protège du Vent et de la Pluie Jusqu'à 112 km/h et Jusqu'à 45 cm de Neige




**FOR
A WORLD
THAT'S
ALWAYS ON™**

PORTABLE GENERATOR RUNNING COVERS


PORTABLE OPEN FRAME GENERATOR RUNNING COVER

Part Number	A076C159
Compatibility	P9500DF P9500DF EFI
Non-Cummins Generator Compatibility	80 in to 107 in Perimeter
Max Wind Load	70 mph
Max Snow Load	18 in
Warranty	1 Year Limited Cummins Parts Warranty*
Safety	NFPA 701 FR Materials Tested, CO Sensor Compatible



PORTABLE INVERTER GENERATOR RUNNING COVER

Part Number	A076C160
Compatibility	P4500i P4500iDF P5000iDF EFI
Non-Cummins Generator Compatibility	Up to 124 in Perimeter
Max Wind Load	70 mph
Max Snow Load	18 in
Warranty	1 Year Limited Cummins Parts Warranty*
Safety	NFPA 701 FR Materials Tested, CO Sensor Compatible



*See owner's manual for exclusions



Cummins Inc.
Box 3005
Columbus, IN 47202-3005
U.S.A.

cummins.com

Bulletin 6579193 Produced in U.S.A. 8/24
©2024 Cummins Inc.