



Give Your Vessel a
New Heartbeat.

Mechanical ReCon® Engines.




Repower with a ReCon® Engine.

Many engine rebuilders fix only what is broken – they may not replace worn parts that are borderline or hidden from view. Cummins ReCon® engines are completely disassembled, inspected, remanufactured to factory specifications, performance tested and backed by a full 2-year/2000-hour Cummins warranty. After product installation, all ReCon engines receive an installation review and sea trial from a certified Cummins representative.

For a genuine Cummins solution with less downtime, and performance you can depend on, count on Cummins ReCon engines. Every™ Time.

The Power of Cummins ReCon Engines:

- After product installation, all ReCon engines receive an installation review and sea trial from a certified Cummins representative
- Complete Repower package: Instrument panel, isolator mounts, extension harness, exhaust elbow, and front mounting brackets
- Available with new transmissions
- Extended warranties available
- Lower cost versus “New”
- Core value for your old Cummins engine
- Application engineers to help with your installation needs
- Also available, ReCon exchange engines or short/long blocks.



Mechanical ReCon Marine Engines Available:

- DR6503RX 4BT TO M 150/155@2800 INT/HO R
- DR6500RX 6BT T1 M 210/220@2600 INT/HO R
- DR6510RX 6BTA T1 M 260/270@2600 INT/HO R
- DR6489RX 6BTA T1 M 315/330@2800 INT/HO R
- DR6508RX 6CTA T1 M 430/450@2600 INT/HO R

Includes the following: Rear Mount Exhaust, Air Cleaner, Shallow Sump Oil Pan, Heat Exchanger, 12 Volt System, Instrument Panel, Extension Harness, Isolator Mounts, Alternator, Flywheel Housing, Wiring Harness, Flywheel, Front Engine Support, Starter, Exhaust Connection, and Sea Water Pump.

For additional information on the options for repowering your vessel with a marine engine contact your local Cummins service provider. To locate your nearest Cummins service provider, call 1-800-DIESELS™ or visit locator.cummins.com.



Cummins Inc.
Box 3005
Columbus, IN 47202-3005
U.S.A.

Phone: 1-800-DIESELS™ (1-800-343-7357)
Fax: 1-800-232-6393
Internet: cumminsengines.com

[Twitter.com/CumminsEngines](https://twitter.com/CumminsEngines)
[YouTube.com/CumminsEngines](https://www.youtube.com/CumminsEngines)

Bulletin 5410629 09/16
©2016 Cummins Inc.

Cummins ReCon® product offerings and specifications are subject to change without notice.