

PERFORMANCE HAS A NAME.

X15™

PERFORMANCE
S E R I E S

The X15 Performance Series engine is an undisputed leader in its class, delivering power, machine capability and productivity to operators globally. The X15 is tailored to your machine, responding precisely when you need it to and maximizing productivity, even in the toughest conditions. When you can't afford to stop, we're Always On.



MORE PERFORMANCE

$$\left[\begin{array}{c} 15\% \\ \text{MORE POWER} \end{array} \right] + \left[\begin{array}{c} 60\% \\ \text{MORE TORQUE} \end{array} \right] = \text{MORE PRODUCTIVITY}$$

Compared to the previous model

MORE RELIABILITY

- Expert fault recommendations through Connected Diagnostics™
- Remote monitoring that extends engine life and reduces downtime

MORE PROVEN

- Award winning VGT™ Turbocharger
- XPI fuel system
- Proven DOC, SCR and DPF technology

MORE GLOBAL

- Common products across emissions levels and locations
- Certified to both EU Stage V and EPA Tier 4 Final emissions standards

LESS COST OF OPERATION



LESS COMPLEXITY

- SIMPLER ARCHITECTURE
- EASIER INSTALLATION

LESS FUEL USAGE


- LESS FUEL CONSUMPTION AND NOISE
- FULLY INTEGRATED COMPONENTS FOR MAXIMUM OPTIMIZATION



ALWAYS ON

MORE POWER

- 15% more power than the previous model
- More machine capability with higher power density
- Exceptional reliability maintained with performance increases
- Ratings ranging from 675 hp to 450 hp





MORE TORQUE

- 60% higher peak torque
- Torque curve increases below rated speed support machine productivity improvements

X15™

PERFORMANCE SERIES



Power HP (kW)	Peak Torque lb-ft (N•m) @ rpm
X15 Power Ratings	
675 (503)	2050 (2778) @ 1400
650 (485)	2050 (2778) @ 1400
630 (470)	2050 (2778) @ 1400
625 (466)	2050 (2779) @ 1400
600 (447)	2050 (2779) @ 1400
575 (429)	1950 (2645) @ 1400
550 (410)	1750 (2373) @ 1400
535 (399)	1950 (2645) @ 1400
525 (391)	1750 (2373) @ 1400
500 (373)	1600 (2169) @ 1400
472 (352)	1700 (2305) @ 1400
450 (336)	1700 (2305) @ 1400

*Additional ratings may be available; contact your distributor for more information.

MORE SUPPORT

Cummins Care is not a typical call center. We are a solutions center helping to prevent issues, provide answers quickly and reimburse accurately. We are your connection to a whole new level of customer service that is Always On to support and deliver faster personal attention with rapid results. From the moment you engage with Cummins Care, you will have access to a Cummins expert with specialized skill sets, experience and in-depth knowledge to take care of your needs.



cummins.com

All rights reserved. Cummins is a registered trademark of Cummins Inc.

Bulletin 5544052 Printed in U.S.A. Rev. 9/19 ©2019 Cummins Inc.