



# Cummins B6.7™ for motorhomes


You deserve a diesel. One with proven reliability and performance. Cummins B6.7 fits that description, and features improved fuel economy and extended maintenance intervals. Plus, it's a prime example of American ingenuity as it's designed in Indiana and built in North Carolina.

## PERFORMANCE

- **Quiet responsiveness:** Cummins VGT® Turbo and High Pressure Common Rail (HPCR) fuel system provide exceptional throttle response at every rpm.
- **Torque where you drive:** Cummins B6.7 has maximum torque over a wide operating range to minimize downshifting.
- **Proven performance:** Over 12 million B Series engines have been sold in the last 35-plus years.
- **Optimized emissions control:** Cummins Single Module™ aftertreatment system has exceptional thermal efficiency and meets the latest emissions requirements.

## COST OF OPERATION

- **Improved fuel economy:** Improved aftertreatment and engine controls result in greater efficiency and fewer regenerations.
- **Reduced maintenance:** Up to 18 month fluid and filter changes with a maintenance free crankcase breather
- **Full vehicle integration:** Each OEM installation undergoes rigorous testing to optimize dependability.



## SUPPORT


- **Peace of mind:** With a standard 5-year/100,000-mile base warranty and optional full engine and aftertreatment coverages for up to eight years, we've got you covered.
- **Cummins on every corner:** Over 3,700 authorized locations across North America to support parts and service needs
- **One source for service:** Your local Cummins Sales and Service location supports both Cummins engines and Cummins Onan generators.
- **World-class support:** Call 1-800-CUMMINS (1-800-343-7357) for answers to your questions and support for your service needs.
- **Cummins Guidanz™ and INLINE Mini:** Allow you to read check engine lights and share via email with your service provider

## POWERING YOUR DRIVE AND YOUR RELAXATION

Cummins covers all your power needs by also offering a range of generators for the RV market.



## MORE TORQUE WHERE YOU DRIVE FOR 2021



## B6.7 RATINGS

| Engine   | Maximum HP (kW) | Governed speed (RPM) | Peak torque LB-FT (N·M) @ RPM |
|----------|-----------------|----------------------|-------------------------------|
| B6.7 360 | 360 (269)       | 2,600                | 800 (1085) @ 1,800            |
| B6.7 340 | 340 (254)       | 2,600                | 700 (949) @ 1,600             |
| B5.6 325 | 325 (242)       | 2,600                | 750 (1017) @ 1,800            |
| B6.7 300 | 300 (224)       | 2,600                | 660 (895) @ 1,600             |
| B6.7 280 | 280 (209)       | 2,600                | 660 (895) @ 1,600             |
| B6.7 260 | 260 (194)       | 2,400                | 660 (895) @ 1,600             |

## B6.7 TYPICAL MAINTENANCE INTERVALS

| Maintenance item          | Miles/Kilometers*     | Months* |
|---------------------------|-----------------------|---------|
| Oil and filter            | 20,000 mi/32,000 km   | 18      |
| Fuel filter               | 60,000 mi/97,000 km   | 18      |
| Valve lash check          | 150,000 mi/240,000 km | —       |
| Crankcase breather filter | Maintenance free      |         |

\* Whichever occurs first. Consult your chassis and engine Owners Manuals for more information.

## B6.7 SPECIFICATIONS

|                            |                          |
|----------------------------|--------------------------|
| Configuration              | Inline 6                 |
| Displacement               | 408 cu in/6.7 L          |
| Lube oil capacity          | 17.6-20.8 qt/16.7-19.7 L |
| Idle speed                 | 700-900 rpm              |
| Optional compression brake | Up to 182 hp @ 3200 rpm  |
| No load governed speed     | 2,800 rpm                |
| Engine weight (dry)        | 1,150 lb/522 kg          |
| Aftertreatment weight      | 125-167 lb/57-76 kg      |
| Biodiesel compatibility    | Up to B20                |
| Maximum overspeed          | 4,200 rpm                |

## GET THE LATEST INFORMATION

Visit [rv.cummins.com](http://rv.cummins.com) to learn more about Cummins B6.7 engines and Onan generators.



Cummins Inc.  
Box 3005  
Columbus, IN 47202-3005  
U.S.A.

[cummins.com](http://cummins.com)

Bulletin 5410643 Produced in U.S.A. Rev. 3/25  
©2025 Cummins Inc.