

# QSG12




335-512 hp  
250-382 kW

Cummins  
Direct Flow™  
Air Cleaner



12-Liter  
6-Cylinder




Diesel Particulate Filter (DPF) and  
Selective Catalytic Reduction (SCR)



- Best-in-class performance in a smaller package with lower total installation cost
- Superior torque with Cummins Xtra-High Pressure Injection (XPI) fuel system
- No Exhaust Gas Recirculation (EGR)
- Outstanding service and support, with a dealer network of over 6,500 distributor and dealer locations in 190 countries
- 24/7/365 support by calling Cummins Care at 1-800-DIESELS™ (1-800-343-7357)

- Proven aftertreatment solution to meet EPA Tier 4 Final regulations
- Virtually passive operation
- Active regeneration required in less than 1 percent of runtime

# Forward To Final.



Power Output	335-512 hp	(250-382 kW)
Peak Torque	1696 lb-ft	(2299 N•m)
Engine Weight (Wet)	1,896 lbs	(860 kg)
Aftertreatment Weight	300 lbs	(136 kg)
Fuel System	Electronic XPI Fuel System	
Air Intake	Cummins Direct Flow Air Cleaner	
Turbo	Cummins Wastegate Turbo	
Emissions Control	DPF + SCR	
Electronics	Engine Mount Electronic Control Module (ECM)	
Crankcase Filter	Open Crankcase Ventilation	
Fuel Performance	BSFC Optimized for Industrial Duty Cycles	



**Cummins Inc.**  
**Box 3005**  
**Columbus, IN 47202-3005**  
**U.S.A.**

Phone: 1-800-DIESELS™ (1-800-343-7357)  
Fax: 1-800-232-6393  
Internet: cumminsengines.com

Twitter.com/CumminsEngines  
YouTube.com/CumminsEngines

Bulletin 4087362 Printed in U.S.A. 6/14  
©2014 Cummins Inc.