




CUMMINS INC.
 Charleston, SC 29405
 Marine Performance Curves
marine.cummins.com

Basic Engine Model QSB 6.7 HO	Curve Number: M-94977	
Engine Configuration D313011MX03	CPL Code: 4699	Date: 29-Jul-14

Displacement: **6.7 liter [408 in³]**
 Bore: **107 mm [4.21 in]**
 Stroke: **124 mm [4.88 in]**
 Cylinders: **6**
 Fuel System: **Cummins High Pressure Common Rail**

Rated Power: **312 kw [419 bhp, 425 mhp]**
 Rated Speed: **3000 rpm**
 Rating Type: **High Output**
 Aspiration: **Turbocharged / Sea Water Aftercooled**

CERTIFIED: This diesel engine complies with or is certified to the following agencies requirements:
 EPA Tier 3 - Model year requirements of the EPA marine regulation (40CFR1042)
 IMO Tier II (Two) NOx requirements of International Maritime Organization (IMO), MARPOL 73/78 Annex VI, Regulation 13
 RCD - meets the requirements of the Recreational Craft Directive 94/25/EC as amended by 2003/44/EC in accordance with ISO 8178-1



Speed rpm	Full Throttle				Propeller Demand					
	Power		Torque		Power		Torque		Fuel Consumption	
	kw	(hp)	N·m	(ft·lb)	kw	(hp)	N·m	(ft·lb)	L/hr	(gal/hr)
3075	312	(419)	995	(716)						
3000	312	(419)	995	(734)	312	(419.0)	995	(733.5)	86.0	(22.7)
2900	314	(421)	1033	(762)	285	(382.4)	939	(692.4)	77.7	(20.5)
2800	314	(421)	1071	(790)	259	(347.8)	884	(652.3)	70.5	(18.6)
2700	314	(422)	1112	(820)	235	(315.3)	831	(613.2)	63.5	(16.8)
2600	314	(421)	1152	(850)	212	(284.7)	780	(575.1)	55.7	(14.7)
2500	314	(421)	1200	(885)	191	(256.1)	729	(538.0)	50.1	(13.2)
2400	314	(420)	1247	(920)	171	(229.4)	681	(502.0)	44.9	(11.9)
2300	311	(417)	1291	(952)	152	(204.5)	633	(466.9)	39.5	(10.4)
2200	308	(413)	1335	(985)	135	(181.4)	587	(432.9)	35.4	(9.4)
2100	303	(407)	1380	(1017)	119	(159.9)	542	(400.0)	30.8	(8.1)
2000	298	(400)	1424	(1050)	105	(140.2)	499	(368.2)	28.0	(7.4)
1900	254	(340)	1274	(940)	91	(122.1)	457	(337.4)	22.2	(5.9)
1800	223	(299)	1181	(871)	79	(105.5)	417	(307.8)	21.2	(5.6)
1700	194	(260)	1088	(803)	67	(90.4)	379	(279.3)	16.4	(4.3)
1600	167	(224)	995	(734)	57	(76.8)	342	(252.0)	15.3	(4.0)
1500	134	(179)	850	(627)	48	(64.5)	306	(225.8)	12.7	(3.4)

*** Cummins Full Throttle Requirements:**

- Engine achieves or exceeds rated rpm at full throttle under any steady operating condition
- Engine achieves or exceeds rated rpm when accelerating from idle to full throttle

Rated Conditions: Ratings are based upon ISO 15550 reference conditions; air pressure of 100 kPa [29.612 in Hg], air temperature 25deg. C [77 deg. F] and 30% relative humidity. Member NMMA. Unless otherwise specified, tolerance on all values is +/-5%. Values from engine control modules and displayed on instrument panels are not absolute. Tolerance varies, but is generally less than +/-5% when operating within 30% of rated power.

Full Throttle curve represents power at the crankshaft for mature gross engine performance corrected in accordance with ISO 15550. Propeller Curve represents approximate power demand from a typical propeller. Propeller Shaft Power is approximately 3% less than rated crankshaft power after typical reverse/reduction gear losses and may vary depending on the type of gear or propulsion system used.

Fuel Consumption is based on fuel of 35 deg. API gravity at 16 deg C [60 deg. F] having LHV of 42,780 kJ/kg [18390 Btu/lb] and weighing 838.9 g/liter [7.001 lb/U.S. gal].

High Output (HO): Intended for use in variable load applications where full power is limited to one hour out of every eight hours of operation. Also, reduced power must be at or below 200 rpm of the maximum rated rpm. This power rating is for pleasure/non-revenue generating applications that operate 500 hours per year or less.

TECHNICAL DATA DEPT.

CHIEF ENGINEER

Propulsion Marine Engine Performance Data

Curve No. M-94977
 DS: 0
 CPL: 4699
 DATE: 29-Jul-14

General Engine Data

Engine Model	QSB 6.7 HO	
Rating Type	High Output	
Rated Engine Power	312 [419]	kW [hp]
Rated Engine Speed	3000	rpm
Rated Power Production Tolerance	5	±%
Rated Engine Torque	995 [734]	N·m [lb·ft]
Peak Engine Torque @ 2000 rpm.....	1424 [1050]	N·m [lb·ft]
Brake Mean Effective Pressure	1868 [271]	kPa [psi]
Indicated Mean Effective Pressure.....	1868 [271]	kPa [psi]
Maximum Allowable Engine Speed	3085	rpm

Maximum Continuous Torque Capacity from Front of Crank Specifications

Maximum Torque Capacity from Front of Crank ²	995 [734]	N·m [lb·ft]
Compression Ratio	16.5:1	
Piston Speed	12.4 [2441]	m/sec [ft/min]
Firing Order	1-5-3-6-2-4	
Weight (Dry) - Engine With Heat Exchanger System - Average.....	630 [1390]	kg [lb]

Governor Settings

Default Droop Value.....	0%	Refer to MAB 2.04.00-03/23/2006 for Droop explanation
High Speed Governor Break Point.....	3075	rpm
Minimum Idle Speed Setting	600	rpm
Normal Idle Speed Variation	10	±rpm
High Idle Speed Range Minimum	3070	rpm
Maximum	3080	rpm

Noise and Vibration

Average Noise Level - Top	(Idle).....	dBA @ 1m	75
	(Rated)	dBA @ 1m	100
Average Noise Level - Right Side	(Idle).....	dBA @ 1m	75
	(Rated)	dBA @ 1m	100
Average Noise Level - Left Side	(Idle).....	dBA @ 1m	76
	(Rated)	dBA @ 1m	102
Average Noise Level - Front	(Idle).....	dBA @ 1m	76
	(Rated)	dBA @ 1m	101

Fuel System¹

Avg. Fuel Consumption - ISO 8178 E5 Standard Test Cycle	28.9 [7.6]	l/hr [gal/hr]
Fuel Consumption at Rated Speed	85.9 [22.7]	l/hr [gal/hr]
Approximate Fuel Flow to Pump	215.8 [57.0]	l/hr [gal/hr]
Maximum Allowable Fuel Supply to Pump Temperature	60.0 [140]	°C [°F]
Approximate Fuel Flow Return to Tank	129.9 [34.3]	l/hr [gal/hr]
Approximate Fuel Return to Tank Temperature	79.5 [175]	°C [°F]
Maximum Heat Rejection to Drain Fuel	2.4 [136]	kW [Btu/min]
Fuel Pressure - Pump Out/Rail . INSITE Reading	170300 [24,700]	kPa [psi]

TBD= To Be Determined

N/A = Not Applicable

N.A. = Not Available

- ¹ Unless otherwise specified, all data is at rated power conditions and can vary ± 5%.
- ² No rear loads can be applied when the FPTO is fully loaded. Max PTO torque is contingent on torsional analysis results for the specific drive system. Consult Installation Direction Booklet for Limitations.
- ³ Heat rejection to coolant values are based on 50% water/50% ethylene glycol mix and do NOT include fouling factors. If sourcing your own cooler, a service fouling factor should be applied according to the cooler manufacturer's recommendation.
- ⁴ Consult option notes for flow specifications of optional Cummins seawater pumps, if applicable.

CUMMINS INC.
 COLUMBUS, INDIANA

All Data is Subject to Change Without Notice - Consult the following Cummins website for the most recent data:

<http://marine.cummins.com>

Propulsion Marine Engine Performance Data

Curve No. M-94977
 DS: 0
 CPL: 4699
 DATE: 29-Jul-14

Air System¹

Intake Manifold Pressure	kPa [in Hg]	233 [69]
Intake Air Flow	l/sec [cfm]	419 [887]
Heat Rejection to Ambient	kW [Btu/min]	26 [1458.03]

Exhaust System¹

Exhaust Gas Flow	l/sec [cfm]	886 [1,878]
Exhaust Gas Temperature (Turbine Out)	°C [°F]	444 [831]
Exhaust Gas Temperature (Manifold)	°C [°F]	654 [1,209]

Emissions (in accordance with ISO 8178 Cycle E5)

NO _x (Oxides of Nitrogen)	g/kw·hr [g/hp·hr]	4.96 [3.69]
HC (Hydrocarbons)	g/kw·hr [g/hp·hr]	0.20 [0.15]
CO (Carbon Monoxide)	g/kw·hr [g/hp·hr]	0.44 [0.33]
PM (Particulate Matter)	g/kw·hr [g/hp·hr]	0.04 [0.03]
CO ₂ (Carbon dioxide)	g/kw·hr [g/hp·hr]	704.00 [524.97]
CH ₄ (Methane)	g/kw·hr [g/hp·hr]	0.01 [0.00]

Cooling System¹

Sea Water Pump Specifications	MAB 0.08.17-07/16/2001	
Pressure Cap Rating	kPa [psi]	103 [15]
Max. Coolant Outlet Pressure from the Engine.....	kPa [psi]	414 [60]
Max. Pressure Drop Across Any External Cooling System Circuit	kPa [psi]	34 [5]

Sea Water Aftercooled Engine (SWAC)

Coolant Flow to Engine Heat Exchanger	l/min [gal/min]	263 [69.5]
Standard Thermostat Operating Range (Start to Open)	°C [°F]	71 [160]
Standard Thermostat Operating Range (Full Open)	°C [°F]	83 [182]
Heat Rejection to Engine Coolant ³	kW [Btu/min]	N/A [N.A.]

TBD= To Be Determined

N/A = Not Applicable

N.A. = Not Available

- ¹ Unless otherwise specified, all data is at rated power conditions and can vary ± 5%.
- ² No rear loads can be applied when the FPTO is fully loaded. Max PTO torque is contingent on torsional analysis results for the specific drive system. Consult Installation Direction Booklet for Limitations.
- ³ Heat rejection to coolant values are based on 50% water/50% ethylene glycol mix and do NOT include fouling factors. If sourcing your own cooler, a service fouling factor should be applied according to the cooler manufacturer's recommendation.
- ⁴ Consult option notes for flow specifications of optional Cummins seawater pumps, if applicable.

CUMMINS INC.
 COLUMBUS, INDIANA

All Data is Subject to Change Without Notice - Consult the following Cummins website for the most recent data:

<http://marine.cummins.com>