



CUMMINS INC.
Columbus, IN 47201
Marine Performance Curves
marine.cummins.com

Basic Engine Model
QSC8.3-500 INT
Engine Configuration
D413038MX03

Curve Number:
M-92044
CPL Code: **0906** Date: **12-Dec-12**


Displacement: **8.3 liter [505 in³]** Rated Power: **368 kw [493 bhp, 500 mhp]**
Bore: **114 mm [4.49 in]** Rated Speed: **2600 rpm**
Stroke: **135 mm [5.31 in]** Rating Type: **Intermittent Duty**
Fuel System: **HPCR** Aspiration: **Turbocharged / Sea Water Aftercooled**
Cylinders: **6**

CERTIFIED: This diesel engine complies with or is certified to the following agencies requirements:

EPA Tier 2 - Model year requirements of the EPA marine regulation (40CFR94)

EU Stage IIIa - EC Nonroad Mobile Machinery Directive (2004/26/EC)

IMO Tier II - Tier 2 (Two) NOx requirements of International Maritime Organization (IMO), MARPOL 73/78 Annex VI, Regulation 13



Speed	Full Throttle- Power		Full Throttle- Torque		Fuel Cons.- Prop. Curve 2.7 Exp.	
	rpm	kw (hp)	N·m (ft·lb)	L/hr (gal/hr)		
2665	368	(493)	1317	(972)	96.1	(25.4)
2600	368	(493)	1350	(996)	76.1	(20.1)
2400	367	(493)	1462	(1078)	59.4	(15.7)
2200	365	(490)	1586	(1170)	46.2	(12.2)
2000	353	(474)	1687	(1244)	35.7	(9.4)
1800	339	(455)	1735	(1280)	26.5	(7.0)
1600	291	(390)	1223	(902)	18.9	(5.0)
1400	179	(240)	874	(645)	12.4	(3.3)
1200	110	(147)	750	(553)	7.8	(2.1)
1000	79	(105)	617	(455)	5.0	(1.3)
800	52	(69)				

* Cummins Full Throttle Requirements:

- Engine achieves or exceeds rated rpm at full throttle under any steady operating condition
- Engines in variable displacement boats (such as pushboats, tugboats, net druggers, etc.) achieve no less than 100 rpm below rated speed at full throttle during a dead push or bollard pull
- Engine achieves or exceeds rated rpm when accelerating from idle to full throttle

Rated Conditions: Ratings are based upon ISO 15550 reference conditions; air pressure of 100 kPa [29.612 in Hg], air temperature 25deg. C [77 deg. F] and 30% relative humidity. Power is in accordance with IMCI procedure. Member NMMA. Unless otherwise specified, tolerance on all values is +/-5%.

Full Throttle curve represents power at the crankshaft for mature gross engine performance corrected in accordance with ISO 15550. Propeller Curve represents approximate power demand from a typical propeller. Propeller Shaft Power is approximately 3% less than rated crankshaft power after typical reverse/reduction gear losses and may vary depending on the type of gear or propulsion system used.

Fuel Consumption is based on fuel of 35 deg. API gravity at 16 deg C [60 deg. F] having LHV of 42,780 kJ/kg [18390 Btu/lb] and weighing 838.9 g/liter [7.001 lb/U.S. gal].

Intermittent Duty (INT): Intended for intermittent use in variable load applications where full power is limited to two hours out of every eight hours of operation. Also, reduced power operations must be at or below 200 rpm of the maximum rated rpm. This rating is an ISO 15550 fuel stop power rating and is for applications that operate less than 1,500 hours per year.

[Signature]

Propulsion Marine Engine Performance Data

Curve No. M-92044
DS: 3075
CPL: 0906
DATE: 12-Dec-12

General Engine Data

Engine Model		QSC8.3-500 INT
Rating Type		Intermittent Duty
Rated Engine Power	kW [hp]	368 [493]
Rated Engine Speed	rpm	2600
Rated Power Production Tolerance	±%	5
Rated Engine Torque	N·m [lb·ft]	1350 [996]
Peak Engine Torque @ 1800 rpm.....	N·m [lb·ft]	1799 [1327]
Brake Mean Effective Pressure	kPa [psi]	2052 [298]
Indicated Mean Effective Pressure.....	kPa [psi]	N.A. [N.A.]
Maximum Allowable Engine Speed	rpm	2685
Maximum Torque Capacity from Front of Crank ²	N·m [lb·ft]	271 [200]
Compression Ratio		16.3:1
Piston Speed	m/sec [ft/min]	11.7 [2303]
Firing Order		1-5-3-6-2-4
Weight (Dry) - Engine Only - Average	kg [lb]	N.A. [N.A.]
Weight (Dry) - Engine With Heat Exchanger System - Average.....	kg [lb]	896 [1975]
Weight Tolerance (Dry) Engine Only	3xStd Dev(±%)	N.A.

Governor Settings

High Speed Governor Break Point.....		rpm	2665
Minimum Idle Speed Setting		rpm	600
Normal Idle Speed Variation		±rpm	10
High Idle Speed Range Minimum		rpm	2665
Maximum		rpm	2685

Noise and Vibration

Average Noise Level - Top	(Idle).....	dBA @ 1m	82
	(Rated)	dBA @ 1m	98
Average Noise Level - Right Side	(Idle).....	dBA @ 1m	82
	(Rated)	dBA @ 1m	98
Average Noise Level - Left Side	(Idle).....	dBA @ 1m	82
	(Rated)	dBA @ 1m	98
Average Noise Level - Front	(Idle).....	dBA @ 1m	82
	(Rated)	dBA @ 1m	98

Fuel System¹

Avg. Fuel Consumption - ISO 8178 E3 Standard Test Cycle		l/hr [gal/hr]	65.3 [17.3]
Fuel Consumption at Rated Speed		l/hr [gal/hr]	96.1 [25.4]
Approximate Fuel Flow to Pump		l/hr [gal/hr]	151.4 [40.0]
Maximum Allowable Fuel Supply to Pump Temperature		°C [°F]	60.0 [140]
Approximate Fuel Flow Return to Tank		l/hr [gal/hr]	55.3 [14.6]
Approximate Fuel Return to Tank Temperature		°C [°F]	85.1 [185]
Maximum Heat Rejection to Drain Fuel		kW [Btu/min]	1.3 [73]
Fuel Transfer Pump Pressure Range.....		kPa [psi]	N.A.
Fuel Pressure - Pump Out/Rail . Mechanical Gauge		kPa [psi]	N.A.
INSITE Reading		kPa [psi]	160000 [23206]

TBD= To Be Determined

N/A = Not Applicable

N.A. = Not Available

- ¹ Unless otherwise specified, all data is at rated power conditions and can vary ± 5%.
- ² No rear loads can be applied when the FPTO is fully loaded. Max PTO torque is contingent on torsional analysis results for the specific drive system. Consult Installation Direction Booklet for Limitations.
- ³ Heat rejection to coolant values are based on 50% water/50% ethylene glycol mix and do NOT include fouling factors. If sourcing your own cooler, a service fouling factor should be applied according to the cooler manufacturer's recommendation.
- ⁴ Consult option notes for flow specifications of optional Cummins seawater pumps, if applicable.
- ⁵ May not be at rated load and speed. Maximum heat rejection may occur at other than rated conditions.

CUMMINS INC.
COLUMBUS, INDIANA

All Data is Subject to Change Without Notice - Consult the following Cummins Web site for the most recent data:

<http://marine.cummins.com/>

Propulsion Marine Engine Performance Data

Curve No. M-92044
 DS: 3075
 CPL: 0906
 DATE: 12-Dec-12

Air System¹

Intake Manifold Pressure	kPa [in Hg]	202 [60]
Intake Air Flow	l/sec [cfm]	452 [958]
Heat Rejection to Ambient	kW [Btu/min]	34 [1931]

Exhaust System¹

Exhaust Gas Flow	l/sec [cfm]	1098 [2326]
Exhaust Gas Temperature (Turbine Out)	°C [°F]	455 [850]
Exhaust Gas Temperature (Manifold)	°C [°F]	649 [1200]

Emissions (in accordance with ISO 8178 Cycle E3)

NOx (Oxides of Nitrogen)	g/kw-hr [g/hp-hr]	5.62 [4.19]
HC (Hydrocarbons)	g/kw-hr [g/hp-hr]	0.12 [0.09]
CO (Carbon Monoxide)	g/kw-hr [g/hp-hr]	0.31 [0.23]
PM (Particulate Matter)	g/kw-hr [g/hp-hr]	0.10 [0.08]

Cooling System¹

Sea Water Pump Specifications	MAB 0.08.17-07/16/2001	
Pressure Cap Rating (With Heat Exchanger Option)	kPa [psi]	103 [15]

Engines without Low Temperature Aftercooling (LTA)

Sea Water Aftercooled Engine (SWAC)

Coolant Flow to Engine Heat Exchanger	l/min [gal/min]	454 [120]
Standard Thermostat Operating Range (Start to Open)	°C [°F]	71 [160]
Standard Thermostat Operating Range (Full Open)	°C [°F]	81 [178]
Heat Rejection to Engine Coolant ³	kW [Btu/min]	234 [13337]

TBD= To Be Determined

N/A = Not Applicable

N.A. = Not Available

- ¹ Unless otherwise specified, all data is at rated power conditions and can vary ± 5%.
- ² No rear loads can be applied when the FPTO is fully loaded. Max PTO torque is contingent on torsional analysis results for the specific drive system. Consult Installation Direction Booklet for Limitations.
- ³ Heat rejection to coolant values are based on 50% water/50% ethylene glycol mix and do NOT include fouling factors. If sourcing your own cooler, a service fouling factor should be applied according to the cooler manufacturer's recommendation.
- ⁴ Consult option notes for flow specifications of optional Cummins seawater pumps, if applicable.
- ⁵ May not be at rated load and speed. Maximum heat rejection may occur at other than rated conditions.

CUMMINS INC.
 COLUMBUS, INDIANA

All Data is Subject to Change Without Notice - Consult the following Cummins Web site for the most recent data:

<http://marine.cummins.com/>