

# B3.3 Series Generator Sets

More Performance. Less Noise.



# INTRODUCING

## The 44-66kVA Product Range


- EU Stage IIIA 50 Hz
- EPA Tier 3 60 Hz
- Unregulated Fuel Efficient 50 Hz

**Cummins 4BTAA3.3** 3 litre in-line  
4 cylinder, diesel engine


Regulatory compliance:  
**Electrical 300914 (AS/NZS3000),  
GOST-r/EAC & SONCAP**

Transport-optimised footprint:  
STD 20 ft ISO: 6 Open/5 Enclosed  
STD 40 ft ISO: 12 Open/10 Enclosed

**Noise & LAT efficient**  
enclosure options



■ All major components designed & built by Cummins




■ **-5°C** Unaided cold start capability

■ **Extended service intervals**  
500 hours

■ **12 hours** of fuel autonomy  
**24 hours** dual wall fuel tank optional

■ Removable feet

# Global Company, Local Support



■ **7,200** sales & service locations  
■ **20** parts distribution centers

■ **15** technical centers  
■ **88** manufacturing facilities

■ **600** distributors  
■ **52,600** employees in 190 countries



For more product details, visit: [cummins.com](http://cummins.com)

Specifications are subject to change without notice.

Cummins® and the "C" logo are trademarks or registered trademarks of Cummins Inc. All Rights Reserved. Bulletin 5544204 Printed 10/18 ©2018 Cummins Ltd.