







CFP60E CONNECTION INFORMATION	
SAE #0	FLYWHEEL HOUSING
3/4" NPT	FUEL INLET
3/4" NPT	FUEL OUTLET
2-1/2" NPT	RAW WATER INLET
3" NPT/FLANGE	RAW WATER DISCHARGE
240/480 VAC	COOLANT HEATER (12840 WATTS)
10" ANSI FLANGE	EXHAUST CONNECTION


NOTES:
1. ALL PLUMBING MUST BE SUPPORTED AND/OR ISOLATED SO THAT NO WEIGHT OR STRESS IS APPLIED TO ANY ENGINE COMPONENT.
2. REFER TO ENGINE DATA SHEET FOR CUSTOMER CONNECTION RECOMMENDATIONS.
3. DRAWING SUBJECT TO CHANGE WITH OUT NOTICE.

LEGEND AND DATUM IDENTIFIER	
SHEET 1	INSTALLATION DRAWING
DATUM "A"	FACE OF FLYWHEEL HOUSING
DATUM "B"	REAR LEG BOLT LOCATION
DATUM "C"	FLYWHEEL MOUNTING SURFACE



M16 X 2-6H
1.20 DEEP MINIMUM
12 HOLSE EQUALLY SPACED
ON A Ø21.38 BOLT CIRCLE

M12 X 2-6H
1.10 DEEP MINIMUM
8 HOLSE EQUALLY SPACED
ON A Ø17.26 BOLT CIRCLE



DIMENSIONS ARE IN: INCHES () ARE IN: .	DO NOT SCALE PRINT	CMI DATA CLASSIFICATION Cummins Confidential	Cummins Sales and Service
DIMENSION TOLERANCES X.X: ±0.030IN OR 0.76mm X.XX: ±0.015IN OR 0.38mm ANGULAR TOLERANCE: ±1°	SCALE .040	DWN HE392 CKD APVD NE627 DATE 22AUG17	ITEM NAME ASSEMBLY, FIRE PUMP CFP60E-F10/20/30/40
THIS DOCUMENT (AND THE INFORMATION SHOWN THEREON) IS CONFIDENTIAL AND PROPRIETARY AND SHALL NOT BE DISCLOSED TO OTHERS IN HARD COPY OR ELECTRONIC FORM, REPRODUCED BY ANY MEANS, OR USED FOR ANY PURPOSE WITHOUT WRITTEN CONSENT OF CUMMINS, INC.	FOR INTERPRETATION OF DIMENSIONING AND TOLERANCING, SEE ASME Y14.5-2009	MUST CONFORM TO CES 10903	ITEM NUMBER A059H023
			CAD SHEET 1 OF 1