

COMMERCIAL DIESEL GENERATORS

NORTH AMERICA MODEL RANGE

60 Hz RANGE

ISSUE 2 — JUNE 2021

MODEL NAME	STANDBY RATINGS		PRIME RATINGS		DCC RATINGS		CONTINUOUS RATINGS		ENGINE MODEL	STANDARD ALTERNATOR	STANDARD CONTROL	EMISSIONS COMPLIANCE	SOUND ENCLOSURE
	kVA	kWe	kVA	kWe	kVA	kWe	kVA	kWe					
C10D6	12.5	10	11.4	9.1	—	—	—	—	D1703-M	CA115	PC 1.1	EPA Tier 4i	•
C15D6	18.8	15	17	13.6	—	—	—	—	D1703-M	CA115	PC 1.1	EPA Tier 4i	•
C20D6	25	20	22.8	18.2	—	—	—	—	V2203-M	CA115	PC 1.1	EPA Tier 4i	•
C25D6	31.3	25	28.3	22.7	—	—	—	—	B3.3-G5	CA115	PC 1.1	EPA Tier 3	•
C30D6	37.5	30	33.7	27	—	—	—	—	B3.3-G5	CA115	PC 1.1	EPA Tier 3	•
C35D6	43.7	35	45	32	—	—	—	—	B3.3-G5	CA115	PC 1.1	EPA Tier 3	•
C40D6	50	40	45	36	—	—	—	—	B3.3-G5	CA115	PC 1.1	EPA Tier 3	•
C50D6	63	50	56	45	—	—	—	—	B3.3-G7	CA125	PC 1.1	EPA Tier 3	•
C50D6C	63	50	56	45	—	—	—	—	QSB5-G13	UC2D	PC 2.3	EPA Tier 3	•
C60D6	75	60	68	54	—	—	—	—	B3.3-G7	CA125	PC 1.1	EPA Tier 3	•
C60D6C	75	60	68	54	—	—	—	—	QSB5-G13	UC2F	PC 2.3	EPA Tier 3	•
C80D6C	100	80	90	72	—	—	—	—	QSB5-G13	UC2G	PC 2.3	EPA Tier 3	•
C100D6C	125	100	113	90	—	—	—	—	QSB5-G13	UC3D	PC 2.3	EPA Tier 3	•
C125D6C	156	125	141	113	—	—	—	—	QSB5-G6	UC3E	PC 2.3	EPA Tier 3	•
C125D6D	156	125	141	113	—	—	—	—	QSB7-G5	UC3E	PC 1.1	EPA Tier 3	•
C130D6B	—	—	150	120	—	—	—	—	QSB5-G12	UC1274F	PC 3.3	EPA Tier 4F	—
C150D6D	188	150	169	135	—	—	—	—	QSB7-G5	UC3G	PC 1.1	EPA Tier 3	•
C175D6D	219	175	200	160	—	—	—	—	QSB7-G5	UC3H	PC 1.1	EPA Tier 3	•
C200D6D	250	200	225	180	—	—	—	—	QSB7-G5	UC3H	PC 1.1	EPA Tier 3	•
DSHAD	288	230	263	210	—	—	—	—	QSL9-G2	UCD3J	PC 2.3**	EPA Tier 3	•
DQDAA	313	250	281	225	—	—	—	—	QSL9-G7	HC4E	PC 2.3**	EPA Tier 3	•
DQDAB	344	275	313	250	—	—	—	—	QSL9-G7	HC4E	PC 2.3**	EPA Tier 3	•
DQDAC	375	300	338	270	—	—	—	—	QSL9-G7	HC4F	PC 2.3**	EPA Tier 3	•
C400D6B	500	400	—	—	—	—	—	—	QSZ13-G7	S4-G	PC 3.3	EPA Tier 3	•
DJEJ	563	450	513	410	513	410	—	—	QSK15-G9	HC5D	PC 2.3	EPA Tier 2	•
DJEK	625	500	569	455	569	455	—	—	QSK15-G9	HC5E	PC 2.3	EPA Tier 2	•
DQCA	750	600	681	545	681	545	—	—	QSK23-G7	S6D***	PC 2.3	EPA Tier 2	•
DQCB	938	750	850	680	850	680	—	—	QSK23-G7	S6E***	PC 2.3	EPA Tier 2	•
DQFAA	938	750	850	680	850	680	—	—	QST30-G5	S6D***	PC 3.3	EPA Tier 2	•
DQCC	1000	800	906	725	906	725	—	—	QSK23-G7	S6E***	PC 2.3	EPA Tier 2	•
DQFAB	1000	800	906	725	906	725	—	—	QST30-G5	S6E***	PC 3.3	EPA Tier 2	•
DQFAC	1125	900	1023	818	1023	818	—	—	QST30-G5	S6F***	PC 3.3	EPA Tier 2	•
DQFAD	1250	1000	1125	900	1125	900	—	—	QST30-G5	S6F***	PC 3.3	EPA Tier 2	•
DQFAH	1250	1000	1125	900	1125	900	—	—	QST30-G17	HC6K	PC 3.3	EPA Tier 4	—
DQGAA	1563	1250	1375	1100	—	—	—	—	QSK50-G4	PI734B	PC 3.3	EPA Tier 2	—
DQGAE	1563	1250	1419	1135	1419	1135	1250	1000	QSK50-G5	PI734B	PC 3.3	EPA Tier 2	—
DQGAB	1875	1500	1688	1350	—	—	—	—	QSK50-G4	PI734C	PC 3.3	EPA Tier 2	—
DQGAF	1875	1500	1706	1365	1706	1365	1375	1100	QSK50-G5	PI734C	PC 3.3	EPA Tier 2	—
DQGAS	1875	1500	1706	1365	1706	1365	1375	1100	QSK50-G8	PI734C	PC 3.3	EPA Tier 4	—
DQKAA	2188	1750	2000	1600	—	—	—	—	QSK60-G6	PI734C	PC 3.3	EPA Tier 2	—
DQKAD	2188	1750	2000	1600	2000	1600	1813	1450	QSK60-G6	PI734C	PC 3.3	EPA Tier 2	—
DQKAB	2500	2000	2281	1825	—	—	—	—	QSK60-G6	PI734F	PC 3.3	EPA Tier 2	—
DQKAE	2500	2000	2281	1825	2281	1825	2000	1600	QSK60-G6	PI734F	PC 3.3	EPA Tier 2	—
DQKAF	2813	2250	2281	1825	2500	2000	—	—	QSK60-G14	PI734G	PC 3.3	EPA Tier 2	—
DQKAM	2813	2250	2281	1825	2500	2000	—	—	QSK60-G17	PI734G	PC 3.3	EPA Tier 4	—
DQKAN	3125	2500	—	—	2813	2250	—	—	QSK60-G19	LVS1804X	PC 3.3	EPA Tier 2*	—
DQLE	3125	2500	2844	2275	2844	2275	2500	2000	QSK78-G12	LVS1804S	PC 3.3	EPA Tier 2*	—
DQLF	3438	2750	3125	2500	3125	2500	2625	2100	QSK78-G12	LVS1804S	PC 3.3	EPA Tier 2	—
DQLH	3438	2750	3125	2500	3125	2500	2625	2100	QSK78-G14	LVS1804S	PC 3.3	EPA Tier 4	—
C3000D6	3750	3000	3438	2750	3438	2750	3125	2500	QSK95-G2	LVS1804W	PC 3.3	—	—
C3000D6e	3750	3000	3438	2750	3438	2750	3125	2500	QSK95-G9	LVS1804W	PC 3.3	EPA Tier 2*	—
C3250D6	4063	3250	3750	3000	3750	3000	3125	2500	QSK95-G2	LVS1804W	PC 3.3	—	—
C3250D6e	4063	3250	3750	3000	3750	3000	3125	2500	QSK95-G9	LVS1804W	PC 3.3	EPA Tier 2*	—
C3500D6	4375	3500	3750	3000	4188	3350	3438	2750	QSK95-G2	LVS1804X	PC 3.3	—	—
C3500D6e	4375	3500	3750	3000	4188	3350	3438	2750	QSK95-G9	LVS1804X	PC 3.3	EPA Tier 2	—

*Enhanced low Nox available, please contact SAE for more details

**Available from Q3 2021

***Available from Q4 2021

For more product information contact your local Cummins distributor or visit cummins.com

Data & Specification sheets available at powersuite.cummins.com

For rating definitions refer to data sheet. Specifications may change without notice.



cummins.com

Bulletin 5676550 Produced in U.S.A. 6/21 ©2021 Cummins Inc.