

HyLYZER® WATER ELECTROLYZERS




HyLYZER® is Cummins' globally proven modular water electrolyzer system designed for easy on-site installation inside or out, with simple interconnectivity to scale up, and an unrivaled record for reliability, low maintenance and on-site safety. Recommended for projects between 400 - 2,000 Nm³/h.

Proven technology, compliant with highest safety standards

Turnkey solution

Exceptionally compact

30 bar pressurized stacks



FEATURES

	HyLYZER® - 400	HyLYZER® - 500
Technology	PEM water electrolysis	
Hydrogen production	400 Nm³/h (862 kg/day)	500 Nm³/h (1080 kg/day)
H ₂ delivery pressure	30 bar _g (435 psig) without a compressor	
H ₂ quality max impurities	99.998% O ₂ < 2 ppm, N ₂ < 12 ppm (higher purities optional); Atm. Dew point: -75°C	

TECHNICAL SPECIFICATIONS

	HyLYZER® - 400	HyLYZER® - 500
Operating range	5-100%	
DC power consumption at stack	40 to 48 kWh/kg (3.6 to 4.3 kWh/Nm ³)	
System specific consumption*	≤ 54 kWh/kg	
Utilities required to operate the plant	Electrical power, potable water, nitrogen for purging requirements	
Rectifier specifications	6 to 36kV± 10% - 50/60 Hz - 3.2 MVA 97% efficiency	
Auxiliary installed power	125 kVA	
Potable water consumption	Scope of supply includes a water treatment plant with reverse osmosis that requires 1.2 to 1.5 L/Nm ³ [13 to 17 L/kg of H ₂] to produce 0.8 L/Nm ³ of demin water for the electrolysis process	
Total footprint (including maintenance area)	18 m x 11 m (~ 198 m ²)	
Product setup	Outdoor (2x 40ft ISO container)	
Installation environment	Outdoors -20°C to 40°C / -4°F to 104°F	

*System specific consumption considers: the standard scope of supply (refer to BOS and BOP tables); 100% Load capacity; Beginning Of Life; 1% increase per annum (at ≥8500 hours operation)

STACK AND BALANCE-OF-STACK (BOS)

	Outdoor	Indoor
Cell stacks and gas generation system	■	
Power rectifiers	■	
Control panel	■	
Water polishing system	■	

BALANCE-OF-PLANT (BOP)

	Outdoor	Indoor
Rectifier cooling	■	
Gas cooling	■	
Electrolysis cooling	■	
Water purification system	■	
Instrument air compressor	■	
Hydrogen purification system	■	

Applicable Codes and Standards Pressure Equipment Directive 2014/68/EU, Low Voltage Directive 2014/35/EU, Machinery Directive 2006/42/EC, Electro-Magnetic Compatibility 2014/30/EU, ATEX Directive 2014/34/EU, IEC 61511, IEC 61508, IEC 60079-10-1, NFPA 2, NFPA 497, National Electrical Code (NEC), ANSI/NFPA 70, ASME B31.3-2016, ASME Boiler and Pressure Vessel Code 2017, CSA C22.1 and C22.2, CSA B51 2019, CAN/BNQ 1784-000/2007. Other jurisdictions available on request.

The content of this document may contain technical inaccuracies or typographical errors. Cummins reserves the right to make changes or updates at any time without prior notice. Copying or distributing in whole or in part of the content without consent of Cummins is not allowed.



cummins.com

Bulletin 5676517 Produced in U.K. 9/21
©2021 Cummins Inc.