




L9-G17

EU Stage V and Tier 4 Final



Description

The new Cummins G-Drive engines are designed with next generation aftertreatment technology, providing an optimised solution to meet EU Stage V, and US Tier 4 Final emissions. This unique and simplistic design brings an improvement in reliability and fuel economy, as well as longer intervals for scheduled maintenance.

Features

Integrated Aftertreatment Design. Full single module (DOC/DPF/SCR) with compact size for reduced installation impact. Industry leading DPF technology expertise with best in class reliability and service intervals.

EGR-Free Design (supported by better NOx conversion performance) allows a higher sulphur tolerance for global capability and puts the B6.7 and L9 on par with lower emissions level engines. A streamlined design also delivers a significant reduction in installation complexity and cost.

Improved Performance Higher power density (vs Tier 4F). Meets ISO 8528 transient and steady state performance.

Air Control Throttle Reduced operator interface, intake throttle for increased thermal management capability. Aftertreatment specification capable of low load operation up to -25° C.

Cooling System 50°C LAT capability with noise optimized fan.

Air Cleaner Normal and heavy-duty air cleaner options.



This engine has been designed in facilities certified to ISO9001 and manufactured in facilities certified to ISO9001 or ISO9002.

This equipment has been designed and tested to meet EU product safety regulations. Material compliance declaration is available upon request

1500 rpm (50 Hz ratings)

Gross engine output			Net engine output			Typical generator set output					
Standby	Prime	Base	Standby	Prime	Base	Standby (ESP)		Prime (PRP)		Base (COP)	
kWm/BHP			kWm/BHP			kWe	kVA	kWe	kVA	kWe	kVA
262/351	238/319	214/287	244/327	223/299	199/267	227	284	207	259	185	231

1800 rpm (60 Hz ratings)

Gross engine output			Net engine output			Typical generator set output					
Standby	Prime	Base	Standby	Prime	Base	Standby (ESP)		Prime (PRP)		Base (COP)	
kWm/BHP			kWm/BHP			kWe	kVA	kWe	kVA	kWe	kVA
274/368	250/335	224/301	250/335	228/306	202/271	232	290	212	265	188	235

General engine data

Fuel Rating	FR97286
Type	Inline 4-Cycle Diesel, Turbocharged & Charge Air Cooled
Bore mm	114mm (4.49in)
Stroke mm	145mm (5.71in)
Displacement litre	8.9L (543 in ³)
Cylinder block	Cast Iron, 6 cylinder
Battery charging alternator	70A/95A/100A
Starting voltage	24V
Fuel system	Cummins XPI
Fuel filter	Spin-on, full flow with water separator and WIF sensor
Lube oil filter type(s)	Spin-on, full flow
Lube oil capacity (l)	27.5
Flywheel dimensions	SAE 1/14 or SAE 2/11.5

Coolpac performance data

Cooling system design	Jacket Water and Charge Air Cooled
Coolant ratio	50% ethylene glycol; 50% water
Coolant capacity (l)	20.46
Limiting ambient temp.** (°C)	71.2C (60Hz) / 67.9C (50Hz)
Fan power (kWm)	20.5 (60Hz) / 14 (50Hz)
Cooling system air flow (m ³ /s)**	7.78 (60Hz) / 7.49 (50Hz)
Air cleaner type	Normal and Heavy-duty dry replaceable element options with restriction indicator and TBAP sensor


** @ 0.5" H2O

Fluid consumption 1500 (50 Hz)

Output Power			Fuel		DEF
%	kWm	BHP	L/hr	US Gal/hr	L/h
Standby Power					
100	262	351	63	16.6	7.4
Prime Power					
100	238	319	56	14.9	6.6
75	178	239	43	11.3	4.4
50	119	160	30	7.8	2.3
25	59	80	16	4.3	1.1
Continuous Power					
100	214	287	51	13.5	5.8

Fluid consumption 1800 (60 Hz)

Output Power			Fuel		DEF
%	kWm	BHP	L/hr	US Gal/hr	L/h
Standby Power					
100	274	368	68	17.9	6.8
Prime Power					
100	250	335	62	16.3	6.1
75	187	251	47	12.4	3.8
50	125	168	32	8.6	2.3
25	62	84	21	5.4	0.8
Continuous Power					
100	224	301	56	14.7	5.3



Note: Drawing shown for illustration purposes only

Weights and dimensions

Length mm	Width mm	Height mm	Weight (dry) kg
1787	1290	1588	1031.7

Ratings definitions

Emergency Standby Power (ESP):	Limited-Time Running Power (LTP):	Prime Power (PRP):	Base Load (Continuous) Power (COP):
Applicable for supplying power to varying electrical load for the duration of power interruption of a reliable utility source. Emergency Standby Power (ESP) is in accordance with ISO 8528. Fuel Stop power in accordance with ISO 3046, AS 2789, DIN 6271 and BS 5514.	Applicable for supplying power to a constant electrical load for limited hours. Limited-Time Running Power (LTP) is in accordance with ISO 8528.	Applicable for supplying power to varying electrical load for unlimited hours. Prime Power (PRP) is in accordance with ISO 8528. Ten percent overload capability is available in accordance with ISO 3046, AS 2789, DIN 6271 and BS 5514.	Applicable for supplying power continuously to a constant electrical load for unlimited hours. Continuous Power (COP) in accordance with ISO 8528, ISO 3046, AS 2789, DIN6271 and BS 5514.

For more information contact your local Cummins distributor or visit cummins.com

Our energy working for you.™

