

PREMIUM STOPPING PERFORMANCE

SPECIALTY BRAKING SOLUTIONS



ADVANCED BRAKING SOLUTIONS

Cummins understands that premium stopping performance is a must in Specialty service applications, which often require safe but aggressive driving at maximum payloads. Whatever brake package best suits your axle and application, trust that our heritage of braking performance serving Specialty vocations ensures it's engineered for performance in demanding applications.



FOUNDATION BRAKING AT ITS BEST

As an industry brake leader, you can expect an array of braking options to choose what's best suited for your application. Q+™ and Cast+ drum brakes are an industry standard, offering premium stopping performance and minimal maintenance. For high resistance to fade – in even the most severe conditions – the EX+™ family of air disc brakes offer proven reliability in frequent stop applications.




EX+ L AIR DISC BRAKES

EX+ L air disc brakes were developed to meet the tough challenges faced by heavy-duty tractors, trucks and trailers. Today's commercial vehicle market demands superior performance and lower lifecycle costs, and EX+ L air disc brakes deliver every time.

EX+ L air disc brake advantages:

- Increased brake fade resistance for high-demand Specialty service applications
- In-line braking stability for safe, smooth stops
- Reduced maintenance time and lower maintenance costs



Q+ DRUM BRAKES

Q+ drum brakes for vocational applications deliver consistent performance and stopping distance, exceptional durability and reduced downtime. Available with wider brake shoe packages and advanced friction material, the Q+ offers longer lining life and helps fleets meet reduced stopping distance regulations.

CAST+ DRUM BRAKES

Cast+ drum brakes offer added durability and reliability with a single-piece, cast shoe and thick, extended-life brake linings that provide exceptional resistance to heat related wear in heavy-duty applications. Available in 16.5-inch x 6-inch or the larger 16.5-inch x 8.625-inch sizes.

SPECIALTY PRODUCTS DEMAND SPECIAL SERVICE

WE'RE BEHIND YOU ALL THE WAY

You can count on DriveForce™ to keep moving your operation forward. With more than 100 field representatives in North America, DriveForce provides an extensive support network in the commercial vehicle industry. To locate your DriveForce representative, visit <https://www.cummins.com/components/drivetrain-systems/customer-support>

YOUR TRAINING RESOURCE

BullPen is a convenient web portal designed for dealers, fleets and service garages to access product information and receive online training at one central location. The BullPen provides access to more than 1,000 items including product presentations, sales literature, product videos and photos, service bulletins and parts books. For more information or to register for courses, visit meritorbullpen.com.

WARRANTY HELP IS A PHONE CALL AWAY

Every specialty product is backed by strong support from DriveForce plus the OnTrac™ technical support center. The OnTrac team is equipped with expert service professionals who will help you with troubleshooting and handling warranty issues, such as validating coverage, opening a new claim, following-up on an ongoing claim or closing an existing claim. Call **866-668-7221 (OnTrac1)** for assistance with diagnostics, repair and warranty solutions. OnTrac offers extended hours for your convenience—the team is standing by 8 a.m. – 8 p.m. EST Monday – Friday and 9 a.m. – 6 p.m. Saturday.

UNSURPASSED CUSTOMER SUPPORT

Every specialty product is backed by strong support from DriveForce plus the OnTrac™ technical support center. For more information, call **866-668-7221 (OnTrac1)** or visit cummins.com today.



Cummins Inc.
Box 3005
Columbus, IN 47202-3005
U.S.A.

cummins.com

SP-20151
Bulletin 6461171 Produced in U.S.A. Rev. 10/25
©2025 Cummins Inc.