

HyLYZER® WATER ELECTROLYZERS




HyLYZER® is Cummins' globally proven modular water electrolyzer system designed for easy on-site installation inside or out, with simple interconnectivity to scale up, and an unrivaled record for reliability, low maintenance and on-site safety. Recommended for projects between 1,000 - 10,000 Nm³/h.

Proven technology, compliant with highest safety standards

Exceptionally compact

30 bar pressurized stacks



FEATURES

	HyLYZER® - 1000
Technology	PEM water electrolysis
Hydrogen production	1000 Nm ³ /h (2160 kg/day)
H ₂ delivery pressure	30 bar _g (435 psig) without a compressor
H ₂ quality max impurities	99.99% dry basis, gas is fully saturated with water O ₂ < 100 ppm Optional > 99.998% with hydrogen purification system

TECHNICAL SPECIFICATIONS

	HyLYZER® - 1000
Operating range	5-125%
DC power consumption at stack	40 to 50 kWh/kg, 48 at nominal load (3.6 to 4.5 kWh/Nm ³ , 4.3 at nominal load)
System specific consumption*	≤ 51 kWh/kg
Utilities required to operate the plant	Electrical power, demineralized water, cooling water, HVAC, instrument air, nitrogen for purge
Rectifier specifications	4.1 to 30kV 50/60 Hz, 7 MVA 97% efficiency
Auxiliary installed power	45 kVA
Demineralized Water Consumption and Recommended Water Quality	~0.8 L/Nm ³ of H ₂ [9 L/kg of H ₂] ASTM D1193 Type
Electrolyzer Cooling Water Requirement	Max. 2,500 LPM between 5-40°C (max ΔT: 10°C)
Total footprint (including maintenance area)	Electrolyzer dimensions (L x W) = 8.4 m x 2.3 m (27.7 x 7.5 ft) Rectifier dimensions (L x W) = 4.5 x 2.5 m (14.8 x 8.2 ft)
Installation environment	Indoors 5°C to 40°C / 41°F to 104°F

*System specific consumption considers: the standard scope of supply (refer to BOS table); 100% Load capacity; Beginning Of Life; 1% increase per annum (at ≥8500 hours operation); Range for indoor setup; HPS not included

STACK AND BALANCE-OF-STACK (BOS)

	Outdoor	Indoor
Cell stacks and gas generation system		■
Power rectifiers		■
Control panel		■
Water polishing system		■

BALANCE-OF-PLANT (BOP)

	Outdoor	Indoor
Rectifier cooling		
Gas cooling		
Electrolysis cooling		
Water purification system		
Instrument air compressor		
Hydrogen purification system		Optional

Applicable Codes and Standards Pressure Equipment Directive 2014/68/EU, Low Voltage Directive 2014/35/EU, Machinery Directive 2006/42/EC, Electro-Magnetic Compatibility 2014/30/EU, ATEX Directive 2014/34/EU, IEC 61511, IEC 61508, IEC 60079-10-1, NFPA 2, NFPA 497, National Electrical Code (NEC), ANSI/NFPA 70, ASME B31.3-2016, ASME Boiler and Pressure Vessel Code 2017, CSA C22.1 and C22.2, CSA B51 2019, CAN/BNQ 1784-000/2007. Other jurisdictions available on request.

The content of this document may contain technical inaccuracies or typographical errors. Cummins reserves the right to make changes or updates at any time without prior notice. Copying or distributing in whole or in part of the content without consent of Cummins is not allowed.



cummins.com

Bulletin 5676518 Produced in U.K. 9/21
©2021 Cummins Inc.