

OPTIMUM PERFORMANCE AND RELIABILITY FROM THE X15 STAGE V



**FOR
A WORLD
THAT'S
ALWAYS ON™**

CUMMINS X15 STAGE V FOR EUROPEAN INLAND WATERWAYS


Designed and tested based on Inland Waterway customer requirements, the X15 Stage V is certified to the latest emission standard and able to deliver optimum performance and efficiency.

This integrated engine and aftertreatment package was developed in-house for key European Inland Waterways applications including bow thrusters and main propulsion.



CUSTOM OPTIONS

Flexible aftertreatment mounting options including side and top mounted, better accommodates for existing vessel engine room space.



PROVEN ADVANTAGES

- Cummins 15 litre engines are proven in multiple global applications
- The aftertreatment is fine-tuned to deliver maximum efficiency, productivity, reliability and uptime
- C Command Elite offers additional functionality and monitoring with the added benefit of an easy-to-read and customer configured colour display.
- Full Cummins warranty and supported by a robust dealer network in Europe

COMMERCIAL MARINE RATINGS

kW	HP	RPM
Continuous		
373	500	1800
391	525	1800
Intermittent		
410	550	1800
429	575	1800
447	600	1800
447	600	2100

DELIVERING OPTIMUM PERFORMANCE



Reliable and dependable

Proven engine

Emission Compliant

Complies with EU Stage V emission standard

The complete package

Meets the needs of operators

CONTROL AND MONITORING



C Command Elite
Customer Interface Box

C Command Elite offers additional functionality and system monitoring with an easy-to-read customer configured colour display.

The engine control module (ECM) controls everything, from air intake to exhaust aftertreatment, to deliver peak performance and near-zero emissions.



Remote Panel – Featuring an 8.4" colour touchscreen panel with a high resolution screen. Capable of simultaneously monitoring and controlling up to eight engines.

ANY CUSTOMER, ANY QUESTION, ANY CHANNEL, **ANY TIME.**

Cummins Care is not a typical call centre. We are a solutions center helping to prevent issues, provide answers quickly and reimburse accurately. We are your connection to a whole new level of customer service, to support and deliver faster personal attention with rapid results. From the moment you engage Cummins Care, you will have access to a Cummins expert with specialised skill sets, experience and in-depth knowledge to take care of your needs.

- **CUSTOMER SERVICE**
- **TECHNICAL SUPPORT**


- **WARRANTY ASSISTANCE**
- **CONNECTED SERVICE**

We are experts with advanced technology to make your life easier while providing a seamless support experience. Contact us at **00 8000 286 6467** or email **cceurope@cummins.com**.



EUROPEAN SUPPORT NETWORK

CUMMINS' EUROPEAN FOOTPRINT OF ENGINEERING, MANUFACTURING, AND SERVICE LOCATIONS MEANS WE ARE WHERE OUR CUSTOMERS NEED US TO BE.



TO FIND OUT MORE, CONTACT YOUR LOCAL DEALER
OR DISTRIBUTOR VIA [CUMMINS.COM/LOCATIONS](https://www.cummins.com/locations)



Cummins Inc.
Box 3005
Columbus, IN 47202-3005
U.S.A.

[cummins.com](https://www.cummins.com)

Bulletin 5676597 Produced in U.K. 10/21
©2021 Cummins Inc.